



# UniFlood M gen2: A high power floodlight with true modularity

## UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

### Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

# UniFlood M G2

## Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

## Warnings and Safety

- For outdoor use only.

## Versions



UniFlood M Gen2



UniFlood M Gen2







UniFlood M Gen2





UniFlood M Gen2

## Dimensional drawing



# UniFlood M G2

## Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Light source color	RGBW
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	>80
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

## Light Technical

Order Code	Full Product Name	Luminous Flux
911401747203	BVP353 32LED RGBWW 220V L30 45 DMX	3,000 lm
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	11,520 lm
911401749553	BVP354 144LED RGBNW 220V L57 15 DMX	15,785 lm
911401749643	BVP354 144LED RGBNW 220V L57 30 DMX	16,345 lm
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	15,785 lm
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	7,890 lm
911401747573	BVP353 36LED RGBNW 220V L35 45 DMX	3,995 lm
911401750363	BVP355 180LED RGBNW 220V L50 30 DMX	20,435 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401747203	BVP353 32LED RGBWW 220V L30 45 DMX	60 W
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
911401749553	BVP354 144LED RGBNW 220V L57 15 DMX	300 W
911401749643	BVP354 144LED RGBNW 220V L57 30 DMX	300 W

Order Code	Full Product Name	Power Consumption
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
911401747573	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
911401750363	BVP355 180LED RGBNW 220V L50 30 DMX	360 W

