



UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2


Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

Warnings and Safety

- For outdoor use only.

Dimensional drawing



General Information

Driver included	Yes
-----------------	-----

Light Technical

Color rendering index (CRI)	>80
-----------------------------	-----

Operating and Electrical

Power Consumption	60 W
-------------------	------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Optical cover type	Clear glass
--------------------	-------------

Housing Color	Dark gray
---------------	-----------

Mech. impact protection code	IK06
------------------------------	------

Ingress protection code	IP66
-------------------------	------

Approval and Application

CE mark	Yes
---------	-----

Flammability mark	For mounting on normally flammable surfaces
-------------------	--

Light Technical

Order Code	Full Product Name	Correlated Color		
		Light source color	Temperature (Nom)	Luminous Flux
911401746873	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K	4,710 lm
911401746953	BVP353 30LED 27K 220V L30 15	827 warm white	2700 K	4,740 lm
911401747133	BVP353 30LED 27K 220V L30 45	827 warm white	2700 K	4,740 lm

UniFlood M G2



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2023, April 13 - data subject to change