



Architectural LED floodlight for fixed or dynamic lighting

UniFlood C Pro

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for DMX signal via dedicated cables with IP67 connectors

UniFlood C Pro

Application

- Bridges, Monuments, Façades
- Landscape
- Parks and Plazas

Warnings and Safety


- For outdoor use only

Versions



UniFlood C Pro

Dimensional drawing



General Information

Driver included	Yes
-----------------	-----

Mechanical and Housing

Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66

Approval and Application

CE mark	Yes
---------	-----

Light Technical

UniFlood C Pro

		Correlated					
Order Code	Name	Light	Color	Color	Rendering	Luminous Flux	Color
		Full Product	source	Temperature			
911401773763	BVP371 12LED	830	3000 K	>80		1,450 lm	
	30K 220V 45	warm					
	24W HE	white					
911401773783	BVP371 12LED	830	3000 K	>80		1,405 lm	
	30K 220V 60	warm					
	24W HE	white					

		Correlated					
Order Code	Name	Light	Color	Color	Rendering	Luminous Flux	Color
		Full Product	source	Temperature			
911401774863	BVP372 20LED	RGBW	-			N.A.	2,230 lm
	RGBNW 220V 15						
	DMX 50W HP						
911401774893	BVP372 20LED	RGBW	-			N.A.	1,835 lm
	RGBNW 220V						
	60 DMX 50W HP						

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401773763	BVP371 12LED 30K 220V 45 24W HE	24 W
911401773783	BVP371 12LED 30K 220V 60 24W HE	24 W

Order Code	Full Product Name	Power Consumption
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	50 W
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	50 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401773763	BVP371 12LED 30K 220V 45 24W HE	No
911401773783	BVP371 12LED 30K 220V 60 24W HE	No

Order Code	Full Product Name	Dimmable
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	Yes
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	Yes

