



Sophisticated and compact outdoor spotlight

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobstrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Benefits

- Sleek and minimalist design, suitable for diverse application scenarios
- A variety of optics and color selections
- Multiple mounting methods suitable for different lighting applications

Applications

- Bridges, Monuments, Facades
- Municipal Buildings
- Parks and Plazas

Features


- Standard: RGB+3000K, RGB+4000K, RGB, 3000K, and 4000K
- Optional 2200K, 2700K, 3500K, 5000K, 5700K, 6500K, monochrome, and RGB+5700K,
- Wide range of beam angles, from narrow spot to wide flood
- Robust design with IP66 rating for outdoor use
- Adjustable vertical 130° and horizontal 340° tilting angle range

Versions

RTP-OF-UniSpot



Dimensional drawing



BVP376 1LED RGB40K 24V 30 DMX 16W

General Information	
Driver included	No
Light Technical	
Luminous Flux	505 lm
Correlated Color Temperature (Nom)	RGBW
Color rendering index (CRI)	>80
Light source color	Red, green, blue and white
Operating and Electrical	
Power Consumption	16 W
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing

Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass

Approval and Application

CE mark	Yes
---------	-----