

PHILIPS

Lighting



GameVision : the 1:1 retrofit of conventional floodlights for recreational sports.

GameVision

GameVision is a simple, easy to choose led floodlight to replace conventional installations in municipal football stadiums, hockey fields... Its specific hooded shape design ensures a limited perception of light outside the field of play, hence a better comfort for people living nearby, but also favors dark skies. The light distribution is maintained all along the product lifetime as the reflector inside is protected against pollution and corrosion.

Benefits

- 1:1 retrofit of conventional floodlights in recreational sports
- Easy to choose
- Low glare perception
- Favors dark skies

Features

- 1 “do-it-all” light distribution
- 2 levels of light output
- Weight and SCx similar to OptiVision HID (MVP507)
- Low to 0 tilt angle in application

Application

- Arena and Sports

Versions







BVP440 GameVision HGB PP



BVP440 GameVision BV PP

Dimensional drawing



Product details



BVP440 GameVision tilt aiming DP

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Luminaire light beam spread	-
Light source color	757 cool white
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	70
Optic type outdoor	Asymmetrical
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/ Differential)	Surge protection level until 10 kV differential mode and 10 kV common mode
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Aluminum
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	10°
Approval and Application	
CE mark	Yes
Flammability mark	-
Product Data	
Product family code	BVP440

General Information

Order Code	Full Product Name	Lamp family code	Service tag
912300060576	BVP440 LED1760/757 DW HGB FG PSD ALU D9	LED1760	-
912300060577	BVP440 LED1200/757 DW HGB FG PSD ALU D9	LED1200	-
912300060572	BVP440 LED1760/757 DW BV FG PSD ALU D9	LED1760	Yes
912300060573	BVP440 LED1200/757 DW BV FG PSD ALU D9	LED1200	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux
912300060576	BVP440 LED1760/757 DW HGB FG PSD ALU D9	142,972 lm
912300060577	BVP440 LED1200/757 DW HGB FG PSD ALU D9	110,769 lm


Order Code	Full Product Name	Luminous Flux
912300060572	BVP440 LED1760/757 DW BV FG PSD ALU D9	142,972 lm
912300060573	BVP440 LED1200/757 DW BV FG PSD ALU D9	110,769 lm

Operating and Electrical


Order Code	Full Product Name	Power Consumption
912300060576	BVP440 LED1760/757 DW HGB FG PSD ALU D9	1,000 W
912300060577	BVP440 LED1200/757 DW HGB FG PSD ALU D9	736 W

Order Code	Full Product Name	Power Consumption
912300060572	BVP440 LED1760/757 DW BV FG PSD ALU D9	1,000 W
912300060573	BVP440 LED1200/757 DW BV FG PSD ALU D9	736 W


Polar Wide Diagrams




Polar Normal (separate) - BVP440I -
912300060576



Polar Normal (separate) - BVP440I -
912300060577



Polar Normal (separate) - BVP440I -
912300060572



Polar Normal (separate) - BVP440I -
912300060573

