



OptiVision LED gen3.5 –Smart area and recreational sports lighting

OptiVision LED gen3.5

The OptiVision LED gen3.5 floodlighting system provides a complete lighting solution for the simplest through to the most complex area and recreational sports lighting applications. The high-efficiency floodlight comes with a single piece die cast housing, hosting 2 and 3 LED engines respectively, which also function with an external driver box – separate for use at a distance from the floodlight (BV), or pre-fixed onto the mounting bracket of the floodlight (HGB) for ease of installation and lower initial cost. It meets the highest performance standards, provides outstanding light, quality, uniformity and ensures safety and visual comfort.

Benefits

- The wide range of optics ensure maximum optical efficiency and enables highly precise light distribution with minimum spill light
- 0-tilt allows for low sCx value for projects that want to re-use installed pole structures to minimize required investment. 0 tilt option further increases comfort and minimizes complaints on light trespass from residents
- When combined with controls or Interact Sports lighting management system, the floodlight enables additional energy savings (up to 65%) in different area lighting applications
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

OptiVision LED gen3.5

Features

- Single piece pressure die cast housing, with a protection level of IP66 against dust and water
- Wide range of ambient temperature tolerance making it suitable for a variety of sports and area lighting applications
- Option to add additional accessories to have the best in class spill light, 0 tilt, glare and up-light control
- Single High-power driver with IP66 protection pressure die cast housing and 10kV surge protection
- Programmable DALI Driver making it suitable to connect to lighting management systems like Interact Sports

Application


- Logistics areas (Ports)
- Apron lighting (Airports), Parking and Industrial areas
- Recreational sports lighting applications (Football, Hockey, Basketball, Golf, Tennis, etc)

Versions




OptiVision LED gen3 5 BVP528 HGB PP

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Luminaire light beam spread	5° - 13° x 120°
Color rendering index (CRI)	70
Optic type outdoor	Asymmetrical
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/Differential)	Surge protection level until 10 kV differential mode
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover clear
Housing Color	Aluminum
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family code
55317000	BVP518 1720/740 BV A35-WB D9 T35 OUT	LED1720
55318700	BVP518 1720/740 BV A35-WB D9 T35 OUT LO	LED1720
55320000	BVP518 1720/757 BV A35-WB D9 T35 OUT	LED1720
55322400	BVP518 1650/730 BV A35-WB D9 T35 OUT LO	LED1650
55324800	BVP518 1720/740 BV A65-WB D9 T35 OUT	LED1720
55319400	BVP518 1720/740 HGB A35-WB D9 T35 OUT	LED1720
55321700	BVP518 1720/757 HGB A35-WB D9 T35 OUT	LED1720
55328600	BVP528 2590/740 HGB A35-WB D9 T35 OUT	LED2600
55330900	BVP528 2590/757 HGB A35-WB D9 T35 OUT	LED2600
55325500	BVP528 2590/740 BV A35-NB D9 T35 OUT LO	LED2600
55326200	BVP528 2590/740 BV A35-WB D9 T35 OUT	LED2600
55327900	BVP528 2590/740 BV A35-WB D9 T35 OUT LO	LED2600
55329300	BVP528 2590/757 BV A35-WB D9 T35 OUT	LED2600
55331600	BVP528 2470/730 BV A35-NB D9 T35 OUT LO	LED2500
55332300	BVP528 2470/730 BV A35-WB D9 T35 OUT LO	LED2500
55333000	BVP528 2590/740 BV A65-WB D9 T35 OUT	LED2600

Light Technical

Order Code	Full Product Name	Correlated Color		
		Light source color	Temperature (Nom)	Luminous Flux
55317000	BVP518 1720/740 BV A35-WB D9 T35 OUT	740 neutral white	4000 K	149,640 lm
55318700	BVP518 1720/740 BV A35-WB D9 T35 OUT LO	740 neutral white	4000 K	120,400 lm
55320000	BVP518 1720/757 BV A35-WB D9 T35 OUT	757 cool white	5700 K	149,640 lm
55322400	BVP518 1650/730 BV A35-WB D9 T35 OUT LO	730 warm white	3000 K	120,400 lm
55324800	BVP518 1720/740 BV A65-WB D9 T35 OUT	740 neutral white	4000 K	149,640 lm
55319400	BVP518 1720/740 HGB A35-WB D9 T35 OUT	740 neutral white	4000 K	149,640 lm
55321700	BVP518 1720/757 HGB A35-WB D9 T35 OUT	757 cool white	5700 K	149,640 lm
55328600	BVP528 2590/740 HGB A35-WB D9 T35 OUT	740 neutral white	4000 K	225,330 lm

Order Code	Full Product Name	Correlated Color		
		Light source color	Temperature (Nom)	Luminous Flux
55330900	BVP528 2590/757 HGB A35-WB D9 T35 OUT	757 cool white	5700 K	225,330 lm
55325500	BVP528 2590/740 BV A35-NB D9 T35 OUT LO	740 neutral white	4000 K	181,300 lm
55326200	BVP528 2590/740 BV A35-WB D9 T35 OUT	740 neutral white	4000 K	225,330 lm
55327900	BVP528 2590/740 BV A35-WB D9 T35 OUT LO	740 neutral white	4000 K	181,300 lm
55329300	BVP528 2590/757 BV A35-WB D9 T35 OUT	757 cool white	5700 K	225,330 lm
55331600	BVP528 2470/730 BV A35-NB D9 T35 OUT LO	730 warm white	3000 K	170,430 lm
55332300	BVP528 2470/730 BV A35-WB D9 T35 OUT LO	730 warm white	3000 K	170,430 lm
55333000	BVP528 2590/740 BV A65-WB D9 T35 OUT	740 neutral white	4000 K	196,840 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
55317000	BVP518 1720/740 BV A35-WB D9 T35 OUT	1,000 W
55318700	BVP518 1720/740 BV A35-WB D9 T35 OUT LO	1,000 W
55320000	BVP518 1720/757 BV A35-WB D9 T35 OUT	1,000 W
55322400	BVP518 1650/730 BV A35-WB D9 T35 OUT LO	1,000 W
55324800	BVP518 1720/740 BV A65-WB D9 T35 OUT	1,000 W
55319400	BVP518 1720/740 HGB A35-WB D9 T35 OUT	1,000 W
55321700	BVP518 1720/757 HGB A35-WB D9 T35 OUT	1,000 W
55328600	BVP528 2590/740 HGB A35-WB D9 T35 OUT	1,500 W

Order Code	Full Product Name	Power Consumption
55330900	BVP528 2590/757 HGB A35-WB D9 T35 OUT	1,500 W
55325500	BVP528 2590/740 BV A35-NB D9 T35 OUT LO	1,500 W
55326200	BVP528 2590/740 BV A35-WB D9 T35 OUT	1,500 W
55327900	BVP528 2590/740 BV A35-WB D9 T35 OUT LO	1,500 W
55329300	BVP528 2590/757 BV A35-WB D9 T35 OUT	1,500 W
55331600	BVP528 2470/730 BV A35-NB D9 T35 OUT LO	1,500 W
55332300	BVP528 2470/730 BV A35-WB D9 T35 OUT LO	1,500 W
55333000	BVP528 2590/740 BV A65-WB D9 T35 OUT	1,500 W

Product Data

Order Code	Full Product Name	Product family code
55317000	BVP518 1720/740 BV A35-WB D9 T35 OUT	BVP518
55318700	BVP518 1720/740 BV A35-WB D9 T35 OUT LO	BVP518
55320000	BVP518 1720/757 BV A35-WB D9 T35 OUT	BVP518
55322400	BVP518 1650/730 BV A35-WB D9 T35 OUT LO	BVP518
55324800	BVP518 1720/740 BV A65-WB D9 T35 OUT	BVP518
55319400	BVP518 1720/740 HGB A35-WB D9 T35 OUT	BVP518
55321700	BVP518 1720/757 HGB A35-WB D9 T35 OUT	BVP518
55328600	BVP528 2590/740 HGB A35-WB D9 T35 OUT	BVP528

Order Code	Full Product Name	Product family code
55330900	BVP528 2590/757 HGB A35-WB D9 T35 OUT	BVP528
55325500	BVP528 2590/740 BV A35-NB D9 T35 OUT LO	BVP528
55326200	BVP528 2590/740 BV A35-WB D9 T35 OUT	BVP528
55327900	BVP528 2590/740 BV A35-WB D9 T35 OUT LO	BVP528
55329300	BVP528 2590/757 BV A35-WB D9 T35 OUT	BVP528
55331600	BVP528 2470/730 BV A35-NB D9 T35 OUT LO	BVP528
55332300	BVP528 2470/730 BV A35-WB D9 T35 OUT LO	BVP528
55333000	BVP528 2590/740 BV A65-WB D9 T35 OUT	BVP528

