

Direct View Pixel Luminaires for Creative Architectural and Media Façade Applications

UniString

UniString is a surface mounted, exterior-rated and compact sized architectural LED direct view string that is designed for architectural and media façade outdoor lighting applications. The robust mechanical design, easy installation and unique optical lenses make UniString ideal for buildings/media facades, bridges, arenas, theaters, amusement parks and recreational centers. Available in white, monochromatic colors, RGB, RGBW and tunable white. Available in symmetrical and asymmetrical optical distributions with DMX control option to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Available in three sizes and three power ranges to fit any application requirements.
- Robust Design & IP66 rating for outdoor use.
- Asymmetric beam option available to provide higher efficiency, better visual clearance and reduce lighting pollution in tall buildings and towers
- Through wiring for power and DMX data via IP67 connectors
- Available in track and surface mounting options

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, Monochromatic Colors and Tunable Wh
- Standard pixel pitch of 125mm (center-to-center) for small and medium sizes
- Standard pixel pitch of 200mm (center-to-center) for large size
- Customized mounting tracks available (sold separately)

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

Versions



159A0582



159A0345





159A0331










159A0652







Dimensional drawing



Dimensional drawing



Dimensional drawing



General Information	
Driver included	No
Light source replaceable	No
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover clear
Housing Color	Black
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 750 °C, duration 30 s

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
911401754042	BWS302 8LED 27K 24V A TB N10P20	85° x 110°	Warm white	2700 K	80
911401754122	BWS302 8LED 30K 24V A TB N10P20	85° x 110°	Warm white	3000 K	80
911401754202	BWS302 8LED 40K 24V A TB N10P20	85° x 110°	Neutral white	4000 K	80
911401753372	BWS301 6LED 27K 24V S TM N16P12	110° x 110°	Warm white	2700 K	80
911401753412	BWS301 6LED 30K 24V S TM N16P12	110° x 110°	Warm white	3000 K	80
911401753452	BWS301 6LED 40K 24V S TM N16P12	110° x 110°	Neutral white	4000 K	80
911401753082	BWS301 3LED 27K 15V A LR N16P12	85° x 110°	Warm white	2700 K	80
911401753162	BWS301 3LED 30K 15V A LR N16P12	85° x 110°	Warm white	3000 K	80
911401753242	BWS301 3LED 40K 15V A LR N16P12	85° x 110°	Neutral white	4000 K	80
911401752922	BWS300 4LED 27K 15V S N16P12	110° x 110°	Warm white	2700 K	80
911401752962	BWS300 4LED 30K 15V S N16P12	110° x 110°	Warm white	3000 K	80
911401753002	BWS300 4LED 40K 15V S N16P12	110° x 110°	Neutral white	4000 K	80
911401753522	BWS301 6LED 27K 24V A LR N16P12	85° x 110°	Warm white	2700 K	80
911401753602	BWS301 6LED 30K 24V A LR N16P12	85° x 110°	Warm white	3000 K	80
911401753682	BWS301 6LED 40K 24V A LR N16P12	85° x 110°	Neutral white	4000 K	80
911401753362	BWS301 6LED 27K 24V S N16P12	110° x 110°	Warm white	2700 K	80
911401753402	BWS301 6LED 30K 24V S N16P12	110° x 110°	Warm white	3000 K	80
911401753442	BWS301 6LED 40K 24V S N16P12	110° x 110°	Neutral white	4000 K	80
911401753852	BWS302 8LED 27K 24V S TM N10P20	110° x 110°	Warm white	2700 K	80
911401753892	BWS302 8LED 30K 24V S TM N10P20	110° x 110°	Warm white	3000 K	80
911401753932	BWS302 8LED 40K 24V S TM N10P20	110° x 110°	Neutral white	4000 K	80
911401753992	BWS302 9LED RGBNW 24V S DMX TM N10P20	110° x 110°	Red, green, blue and white	-	-
911401752932	BWS300 4LED 27K 15V S TM N16P12	110° x 110°	Warm white	2700 K	80
911401752972	BWS300 4LED 30K 15V S TM N16P12	110° x 110°	Warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color	Color rendering
				Temperature (Nom)	index (CRI)
911401753012	BWS300 4LED 40K 15V S TM N16P12	110° x 110°	Neutral white	4000 K	80
911401753122	BWS301 3LED 27K 15V A TB N16P12	85° x 110°	Warm white	2700 K	80
911401753202	BWS301 3LED 30K 15V A TB N16P12	85° x 110°	Warm white	3000 K	80
911401753282	BWS301 3LED 40K 15V A TB N16P12	85° x 110°	Neutral white	4000 K	80
911401753842	BWS302 8LED 27K 24V S N10P20	110° x 110°	Warm white	2700 K	80
911401753882	BWS302 8LED 30K 24V S N10P20	110° x 110°	Warm white	3000 K	80
911401753922	BWS302 8LED 40K 24V S N10P20	110° x 110°	Neutral white	4000 K	80
911401754052	BWS302 8LED 27K 24V A TM TB N10P20	85° x 110°	Warm white	2700 K	80
911401754132	BWS302 8LED 30K 24V A TM TB N10P20	85° x 110°	Warm white	3000 K	80
911401754212	BWS302 8LED 40K 24V A TM TB N10P20	85° x 110°	Neutral white	4000 K	80
911401753572	BWS301 6LED 27K 24V A TM TB N16P12	85° x 110°	Warm white	2700 K	80
911401753652	BWS301 6LED 30K 24V A TM TB N16P12	85° x 110°	Warm white	3000 K	80
911401753732	BWS301 6LED 40K 24V A TM TB N16P12	85° x 110°	Neutral white	4000 K	80
911401754002	BWS302 8LED 27K 24V A LR N10P20	85° x 110°	Warm white	2700 K	80
911401754082	BWS302 8LED 30K 24V A LR N10P20	85° x 110°	Warm white	3000 K	80
911401754162	BWS302 8LED 40K 24V A LR N10P20	85° x 110°	Neutral white	4000 K	80
911401753562	BWS301 6LED 27K 24V A TB N16P12	85° x 110°	Warm white	2700 K	80
911401753642	BWS301 6LED 30K 24V A TB N16P12	85° x 110°	Warm white	3000 K	80
911401753722	BWS301 6LED 40K 24V A TB N16P12	85° x 110°	Neutral white	4000 K	80
911401753132	BWS301 3LED 27K 15V A TM TB N16P12	85° x 110°	Warm white	2700 K	80
911401753212	BWS301 3LED 30K 15V A TM TB N16P12	85° x 110°	Warm white	3000 K	80
911401753292	BWS301 3LED 40K 15V A TM TB N16P12	85° x 110°	Neutral white	4000 K	80
911401753092	BWS301 3LED 27K 15V A TM LR N16P12	85° x 110°	Warm white	2700 K	80
911401753172	BWS301 3LED 30K 15V A TM LR N16P12	85° x 110°	Warm white	3000 K	80
911401753252	BWS301 3LED 40K 15V A TM LR N16P12	85° x 110°	Neutral white	4000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color	Color
				Temperature (Nom)	rendering index (CRI)
911401753532	BWS301 6LED 27K 24V A TM LR N16P12	85° x 110°	Warm white	2700 K	80
911401753612	BWS301 6LED 30K 24V A TM LR N16P12	85° x 110°	Warm white	3000 K	80
911401753692	BWS301 6LED 40K 24V A TM LR N16P12	85° x 110°	Neutral white	4000 K	80

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Order Code	Full Product Name	Luminous Flux
911401754042	BWS302 8LED 27K 24V A TB N10P20	126 lm	911401753202	BWS301 3LED 30K 15V A TB N16P12	51 lm
911401754122	BWS302 8LED 30K 24V A TB N10P20	126 lm	911401753282	BWS301 3LED 40K 15V A TB N16P12	55 lm
911401754202	BWS302 8LED 40K 24V A TB N10P20	134 lm	911401753842	BWS302 8LED 27K 24V S N10P20	142 lm
911401753372	BWS301 6LED 27K 24V S TM N16P12	101 lm	911401753882	BWS302 8LED 30K 24V S N10P20	142 lm
911401753412	BWS301 6LED 30K 24V S TM N16P12	101 lm	911401753922	BWS302 8LED 40K 24V S N10P20	151 lm
911401753452	BWS301 6LED 40K 24V S TM N16P12	108 lm	911401754052	BWS302 8LED 27K 24V A TM TB N10P20	126 lm
911401753082	BWS301 3LED 27K 15V A LR N16P12	51 lm	911401754132	BWS302 8LED 30K 24V A TM TB N10P20	126 lm
911401753162	BWS301 3LED 30K 15V A LR N16P12	51 lm	911401754212	BWS302 8LED 40K 24V A TM TB N10P20	134 lm
911401753242	BWS301 3LED 40K 15V A LR N16P12	55 lm	911401753572	BWS301 6LED 27K 24V A TM TB N16P12	87 lm
911401752922	BWS300 4LED 27K 15V S N16P12	67 lm	911401753652	BWS301 6LED 30K 24V A TM TB N16P12	87 lm
911401752962	BWS300 4LED 30K 15V S N16P12	67 lm	911401753732	BWS301 6LED 40K 24V A TM TB N16P12	92 lm
911401753002	BWS300 4LED 40K 15V S N16P12	71 lm	911401754002	BWS302 8LED 27K 24V A LR N10P20	126 lm
911401753522	BWS301 6LED 27K 24V A LR N16P12	87 lm	911401754082	BWS302 8LED 30K 24V A LR N10P20	126 lm
911401753602	BWS301 6LED 30K 24V A LR N16P12	87 lm	911401754162	BWS302 8LED 40K 24V A LR N10P20	134 lm
911401753682	BWS301 6LED 40K 24V A LR N16P12	92 lm	911401753562	BWS301 6LED 27K 24V A TB N16P12	87 lm
911401753362	BWS301 6LED 27K 24V S N16P12	101 lm	911401753642	BWS301 6LED 30K 24V A TB N16P12	87 lm
911401753402	BWS301 6LED 30K 24V S N16P12	101 lm	911401753722	BWS301 6LED 40K 24V A TB N16P12	92 lm
911401753442	BWS301 6LED 40K 24V S N16P12	108 lm	911401753132	BWS301 3LED 27K 15V A TM TB N16P12	51 lm
911401753852	BWS302 8LED 27K 24V S TM N10P20	142 lm	911401753212	BWS301 3LED 30K 15V A TM TB N16P12	51 lm
911401753892	BWS302 8LED 30K 24V S TM N10P20	142 lm	911401753292	BWS301 3LED 40K 15V A TM TB N16P12	55 lm
911401753932	BWS302 8LED 40K 24V S TM N10P20	151 lm	911401753092	BWS301 3LED 27K 15V A TM LR N16P12	51 lm
911401753992	BWS302 9LED RGBNW 24V S DMX TM N10P20	53 lm	911401753172	BWS301 3LED 30K 15V A TM LR N16P12	51 lm
911401752932	BWS300 4LED 27K 15V S TM N16P12	67 lm	911401753252	BWS301 3LED 40K 15V A TM LR N16P12	55 lm
911401752972	BWS300 4LED 30K 15V S TM N16P12	67 lm	911401753532	BWS301 6LED 27K 24V A TM LR N16P12	87 lm
911401753012	BWS300 4LED 40K 15V S TM N16P12	71 lm	911401753612	BWS301 6LED 30K 24V A TM LR N16P12	87 lm
911401753122	BWS301 3LED 27K 15V A TB N16P12	51 lm	911401753692	BWS301 6LED 40K 24V A TM LR N16P12	92 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401754042	BWS302 8LED 27K 24V A TB N10P20	20 W	911401752922	BWS300 4LED 27K 15V S N16P12	16 W
911401754122	BWS302 8LED 30K 24V A TB N10P20	20 W	911401752962	BWS300 4LED 30K 15V S N16P12	16 W
911401754202	BWS302 8LED 40K 24V A TB N10P20	20 W	911401753002	BWS300 4LED 40K 15V S N16P12	16 W
911401753372	BWS301 6LED 27K 24V S TM N16P12	24 W	911401753522	BWS301 6LED 27K 24V A LR N16P12	24 W
911401753412	BWS301 6LED 30K 24V S TM N16P12	24 W	911401753602	BWS301 6LED 30K 24V A LR N16P12	24 W
911401753452	BWS301 6LED 40K 24V S TM N16P12	24 W	911401753682	BWS301 6LED 40K 24V A LR N16P12	24 W
911401753082	BWS301 3LED 27K 15V A LR N16P12	16 W	911401753362	BWS301 6LED 27K 24V S N16P12	24 W
911401753162	BWS301 3LED 30K 15V A LR N16P12	16 W	911401753402	BWS301 6LED 30K 24V S N16P12	24 W
911401753242	BWS301 3LED 40K 15V A LR N16P12	16 W	911401753442	BWS301 6LED 40K 24V S N16P12	24 W

Order Code	Full Product Name	Power Consumption
911401753852	BWS302 8LED 27K 24V S TM N10P20	20 W
911401753892	BWS302 8LED 30K 24V S TM N10P20	20 W
911401753932	BWS302 8LED 40K 24V S TM N10P20	20 W
911401753992	BWS302 9LED RGBNW 24V S DMX TM N10P20	2 W
911401752932	BWS300 4LED 27K 15V S TM N16P12	16 W
911401752972	BWS300 4LED 30K 15V S TM N16P12	16 W
911401753012	BWS300 4LED 40K 15V S TM N16P12	16 W
911401753122	BWS301 3LED 27K 15V A TB N16P12	16 W
911401753202	BWS301 3LED 30K 15V A TB N16P12	16 W
911401753282	BWS301 3LED 40K 15V A TB N16P12	16 W
911401753842	BWS302 8LED 27K 24V S N10P20	20 W
911401753882	BWS302 8LED 30K 24V S N10P20	20 W
911401753922	BWS302 8LED 40K 24V S N10P20	20 W
911401754052	BWS302 8LED 27K 24V A TM TB N10P20	20 W
911401754132	BWS302 8LED 30K 24V A TM TB N10P20	20 W
911401754212	BWS302 8LED 40K 24V A TM TB N10P20	20 W
911401753572	BWS301 6LED 27K 24V A TM TB N16P12	24 W

Order Code	Full Product Name	Power Consumption
911401753652	BWS301 6LED 30K 24V A TM TB N16P12	24 W
911401753732	BWS301 6LED 40K 24V A TM TB N16P12	24 W
911401754002	BWS302 8LED 27K 24V A LR N10P20	20 W
911401754082	BWS302 8LED 30K 24V A LR N10P20	20 W
911401754162	BWS302 8LED 40K 24V A LR N10P20	20 W
911401753562	BWS301 6LED 27K 24V A TB N16P12	24 W
911401753642	BWS301 6LED 30K 24V A TB N16P12	24 W
911401753722	BWS301 6LED 40K 24V A TB N16P12	24 W
911401753132	BWS301 3LED 27K 15V A TM TB N16P12	16 W
911401753212	BWS301 3LED 30K 15V A TM TB N16P12	16 W
911401753292	BWS301 3LED 40K 15V A TM TB N16P12	16 W
911401753092	BWS301 3LED 27K 15V A TM LR N16P12	16 W
911401753172	BWS301 3LED 30K 15V A TM LR N16P12	16 W
911401753252	BWS301 3LED 40K 15V A TM LR N16P12	16 W
911401753532	BWS301 6LED 27K 24V A TM LR N16P12	24 W
911401753612	BWS301 6LED 30K 24V A TM LR N16P12	24 W
911401753692	BWS301 6LED 40K 24V A TM LR N16P12	24 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401754042	BWS302 8LED 27K 24V A TB N10P20	No	-
911401754122	BWS302 8LED 30K 24V A TB N10P20	No	-
911401754202	BWS302 8LED 40K 24V A TB N10P20	No	-
911401753372	BWS301 6LED 27K 24V S TM N16P12	No	-
911401753412	BWS301 6LED 30K 24V S TM N16P12	No	-
911401753452	BWS301 6LED 40K 24V S TM N16P12	No	-
911401753082	BWS301 3LED 27K 15V A LR N16P12	No	-
911401753162	BWS301 3LED 30K 15V A LR N16P12	No	-
911401753242	BWS301 3LED 40K 15V A LR N16P12	No	-
911401752922	BWS300 4LED 27K 15V S N16P12	No	-
911401752962	BWS300 4LED 30K 15V S N16P12	No	-
911401753002	BWS300 4LED 40K 15V S N16P12	No	-
911401753522	BWS301 6LED 27K 24V A LR N16P12	No	-
911401753602	BWS301 6LED 30K 24V A LR N16P12	No	-
911401753682	BWS301 6LED 40K 24V A LR N16P12	No	-
911401753362	BWS301 6LED 27K 24V S N16P12	No	-
911401753402	BWS301 6LED 30K 24V S N16P12	No	-
911401753442	BWS301 6LED 40K 24V S N16P12	No	-
911401753852	BWS302 8LED 27K 24V S TM N10P20	No	-
911401753892	BWS302 8LED 30K 24V S TM N10P20	No	-
911401753932	BWS302 8LED 40K 24V S TM N10P20	No	-
911401753992	BWS302 9LED RGBNW 24V S DMX TM N10P20	Yes	5%
911401752932	BWS300 4LED 27K 15V S TM N16P12	No	-
911401752972	BWS300 4LED 30K 15V S TM N16P12	No	-
911401753012	BWS300 4LED 40K 15V S TM N16P12	No	-
911401753122	BWS301 3LED 27K 15V A TB N16P12	No	-

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401753202	BWS301 3LED 30K 15V A TB N16P12	No	-
911401753282	BWS301 3LED 40K 15V A TB N16P12	No	-
911401753842	BWS302 8LED 27K 24V S N10P20	No	-
911401753882	BWS302 8LED 30K 24V S N10P20	No	-
911401753922	BWS302 8LED 40K 24V S N10P20	No	-
911401754052	BWS302 8LED 27K 24V A TM TB N10P20	No	-
911401754132	BWS302 8LED 30K 24V A TM TB N10P20	No	-
911401754212	BWS302 8LED 40K 24V A TM TB N10P20	No	-
911401753572	BWS301 6LED 27K 24V A TM TB N16P12	No	-
911401753652	BWS301 6LED 30K 24V A TM TB N16P12	No	-
911401753732	BWS301 6LED 40K 24V A TM TB N16P12	No	-
911401754002	BWS302 8LED 27K 24V A LR N10P20	No	-
911401754082	BWS302 8LED 30K 24V A LR N10P20	No	-
911401754162	BWS302 8LED 40K 24V A LR N10P20	No	-
911401753562	BWS301 6LED 27K 24V A TB N16P12	No	-
911401753642	BWS301 6LED 30K 24V A TB N16P12	No	-
911401753722	BWS301 6LED 40K 24V A TB N16P12	No	-
911401753132	BWS301 3LED 27K 15V A TM TB N16P12	No	-
911401753212	BWS301 3LED 30K 15V A TM TB N16P12	No	-
911401753292	BWS301 3LED 40K 15V A TM TB N16P12	No	-
911401753092	BWS301 3LED 27K 15V A TM LR N16P12	No	-
911401753172	BWS301 3LED 30K 15V A TM LR N16P12	No	-
911401753252	BWS301 3LED 40K 15V A TM LR N16P12	No	-
911401753532	BWS301 6LED 27K 24V A TM LR N16P12	No	-
911401753612	BWS301 6LED 30K 24V A TM LR N16P12	No	-
911401753692	BWS301 6LED 40K 24V A TM LR N16P12	No	-

