

**PHILIPS**

**Lighting**



# **Ledinaire highbay – For your everyday lighting jobs, easy to choose from the shelf and to install.**

## **Ledinaire High-bay**

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables, simple and flexible installation, either on a hook, or optional bracket. Products can be installed with optional reflectors for lower glare.

### **Benefits**

- Philips quality and reliability
- Energy savings
- Easy and quick installation
- Wide application coverage

### **Features**

- Modern, unobtrusive design
- Two lumen packages and sizes; 10,000lm 24cm (BY020P), 20,000lm 34cm (BY021P)
- High protection rates (IP65) rating perfect for any application
- Including IP65 connector
- Single suspension with installation hook

# Ledinaire High-bay

## Application

- Warehouses
- Manufacturing

## Versions



Ledinaire Highbay BY020P G3










Ledinaire Highbay BY021P G3



Ledinaire Highbay All-in BY30P

## Dimensional drawing



# Ledinaire High-bay

## Product details



Ledinaire BY030P CCT swtch  
DDP3



Ledinaire BY030P sensor install  
DPP

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Explosion hazard class	-
Ingress protection code	IP65
Emergency Operation	
Central Emergency	No
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

## Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Color	Luminous
			Beam angle of rendering	Efficacy (rated)
911401565044	BY020P G3 LED105S/840 PSU WB GR	-	116 degree(s)	80 150 lm/W
911401565144	BY021P G3 LED200S/840 PSU WB GR	-	116 degree(s)	80 150 lm/W
911401565244	BY022P G3 LED280S/840 PSU WB GR	-	116 degree(s)	80 150 lm/W
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	All-in, Multi Lumen	>80	152 lm/W

## Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type
911401565044	BY020P G3 LED105S/840 PSU WB GR	10,500 lm	Wide beam
911401565144	BY021P G3 LED200S/840 PSU WB GR	20,000 lm	Wide beam
911401565244	BY022P G3 LED280S/840 PSU WB GR	28,000 lm	Wide beam

Order Code	Full Product Name	Luminous Flux	Optic type
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	15,000 lm	Symmetrical

## Operating and Electrical

# Ledinaire High-bay

Order Code	Full Product Name	Input			Power Consumption	Suitable for random switching
		Voltage	Power	random switching		
911401565044	BY020P G3 LED105S/840 PSU WB GR	220-240 V	70 W	Yes		
911401565144	BY021P G3 LED200S/840 PSU WB GR	220-240 V	133 W	Yes		
911401565244	BY022P G3 LED280S/840 PSU WB GR	220-240 V	185 W	Yes		

Order Code	Full Product Name	Input			Power Consumption	Suitable for random switching
		Voltage	Power	random switching		
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	220 to 240 V	195 W	No		

## Controls and Dimming

Order Code	Full Product Name	Embedded control		Maximum dim level
		control	Maximum dim level	
911401565044	BY020P G3 LED105S/840 PSU WB GR	Constant light output	Not applicable	
911401565144	BY021P G3 LED200S/840 PSU WB GR	Constant light output	Not applicable	

Order Code	Full Product Name	Embedded control		Maximum dim level
		control	Maximum dim level	
911401565244	BY022P G3 LED280S/840 PSU WB GR	Constant light output	Not applicable	
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	-	-	

## Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection	
		Housing Color	code
911401565044	BY020P G3 LED105S/840 PSU WB GR	Grey	IK06
911401565144	BY021P G3 LED200S/840 PSU WB GR	Grey	IK06
911401565244	BY022P G3 LED280S/840 PSU WB GR	Grey	IK06

Order Code	Full Product Name	Mech. impact protection	
		Housing Color	code
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	Aluminum and black	IK07

## Approval and Application

Order Code	Full Product Name	Stroboscopic effect visibility		
		Ambient temperature range	measure (SVM)	
911401565044	BY020P G3 LED105S/840 PSU WB GR	-20 °C to 45 °C	-	
911401565144	BY021P G3 LED200S/840 PSU WB GR	-20 °C to 45 °C	-	

Order Code	Full Product Name	Stroboscopic effect visibility		
		Ambient temperature range	measure (SVM)	
911401565244	BY022P G3 LED280S/840 PSU WB GR	-20 °C to 45 °C	-	
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	-30 to +50 °C	0.9	

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity		Luminous flux tolerance
		chromaticity	tolerance	
911401565044	BY020P G3 LED105S/840 PSU WB GR	0.38;0.38	+/-10%	
911401565144	BY021P G3 LED200S/840 PSU WB GR	0.38;0.38	+/-10%	

Order Code	Full Product Name	Initial chromaticity		Luminous flux tolerance
		chromaticity	tolerance	
911401565244	BY022P G3 LED280S/840 PSU WB GR	0.38;0.38	+/-10%	
911401822687	BY030P LED150_220_280S/840_50_65 PSU WB	(0.38, 0.38); (0.31, 0.34)	+/-10% / +10% SDCM≤5	

## Ledinaire High-bay



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)  
2025, December 13 - data subject to change