



# Classic, economical and reliable highbay luminaire

## GreenUp Round Highbay

The GreenUp Round Highbay range of luminaires provides the optimal balance between basic performance and price. The family covers a wide product range with a variety of options, competitive specifications, and long-term quality and reliability. The range is suitable for most industrial applications.

### Benefits

- Excellent energy savings, great value for money
- High light quality with a range of lumen packages for different applications
- Robust and reliable

### Features

- 140 lm/W system efficacy
- Narrow and wide beam options
- IP65/IK06 protection
- 50,000 hours lifetime @Ta 35°C
- -20°C to 45°C working temperature

### Application

- Manufacturing
- Warehouse

### Specifications

|               |           |                             |               |
|---------------|-----------|-----------------------------|---------------|
| Mounting type | Surface   | Operating Temperature range | -20 to +45 °C |
|               | Suspended |                             |               |
|               | Pipe      |                             |               |
| Light Source  |           | LED                         |               |

GreenUp Round Highbay

|                                                 |                            |
|-------------------------------------------------|----------------------------|
| Mains Voltage                                   | 220-240V / 50-60Hz         |
| Mains connection                                | Flying cable               |
| Mechanical Accessories                          | Mounting bracket           |
| Optical Accessories                             | Reflector                  |
| Dimming                                         | PSU: non-dimmable          |
| Material                                        | Housing: die-cast aluminum |
| Lumen maintenance at median useful life 50.000h | L70                        |
| Flicker / Pst / SVM                             | <15%                       |
| Luminous flux                                   | 11klm - 30klm              |
| Power consumption                               | 77W - 207W                 |
| Luminaire efficacy                              | Up to 143lm/W              |
| Correlated color temperature - CCT              | 4000K<br>6500K             |

|                              |          |
|------------------------------|----------|
| Color Rendering index - 80   |          |
| CRI                          |          |
| Beam angle                   | WB       |
|                              | NB       |
| Reflector material           | Aluminum |
| Optical cover/lens material  | PC       |
| Optical cover/lens finish    | Clear    |
| Protection Class             | Class I  |
| IEC61140                     |          |
| Mechanical impact protection | IK06     |
| Ingress protection           | IP65     |

Versions








GreenUp-Round-Highbay-  
Additional-Product-Photo-  
BY518P-SE








Size S

Dimensional drawing



# GreenUp Round Highbay

## Dimensional drawing



| General Information                 |                |
|-------------------------------------|----------------|
| Gear                                | -              |
| Light Technical                     |                |
| Color rendering index (CRI)         | >80            |
| Operating and Electrical            |                |
| Protection class IEC                | Safety class I |
| Line Frequency                      | 50 or 60 Hz    |
| Controls and Dimming                |                |
| Dimmable                            | No             |
| Mechanical and Housing              |                |
| Optical cover type                  | Lens           |
| Mech. impact protection code        | IK06           |
| Ingress protection code             | IP65           |
| Approval and Application            |                |
| CE mark                             | Yes            |
| ENEC mark                           | -              |
| Flammability mark                   | -              |
| Glow-wire test                      | -              |
| Initial Performance (IEC Compliant) |                |
| Luminous flux tolerance             | +/-10%         |

## General Information

| Order Code   | Full Product Name             | Driver included | Number of gear units | Service tag |
|--------------|-------------------------------|-----------------|----------------------|-------------|
| 911401588745 | BY518P SE LED50/NW PSU WB     | Yes             | 1 unit               | -           |
| 911401588845 | BY518P SE LED50/CW PSU WB     | Yes             | 1 unit               | -           |
| 911401588945 | BY518P SE LED70/NW PSU WB     | Yes             | 1 unit               | -           |
| 911401589045 | BY518P SE LED70/CW PSU WB     | Yes             | 1 unit               | -           |
| 911401647607 | BY518P LED210/NW PSU WB GM    | -               | -                    | Yes         |
| 911401647707 | BY518P LED210/CW PSU WB GM    | -               | -                    | Yes         |
| 911401648307 | BY518P LED210/CW PSU NB GM    | -               | -                    | Yes         |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678508 | BY518P SE LED245/CW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678608 | BY518P SE LED290/NW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401678708 | BY518P SE LED290/CW PSU WB GM | Yes             | 1 unit               | Yes         |
| 911401648107 | BY518P LED300/CW PSU WB GM    | -               | -                    | Yes         |
| 911401648707 | BY518P LED300/CW PSU NB GM    | -               | -                    | Yes         |
| 911401672007 | BY518P LED110/NW PSU WB GM    | -               | -                    | Yes         |
| 911401672107 | BY518P LED110/CW PSU WB GM    | -               | -                    | Yes         |
| 911401672207 | BY518P LED160/NW PSU WB GM    | -               | -                    | Yes         |
| 911401672307 | BY518P LED160/CW PSU WB GM    | -               | -                    | Yes         |
| 911401672507 | BY518P LED110/CW PSU NB GM    | -               | -                    | Yes         |
| 911401672707 | BY518P LED160/CW PSU NB GM    | -               | -                    | Yes         |

| Order Code   | Full Product Name          | Driver included | Number of gear units | Service tag |
|--------------|----------------------------|-----------------|----------------------|-------------|
| 911401647807 | BY518P LED260/NW PSU WB GM | -               | -                    | Yes         |
| 911401647907 | BY518P LED260/CW PSU WB GM | -               | -                    | Yes         |

## Light Technical (1/2)

| Order Code   | Full Product Name                   | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-------------------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401588745 | BY518P SE<br>LED50/NW<br>PSU WB     | 120<br>degree(s)           | 4000 K                             | 163 lm/W                        | 5,000 lm      |
| 911401588845 | BY518P SE<br>LED50/CW<br>PSU WB     | 120<br>degree(s)           | 6500 K                             | 163 lm/W                        | 5,000 lm      |
| 911401588945 | BY518P SE<br>LED70/NW<br>PSU WB     | 120<br>degree(s)           | 4000 K                             | 159 lm/W                        | 7,000 lm      |
| 911401589045 | BY518P SE<br>LED70/CW<br>PSU WB     | 120<br>degree(s)           | 6500 K                             | 159 lm/W                        | 7,000 lm      |
| 911401647607 | BY518P<br>LED210/NW<br>PSU WB GM    | -                          | 4000 K                             | 137 lm/W                        | 21,000 lm     |
| 911401647707 | BY518P<br>LED210/CW<br>PSU WB GM    | -                          | 6500 K                             | 137 lm/W                        | 21,000 lm     |
| 911401648307 | BY518P<br>LED210/CW<br>PSU NB GM    | -                          | 6500 K                             | 137 lm/W                        | 21,000 lm     |
| 911401677808 | BY518P SE<br>LED105/NW<br>PSU WB GM | 120<br>degree(s)           | 4000 K                             | 150 lm/W                        | 10,500 lm     |
| 911401677908 | BY518P SE<br>LED105/CW<br>PSU WB GM | 120<br>degree(s)           | 6500 K                             | 150 lm/W                        | 10,500 lm     |
| 911401678008 | BY518P SE<br>LED140/NW<br>PSU WB GM | 120<br>degree(s)           | 4000 K                             | 143 lm/W                        | 14,000 lm     |
| 911401678108 | BY518P SE<br>LED140/CW<br>PSU WB GM | 120<br>degree(s)           | 6500 K                             | 143 lm/W                        | 14,000 lm     |
| 911401678208 | BY518P SE<br>LED200/NW<br>PSU WB GM | 120<br>degree(s)           | 4000 K                             | 148 lm/W                        | 20,000 lm     |
| 911401678308 | BY518P SE<br>LED200/CW<br>PSU WB GM | 120<br>degree(s)           | 6500 K                             | 148 lm/W                        | 20,000 lm     |
| 911401678408 | BY518P SE<br>LED245/NW<br>PSU WB GM | 120<br>degree(s)           | 4000 K                             | 153 lm/W                        | 24,500 lm     |
| 911401678508 | BY518P SE<br>LED245/CW<br>PSU WB GM | 120<br>degree(s)           | 6500 K                             | 153 lm/W                        | 24,500 lm     |
| 911401678608 | BY518P SE<br>LED290/NW<br>PSU WB GM | 120<br>degree(s)           | 4000 K                             | 151 lm/W                        | 29,000 lm     |
| 911401678708 | BY518P SE<br>LED290/CW<br>PSU WB GM | 120<br>degree(s)           | 6500 K                             | 151 lm/W                        | 29,000 lm     |
| 911401648107 | BY518P<br>LED300/CW<br>PSU WB GM    | -                          | 6500 K                             | 143 lm/W                        | 30,000 lm     |
| 911401648707 | BY518P<br>LED300/CW<br>PSU NB GM    | -                          | 6500 K                             | 143 lm/W                        | 30,000 lm     |
| 911401672007 | BY518P<br>LED110/NW<br>PSU WB GM    | -                          | 4000 K                             | 143 lm/W                        | 11,000 lm     |
| 911401672107 | BY518P<br>LED110/CW<br>PSU WB GM    | -                          | 6500 K                             | 143 lm/W                        | 11,000 lm     |
| 911401672207 | BY518P<br>LED160/NW<br>PSU WB GM    | -                          | 4000 K                             | 139 lm/W                        | 16,000 lm     |
| 911401672307 | BY518P<br>LED160/CW<br>PSU WB GM    | -                          | 6500 K                             | 139 lm/W                        | 16,000 lm     |
| 911401672507 | BY518P<br>LED110/CW<br>PSU NB GM    | -                          | 6500 K                             | 143 lm/W                        | 11,000 lm     |
| 911401672707 | BY518P<br>LED160/CW<br>PSU NB GM    | -                          | 6500 K                             | 139 lm/W                        | 16,000 lm     |
| 911401647807 | BY518P<br>LED260/NW<br>PSU WB GM    | -                          | 4000 K                             | 139 lm/W                        | 26,000 lm     |
| 911401647907 | BY518P<br>LED260/CW<br>PSU WB GM    | -                          | 6500 K                             | 139 lm/W                        | 26,000 lm     |

GreenUp Round Highbay

Light Technical (2/2)

| Order Code   | Full Product Name             | Number of light |            |
|--------------|-------------------------------|-----------------|------------|
|              |                               | sources         | Optic type |
| 911401588745 | BY518P SE LED50/NW PSU WB     | 1               | Wide beam  |
| 911401588845 | BY518P SE LED50/CW PSU WB     | 1               | Wide beam  |
| 911401588945 | BY518P SE LED70/NW PSU WB     | 1               | Wide beam  |
| 911401589045 | BY518P SE LED70/CW PSU WB     | 1               | Wide beam  |
| 911401647607 | BY518P LED210/NW PSU WB GM    | -               | -          |
| 911401647707 | BY518P LED210/CW PSU WB GM    | -               | -          |
| 911401648307 | BY518P LED210/CW PSU NB GM    | -               | -          |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | 1               | Wide beam  |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | 1               | Wide beam  |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | 1               | Wide beam  |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | 1               | Wide beam  |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | 1               | Wide beam  |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | 1               | Wide beam  |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | 1               | Wide beam  |

| Order Code   | Full Product Name             | Number of light |            |
|--------------|-------------------------------|-----------------|------------|
|              |                               | sources         | Optic type |
| 911401678508 | BY518P SE LED245/CW PSU WB GM | 1               | Wide beam  |
| 911401678608 | BY518P SE LED290/NW PSU WB GM | 1               | Wide beam  |
| 911401678708 | BY518P SE LED290/CW PSU WB GM | 1               | Wide beam  |
| 911401648107 | BY518P LED300/CW PSU WB GM    | -               | -          |
| 911401648707 | BY518P LED300/CW PSU NB GM    | -               | -          |
| 911401672007 | BY518P LED110/NW PSU WB GM    | -               | -          |
| 911401672107 | BY518P LED110/CW PSU WB GM    | -               | -          |
| 911401672207 | BY518P LED160/NW PSU WB GM    | -               | -          |
| 911401672307 | BY518P LED160/CW PSU WB GM    | -               | -          |
| 911401672507 | BY518P LED110/CW PSU NB GM    | -               | -          |
| 911401672707 | BY518P LED160/CW PSU NB GM    | -               | -          |
| 911401647807 | BY518P LED260/NW PSU WB GM    | -               | -          |
| 911401647907 | BY518P LED260/CW PSU WB GM    | -               | -          |

Operating and Electrical

| Order Code   | Full Product Name             | Power         |             | Suitable for random switching |
|--------------|-------------------------------|---------------|-------------|-------------------------------|
|              |                               | Input Voltage | Consumption |                               |
| 911401588745 | BY518P SE LED50/NW PSU WB     | 220-240 V     | 30.5 W      | No                            |
| 911401588845 | BY518P SE LED50/CW PSU WB     | 220-240 V     | 30.5 W      | No                            |
| 911401588945 | BY518P SE LED70/NW PSU WB     | 220-240 V     | 44 W        | No                            |
| 911401589045 | BY518P SE LED70/CW PSU WB     | 220-240 V     | 44 W        | No                            |
| 911401647607 | BY518P LED210/NW PSU WB GM    | 220-240 V     | 154 W       | -                             |
| 911401647707 | BY518P LED210/CW PSU WB GM    | 220-240 V     | 154 W       | -                             |
| 911401648307 | BY518P LED210/CW PSU NB GM    | 220-240 V     | 154 W       | -                             |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | 220 to 240 V  | 70 W        | No                            |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | 220 to 240 V  | 70 W        | No                            |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | 220 to 240 V  | 98 W        | No                            |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | 220 to 240 V  | 98 W        | No                            |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | 220 to 240 V  | 135 W       | No                            |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | 220 to 240 V  | 135 W       | No                            |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | 220 to 240 V  | 160 W       | No                            |

| Order Code   | Full Product Name             | Power         |             | Suitable for random switching |
|--------------|-------------------------------|---------------|-------------|-------------------------------|
|              |                               | Input Voltage | Consumption |                               |
| 911401678508 | BY518P SE LED245/CW PSU WB GM | 220 to 240 V  | 160 W       | No                            |
| 911401678608 | BY518P SE LED290/NW PSU WB GM | 220 to 240 V  | 192 W       | No                            |
| 911401678708 | BY518P SE LED290/CW PSU WB GM | 220 to 240 V  | 192 W       | No                            |
| 911401648107 | BY518P LED300/CW PSU WB GM    | 220-240 V     | 207 W       | -                             |
| 911401648707 | BY518P LED300/CW PSU NB GM    | 220-240 V     | 207 W       | -                             |
| 911401672007 | BY518P LED110/NW PSU WB GM    | 220-240 V     | 77 W        | -                             |
| 911401672107 | BY518P LED110/CW PSU WB GM    | 220-240 V     | 77 W        | -                             |
| 911401672207 | BY518P LED160/NW PSU WB GM    | 220-240 V     | 115 W       | -                             |
| 911401672307 | BY518P LED160/CW PSU WB GM    | 220-240 V     | 115 W       | -                             |
| 911401672507 | BY518P LED110/CW PSU NB GM    | 220-240 V     | 77 W        | -                             |
| 911401672707 | BY518P LED160/CW PSU NB GM    | 220-240 V     | 115 W       | -                             |
| 911401647807 | BY518P LED260/NW PSU WB GM    | 220-240 V     | 187 W       | -                             |
| 911401647907 | BY518P LED260/CW PSU WB GM    | 220-240 V     | 187 W       | -                             |

Controls and Dimming

| Order Code   | Full Product Name             | Maximum dim level |
|--------------|-------------------------------|-------------------|
| 911401588745 | BY518P SE LED50/NW PSU WB     | Not applicable    |
| 911401588845 | BY518P SE LED50/CW PSU WB     | Not applicable    |
| 911401588945 | BY518P SE LED70/NW PSU WB     | Not applicable    |
| 911401589045 | BY518P SE LED70/CW PSU WB     | Not applicable    |
| 911401647607 | BY518P LED210/NW PSU WB GM    | -                 |
| 911401647707 | BY518P LED210/CW PSU WB GM    | -                 |
| 911401648307 | BY518P LED210/CW PSU NB GM    | -                 |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | Not applicable    |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | Not applicable    |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | Not applicable    |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | Not applicable    |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | Not applicable    |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | Not applicable    |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | Not applicable    |

| Order Code   | Full Product Name             | Maximum dim level |
|--------------|-------------------------------|-------------------|
| 911401678508 | BY518P SE LED245/CW PSU WB GM | Not applicable    |
| 911401678608 | BY518P SE LED290/NW PSU WB GM | Not applicable    |
| 911401678708 | BY518P SE LED290/CW PSU WB GM | Not applicable    |
| 911401648107 | BY518P LED300/CW PSU WB GM    | -                 |
| 911401648707 | BY518P LED300/CW PSU NB GM    | -                 |
| 911401672007 | BY518P LED110/NW PSU WB GM    | -                 |
| 911401672107 | BY518P LED110/CW PSU WB GM    | -                 |
| 911401672207 | BY518P LED160/NW PSU WB GM    | -                 |
| 911401672307 | BY518P LED160/CW PSU WB GM    | -                 |
| 911401672507 | BY518P LED110/CW PSU NB GM    | -                 |
| 911401672707 | BY518P LED160/CW PSU NB GM    | -                 |
| 911401647807 | BY518P LED260/NW PSU WB GM    | -                 |
| 911401647907 | BY518P LED260/CW PSU WB GM    | -                 |

Mechanical and Housing

| Order Code   | Full Product Name             | Housing Color |
|--------------|-------------------------------|---------------|
| 911401588745 | BY518P SE LED50/NW PSU WB     | Grey          |
| 911401588845 | BY518P SE LED50/CW PSU WB     | Grey          |
| 911401588945 | BY518P SE LED70/NW PSU WB     | Grey          |
| 911401589045 | BY518P SE LED70/CW PSU WB     | Grey          |
| 911401647607 | BY518P LED210/NW PSU WB GM    | Gray          |
| 911401647707 | BY518P LED210/CW PSU WB GM    | Gray          |
| 911401648307 | BY518P LED210/CW PSU NB GM    | Gray          |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | Grey          |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | Grey          |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | Grey          |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | Grey          |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | Grey          |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | Grey          |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | Grey          |

| Order Code   | Full Product Name             | Housing Color |
|--------------|-------------------------------|---------------|
| 911401678508 | BY518P SE LED245/CW PSU WB GM | Grey          |
| 911401678608 | BY518P SE LED290/NW PSU WB GM | Grey          |
| 911401678708 | BY518P SE LED290/CW PSU WB GM | Grey          |
| 911401648107 | BY518P LED300/CW PSU WB GM    | Gray          |
| 911401648707 | BY518P LED300/CW PSU NB GM    | Gray          |
| 911401672007 | BY518P LED110/NW PSU WB GM    | Gray          |
| 911401672107 | BY518P LED110/CW PSU WB GM    | Gray          |
| 911401672207 | BY518P LED160/NW PSU WB GM    | Gray          |
| 911401672307 | BY518P LED160/CW PSU WB GM    | Gray          |
| 911401672507 | BY518P LED110/CW PSU NB GM    | Gray          |
| 911401672707 | BY518P LED160/CW PSU NB GM    | Gray          |
| 911401647807 | BY518P LED260/NW PSU WB GM    | Gray          |
| 911401647907 | BY518P LED260/CW PSU WB GM    | Gray          |

Approval and Application

| Order Code   | Full Product Name             | Ambient temperature range |
|--------------|-------------------------------|---------------------------|
| 911401588745 | BY518P SE LED50/NW PSU WB     | -30 to +45 °C             |
| 911401588845 | BY518P SE LED50/CW PSU WB     | -30 to +45 °C             |
| 911401588945 | BY518P SE LED70/NW PSU WB     | -30 to +45 °C             |
| 911401589045 | BY518P SE LED70/CW PSU WB     | -30 to +45 °C             |
| 911401647607 | BY518P LED210/NW PSU WB GM    | -20 to +45 °C             |
| 911401647707 | BY518P LED210/CW PSU WB GM    | -20 to +45 °C             |
| 911401648307 | BY518P LED210/CW PSU NB GM    | -20 to +45 °C             |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | -30 to +45 °C             |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | -30 to +45 °C             |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | -30 to +45 °C             |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | -30 to +45 °C             |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | -30 to +45 °C             |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | -30 to +45 °C             |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | -30 to +45 °C             |

| Order Code   | Full Product Name             | Ambient temperature range |
|--------------|-------------------------------|---------------------------|
| 911401678508 | BY518P SE LED245/CW PSU WB GM | -30 to +45 °C             |
| 911401678608 | BY518P SE LED290/NW PSU WB GM | -30 to +45 °C             |
| 911401678708 | BY518P SE LED290/CW PSU WB GM | -30 to +45 °C             |
| 911401648107 | BY518P LED300/CW PSU WB GM    | -20 to +45 °C             |
| 911401648707 | BY518P LED300/CW PSU NB GM    | -20 to +45 °C             |
| 911401672007 | BY518P LED110/NW PSU WB GM    | -20 to +45 °C             |
| 911401672107 | BY518P LED110/CW PSU WB GM    | -20 to +45 °C             |
| 911401672207 | BY518P LED160/NW PSU WB GM    | -20 to +45 °C             |
| 911401672307 | BY518P LED160/CW PSU WB GM    | -20 to +45 °C             |
| 911401672507 | BY518P LED110/CW PSU NB GM    | -20 to +45 °C             |
| 911401672707 | BY518P LED160/CW PSU NB GM    | -20 to +45 °C             |
| 911401647807 | BY518P LED260/NW PSU WB GM    | -20 to +45 °C             |
| 911401647907 | BY518P LED260/CW PSU WB GM    | -20 to +45 °C             |

Initial Performance (IEC Compliant)

| Order Code   | Full Product Name             | Initial chromaticity  | Order Code   | Full Product Name             | Initial chromaticity  |
|--------------|-------------------------------|-----------------------|--------------|-------------------------------|-----------------------|
| 911401588745 | BY518P SE LED50/NW PSU WB     | (0.38, 0.375) SDCM<5  | 911401678508 | BY518P SE LED245/CW PSU WB GM | (0.313, 0.329) SDCM<5 |
| 911401588845 | BY518P SE LED50/CW PSU WB     | (0.313, 0.329) SDCM<5 | 911401678608 | BY518P SE LED290/NW PSU WB GM | (0.38, 0.375) SDCM<5  |
| 911401588945 | BY518P SE LED70/NW PSU WB     | (0.38, 0.375) SDCM<5  | 911401678708 | BY518P SE LED290/CW PSU WB GM | (0.313, 0.329) SDCM<5 |
| 911401589045 | BY518P SE LED70/CW PSU WB     | (0.313, 0.329) SDCM<5 | 911401648107 | BY518P LED300/CW PSU WB GM    | (0.316, 0.332) SDCM<5 |
| 911401647607 | BY518P LED210/NW PSU WB GM    | (0.385, 0.380) SDCM<5 | 911401648707 | BY518P LED300/CW PSU NB GM    | (0.316, 0.332) SDCM<5 |
| 911401647707 | BY518P LED210/CW PSU WB GM    | (0.316, 0.332) SDCM<5 | 911401672007 | BY518P LED110/NW PSU WB GM    | (0.385, 0.380) SDCM<5 |
| 911401648307 | BY518P LED210/CW PSU NB GM    | (0.316, 0.332) SDCM<5 | 911401672107 | BY518P LED110/CW PSU WB GM    | (0.316, 0.332) SDCM<5 |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | (0.38, 0.375) SDCM<5  | 911401672207 | BY518P LED160/NW PSU WB GM    | (0.385, 0.380) SDCM<5 |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | (0.313, 0.329) SDCM<5 | 911401672307 | BY518P LED160/CW PSU WB GM    | (0.316, 0.332) SDCM<5 |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | (0.38, 0.375) SDCM<5  | 911401672507 | BY518P LED110/CW PSU NB GM    | (0.316, 0.332) SDCM<5 |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | (0.313, 0.329) SDCM<5 | 911401672707 | BY518P LED160/CW PSU NB GM    | (0.316, 0.332) SDCM<5 |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | (0.38, 0.375) SDCM<5  | 911401647807 | BY518P LED260/NW PSU WB GM    | (0.385, 0.380) SDCM<5 |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | (0.313, 0.329) SDCM<5 | 911401647907 | BY518P LED260/CW PSU WB GM    | (0.316, 0.332) SDCM<5 |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | (0.38, 0.375) SDCM<5  |              |                               |                       |

