

Cleanroom LED CR250B

CR250B



Cleanroom: uniform, reliable, value-for-money solution

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65 and IP54-rated luminaires that are safe to use and come at an attractive price. This family of Philips Cleanroom CR250B fixtures represent true value for money: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this cleanroom LED lighting family can be used in a wide range of applications. These cleanroom luminaires are also compliant with all relevant standards (CE, EMC, RoHS).

Benefits

- Value-for-money investment
- Low maintenance costs due to the long lifetime of the luminaire
- Meets light-level requirements for main applications


Applications

- Food production facilities and kitchens
- Hospitals and Care Centers
- Clean production areas

Features

- Uniform surface of light
- IP65 (glass cover) and IP54 (PMMA cover) versions
- Light output 3500 to 5500 lm
- Works with different ceiling types
- Class II

Versions



Cleanroom LED-CR150B
W60L60



Cleanroom LED-CR150B
W30L120




Cleanroom LED-CR250B
W60L60



Cleanroom LED-CR250B
W30L120


Dimensional drawing





CR150B W60L60




CR150B W30L120



CR250B W60L60



CR250B W30L120



Product details



Cleanroom_LED-
CR250B_W60L60-DP01



Cleanroom_LED-
CR250B_W60L60-DP02



Cleanroom_LED-
CR150B_W30L120_PSU-DP04



Cleanroom_LED-
CR150B_W30L120_PSD-DP05



Cleanroom_LED-CR150B-
PSU_W30L120_PSU-DP06



Cleanroom_LED-
CR150B_W30L120_PSD-DP07



Cleanroom_LED-CR250B_PSU-
DP08



Cleanroom_LED-
CR150B_W30L120_CR150Z_S
MB-DP11



Cleanroom_LED-
CR150B_W60L60_CR150Z_SM
B-DP12



Cleanroom_LED-
CR250B_W30L120_CR250Z_S
MB-DP13



Cleanroom_LED-
CR250B_W60L60_CR250Z_SM
B-DP14

General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	No

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Number of light sources	2
Optic type	-

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Protection class IEC	Safety class II

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
-------------------------	-------

General Information

Order Code	Full Product Name	Lamp family code
910503910175	CR150B LED35S/840 PSU W60L60 IP54	GRN35
910503910176	CR150B LED35S/840 PSD W60L60 IP54	GRN35
910503910177	CR150B LED35S/840 PSU W30L120 IP54	GRN35
910503910178	CR150B LED35S/840 PSD W30L120 IP54	GRN35
910503910167	CR250B LED35S/840 PSU W60L60 IP65	GRN35
910503910168	CR250B LED35S/840 PSD W60L60 IP65	GRN35
910503910169	CR250B LED55S/840 PSU W60L60 IP65	GRN55
910503910170	CR250B LED55S/840 PSD W60L60 IP65	GRN55
910503910171	CR250B LED35S/840 PSU W30L120 IP65	GRN35
910503910172	CR250B LED35S/840 PSD W30L120 IP65	GRN35
910503910173	CR250B LED55S/840 PSU W30L120 IP65	GRN55
910503910174	CR250B LED55S/840 PSD W30L120 IP65	GRN55

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
910503910175	CR150B LED35S/840 PSU W60L60 IP54	3,500 lm	88 lm/W
910503910176	CR150B LED35S/840 PSD W60L60 IP54	3,500 lm	88 lm/W
910503910177	CR150B LED35S/840 PSU W30L120 IP54	3,500 lm	88 lm/W
910503910178	CR150B LED35S/840 PSD W30L120 IP54	3,500 lm	88 lm/W
910503910167	CR250B LED35S/840 PSU W60L60 IP65	3,500 lm	88 lm/W
910503910168	CR250B LED35S/840 PSD W60L60 IP65	3,500 lm	88 lm/W
910503910169	CR250B LED55S/840 PSU W60L60 IP65	5,500 lm	87 lm/W
910503910170	CR250B LED55S/840 PSD W60L60 IP65	5,500 lm	87 lm/W
910503910171	CR250B LED35S/840 PSU W30L120 IP65	3,500 lm	88 lm/W
910503910172	CR250B LED35S/840 PSD W30L120 IP65	3,500 lm	88 lm/W
910503910173	CR250B LED55S/840 PSU W30L120 IP65	5,500 lm	87 lm/W
910503910174	CR250B LED55S/840 PSD W30L120 IP65	5,500 lm	87 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910503910175	CR150B LED35S/840 PSU W60L60 IP54	40 W
910503910176	CR150B LED35S/840 PSD W60L60 IP54	40 W
910503910177	CR150B LED35S/840 PSU W30L120 IP54	40 W
910503910178	CR150B LED35S/840 PSD W30L120 IP54	40 W
910503910167	CR250B LED35S/840 PSU W60L60 IP65	40 W
910503910168	CR250B LED35S/840 PSD W60L60 IP65	40 W
910503910169	CR250B LED55S/840 PSU W60L60 IP65	63 W
910503910170	CR250B LED55S/840 PSD W60L60 IP65	63 W
910503910171	CR250B LED35S/840 PSU W30L120 IP65	40 W
910503910172	CR250B LED35S/840 PSD W30L120 IP65	40 W
910503910173	CR250B LED55S/840 PSU W30L120 IP65	63 W
910503910174	CR250B LED55S/840 PSD W30L120 IP65	63 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910503910175	CR150B LED35S/840 PSU W60L60 IP54	No
910503910176	CR150B LED35S/840 PSD W60L60 IP54	Yes
910503910177	CR150B LED35S/840 PSU W30L120 IP54	No
910503910178	CR150B LED35S/840 PSD W30L120 IP54	Yes
910503910167	CR250B LED35S/840 PSU W60L60 IP65	No
910503910168	CR250B LED35S/840 PSD W60L60 IP65	Yes
910503910169	CR250B LED55S/840 PSU W60L60 IP65	No
910503910170	CR250B LED55S/840 PSD W60L60 IP65	Yes
910503910171	CR250B LED35S/840 PSU W30L120 IP65	No
910503910172	CR250B LED35S/840 PSD W30L120 IP65	Yes
910503910173	CR250B LED55S/840 PSU W30L120 IP65	No
910503910174	CR250B LED55S/840 PSD W30L120 IP65	Yes

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code	Optical cover type
910503910175	CR150B LED35S/840 PSU W60L60 IP54	IP54	IK03	Polymethyl methacrylate bowl/cover
910503910176	CR150B LED35S/840 PSD W60L60 IP54	IP54	IK03	Polymethyl methacrylate bowl/cover
910503910177	CR150B LED35S/840 PSU W30L120 IP54	IP54	IK03	Polymethyl methacrylate bowl/cover
910503910178	CR150B LED35S/840 PSD W30L120 IP54	IP54	IK03	Polymethyl methacrylate bowl/cover
910503910167	CR250B LED35S/840 PSU W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910168	CR250B LED35S/840 PSD W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910169	CR250B LED55S/840 PSU W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910170	CR250B LED55S/840 PSD W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910171	CR250B LED35S/840 PSU W30L120 IP65	IP65	IK07	Clear glass with diffuser foil

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code	Optical cover type
910503910172	CR250B LED35S/840 PSD W30L120 IP65	IP65	IK07	Clear glass with diffuser foil
910503910173	CR250B LED55S/840 PSU W30L120 IP65	IP65	IK07	Clear glass with diffuser foil
910503910174	CR250B LED55S/840 PSD W30L120 IP65	IP65	IK07	Clear glass with diffuser foil


Approval and Application

Order Code	Full Product Name	Glow-wire test	Ambient temperature range
910503910175	CR150B LED35S/840 PSU W60L60 IP54	Temperature 650 °C, duration 30 s	0 to +40 °C
910503910176	CR150B LED35S/840 PSD W60L60 IP54	Temperature 650 °C, duration 30 s	0 to +40 °C
910503910177	CR150B LED35S/840 PSU W30L120 IP54	Temperature 650 °C, duration 30 s	0 to +40 °C
910503910178	CR150B LED35S/840 PSD W30L120 IP54	Temperature 650 °C, duration 30 s	0 to +40 °C
910503910167	CR250B LED35S/840 PSU W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910168	CR250B LED35S/840 PSD W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910169	CR250B LED55S/840 PSU W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910170	CR250B LED55S/840 PSD W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910171	CR250B LED35S/840 PSU W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910172	CR250B LED35S/840 PSD W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910173	CR250B LED55S/840 PSU W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910174	CR250B LED55S/840 PSD W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C


Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910503910175	CR150B LED35S/840 PSU W60L60 IP54	(0.38, 0.38) SDCM <4
910503910176	CR150B LED35S/840 PSD W60L60 IP54	(0.38, 0.38) SDCM <4
910503910177	CR150B LED35S/840 PSU W30L120 IP54	(0.38, 0.38) SDCM <4
910503910178	CR150B LED35S/840 PSD W30L120 IP54	(0.38, 0.38) SDCM <4
910503910167	CR250B LED35S/840 PSU W60L60 IP65	(0.38, 0.38) SDCM <4
910503910168	CR250B LED35S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <4
910503910169	CR250B LED55S/840 PSU W60L60 IP65	(0.38, 0.38) SDCM <3
910503910170	CR250B LED55S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <3
910503910171	CR250B LED35S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <4
910503910172	CR250B LED35S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <4
910503910173	CR250B LED55S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <3
910503910174	CR250B LED55S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <3


Polar normal diagrams




910503910172




910503910169




910503910175




910503910177




910503910171




910503910178




910503910168




910503910176




910503910170



910503910174



910503910167



910503910173