

Cleanroom LED CR250B

CR250B



Cleanroom: uniform, reliable, value-for-money solution

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65- and IP54-rated luminaires that are safe to use and are an economical investment. This family of fixtures represents an affordable solution: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this family can be used in a wide range of applications. The fixtures are also compliant with all relevant standards (CE, EMC, RoHS).

Benefits

- Value-for-money investment
- Low maintenance due to the long lifetime of the luminaire
- Meets light-level requirements for main applications


Applications

- Food production facilities and kitchens
- Hospitals and other healthcare facilities
- Clean production areas

Features

- Uniform surface of light
- IP65 (glass cover) and IP54 (PMMA cover) versions
- Light output 3,500 to 5,500 lm
- Works with different ceiling types
- Class II

Versions



Cleanroom LED-CR150B
W60L60



Cleanroom LED-CR250B
W60L60




Cleanroom LED-CR250B
W30L120

Dimensional drawing



CR150B LED35S/840 PSD W60L60 IP54



CR250B LED55S/840 PSD W60L60 IP65



CR250B LED55S/840 PSU W30L120 IP65

Product details



Cleanroom_LED-
CR250B_W60L60-DP01



Cleanroom_LED-
CR250B_W60L60-DP02



Cleanroom_LED-CR250B_PSU-DP08



Cleanroom_LED-CR150B_W60L60_CR150Z_SM B-DP12



Cleanroom_LED-CR250B_W30L120_CR250Z_S MB-DP13



Cleanroom_LED-CR250B_W60L60_CR250Z_SM B-DP14

General Information

Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Service Tag	No

Light Technical

Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	>80
Number of light sources	2
Optic type	-

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Protection class IEC	Safety class II

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Colour	White
----------------	-------

Approval and Application

Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
-------------------------	-------

General Information

Order Code	Full Product Name	Lamp family code
910503910176	CR150B LED35S/840 PSD W60L60 IP54	GRN35
910503910168	CR250B LED35S/840 PSD W60L60 IP65	GRN35
910503910169	CR250B LED55S/840 PSU W60L60 IP65	GRN55
910503910170	CR250B LED55S/840 PSD W60L60 IP65	GRN55
910503910171	CR250B LED35S/840 PSU W30L120 IP65	GRN35
910503910172	CR250B LED35S/840 PSD W30L120 IP65	GRN35
910503910173	CR250B LED55S/840 PSU W30L120 IP65	GRN55
910503910174	CR250B LED55S/840 PSD W30L120 IP65	GRN55

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous efficacy (rated) (nom.)
910503910176	CR150B LED35S/840 PSD W60L60 IP54	3,500 lm	88 lm/W
910503910168	CR250B LED35S/840 PSD W60L60 IP65	3,500 lm	88 lm/W
910503910169	CR250B LED55S/840 PSU W60L60 IP65	5,500 lm	87 lm/W
910503910170	CR250B LED55S/840 PSD W60L60 IP65	5,500 lm	87 lm/W
910503910171	CR250B LED35S/840 PSU W30L120 IP65	3,500 lm	88 lm/W
910503910172	CR250B LED35S/840 PSD W30L120 IP65	3,500 lm	88 lm/W
910503910173	CR250B LED55S/840 PSU W30L120 IP65	5,500 lm	87 lm/W
910503910174	CR250B LED55S/840 PSD W30L120 IP65	5,500 lm	87 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910503910176	CR150B LED35S/840 PSD W60L60 IP54	40 W
910503910168	CR250B LED35S/840 PSD W60L60 IP65	40 W
910503910169	CR250B LED55S/840 PSU W60L60 IP65	63 W
910503910170	CR250B LED55S/840 PSD W60L60 IP65	63 W
910503910171	CR250B LED35S/840 PSU W30L120 IP65	40 W
910503910172	CR250B LED35S/840 PSD W30L120 IP65	40 W
910503910173	CR250B LED55S/840 PSU W30L120 IP65	63 W
910503910174	CR250B LED55S/840 PSD W30L120 IP65	63 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910503910176	CR150B LED35S/840 PSD W60L60 IP54	Yes
910503910168	CR250B LED35S/840 PSD W60L60 IP65	Yes
910503910169	CR250B LED55S/840 PSU W60L60 IP65	No
910503910170	CR250B LED55S/840 PSD W60L60 IP65	Yes
910503910171	CR250B LED35S/840 PSU W30L120 IP65	No
910503910172	CR250B LED35S/840 PSD W30L120 IP65	Yes
910503910173	CR250B LED55S/840 PSU W30L120 IP65	No
910503910174	CR250B LED55S/840 PSD W30L120 IP65	Yes

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code	Optical cover type
910503910176	CR150B LED35S/840 PSD W60L60 IP54	IP54	IK03	Polymethyl methacrylate bowl/cover
910503910168	CR250B LED35S/840 PSD W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910169	CR250B LED55S/840 PSU W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910170	CR250B LED55S/840 PSD W60L60 IP65	IP65	IK07	Clear glass with diffuser foil
910503910171	CR250B LED35S/840 PSU W30L120 IP65	IP65	IK07	Clear glass with diffuser foil
910503910172	CR250B LED35S/840 PSD W30L120 IP65	IP65	IK07	Clear glass with diffuser foil
910503910173	CR250B LED55S/840 PSU W30L120 IP65	IP65	IK07	Clear glass with diffuser foil
910503910174	CR250B LED55S/840 PSD W30L120 IP65	IP65	IK07	Clear glass with diffuser foil


Approval and Application


Order Code	Full Product Name	Glow-wire test	Ambient temperature range
910503910176	CR150B LED35S/840 PSD W60L60 IP54	Temperature 650 °C, duration 30 s	0 to +40 °C
910503910168	CR250B LED35S/840 PSD W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910169	CR250B LED55S/840 PSU W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910170	CR250B LED55S/840 PSD W60L60 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910171	CR250B LED35S/840 PSU W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910172	CR250B LED35S/840 PSD W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910173	CR250B LED55S/840 PSU W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C
910503910174	CR250B LED55S/840 PSD W30L120 IP65	Temperature 850 °C, duration 30 s	-20 to +40 °C

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
910503910176	CR150B LED35S/840 PSD W60L60 IP54	(0.38, 0.38) SDCM <4
910503910168	CR250B LED35S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <4
910503910169	CR250B LED55S/840 PSU W60L60 IP65	(0.38, 0.38) SDCM <3
910503910170	CR250B LED55S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <3
910503910171	CR250B LED35S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <4
910503910172	CR250B LED35S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <4
910503910173	CR250B LED55S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <3
910503910174	CR250B LED55S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <3

Polar normal diagrams





910503910174



910503910173