



Cleanroom: uniform, reliable, value-for-money solution

Cleanroom LED CR250B

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65 and IP54-rated luminaires that are safe to use and come at an attractive price. This family of Philips Cleanroom CR250B fixtures represents true value for money: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this cleanroom LED lighting family can be used in a wide range of applications. These cleanroom luminaires are also compliant with all relevant standards (CE, EMC, RoHS).

Benefits

- Value-for-money investment
- Low maintenance costs due to the long lifetime of the luminaire
- Meets light-level requirements for main applications

Features

- Uniform surface of light
- IP65 (glass cover) and IP54 (PMMA cover) versions
- Light output 3,500 to 5,500 lm
- Works with different ceiling types
- Class II

Application

- Food production facilities and kitchens
- Hospitals and care centres
- Clean production areas

Cleanroom LED CR250B

Versions







Cleanroom LED-CR150B W60L60



Cleanroom LED-CR150B W30L120

Dimensional drawing



Product details



Cleanroom_LED-
CR250B_W60L60-DP01



Cleanroom_LED-
CR250B_W60L60-DP02

Cleanroom LED CR250B

Product details



Cleanroom_LED-
CR150B_W30L120_PSU-DP04



Cleanroom_LED-
CR150B_W30L120_PSD-DP05



Cleanroom_LED-CR150B-
PSU_W30L120_PSU-DP06



Cleanroom_LED-
CR150B_W30L120_PSD-DP07



Cleanroom_LED-CR250B_PSU-
DP08



Cleanroom_LED-
CR150B_W30L120_CR150Z_SMB-
DP11



Cleanroom_LED-
CR150B_W60L60_CR150Z_SMB-
DP12



Cleanroom_LED-
CR250B_W30L120_CR250Z_SMB-
DP13

Cleanroom LED CR250B

Product details



Cleanroom_LED-
CR250B_W60L60_CR250Z_SMB-
DP14

General Information

Driver included	Yes
Light source replaceable	Yes
Number of gear units	Unit

Light Technical

Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	>80
Number of light sources	2
Optic type	-

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes

Mechanical and Housing

Housing Colour	White
----------------	-------

Approval and Application

CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on easily flammable surfaces

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
-------------------------	-------

General Information

Order Code	Full Product Name	Lamp family code
910503910175	CR150B LED35S/840 PSU W60L60 IP54	GRN35
910503910176	CR150B LED35S/840 PSD W60L60 IP54	GRN35
910503910177	CR150B LED35S/840 PSU W30L120 IP54	GRN35
910503910178	CR150B LED35S/840 PSD W30L120 IP54	GRN35
910503910168	CR250B LED35S/840 PSD W60L60 IP65	GRN35
910503910169	CR250B LED55S/840 PSU W60L60 IP65	GRN55
910503910170	CR250B LED55S/840 PSD W60L60 IP65	GRN55
910503910171	CR250B LED35S/840 PSU W30L120 IP65	GRN35
910503910172	CR250B LED35S/840 PSD W30L120 IP65	GRN35
910503910173	CR250B LED55S/840 PSU W30L120 IP65	GRN55
910503910174	CR250B LED55S/840 PSD W30L120 IP65	GRN55

Light Technical

Order Code	Full Product Name	Luminous efficacy (rated) (nom.)	Luminous Flux
910503910175	CR150B LED35S/840 PSU W60L60 IP54	88 lm/W	3,500 lm
910503910176	CR150B LED35S/840 PSD W60L60 IP54	88 lm/W	3,500 lm

Order Code	Full Product Name	Luminous efficacy (rated) (nom.)	Luminous Flux
910503910177	CR150B LED35S/840 PSU W30L120 IP54	88 lm/W	3,500 lm
910503910178	CR150B LED35S/840 PSD W30L120 IP54	88 lm/W	3,500 lm

Cleanroom LED CR250B

Order Code	Full Product Name	Luminous efficacy	
		(rated) (nom.)	Luminous Flux
910503910168	CR250B LED35S/840 PSD W60L60 IP65	88 lm/W	3,500 lm
910503910169	CR250B LED55S/840 PSU W60L60 IP65	87 lm/W	5,500 lm
910503910170	CR250B LED55S/840 PSD W60L60 IP65	87 lm/W	5,500 lm
910503910171	CR250B LED35S/840 PSU W30L120 IP65	88 lm/W	3,500 lm

Order Code	Full Product Name	Luminous efficacy	
		(rated) (nom.)	Luminous Flux
910503910172	CR250B LED35S/840 PSD W30L120 IP65	88 lm/W	3,500 lm
910503910173	CR250B LED55S/840 PSU W30L120 IP65	87 lm/W	5,500 lm
910503910174	CR250B LED55S/840 PSD W30L120 IP65	87 lm/W	5,500 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910503910175	CR150B LED35S/840 PSU W60L60 IP54	40 W
910503910176	CR150B LED35S/840 PSD W60L60 IP54	40 W
910503910177	CR150B LED35S/840 PSU W30L120 IP54	40 W
910503910178	CR150B LED35S/840 PSD W30L120 IP54	40 W
910503910168	CR250B LED35S/840 PSD W60L60 IP65	40 W
910503910169	CR250B LED55S/840 PSU W60L60 IP65	63 W

Order Code	Full Product Name	Power Consumption
910503910170	CR250B LED55S/840 PSD W60L60 IP65	63 W
910503910171	CR250B LED35S/840 PSU W30L120 IP65	40 W
910503910172	CR250B LED35S/840 PSD W30L120 IP65	40 W
910503910173	CR250B LED55S/840 PSU W30L120 IP65	63 W
910503910174	CR250B LED55S/840 PSD W30L120 IP65	63 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910503910175	CR150B LED35S/840 PSU W60L60 IP54	No	-
910503910176	CR150B LED35S/840 PSD W60L60 IP54	Yes	1%
910503910177	CR150B LED35S/840 PSU W30L120 IP54	No	-
910503910178	CR150B LED35S/840 PSD W30L120 IP54	Yes	1%
910503910168	CR250B LED35S/840 PSD W60L60 IP65	Yes	1%
910503910169	CR250B LED55S/840 PSU W60L60 IP65	No	-

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910503910170	CR250B LED55S/840 PSD W60L60 IP65	Yes	1%
910503910171	CR250B LED35S/840 PSU W30L120 IP65	No	-
910503910172	CR250B LED35S/840 PSD W30L120 IP65	Yes	1%
910503910173	CR250B LED55S/840 PSU W30L120 IP65	No	-
910503910174	CR250B LED55S/840 PSD W30L120 IP65	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech.	
			impact protection code	Ingress protection code
910503910175	CR150B LED35S/840 PSU W60L60 IP54	Polymethyl methacrylate bowl/cover	IK03	IP54
910503910176	CR150B LED35S/840 PSD W60L60 IP54	Polymethyl methacrylate bowl/cover	IK03	IP54
910503910177	CR150B LED35S/840 PSU W30L120 IP54	Polymethyl methacrylate bowl/cover	IK03	IP54
910503910178	CR150B LED35S/840 PSD W30L120 IP54	Polymethyl methacrylate bowl/cover	IK03	IP54

Order Code	Full Product Name	Optical cover type	Mech.	
			impact protection code	Ingress protection code
910503910168	CR250B LED35S/840 PSD W60L60 IP65	Clear glass with diffuser foil	IK07	IP65
910503910169	CR250B LED55S/840 PSU W60L60 IP65	Clear glass with diffuser foil	IK07	IP65
910503910170	CR250B LED55S/840 PSD W60L60 IP65	Clear glass with diffuser foil	IK07	IP65
910503910171	CR250B LED35S/840 PSU W30L120 IP65	Clear glass with diffuser foil	IK07	IP65

Cleanroom LED CR250B

Order Code	Full Product Name	Optical cover type	Mech. impact protection code	Ingress protection code
910503910172	CR250B LED35S/840 PSD W30L120 IP65	Clear glass with diffuser foil	IK07	IP65
910503910173	CR250B LED55S/840 PSU W30L120 IP65	Clear glass with diffuser foil	IK07	IP65

Order Code	Full Product Name	Optical cover type	Mech. impact protection code	Ingress protection code
910503910174	CR250B LED55S/840 PSD W30L120 IP65	Clear glass with diffuser foil	IK07	IP65

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910503910175	CR150B LED35S/840 PSU W60L60 IP54	0 to +40 °C	Temperature 650 °C, duration 30 s
910503910176	CR150B LED35S/840 PSD W60L60 IP54	0 to +40 °C	Temperature 650 °C, duration 30 s
910503910177	CR150B LED35S/840 PSU W30L120 IP54	0 to +40 °C	Temperature 650 °C, duration 30 s
910503910178	CR150B LED35S/840 PSD W30L120 IP54	0 to +40 °C	Temperature 650 °C, duration 30 s
910503910168	CR250B LED35S/840 PSD W60L60 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s
910503910169	CR250B LED55S/840 PSU W60L60 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s


Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910503910170	CR250B LED55S/840 PSD W60L60 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s
910503910171	CR250B LED35S/840 PSU W30L120 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s
910503910172	CR250B LED35S/840 PSD W30L120 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s
910503910173	CR250B LED55S/840 PSU W30L120 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s
910503910174	CR250B LED55S/840 PSD W30L120 IP65	-20 to +40 °C	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
910503910175	CR150B LED35S/840 PSU W60L60 IP54	(0.38, 0.38) SDCM <4
910503910176	CR150B LED35S/840 PSD W60L60 IP54	(0.38, 0.38) SDCM <4
910503910177	CR150B LED35S/840 PSU W30L120 IP54	(0.38, 0.38) SDCM <4
910503910178	CR150B LED35S/840 PSD W30L120 IP54	(0.38, 0.38) SDCM <4
910503910168	CR250B LED35S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <4
910503910169	CR250B LED55S/840 PSU W60L60 IP65	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910503910170	CR250B LED55S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <3
910503910171	CR250B LED35S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <4
910503910172	CR250B LED35S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <4
910503910173	CR250B LED55S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <3
910503910174	CR250B LED55S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <3


Polar Wide Diagrams



Polar Normal (separate) - 910503910172




Polar Normal (separate) - 910503910169




Polar Normal (separate) - 910503910175

Cleanroom LED CR250B


Polar Wide Diagrams




Polar Normal (separate) - 910503910177




Polar Normal (separate) - 910503910171




Polar Normal (separate) - 910503910178




Polar Normal (separate) - 910503910168




Polar Normal (separate) - 910503910176



Polar Normal (separate) - 910503910170



Polar Normal (separate) - 910503910174



Polar Normal (separate) - 910503910173

