



Cleanroom: when light has to be hygienic, excellent quality and high definition

Cleanroom CR350B

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

Benefits

- Excellent quality of light
- Complies with cleanroom norms and legislation
- High reliability, low maintenance

Features



- Fully IP65 and ENEC compliant
- Excellent colour rendering CRI >90
- Lumen output up to 6,000 lm
- Low glare UGR <19
- Surface-mounted bracket and safety cable available as an accessory

Cleanroom CR350B

Application

- Surgical and examination rooms
- Laboratories and pharmaceutical facilities
- Cleanroom production areas

Dimensional drawing



Product details



Photo



Photo



Photo



Photo

Cleanroom CR350B

Product details



Photo



Photo

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	Unit
Service Tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Colour Temperature (Nom)	4000 K
Optic type	Wide beam

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Mechanical and Housing

Housing Colour	White
Mech. impact protection code	IK09
Ingress protection code	IP65

Approval and Application

Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Colour	Luminous efficacy (rated)	Luminous Flux
		rendering index (CRI)	(nom.)	
912401483354	CR350B LED40S/940 PSU W60L60	>90	98 lm/W	4,000 lm
912401483355	CR350B LED40S/840 PSD W60L60	>80	108 lm/W	4,000 lm
912401483357	CR350B LED40S/940 PSD W60L60	>90	98 lm/W	4,000 lm
912401483360	CR350B LED60S/940 PSU W60L60	>90	100 lm/W	6,000 lm
912401483361	CR350B LED60S/840 PSD W60L60	>80	109 lm/W	6,000 lm
912401483363	CR350B LED60S/940 PSD W60L60	>90	100 lm/W	6,000 lm
912401483366	CR350B LED40S/940 PSU W30L120	>90	98 lm/W	4,000 lm
912401483367	CR350B LED40S/840 PSD W30L120	>80	108 lm/W	4,000 lm
912401483369	CR350B LED40S/940 PSD W30L120	>90	98 lm/W	4,000 lm
912401483372	CR350B LED60S/940 PSU W30L120	>90	100 lm/W	6,000 lm
912401483373	CR350B LED60S/840 PSD W30L120	>80	109 lm/W	6,000 lm
912401483375	CR350B LED60S/940 PSD W30L120	>90	100 lm/W	6,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
912401483354	CR350B LED40S/940 PSU W60L60	41 W	912401483355	CR350B LED40S/840 PSD W60L60	37 W

Cleanroom CR350B

Order Code	Full Product Name	Power Consumption
912401483357	CR350B LED40S/940 PSD W60L60	41 W
912401483360	CR350B LED60S/940 PSU W60L60	60 W
912401483361	CR350B LED60S/840 PSD W60L60	55 W
912401483363	CR350B LED60S/940 PSD W60L60	60 W
912401483366	CR350B LED40S/940 PSU W30L120	41 W

Order Code	Full Product Name	Power Consumption
912401483367	CR350B LED40S/840 PSD W30L120	37 W
912401483369	CR350B LED40S/940 PSD W30L120	41 W
912401483372	CR350B LED60S/940 PSU W30L120	60 W
912401483373	CR350B LED60S/840 PSD W30L120	55 W
912401483375	CR350B LED60S/940 PSD W30L120	60 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
912401483354	CR350B LED40S/940 PSU W60L60	No	Not applicable
912401483355	CR350B LED40S/840 PSD W60L60	Yes	1%
912401483357	CR350B LED40S/940 PSD W60L60	Yes	1%
912401483360	CR350B LED60S/940 PSU W60L60	No	Not applicable
912401483361	CR350B LED60S/840 PSD W60L60	Yes	1%
912401483363	CR350B LED60S/940 PSD W60L60	Yes	1%


Order Code	Full Product Name	Dimmable	Maximum dim level
912401483366	CR350B LED40S/940 PSU W30L120	No	Not applicable
912401483367	CR350B LED40S/840 PSD W30L120	Yes	1%
912401483369	CR350B LED40S/940 PSD W30L120	Yes	1%
912401483372	CR350B LED60S/940 PSU W30L120	No	Not applicable
912401483373	CR350B LED60S/840 PSD W30L120	Yes	1%
912401483375	CR350B LED60S/940 PSD W30L120	Yes	1%

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
912401483354	CR350B LED40S/940 PSU W60L60	(0.39, 0.38) SDCM <3
912401483355	CR350B LED40S/840 PSD W60L60	(0.38, 0.38) SDCM <3
912401483357	CR350B LED40S/940 PSD W60L60	(0.39, 0.38) SDCM <3
912401483360	CR350B LED60S/940 PSU W60L60	(0.39, 0.38) SDCM <3
912401483361	CR350B LED60S/840 PSD W60L60	(0.38, 0.38) SDCM <3
912401483363	CR350B LED60S/940 PSD W60L60	(0.39, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
912401483366	CR350B LED40S/940 PSU W30L120	(0.39, 0.38) SDCM <3
912401483367	CR350B LED40S/840 PSD W30L120	(0.38, 0.38) SDCM <3
912401483369	CR350B LED40S/940 PSD W30L120	(0.39, 0.38) SDCM <3
912401483372	CR350B LED60S/940 PSU W30L120	(0.39, 0.38) SDCM <3
912401483373	CR350B LED60S/840 PSD W30L120	(0.38, 0.38) SDCM <3
912401483375	CR350B LED60S/940 PSD W30L120	(0.39, 0.38) SDCM <3


Polar Wide Diagrams



Polar Normal (separate) - 912401483355




Polar Normal (separate) - 912401483357




Polar Normal (separate) - 912401483360

Cleanroom CR350B


Polar Wide Diagrams




Polar Normal (separate) - 912401483367




Polar Normal (separate) - 912401483366




Polar Normal (separate) - 912401483361




Polar Normal (separate) - 912401483372




Polar Normal (separate) - 912401483354




Polar Normal (separate) - 912401483373



Polar Normal (separate) - 912401483375



Polar Normal (separate) - 912401483369



Polar Normal (separate) - 912401483363

