

Cleanroom CR350B

CR350B



Cleanroom: when light has to be hygienic, excellent quality and high definition

When operating a facility where the highest levels of hygiene are required, the demands placed on light are also very high. It must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips Cleanroom CR350B luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, these Philips cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

Benefits

- Excellent quality of light
- Complies with cleanroom norms and legislation
- High reliability, low maintenance

Applications

- Surgical and examination rooms
- Laboratories and pharmaceutical facilities
- Cleanroom production areas

Features

- Fully IP65 and ENEC compliant
- Excellent colour rendering CRI >90

- Lumen output up to 6,000 lm
- Low glare UGR <19
- Surface-mounted bracket and safety cable available as an accessory

Versions



Photo



Photo



Dimensional drawing



CR350B LED60S/940 PSD W30L120

CR350B LED60S/940 PSD W60L60

Product details

Photo



Photo





Photo

Photo

Photo

Photo

General Information

Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Service Tag	Yes

Light Technical

Correlated Colour Temperature (Nom)	4000 K
Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Mechanical and Housing

Housing Colour	White
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]

Approval and Application

Glow-wire test	-
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous efficacy (rated) (nom.)	Colour rendering index (CRI)
912401483354	CR350B LED40S/940 PSU W60L60	4,000 lm	98 lm/W	>90
912401483357	CR350B LED40S/940 PSD W60L60	4,000 lm	98 lm/W	>90
912401483360	CR350B LED60S/940 PSU W60L60	6,000 lm	100 lm/W	>90
912401483361	CR350B LED60S/840 PSD W60L60	6,000 lm	109 lm/W	>80
912401483363	CR350B LED60S/940 PSD W60L60	6,000 lm	100 lm/W	>90
912401483366	CR350B LED40S/940 PSU W30L120	4,000 lm	98 lm/W	>90
912401483372	CR350B LED60S/940 PSU W30L120	6,000 lm	100 lm/W	>90
912401483375	CR350B LED60S/940 PSD W30L120	6,000 lm	100 lm/W	>90

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912401483354	CR350B LED40S/940 PSU W60L60	41 W
912401483357	CR350B LED40S/940 PSD W60L60	41 W
912401483360	CR350B LED60S/940 PSU W60L60	60 W
912401483361	CR350B LED60S/840 PSD W60L60	55 W
912401483363	CR350B LED60S/940 PSD W60L60	60 W
912401483366	CR350B LED40S/940 PSU W30L120	41 W
912401483372	CR350B LED60S/940 PSU W30L120	60 W
912401483375	CR350B LED60S/940 PSD W30L120	60 W


Controls and Dimming


Order Code	Full Product Name	Dimmable	Maximum dim level
912401483354	CR350B LED40S/940 PSU W60L60	No	Not applicable
912401483357	CR350B LED40S/940 PSD W60L60	Yes	1%
912401483360	CR350B LED60S/940 PSU W60L60	No	Not applicable
912401483361	CR350B LED60S/840 PSD W60L60	Yes	1%
912401483363	CR350B LED60S/940 PSD W60L60	Yes	1%
912401483366	CR350B LED40S/940 PSU W30L120	No	Not applicable
912401483372	CR350B LED60S/940 PSU W30L120	No	Not applicable
912401483375	CR350B LED60S/940 PSD W30L120	Yes	1%

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
912401483354	CR350B LED40S/940 PSU W60L60	(0.39, 0.38) SDCM <3
912401483357	CR350B LED40S/940 PSD W60L60	(0.39, 0.38) SDCM <3
912401483360	CR350B LED60S/940 PSU W60L60	(0.39, 0.38) SDCM <3
912401483361	CR350B LED60S/840 PSD W60L60	(0.38, 0.38) SDCM <3
912401483363	CR350B LED60S/940 PSD W60L60	(0.39, 0.38) SDCM <3
912401483366	CR350B LED40S/940 PSU W30L120	(0.39, 0.38) SDCM <3
912401483372	CR350B LED60S/940 PSU W30L120	(0.39, 0.38) SDCM <3
912401483375	CR350B LED60S/940 PSD W30L120	(0.39, 0.38) SDCM <3

Polar normal diagrams







912401483361




912401483372



912401483354



912401483375



912401483363