

MASTERColour CDM-R111

DCDMR111



Beautiful sparkle, trendy design

The MASTERColour CDM-R111 combines the trendy look of the 111 mm aluminium reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

Výhody

- Low operating costs
- Easy installation
- Relatively low heat output
- Less glare, comfort for shoppers and staff
- Reduced fading risks

Applications

- Accent and decorative lighting: display lighting with sparkling, theatrical effects, even in surroundings with very high background ambient light levels like shop windows
- General lighting: in downlighters, a warm and comfortable atmosphere can be created

Vlastnosti


- High lamp efficacy
- Long lamp lifetime compared to incandescent and halogen lamps
- The ceramic discharge tube is optimally and stable positioned in the reflector
- Twist & Lock system
- UV-Block burner capsule
- Anti-glare cap design
- Súčasťou predradníka musí byť ochrana na konci životnosti (normy IEC61167, IEC62035).
- Používajte len s elektronickým predradníkom. Svetelné zdroje 35 W/830 môžu používať aj elektromagnetický predradník.

Versions



LPPR CDM-R111 24D 40D

Rozmerový obrázok



Product	D (max)	C (max)
MASTERC CDM-R111 35W/942 GX8.5 24D 1CT	111 mm	95 mm

Všeobecné informácie

Pätica	GX8.5
Prevádzková poloha	UNIVERSAL [Akokoľvek alebo univerzálne (U)]
Spínací cyklus	800

Svetelné technické

Uhol vyžarovania (nom.)	24 stupeň (stupne)
Svetelný tok	1 300 lm
Intenzita svetla (nom.)	7 350 cd
Označenie farby	Studená biela (CW)
Chromatická súradnica X (nom.)	0,371
Chromatická súradnica Y (nom.)	0,366
Náhradná teplota chromatickosti (nom.)	4200 K
Index podania farieb (CRI)	93
LLMF na konci nominálnej životnosti (nom.)	65 %

Prevádzkové a elektrické

Spotreba	39,1 W
Čas zahrievania na 60 % svetla	120 s
Napätie (nom.)	86 V

Ovládanie a stmievanie

Stmievateľné	Nie
--------------	-----

Mechanické časti a teleso

Povrchová úprava žiarovky	Reflektor
Tvar žiarovky	R111

Schválenie a použitie

Obsah ortuti (Hg) (max.)	2,8 mg
Obsah ortuti (Hg) (nom.)	3,0 mg
Spotreba energie kWh/1 000 h	40 kWh