



Beautiful sparkle, reliable life

MASTERColour CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

Benefits

- Stable color impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Relatively low heat output enhances comfort for shoppers and staff
- All types are UV-Block for reduced fading risks

Features

- Crisp white light
- Superior color quality
- Allows small-size luminaires designs that give high beam intensities

Application


- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-T

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 250W/830 G12 1CT/12	25 mm	12.3 mm	71.5 mm	73.5 mm	72.5 mm	135 mm



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 inch	9 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 150W/942 G12 1CT	20 mm	0.75 inch	8 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 35W/830 G12 1CT/12	20 mm	0.75 inch	5 mm	55 mm	57 mm	56 mm	103 mm

General Information	
Cap-Base	G12
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Color		Luminous Efficacy (rated) (Nom)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Designation	Temperature (Nom)		
19697215	MASTERColour CDM-T 35W/830 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	83	79 lm/W
19780115	MASTERColour CDM-T 150W/830 G12 1CT	0.434	0.398	Warm White (WW)	3000 K	88	88 lm/W
20005115	MASTERColour CDM-T 150W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	96	82 lm/W
20801915	MASTERColour CDM-T 250W/830 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	85	111 lm/W
							27,750 lm

Operating and Electrical

MASTERColour CDM-T

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
19697215	MASTERColour CDM-T 35W/830 G12 1CT/12	82 V	39.1 W
19780115	MASTERColour CDM-T 150W/830 G12 1CT	96 V	150.1 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
20005115	MASTERColour CDM-T 150W/942 G12 1CT	90 V	150.1 W
20801915	MASTERColour CDM-T 250W/830 G12 1CT/12	95 V	250.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
19697215	MASTERColour CDM-T 35W/830 G12 1CT/12	T19
19780115	MASTERColour CDM-T 150W/830 G12 1CT	T19

Order Code	Full Product Name	Bulb Shape
20005115	MASTERColour CDM-T 150W/942 G12 1CT	T19
20801915	MASTERColour CDM-T 250W/830 G12 1CT/12	T24

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury Content (Max)	Mercury Content (Nom)
			(Hg)	(Hg)
19697215	MASTERColour CDM-T 35W/830 G12 1CT/12	40 kWh	3.2 mg	3.1 mg
19780115	MASTERColour CDM-T 150W/830 G12 1CT	151 kWh	14.3 mg	14.3 mg
20005115	MASTERColour CDM-T 150W/942 G12 1CT	151 kWh	10.4 mg	10.4 mg
20801915	MASTERColour CDM-T 250W/830 G12 1CT/12	250 kWh	27.5 mg	27.5 mg

