



# Beautiful sparkle, reliable life

## MASTERColour CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

### Benefits

- Stable color impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Relatively low heat output enhances comfort for shoppers and staff
- All types are UV-Block for reduced fading risks

### Features

- Crisp white light
- Superior color quality
- Allows small-size luminaires designs that give high beam intensities

### Application


- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

### Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# MASTERColour CDM-T

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 250W/830 G12 1CT/12	25 mm	12.3 mm	71.5 mm	73.5 mm	72.5 mm	135 mm



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 inch	9 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 150W/942 G12 1CT	20 mm	0.75 inch	8 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 35W/830 G12 1CT/12	20 mm	0.75 inch	5 mm	55 mm	57 mm	56 mm	103 mm

### General Information

Cap-Base	G12
Operating Position	UNIVERSAL

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Bulb Finish	Clear
-------------	-------

### Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Correlated Color		Color rendering	Luminous Efficacy	
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Designation	Temperature (Nom)	index (CRI)	(rated) (Nom)	Luminous Flux
928083105125	MASTERC CDM-T 35W/830 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	83	79 lm/W	3,100 lm
928083705125	MASTERC CDM-T 150W/830 G12 1CT	0.434	0.398	Warm White (WW)	3000 K	88	88 lm/W	13,000 lm
928084605131	MASTERC CDM-T 150W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	96	82 lm/W	12,100 lm
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	85	111 lm/W	27,750 lm

### Operating and Electrical

# MASTERColour CDM-T

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928083105125	MASTERC CDM-T 35W/830 G12	82 V	39.1 W
	1CT/12		

928083705125 MASTERC CDM-T 150W/830 G12 96 V 150.1 W  
1CT

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928084605131	MASTERC CDM-T 150W/942 G12	90 V	150.1 W
	1CT		

928089805131 MASTERC CDM-T 250W/830 G12 95 V 250.0 W  
1CT/12

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928083105125	MASTERC CDM-T 35W/830 G12 1CT/12	T19
928083705125	MASTERC CDM-T 150W/830 G12 1CT	T19

Order Code	Full Product Name	Bulb Shape
928084605131	MASTERC CDM-T 150W/942 G12 1CT	T19
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	T24

## Approval and Application

Order Code	Full Product Name	Energy	Mercury	Mercury
		Consumption	(Hg) Content (Max)	(Hg) Content (Nom)
928083105125	MASTERC CDM-T 35W/830 G12 1CT/12	40 kWh	3.2 mg	3.1 mg
928083705125	MASTERC CDM-T 150W/830 G12 1CT	151 kWh	14.3 mg	14.3 mg
928084605131	MASTERC CDM-T 150W/942 G12 1CT	151 kWh	10.4 mg	10.4 mg
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12	250 kWh	27.5 mg	27.5 mg

