



Product Description

Compact quartz metal halide lamps with double pinch

Benefits

- Allows compact luminaire systems with precision optics for minimal light spill
- Good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers options for semi-professional stadiums and area lighting

Applications

- Recreational sports and area floodlighting

Features

- Double-pinch concept results in long lifetime
- Choice of 1000 W and 2000 W types

Versions




LPPR MHN-FC 2000W 2200W



LPPR MHN-FC 1000W

- Natural white color appearance
- Compact light source allows small luminaire design
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	D	O	X	L	A	C (max)
MASTER MHN-FC 1000W/740 230V XW	33 mm	25.5 mm	42.5 mm	58 mm	144 mm	226 mm	290 mm
MASTER MHN-FC 2000W/740 400V XW	33 mm	25.5 mm	108 mm	58 mm	177 mm	290 mm	357 mm

General Information

Cap base	Double Ended
Operating position	P5 [Parallel +/-5D or Horizontal(HOR)]
Light Technical	
Colour designation	White (WH)
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear

Light Technical

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Correlated Colour Temperature (Nom)	Luminous efficacy (rated) (nom.)	Colour rendering index (CRI)
928070405130	MASTER MHN-FC 2000W/740 400V XW	380	419	4200 K	102 lm/W	60
928075705130	MASTER MHN-FC 1000W/740 230V XW	374	366	4100 K	91 lm/W	65

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Voltage (nom.)
928070405130	MASTER MHN-FC 2000W/740 400V XW	2,050 W	222 V
928075705130	MASTER MHN-FC 1000W/740 230V XW	1,040.0 W	130 V

Approval and Application

Order Code	Full Product Name	Mercury (Hg) content (nom.)	Energy consumption kWh/1,000 hours
928070405130	MASTER MHN-FC 2000W/740 400V XW	105 mg	2,235 kWh
928075705130	MASTER MHN-FC 1000W/740 230V XW	74 mg	1,144 kWh

