



# Product Description

## MASTER MHN-SE

Very compact quartz metal halide lamps with single-pinch GX-22 lamp cap

### Benefits

- Allows compact, highly efficient luminaire systems with high-precision optics for good beam control and minimal light spill
- Very good colour rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers a superior solution for professional stadiums with regular TV coverage

### Features

- Single-pinch concept for superior optical performance
- High luminous efficacy
- Natural white colour appearance, very good colour rendering and good colour stability
- Daylight colour temperature eases transition from daylight to artificial lighting

### Application

- Professional sports lighting

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER MHN-SE

## Versions



LPPR MHN-SE 0002

## Dimensional drawing



Product	D (max)	O	C (max)
MASTER MHN-SE 2000W/956 GX22 400V HO UNP	41 mm	25 mm	198 mm

