



Product Description

MASTER MHN-SE

Very compact quartz metal halide lamps with single-pin GX-22 lamp cap

Benefits

- Allows compact, highly efficient luminaire systems with high-precision optics for good beam control and minimal light spill
- Very good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers a superior solution for professional stadiums with regular TV coverage

Features

- Single-pin concept for superior optical performance
- High luminous efficacy
- Natural white color appearance, very good color rendering and good color stability
- Daylight color temperature eases transition from daylight to artificial lighting

Application

- Professional sports lighting

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER MHN-SE

Versions



LPPR MHN-SE 0002

Dimensional drawing



| Product | D (max) | O | C (max) |
|--|---------|-------|---------|
| MASTER MHN-SE 2000W/956 GX22 400V HO UNP | 41 mm | 25 mm | 198 mm |

