

PHILIPS

Lighting



Suitable for high ceiling delivering comfortable light

GreenSpace Surface mounted

GreenSpace DN397C is brand new offering to accommodate extremely high ceiling with leading efficacy , design compactness and good reliability

Benefits

- Energy saving
- Superior optics with flexibility
- Good light quality for visual comfort
- Easy installation

Features


- High efficacy
- Two beam options
- SDCM 3, CRI >80
- Surface mounted & suspended

Application

- Airport
- Exhibition center
- Semi-outdoor

GreenSpace Surface mounted

Dimensional drawing



GreenSpace Surface mounted

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	≥80
Luminous Flux	12,000 lm
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	102 W
Suitable for random switching	No
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Optical cover type	Lens
Housing Color	White
Mech. impact protection code	IK06
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on easy flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	-
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.0013 %
Median useful life L80B50	34,000 hour(s)
Median useful life L90B50	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
01557351	DN397C LED12/830 PSU WH	3000 K	115 lm/W	Beam angle 55° WB GM
01557451	DN397C LED12/840 PSU WH	4000 K	120 lm/W	Beam angle 55° WB GM
01557751	DN397C LED12/840 PSU WH	4000 K	120 lm/W	Beam angle 30° MB GM

GreenSpace Surface mounted



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2024, August 28 - data subject to change