



Suitable for high ceiling delivering comfortable light

GreenSpace Surface mounted

GreenSpace DN397C is brand new offering to accommodate extremely high ceiling with leading efficacy, design compactness and good reliability

Benefits

- Energy saving
- Superior optics with flexibility
- Good light quality for visual comfort
- Easy installation

Features


- High efficacy
- Two beam options
- SDCM 3, CRI >80
- Surface mounted & suspended

Application

- Airport
- Exhibition center
- Semi-outdoor

GreenSpace Surface mounted

Dimensional drawing



GreenSpace Surface mounted

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	≥80
Luminous Flux	12,000 lm

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	102 W
Suitable for random switching	No

Controls and Dimming

Dimmable	No
Maximum dim level	Not applicable

Mechanical and Housing

Optical cover type	Lens
Housing Color	White
Mech. impact protection code	IK06
Ingress protection code	IP65

Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on easy flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	-
Luminous flux tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.0013 %
Median useful life L80B50	34,000 hour(s)
Median useful life L90B50	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
911401557351	DN397C LED12/830 PSU WH WB GM	3000 K	115 lm/W	Beam angle 55°
911401557451	DN397C LED12/840 PSU WH WB GM	4000 K	120 lm/W	Beam angle 55°
911401557751	DN397C LED12/840 PSU WH MB GM	4000 K	120 lm/W	Beam angle 30°

GreenSpace Surface mounted

