



Philips GreenSpace – High-efficiency, sustainable LED solution with 75% bio-circular materials

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 mm to 280 mm which is the ideal solution for your renovation project. It saves the hassle, avoids time consuming and costly adaptor rings. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made with 75% recycled or mass-balanced bio-circular material, making it a conscious choice for those that want to contribute to a circular economy. GreenSpace can be connected to wireless systems to create a smart office lighting solution with optional integrated sensors as well. Its long lifetime with 100,000 hours at L100 (CLO), L90 (700lm/1400lm/on request 2000lm) makes it a true 'fit and forget' solution.

Benefits

- Low return of investment years due to high efficiency and long lifetime
- Wide range of mounting options to fit different ceiling types
- The perfect fit for retrofit projects, possibility to create custom sizes
- Avoids time consuming and costly adaptor rings and get the downlight that always fits
- Office-compliant, with stable color performance and wide light distribution
- Clean & beautiful ceilings with integrated sensing options for daylight control and presence detection

Applications

- Offices
- Retail
- Hospitals and Care Centers
- Municipal Buildings
- Education
- Healthcare

Features

- Mini (DN500B) and compact (DN510B) sizes for recessed
- Surface mounted, track and pendant versions available
- Custom cut-out sizes between 150mm-280 mm, in total 28 sizes available

Versions

- High-gloss (CR) and White (WR) reflector types
- UGR19 version with anti-glare ring (OC reflector)
- Available in 700-5000 lumen to cover applications with higher ceilings
- Selection of rim colors: White, silver and black as standard, others on request
- IP54 version with a front cover and integrated sensors
- Emergency lighting option available
- Configurable with many driver types such as DALI and wireless with InterAct ready
- Fast installation due to variety of connections and cables
- Printed housing & rim parts with 75% recycled or mass balanced bio-circular material



GreenSpace Mini, office-compliant reflector, white rim



GreenSpace perfect fit 200mm cut-out with sensor



GreenSpace perfect fit 225mm cut-out



GreenSpace Mini, office-compliant reflector, protection cover clear, white rim



GreenSpace perfect fit 225mm cut-out



GreenSpace Mini, high-gloss reflector, grey rim



GreenSpace Compact, white reflector, protection cover opal, white rim



GreenSpace Mini, high-gloss reflector, white rim



GreenSpace Compact, office-compliant reflector, white rim



GreenSpace perfect fit 230mm cut-out



GreenSpace Mini, high-gloss reflector, black rim



GreenSpace Compact, office-compliant reflector, protection cover clear, white rim



GreenSpace Compact, high-gloss reflector, black rim



GreenSpace Compact, high-gloss reflector, protection cover clear, white rim



GreenSpace Compact, high-gloss reflector, white rim



GreenSpace perfect fit 230mm cut-out



GreenSpace perfect fit
180mm cut-out



GreenSpace Mini, high-gloss
reflector, protection cover
clear, white rim



GreenSpace Mini, white
reflector, protection cover
opal, white rim





GreenSpace perfect fit family





GreenSpace Compact, high-
gloss reflector, grey rim


Dimensional drawing




TCTT200 20S/830 U4 OC PCC WH




DN510B 20S/840 PSU-E WR WH PCO




TCTT230 20S/830 PSU-E WH




TCTT165 11S/840 PSU-E WH




TCTT160 11S/840 PSU-E WH




TCTT175 20S/830 PSU-E WH



TCTT180 20S/840 PSU-E WH281



TCTT225 20S/830 PSU-E WH



DN500B 20S/840 PSU-E OC WH PCC

General Information

Number of gear units	1 unit
Gear	-
Driver included	Yes
Service tag	Yes

Light Technical

Number of light sources	1
-------------------------	---

Operating and Electrical

Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Mech. impact protection code IK02 [0.2 J standard]

Emergency Operation

Central Emergency No

Approval and Application

Flammability mark -

CE mark Yes

ENEC mark ENEC mark

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h 10 %

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Beam angle of light source	Optic type
910505105007	DN500B 20S/840 PSU-E OC WH	2,000 lm	4000 K	149 lm/W	80	-	High-gloss mirror
912500108336	TCTT200 20S/830 U4 OC PCC WH	1,729 lm	3000 K	125 lm/W	>80	60 degree(s)	Beam angle 60°
912500102943	TCTT165 11S/840 PSU-E WH	1,130 lm	4000 K	138 lm/W	>80	90 degree(s)	Beam angle 90°
912500104075	TCTT165 11S/830 PSU-E WH	1,098 lm	3000 K	134 lm/W	>80	90 degree(s)	Beam angle 90°
910505105010	DN500B 20S/840 PSU-E OC WH PCC	1,950 lm	4000 K	146 lm/W	80	-	High-gloss mirror
912500103829	TCTT175 20S/830 PSU-E WH	1,797 lm	3000 K	135 lm/W	>80	90 degree(s)	Beam angle 90°
912500104377	TCTT175 20S/840 PSU-E WH	1,849 lm	4000 K	139 lm/W	>80	90 degree(s)	Beam angle 90°
910505105005	DN500B 20S/840 PSU-E C GR	2,100 lm	4000 K	157 lm/W	80	-	High-gloss mirror
910505105016	DN510B 20S/840 PSU-E WR WH PCO	1,950 lm	4000 K	146 lm/W	80	-	High-gloss mirror White reflector without louver
910505104972	DN500B 11S/830 PSU-E C WH	1,150 lm	3000 K	149 lm/W	80	-	High-gloss mirror
910505105003	DN500B 20S/830 PSU-E C WH	1,950 lm	3000 K	146 lm/W	80	-	High-gloss mirror
910505105004	DN500B 20S/840 PSU-E C WH	2,100 lm	4000 K	157 lm/W	80	-	High-gloss mirror
910505105014	DN510B 20S/840 PSU-E OC WH	2,000 lm	4000 K	149 lm/W	80	-	High-gloss mirror
910505105019	DN510B 30S/840 PSU-E OC WH	3,000 lm	4000 K	156 lm/W	80	-	High-gloss mirror
912500103323	TCTT180 20S/840 PSU-E WH281	1,849 lm	4000 K	139 lm/W	>80	90 degree(s)	Beam angle 90°
912500106233	TCTT180 20S/830 PSU-E WH	1,797 lm	3000 K	135 lm/W	>80	90 degree(s)	Beam angle 90°
910505105006	DN500B 20S/840 PSU-E C BK	2,100 lm	4000 K	157 lm/W	80	-	High-gloss mirror
910505105017	DN510B 20S/840 PSU-E OC WH PCC	1,950 lm	4000 K	146 lm/W	80	-	High-gloss mirror
910505105013	DN510B 20S/840 PSU-E C BK	2,100 lm	4000 K	157 lm/W	80	-	High-gloss mirror

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Beam angle of light source	Optic type
910505105015	DN510B 20S/840 PSU-E C WH PCC	2,000 lm	4000 K	149 lm/W	80	-	High-gloss mirror
910505104973	DN510B 20S/830 PSU-E C WH	1,950 lm	3000 K	146 lm/W	80	-	High-gloss mirror
910505105011	DN510B 20S/840 PSU-E C WH	2,100 lm	4000 K	157 lm/W	80	-	High-gloss mirror
910505105018	DN510B 30S/840 PSU-E C WH	3,100 lm	4000 K	161 lm/W	80	-	High-gloss mirror
912500102953	TCTT225 20S/840 PSU-E WH	1,964 lm	4000 K	148 lm/W	>80	90 degree(s)	Beam angle 90°
912500103778	TCTT225 20S/830 PSU-E WH	1,909 lm	3000 K	144 lm/W	>80	90 degree(s)	Beam angle 90°
912500102942	TCTT160 11S/840 PSU-E WH	1,130 lm	4000 K	138 lm/W	>80	90 degree(s)	Beam angle 90°
912500106265	TCTT160 11S/830 PSU-E WH	1,098 lm	3000 K	134 lm/W	>80	90 degree(s)	Beam angle 90°
910505105008	DN500B 20S/840 PSU-E C WH PCC	2,000 lm	4000 K	149 lm/W	80	-	High-gloss mirror
910505105009	DN500B 20S/840 PSU-E WR WH PCO	1,850 lm	4000 K	138 lm/W	80	-	High-gloss mirror White reflector without louver
912500102954	TCTT230 20S/840 PSU-E WH	1,964 lm	4000 K	148 lm/W	>80	90 degree(s)	Beam angle 90°
912500103782	TCTT230 20S/830 PSU-E WH	1,909 lm	3000 K	144 lm/W	>80	90 degree(s)	Beam angle 90°
910505105012	DN510B 20S/840 PSU-E C GR	2,100 lm	4000 K	157 lm/W	80	-	High-gloss mirror

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910505105007	DN500B 20S/840 PSU-E OC WH	220 to 240 V	13.4 W	No
912500108336	TCTT200 20S/830 U4 OC PCC WH	220/240 V	13.8 W	Yes (relates to presence/ movement detection and daylight harvesting)
912500102943	TCTT165 11S/840 PSU-E WH	220/240 V	8.2 W	No
912500104075	TCTT165 11S/830 PSU-E WH	220/240 V	8.2 W	No
910505105010	DN500B 20S/840 PSU-E OC WH PCC	220 to 240 V	13.4 W	No
912500103829	TCTT175 20S/830 PSU-E WH	220/240 V	13.3 W	No
912500104377	TCTT175 20S/840 PSU-E WH	220/240 V	13.3 W	No
910505105005	DN500B 20S/840 PSU-E C GR	220 to 240 V	13.4 W	No
910505105016	DN510B 20S/840 PSU-E WR WH PCO	220 to 240 V	13.4 W	No
910505104972	DN500B 11S/830 PSU-E C WH	220 to 240 V	7.7 W	No
910505105003	DN500B 20S/830 PSU-E C WH	220 to 240 V	13.4 W	No
910505105004	DN500B 20S/840 PSU-E C WH	220 to 240 V	13.4 W	No
910505105014	DN510B 20S/840 PSU-E OC WH	220 to 240 V	13.4 W	No
910505105019	DN510B 30S/840 PSU-E OC WH	220 to 240 V	19.2 W	No
912500103323	TCTT180 20S/840 PSU-E WH281	220/240 V	13.3 W	No
912500106233	TCTT180 20S/830 PSU-E WH	220/240 V	13.3 W	No
910505105006	DN500B 20S/840 PSU-E C BK	220 to 240 V	13.4 W	No
910505105017	DN510B 20S/840 PSU-E OC WH PCC	220 to 240 V	13.4 W	No
910505105013	DN510B 20S/840 PSU-E C BK	220 to 240 V	13.4 W	No
910505105015	DN510B 20S/840 PSU-E C WH PCC	220 to 240 V	13.4 W	No
910505104973	DN510B 20S/830 PSU-E C WH	220 to 240 V	13.4 W	No

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910505105011	DN510B 20S/840 PSU-E C WH	220 to 240 V	13.4 W	No
910505105018	DN510B 30S/840 PSU-E C WH	220 to 240 V	19.2 W	No
912500102953	TCTT225 20S/840 PSU-E WH	220/240 V	13.3 W	No
912500103778	TCTT225 20S/830 PSU-E WH	220/240 V	13.3 W	No
912500102942	TCTT160 11S/840 PSU-E WH	220/240 V	8.2 W	No
912500106265	TCTT160 11S/830 PSU-E WH	220/240 V	8.2 W	No
910505105008	DN500B 20S/840 PSU-E C WH PCC	220 to 240 V	13.4 W	No
910505105009	DN500B 20S/840 PSU-E WR WH PCO	220 to 240 V	13.4 W	No
912500102954	TCTT230 20S/840 PSU-E WH	220/240 V	13.3 W	No
912500103782	TCTT230 20S/830 PSU-E WH	220/240 V	13.3 W	No
910505105012	DN510B 20S/840 PSU-E C GR	220 to 240 V	13.4 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control
910505105007	DN500B 20S/840 PSU-E OC WH	No	-
912500108336	TCTT200 20S/830 U4 OC PCC WH	Yes	Interact SC200 sensor
912500102943	TCTT165 11S/840 PSU-E WH	No	-
912500104075	TCTT165 11S/830 PSU-E WH	No	-
910505105010	DN500B 20S/840 PSU-E OC WH PCC	No	-
912500103829	TCTT175 20S/830 PSU-E WH	No	-
912500104377	TCTT175 20S/840 PSU-E WH	No	-
910505105005	DN500B 20S/840 PSU-E C GR	No	-
910505105016	DN510B 20S/840 PSU-E WR WH PCO	No	-
910505104972	DN500B 11S/830 PSU-E C WH	No	-
910505105003	DN500B 20S/830 PSU-E C WH	No	-
910505105004	DN500B 20S/840 PSU-E C WH	No	-
910505105014	DN510B 20S/840 PSU-E OC WH	No	-
910505105019	DN510B 30S/840 PSU-E OC WH	No	-
912500103323	TCTT180 20S/840 PSU-E WH281	No	-
912500106233	TCTT180 20S/830 PSU-E WH	No	-
910505105006	DN500B 20S/840 PSU-E C BK	No	-
910505105017	DN510B 20S/840 PSU-E OC WH PCC	No	-
910505105013	DN510B 20S/840 PSU-E C BK	No	-
910505105015	DN510B 20S/840 PSU-E C WH PCC	No	-
910505104973	DN510B 20S/830 PSU-E C WH	No	-
910505105011	DN510B 20S/840 PSU-E C WH	No	-
910505105018	DN510B 30S/840 PSU-E C WH	No	-
912500102953	TCTT225 20S/840 PSU-E WH	No	-
912500103778	TCTT225 20S/830 PSU-E WH	No	-
912500102942	TCTT160 11S/840 PSU-E WH	No	-
912500106265	TCTT160 11S/830 PSU-E WH	No	-

Order Code	Full Product Name	Dimmable	Embedded control
910505105008	DN500B 20S/840 PSU-E C WH PCC	No	-
910505105009	DN500B 20S/840 PSU-E WR WH PCO	No	-
912500102954	TCTT230 20S/840 PSU-E WH	No	-
912500103782	TCTT230 20S/830 PSU-E WH	No	-
910505105012	DN510B 20S/840 PSU-E C GR	No	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Ingress protection code
910505105007	DN500B 20S/840 PSU-E OC WH	Gray	IP20
912500108336	TCTT200 20S/830 U4 OC PCC WH	White	IP20/54
912500102943	TCTT165 11S/840 PSU-E WH	White	IP20
912500104075	TCTT165 11S/830 PSU-E WH	White	IP20
910505105010	DN500B 20S/840 PSU-E OC WH PCC	Gray	IP20/54
912500103829	TCTT175 20S/830 PSU-E WH	White	IP20
912500104377	TCTT175 20S/840 PSU-E WH	White	IP20
910505105005	DN500B 20S/840 PSU-E C GR	Gray	IP20
910505105016	DN510B 20S/840 PSU-E WR WH PCO	Gray	IP20/54
910505104972	DN500B 11S/830 PSU-E C WH	Gray	IP20
910505105003	DN500B 20S/830 PSU-E C WH	Gray	IP20
910505105004	DN500B 20S/840 PSU-E C WH	Gray	IP20
910505105014	DN510B 20S/840 PSU-E OC WH	Gray	IP20
910505105019	DN510B 30S/840 PSU-E OC WH	Gray	IP20
912500103323	TCTT180 20S/840 PSU-E WH281	White	IP20
912500106233	TCTT180 20S/830 PSU-E WH	White	IP20
910505105006	DN500B 20S/840 PSU-E C BK	Gray	IP20
910505105017	DN510B 20S/840 PSU-E OC WH PCC	Gray	IP20/54
910505105013	DN510B 20S/840 PSU-E C BK	Gray	IP20
910505105015	DN510B 20S/840 PSU-E C WH PCC	Gray	IP20/54
910505104973	DN510B 20S/830 PSU-E C WH	Gray	IP20
910505105011	DN510B 20S/840 PSU-E C WH	Gray	IP20
910505105018	DN510B 30S/840 PSU-E C WH	Gray	IP20
912500102953	TCTT225 20S/840 PSU-E WH	White	IP20
912500103778	TCTT225 20S/830 PSU-E WH	White	IP20
912500102942	TCTT160 11S/840 PSU-E WH	White	IP20
912500106265	TCTT160 11S/830 PSU-E WH	White	IP20
910505105008	DN500B 20S/840 PSU-E C WH PCC	Gray	IP20/54
910505105009	DN500B 20S/840 PSU-E WR WH PCO	Gray	IP20/54
912500102954	TCTT230 20S/840 PSU-E WH	White	IP20
912500103782	TCTT230 20S/830 PSU-E WH	White	IP20
910505105012	DN510B 20S/840 PSU-E C GR	Gray	IP20

Approval and Application

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)	Ambient temperature range
910505105007	DN500B 20S/840 PSU-E OC WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
912500108336	TCTT200 20S/830 U4 OC PCC WH	Temperature 750 °C, duration 30 s	0.02	0.003	+10 to +40 °C
912500102943	TCTT165 11S/840 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500104075	TCTT165 11S/830 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
910505105010	DN500B 20S/840 PSU-E OC WH PCC	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
912500103829	TCTT175 20S/830 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500104377	TCTT175 20S/840 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
910505105005	DN500B 20S/840 PSU-E C GR	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105016	DN510B 20S/840 PSU-E WR WH PCO	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505104972	DN500B 11S/830 PSU-E C WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105003	DN500B 20S/830 PSU-E C WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105004	DN500B 20S/840 PSU-E C WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105014	DN510B 20S/840 PSU-E OC WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105019	DN510B 30S/840 PSU-E OC WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
912500103323	TCTT180 20S/840 PSU-E WH281	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500106233	TCTT180 20S/830 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
910505105006	DN500B 20S/840 PSU-E C BK	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105017	DN510B 20S/840 PSU-E OC WH PCC	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105013	DN510B 20S/840 PSU-E C BK	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105015	DN510B 20S/840 PSU-E C WH PCC	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505104973	DN510B 20S/830 PSU-E C WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105011	DN510B 20S/840 PSU-E C WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105018	DN510B 30S/840 PSU-E C WH	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
912500102953	TCTT225 20S/840 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500103778	TCTT225 20S/830 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500102942	TCTT160 11S/840 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500106265	TCTT160 11S/830 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
910505105008	DN500B 20S/840 PSU-E C WH PCC	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
910505105009	DN500B 20S/840 PSU-E WR WH PCO	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C
912500102954	TCTT230 20S/840 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
912500103782	TCTT230 20S/830 PSU-E WH	Temperature 750 °C, duration 30 s	1	0.4	+10 to +40 °C
910505105012	DN510B 20S/840 PSU-E C GR	Temperature 650 °C, duration 30 s	-	-	+10 to +35 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance	Initial chromaticity
910505105007	DN500B 20S/840 PSU-E OC WH	+/-10%	(0.38, 0.38) SDCM <3
912500108336	TCTT200 20S/830 U4 OC PCC WH	-10% / +10%	(0.43, 0.40) SDCM < 3
912500102943	TCTT165 11S/840 PSU-E WH	-10% / +10%	(0.38, 0.38) SDCM < 3


Order Code	Full Product Name	Luminous flux tolerance	Initial chromaticity
912500104075	TCTT165 11S/830 PSU-E WH	-10% / +10%	(0.43, 0.40) SDCM < 3
910505105010	DN500B 20S/840 PSU-E OC WH PCC	+/-10%	(0.38, 0.38) SDCM <3
912500103829	TCTT175 20S/830 PSU-E WH	-10% / +10%	(0.43, 0.40) SDCM < 3
912500104377	TCTT175 20S/840 PSU-E WH	-10% / +10%	(0.38, 0.38) SDCM < 3
910505105005	DN500B 20S/840 PSU-E C GR	+/-10%	(0.38, 0.38) SDCM <3
910505105016	DN510B 20S/840 PSU-E WR WH PCO	+/-10%	(0.38, 0.38) SDCM <3
910505104972	DN500B 11S/830 PSU-E C WH	+/-10%	(0.38, 0.38) SDCM <3
910505105003	DN500B 20S/830 PSU-E C WH	+/-10%	(0.38, 0.38) SDCM <3
910505105004	DN500B 20S/840 PSU-E C WH	+/-10%	(0.38, 0.38) SDCM <3
910505105014	DN510B 20S/840 PSU-E OC WH	+/-10%	(0.38, 0.38) SDCM <3
910505105019	DN510B 30S/840 PSU-E OC WH	+/-10%	(0.38, 0.38) SDCM <3
912500103323	TCTT180 20S/840 PSU-E WH281	-10% / +10%	(0.38, 0.38) SDCM < 3
912500106233	TCTT180 20S/830 PSU-E WH	-10% / +10%	(0.43, 0.40) SDCM < 3
910505105006	DN500B 20S/840 PSU-E C BK	+/-10%	(0.38, 0.38) SDCM <3
910505105017	DN510B 20S/840 PSU-E OC WH PCC	+/-10%	(0.38, 0.38) SDCM <3
910505105013	DN510B 20S/840 PSU-E C BK	+/-10%	(0.38, 0.38) SDCM <3
910505105015	DN510B 20S/840 PSU-E C WH PCC	+/-10%	(0.38, 0.38) SDCM <3
910505104973	DN510B 20S/830 PSU-E C WH	+/-10%	(0.38, 0.38) SDCM <3
910505105011	DN510B 20S/840 PSU-E C WH	+/-10%	(0.38, 0.38) SDCM <3
910505105018	DN510B 30S/840 PSU-E C WH	+/-10%	(0.38, 0.38) SDCM <3
912500102953	TCTT225 20S/840 PSU-E WH	-10% / +10%	(0.38, 0.38) SDCM < 3
912500103778	TCTT225 20S/830 PSU-E WH	-10% / +10%	(0.43, 0.40) SDCM < 3
912500102942	TCTT160 11S/840 PSU-E WH	-10% / +10%	(0.38, 0.38) SDCM < 3
912500106265	TCTT160 11S/830 PSU-E WH	-10% / +10%	(0.43, 0.40) SDCM < 3
910505105008	DN500B 20S/840 PSU-E C WH PCC	+/-10%	(0.38, 0.38) SDCM <3
910505105009	DN500B 20S/840 PSU-E WR WH PCO	+/-10%	(0.38, 0.38) SDCM <3
912500102954	TCTT230 20S/840 PSU-E WH	-10% / +10%	(0.38, 0.38) SDCM < 3
912500103782	TCTT230 20S/830 PSU-E WH	-10% / +10%	(0.43, 0.40) SDCM < 3
910505105012	DN510B 20S/840 PSU-E C GR	+/-10%	(0.38, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910505105007	DN500B 20S/840 PSU-E OC WH	DN500B
912500108336	TCTT200 20S/830 U4 OC PCC WH	TCTTPF
912500102943	TCTT165 11S/840 PSU-E WH	TCTTPF
912500104075	TCTT165 11S/830 PSU-E WH	TCTTPF
910505105010	DN500B 20S/840 PSU-E OC WH PCC	DN500B
912500103829	TCTT175 20S/830 PSU-E WH	TCTTPF
912500104377	TCTT175 20S/840 PSU-E WH	TCTTPF
910505105005	DN500B 20S/840 PSU-E C GR	DN500B
910505105016	DN510B 20S/840 PSU-E WR WH PCO	DN510B

Order Code	Full Product Name	Product family code
910505104972	DN500B 11S/830 PSU-E C WH	-
910505105003	DN500B 20S/830 PSU-E C WH	DN500B
910505105004	DN500B 20S/840 PSU-E C WH	DN500B
910505105014	DN510B 20S/840 PSU-E OC WH	DN510B
910505105019	DN510B 30S/840 PSU-E OC WH	DN510B
912500103323	TCTT180 20S/840 PSU-E WH281	TCTTPF
912500106233	TCTT180 20S/830 PSU-E WH	TCTTPF
910505105006	DN500B 20S/840 PSU-E C BK	DN500B
910505105017	DN510B 20S/840 PSU-E OC WH PCC	DN510B
910505105013	DN510B 20S/840 PSU-E C BK	DN510B
910505105015	DN510B 20S/840 PSU-E C WH PCC	DN510B
910505104973	DN510B 20S/830 PSU-E C WH	-
910505105011	DN510B 20S/840 PSU-E C WH	DN510B
910505105018	DN510B 30S/840 PSU-E C WH	DN510B
912500102953	TCTT225 20S/840 PSU-E WH	TCTTPF
912500103778	TCTT225 20S/830 PSU-E WH	TCTTPF
912500102942	TCTT160 11S/840 PSU-E WH	TCTTPF
912500106265	TCTT160 11S/830 PSU-E WH	TCTTPF
910505105008	DN500B 20S/840 PSU-E C WH PCC	DN500B
910505105009	DN500B 20S/840 PSU-E WR WH PCO	DN500B
912500102954	TCTT230 20S/840 PSU-E WH	TCTTPF
912500103782	TCTT230 20S/830 PSU-E WH	TCTTPF
910505105012	DN510B 20S/840 PSU-E C GR	DN510B


Polar normal diagrams




910505105013




910505105004




910505105017




910505105005




910505105014




910505105007




910505105018




910505105019




910505105009




910505105010




910505105011




910505105003




910505105015




910505105016




910505105008




910505105012




910505105006




910505104972



910505104973



TCTTPI - 912500102954



TCTTPI - 912500102953