

LuxSpace Mini, recessed

DN560B



LuxSpace recessed – high efficiency, visual comfort and a stylish design

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

Applications

- Offices
- Retail
- Hospitals
- Hotels
- Airports

Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Rim colors: high-gloss metalized, white (RAL9010), grey, black (RAL9004) as standard (any other RAL color possible upon request)

- Rimless version available
- Surface-mounted version available
- Compliant for central emergency lighting with DC
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring

Versions




IPPR_DN560Bi_0001-Product photo




IPPR_DN560Bi_0009-Product photo

Dimensional drawing



LuxSpace2 Mini Low height recessed



LuxSpace2 Mini Deep recessed

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
Optic type	-

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Protection class IEC	Safety class II

Controls and Dimming

Maximum dim level	1%
Embedded control	Visible light communication

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +25 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
97048200	DN561B LED12S/830UE PSU-E C WH	1,200 lm	3000 K	150 lm/W
97049900	DN561B LED12S/840UE PSU-E C WH	1,250 lm	4000 K	158 lm/W
97055000	DN561B LED12S/840UE DIA-VLC-E C WH	1,250 lm	4000 K	144 lm/W
97044400	DN560B LED12S/830UE PSU-E C WH	1,200 lm	3000 K	150 lm/W
97045100	DN560B LED12S/840UE PSU-E C WH	1,250 lm	4000 K	158 lm/W
97046800	DN560B LED12S/830UE PSU-E C PG WH	1,150 lm	3000 K	144 lm/W
97047500	DN560B LED12S/840UE PSU-E C PG WH	1,200 lm	4000 K	152 lm/W
97053600	DN560B LED12S/840UE DIA-VLC-E C WH	1,250 lm	4000 K	144 lm/W
97056700	DN560B LED20S/830UE PSU-E C WH	2,100 lm	3000 K	163 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
97048200	DN561B LED12S/830UE PSU-E C WH	8.1 W
97049900	DN561B LED12S/840UE PSU-E C WH	8.1 W
97055000	DN561B LED12S/840UE DIA-VLC-E C WH	8.9 W
97044400	DN560B LED12S/830UE PSU-E C WH	8.1 W
97045100	DN560B LED12S/840UE PSU-E C WH	8.1 W
97046800	DN560B LED12S/830UE PSU-E C PG WH	8.1 W
97047500	DN560B LED12S/840UE PSU-E C PG WH	8.1 W
97053600	DN560B LED12S/840UE DIA-VLC-E C WH	8.9 W
97056700	DN560B LED20S/830UE PSU-E C WH	13 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
97048200	DN561B LED12S/830UE PSU-E C WH	No
97049900	DN561B LED12S/840UE PSU-E C WH	No
97055000	DN561B LED12S/840UE DIA-VLC-E C WH	Yes
97044400	DN560B LED12S/830UE PSU-E C WH	No
97045100	DN560B LED12S/840UE PSU-E C WH	No
97046800	DN560B LED12S/830UE PSU-E C PG WH	No
97047500	DN560B LED12S/840UE PSU-E C PG WH	No
97053600	DN560B LED12S/840UE DIA-VLC-E C WH	Yes
97056700	DN560B LED20S/830UE PSU-E C WH	No

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
97048200	DN561B LED12S/830UE PSU-E C WH	IP20
97049900	DN561B LED12S/840UE PSU-E C WH	IP20
97055000	DN561B LED12S/840UE DIA-VLC-E C WH	IP20
97044400	DN560B LED12S/830UE PSU-E C WH	IP20
97045100	DN560B LED12S/840UE PSU-E C WH	IP20
97046800	DN560B LED12S/830UE PSU-E C PG WH	IP20/54
97047500	DN560B LED12S/840UE PSU-E C PG WH	IP20/54
97053600	DN560B LED12S/840UE DIA-VLC-E C WH	IP20
97056700	DN560B LED20S/830UE PSU-E C WH	IP20

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
97048200	DN561B LED12S/830UE PSU-E C WH	(0.43, 0.40) SDCM <2


Order Code	Full Product Name	Initial chromaticity
97049900	DN561B LED12S/840UE PSU-E C WH	(0.38, 0.38) SDCM <2
97055000	DN561B LED12S/840UE DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
97044400	DN560B LED12S/830UE PSU-E C WH	(0.43, 0.40) SDCM <2
97045100	DN560B LED12S/840UE PSU-E C WH	(0.38, 0.38) SDCM <2
97046800	DN560B LED12S/830UE PSU-E C PG WH	(0.43, 0.40) SDCM <2
97047500	DN560B LED12S/840UE PSU-E C PG WH	(0.38, 0.38) SDCM <2
97053600	DN560B LED12S/840UE DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
97056700	DN560B LED20S/830UE PSU-E C WH	(0.43, 0.40) SDCM <2

Product Data


Order Code	Full Product Name	Product family code
97048200	DN561B LED12S/830UE PSU-E C WH	DN561B
97049900	DN561B LED12S/840UE PSU-E C WH	DN561B
97055000	DN561B LED12S/840UE DIA-VLC-E C WH	DN561B
97044400	DN560B LED12S/830UE PSU-E C WH	DN560B
97045100	DN560B LED12S/840UE PSU-E C WH	DN560B
97046800	DN560B LED12S/830UE PSU-E C PG WH	DN560B
97047500	DN560B LED12S/840UE PSU-E C PG WH	DN560B
97053600	DN560B LED12S/840UE DIA-VLC-E C WH	DN560B
97056700	DN560B LED20S/830UE PSU-E C WH	DN560B

Polar normal diagrams







DN560BI - 910505100918




DN560BI - 910505100917




DN560BI - 910505100916



DN560BI - 910505100924



DN560BI - 910505100919



DN560BI - 910505100915