



# LuxSpace square, recessed – high efficiency, visual comfort and a stylish design

## LuxSpace square, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

# LuxSpace square, recessed


## Features

- Choice of four optics: high-gloss, faceted, matt and white
- Rim colors: high-gloss metalized, white (RAL9010), grey, black (RAL9004) as standard (any other RAL color possible upon request)
- Rimless version available
- Compliant for central emergency lighting with DC
- Multiple additional options: emergency lighting (single battery 3 hours), through-wiring

## Application

- Offices
- Retail
- Hospitals
- Hotels
- Airports

## Dimensional drawing



# LuxSpace square, recessed

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +25 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Product Data	
Product family code	DN572B

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505100944	DN572B LED12S/840UE PSU-E C WH	4000 K	160 lm/W	1,250 lm
910505100945	DN572B LED12S/830UE DIA-VLC-E C WH	3000 K	153 lm/W	1,200 lm
910505100946	DN572B LED12S/840UE DIA-VLC-E C WH	4000 K	161 lm/W	1,250 lm
910505100947	DN572B LED20S/830UE PSU-E C WH	3000 K	163 lm/W	2,100 lm
910505100948	DN572B LED20S/840UE PSU-E C WH	4000 K	172 lm/W	2,200 lm
910505100949	DN572B LED20S/830UE DIA-VLC-E C WH	3000 K	164 lm/W	2,100 lm
910505100950	DN572B LED20S/840UE DIA-VLC-E C WH	4000 K	173 lm/W	2,200 lm
910505100951	DN572B LED24S/830UE PSU-E C WH	3000 K	164 lm/W	2,400 lm
910505100952	DN572B LED24S/840UE PSU-E C WH	4000 K	173 lm/W	2,500 lm
910505100953	DN572B LED24S/830UE DIA-VLC-E C WH	3000 K	168 lm/W	2,400 lm
910505100954	DN572B LED24S/840UE DIA-VLC-E C WH	4000 K	177 lm/W	2,500 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505100944	DN572B LED12S/840UE PSU-E C WH	7.9 W
910505100945	DN572B LED12S/830UE DIA-VLC-E C WH	7.9 W
910505100946	DN572B LED12S/840UE DIA-VLC-E C WH	7.9 W
910505100947	DN572B LED20S/830UE PSU-E C WH	13 W
910505100948	DN572B LED20S/840UE PSU-E C WH	13 W
910505100949	DN572B LED20S/830UE DIA-VLC-E C WH	12.8 W

Order Code	Full Product Name	Power Consumption
910505100950	DN572B LED20S/840UE DIA-VLC-E C WH	12.8 W
910505100951	DN572B LED24S/830UE PSU-E C WH	10.8 W
910505100952	DN572B LED24S/840UE PSU-E C WH	14.8 W
910505100953	DN572B LED24S/830UE DIA-VLC-E C WH	14.4 W
910505100954	DN572B LED24S/840UE DIA-VLC-E C WH	14.4 W

## Controls and Dimming

# LuxSpace square, recessed

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100944	DN572B LED12S/840UE PSU-E C WH	No	-	-
910505100945	DN572B LED12S/830UE DIA-VLC-E C WH	Yes	Visible light communication	1%
910505100946	DN572B LED12S/840UE DIA-VLC-E C WH	Yes	Visible light communication	1%
910505100947	DN572B LED20S/830UE PSU-E C WH	No	-	-
910505100948	DN572B LED20S/840UE PSU-E C WH	No	-	-
910505100949	DN572B LED20S/830UE DIA-VLC-E C WH	Yes	Visible light communication	1%


Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100950	DN572B LED20S/840UE DIA-VLC-E C WH	Yes	Visible light communication	1%
910505100951	DN572B LED24S/830UE PSU-E C WH	No	-	-
910505100952	DN572B LED24S/840UE PSU-E C WH	No	-	-
910505100953	DN572B LED24S/830UE DIA-VLC-E C WH	Yes	Visible light communication	1%
910505100954	DN572B LED24S/840UE DIA-VLC-E C WH	Yes	Visible light communication	1%

## Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
910505100944	DN572B LED12S/840UE PSU-E C WH	(0.38, 0.38) SDCM <2
910505100945	DN572B LED12S/830UE DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100946	DN572B LED12S/840UE DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
910505100947	DN572B LED20S/830UE PSU-E C WH	(0.43, 0.40) SDCM <2
910505100948	DN572B LED20S/840UE PSU-E C WH	(0.38, 0.38) SDCM <2
910505100949	DN572B LED20S/830UE DIA-VLC-E C WH	(0.43, 0.40) SDCM <2

Order Code	Full Product Name	Initial chromaticity
910505100950	DN572B LED20S/840UE DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
910505100951	DN572B LED24S/830UE PSU-E C WH	(0.43, 0.40) SDCM <2
910505100952	DN572B LED24S/840UE PSU-E C WH	(0.38, 0.38) SDCM <2
910505100953	DN572B LED24S/830UE DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100954	DN572B LED24S/840UE DIA-VLC-E C WH	(0.38, 0.38) SDCM <2


## Polar Wide Diagrams



Polar Normal (separate) - DN572BI - 910505100945




Polar Normal (separate) - DN572BI - 910505100951




Polar Normal (separate) - DN572BI - 910505100950

# LuxSpace square, recessed


## Polar Wide Diagrams




**Polar Normal (separate) - DN572BI - 910505100953**




**Polar Normal (separate) - DN572BI - 910505100949**




**Polar Normal (separate) - DN572BI - 910505100948**




**Polar Normal (separate) - DN572BI - 910505100944**




**Polar Normal (separate) - DN572BI - 910505100954**



**Polar Normal (separate) - DN572BI - 910505100946**



**Polar Normal (separate) - DN572BI - 910505100952**



**Polar Normal (separate) - DN572BI - 910505100947**

## LuxSpace square, recessed

