

LuxSpace Compact, recessed

DN610B



LuxSpace Compact, recessed: UltraEfficient, stylish and designed for circularity

Philips LuxSpace is designed to provide the perfect combination of efficiency, high visual comfort and stylish design without compromising on lighting performance. LuxSpace offers a long lifetime and efficacy of up to 185 lm/W, along with excellent colour rendering and light distribution which have a major influence on the visual and non-visual effects of light on human health and well-being. The LuxSpace downlight family offers a wide choice of options for creating the desired ambience and supporting user comfort, no matter what the application is. For office applications, LuxSpace offers dedicated tunable white luminaires with lighting controls for circadian lighting solutions and office-compliant versions (UGR19).

Benefits

- Best-in-class efficacy of up to 185 lm/ W
- Gentle, natural light ensures visual comfort
- Extensive design options with mounting types, rim colours and reflectors
- Perfect ceiling integration with narrow rim or rimless versions for plaster ceilings
- Improved glare control complies with office lighting standards
- High colour rendering up to CRI 90 (R9>50)

- Provides uniform lighting thanks to wide light distribution
- Supports circadian lighting solutions with tunable white luminaires and integrated lighting controls

Applications

- Offices
- Retail
- Hospitals and care centres
- Hospitality
- Airports

- Municipal Buildings
- Atriums

Features

- Mini (DN560B/DN561B), Compact (DN610B) and Square (DN572B) types for recessed applications
- Surface-mounted round (DN570C/DN571C) versions
- Choice of five optics: high gloss, faded lines, matte, white and black


- UGR19 is standard for Compact and optional for other versions
- White (RAL9003), grey (RAL9006) and black (RAL9004) are standard, with any other RAL colour possible upon request
- Compliant for central emergency lighting with DC (PSED driver type)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), through-wiring, Eca and B2ca cable and connector options
- Extended useful lifetime of 50,000 hours at L90

Versions



LuxSpace Compact, Recessed
- Clear reflector, White Rim,
240mm cut-out

Dimensional drawing



DN610B 24S/840UE WIA-E C WH

General Information	
Number of gear units	Unit
Driver included	Yes
Service Tag	Yes

Light Technical

Luminous Flux	2,500 lm
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	158 lm/W
Colour rendering index (CRI)	>80
Optic type	-

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	15.8 W
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Colour	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +35 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38,0.38)

Product Data

Product family code	DN610B [LuxSpace Compact, recessed]
---------------------	-------------------------------------

Polar normal diagrams



DN610BI - 910505104745

