



Product Description

MASTER SON-T PIA Plus

High Pressure Sodium lamp with clear tubular outer bulb, high output and long reliable lifetime

Benefits

- Superior technology results in a long and reliable lifetime, high lumen maintenance and a reliable ignition over lifetime
- High energy efficacy and absence of lead (Pb) makes this a sound environmental offer
- High luminous efficacy makes this the most energy efficient HPS lamp

Features

- Clear tubular outer bulb
- Ceramic discharge tube with Philips Integrated Antenna (PIA) for a long and reliable lifetime
- Robust construction with few welding points is highly vibration- and shock-resistant, further reducing early failures and extending lamp life
- ZrCo getter ensures high lumen maintenance and few early failures
- "Plus" concept with high efficacy translated into high light output
- Completely lead-free lamps

Application

- Road and residential lighting
- Decorative floodlighting, illumination
- Industrial area lighting
- Recreational sports facilities Outdoor and Indoor
- Horticultural lighting

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER SON-T PIA Plus

Versions




LPPR SON-TPIA Plus E40



LPPR SON-TPIA 0007

Dimensional drawing



Product	D (max)	O	L	C (max)
MST SON-T PIA Plus 150W E40 1SL/12	47 mm	61 mm	132 mm	209 mm
MST SON-T PIA Plus 600W/220 E40 1SL/12	47 mm	126 mm	174.2 mm	279 mm
MSTSON-TPIA Plus 70W E27 1CT/12	35.75 mm	42 mm	102 mm	156 mm

General Information

Operating Position UNIVERSAL

Light Technical

Color rendering index (CRI) -

Mechanical and Housing

Bulb Finish Clear

General Information

Order Code	Full Product Name	Cap-Base
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	E40
928483400095	MST SON-T PIA Plus 150W E40 1SL/12	E40

Order Code	Full Product Name	Cap-Base
928483200094	MSTSON-TPIA Plus 70W E27 1CT/12	E27

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Correlated Color	Luminous Efficacy (rated)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)	Temperature (Nom)	(Nom)	
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	0.530	0.428	2000 K	149 lm/W	-
928483400095	MST SON-T PIA Plus 150W E40 1SL/12	0.535	0.42	2000 K	115 lm/W	17,800 lm
928483200094	MSTSON-TPIA Plus 70W E27 1CT/12	0.54	0.42	1900 K	91 lm/W	6,650 lm

MASTER SON-T PIA Plus

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	110 V	603 W
928483400095	MST SON-T PIA Plus 150W E40 1SL/12	100 V	155.0 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928483200094	MSTSON-TPIA Plus 70W E27 1CT/12	93 V	74.0 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	No
928483400095	MST SON-T PIA Plus 150W E40 1SL/12	Yes

Order Code	Full Product Name	Dimmable
928483200094	MSTSON-TPIA Plus 70W E27 1CT/12	Yes

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	T46
928483400095	MST SON-T PIA Plus 150W E40 1SL/12	T46

Order Code	Full Product Name	Bulb Shape
928483200094	MSTSON-TPIA Plus 70W E27 1CT/12	T35

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)
928158409227	MST SON-T PIA Plus 600W/220 E40 1SL/12	663 kWh	-	18.9 mg
928483400095	MST SON-T PIA Plus 150W E40 1SL/12	155 kWh	15.1 mg	13.9 mg
928483200094	MSTSON-TPIA Plus 70W E27 1CT/12	73 kWh	12.2 mg	12.2 mg

