

PHILIPS

SON

DSO



Product Description

High Pressure Sodium lamp with opalized ovoid outer bulb

Benefits

- SON is a cost-efficient and reliable solution in High Pressure Sodium
- SON Pro is a cost-efficient and reliable solution in High Pressure Sodium


Applications

- Road and residential lighting
- Road and residential lighting
- Decorative floodlighting
- Decorative floodlighting
- Commercial and industrial applications
- Commercial and industrial applications

Features

- Ovoid, internally white coated outer bulb
- Ovoid, internally white coated outer bulb
- High luminous efficacy
- High luminous efficacy
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Dimming possible with dedicated gear
- Dimming possible with dedicated gear

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



—

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Coated glass
-------------	--------------

Approval and Application

Mercury (Hg) Content (Max)	14.3 mg
----------------------------	---------

General Information

Order Code	Full Product Name	Cap-Base
928486700091	SON 70W E E27 CO 1CT/24	E27
928486800091	SON 150W E E40 CO 1SL/12	E40
928486900091	SON 250W E E40 CO 1SL/12	E40

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
928486700091	SON 70W E E27 CO 1CT/24	1900 K	80 lm/W
928486800091	SON 150W E E40 CO 1SL/12	2000 K	93 lm/W
928486900091	SON 250W E E40 CO 1SL/12	2000 K	106 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Voltage (Nom)
928486700091	SON 70W E E27 CO 1CT/24	72.5 W	95 V
928486800091	SON 150W E E40 CO 1SL/12	147.0 W	100 V
928486900091	SON 250W E E40 CO 1SL/12	250 W	100 V

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928486700091	SON 70W E E27 CO 1CT/24	BF70
928486800091	SON 150W E E40 CO 1SL/12	ED90
928486900091	SON 250W E E40 CO 1SL/12	ED90

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)	Energy Consumption kWh/1000 h
928486700091	SON 70W E E27 CO 1CT/24	14.3 mg	73 kWh
928486800091	SON 150W E E40 CO 1SL/12	20.4 mg	162 kWh
928486900091	SON 250W E E40 CO 1SL/12	20.4 mg	275 kWh

