



Upgrading your traditional luminaire installation base to a more energy-efficient, future-proof LED alternative.

Heritage LED retrofit kit

Specially designed for conventional luminaires and first generation LED variants, our IP66 heritage LED retrofit kit delivers several powerful advantages: existing installations become more energy-efficient, and safer, with a more reliable enclosure rating (IP66). In addition, the historical or traditional aesthetic of the luminaire is completely preserved. Thanks to its dedicated passe-partouts range, the heritage LED kit enables a quick and easy retrofit in our conventional (or LED) Villa, Jargeau, Micenas 1 and 2 luminaires while a universal and adjustable passe-partout completes the range and enables retrofit in most of other types of squarish luminaires of many manufacturers. The heritage LED retrofit kit comes with a wide range of application-tailored optics, enabling point-to-point replacement of conventional light sources. Its high-performing Ledgine optimized LED platform enables significant cost savings compared to conventional street lighting, and offers a short payback period. The heritage LED retrofit kit offers a large choice of standard warm color temperatures, this helps ensure that the installation retains the warm atmosphere of sodium lamps. The heritage LED retrofit kit is designed for customers looking for ways to cut their energy and maintenance costs with an easy-to-install solution while preserving the historical aesthetic of their installations. It also makes luminaires ready for future upgrades.

Heritage LED retrofit kit

Benefits

- Dedicated or adjustable solution, ready for future upgrades: designed to last over time and able to accommodate technological change
- Energy-efficient luminaire: saves energy costs of up to 40 – 60% compared to old conventional installation
- Reliable and long lifetime: reduced maintenance costs and longer lifetime – up to 100K hours

Features

- IP66 LED retrofit kit, both driver and optical unit, for maximum safety and reliability over long lifetime
- Easy adaptation to any squarish heritage luminaire: dedicated passe-partout (Villa, Jargeau, Micenas 1 & 2 product families) or adjustable one (for luminaires sizes between 305x305 mm up to 405x405 mm – luminaire inner dimensions)
- Large choice of color temperatures: 2200K, 2700K, 3000K and 4000K
- Easy and quick installation on site
- Further optimization on performance flux level enabled by the L-Tune

Application

- Road and Street
- Residential
- Parks and Plazas


Warnings and Safety

- With the exception of integration of this product in Jargeau, Villa or Micenas 1 luminaire, conventional or LED variants, Signify N.V. cannot accept any liability with regards to the mechanical fixation of this product into any other luminaire or on/in any other mounting construction, and to all fixation related aspects. It is the sole responsibility of the customer to ensure that this product is mounted and fixed in a safe and reliable manner.

Versions



Villa LED retrofit kit with white mask



Micenas 2 LED retrofit kit with black mask

Heritage LED retrofit kit

Versions



Villa LED retrofit kit with black mask



Micenas 1 LED retrofit kit with black mask









Jargeau LED retrofit kit with white mask






Jargeau LED retrofit kit with black mask

Dimensional drawing



Heritage LED retrofit kit

Dimensional drawing



Product details



Universal LED retrofit kit



Universal LED retrofit kit



Micenas 1 LED retrofit kit
passepartout




Universal LED retrofit kit

Heritage LED retrofit kit

Product details



Universal LED retrofit kit




Jargeau LED retrofit kit passepartout



Universal LED retrofit kit




Universal LED retrofit kit




Villa LED retrofit kit passepartout



Universal LED retrofit kit



Micenas 2 LED retrofit kit passepartout



Round LED retrofit kit passepartout

Heritage LED retrofit kit

General Information	
Driver included	Yes
Lamp family code	LED50
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Upward light output ratio	0.01
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Black
Mech. impact protection code	IK09
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
CE mark	Yes
Flammability mark	-

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color	Color
				Temperature (Nom)	rendering index (CRI)
912300024912	EDP768 LED50/830 II MK-WH DM50 FG SRG10	30° - 5° x 153°	830 warm white	3000 K	80
912300024909	EDP771 LED50/730 II MK-BK DS50 FG H07RN-	152° x 155°	730 warm white	3000 K	70
912300024906	EDP768 LED50/830 II MK-BK DM50 FG SRG10	30° - 5° x 153°	830 warm white	3000 K	80
912300024908	EDP770 LED50/830 II MK-BK DM50 FG SRG10	30° - 5° x 153°	830 warm white	3000 K	80
912300024913	EDP769 LED50/722 II MK-WH DM50 FG SRG10	30° - 5° x 153°	722 warm white	2200 K	70
912300024910	EDP772 LED50/830 II MK-BK DM50 FG H07RN-	30° - 5° x 153°	830 warm white	3000 K	80
912300024914	EDP772 LED50/727 II MK-BK DM50 FG SRG10	30° - 5° x 153°	727 warm white	2700 K	70
912300024911	EDP773 LED50/830 II MK-BK DM50 FG H07RN-	30° - 5° x 153°	830 warm white	3000 K	80
912300024915	EDP773 LED50/830 II MK-BK DM50 FG SRG10	30° - 5° x 153°	830 warm white	3000 K	80
912300024907	EDP769 LED50/722 II MK-BK DX10 FG SRG10	20° - 4° x 150°	722 warm white	2200 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type outdoor	Order Code	Full Product Name	Luminous Flux	Optic type outdoor
912300024912	EDP768 LED50/830 II MK-WH DM50 FG SRG10	3,700 lm	Distribution medium 50	912300024910	EDP772 LED50/830 II MK-BK DM50 FG H07RN-	3,850 lm	Distribution medium 50
912300024909	EDP771 LED50/730 II MK-BK DS50 FG H07RN-	3,400 lm	Distribution symmetrical 50	912300024914	EDP772 LED50/727 II MK-BK DM50 FG SRG10	3,850 lm	Distribution medium 50
912300024906	EDP768 LED50/830 II MK-BK DM50 FG SRG10	3,500 lm	Distribution medium 50	912300024911	EDP773 LED50/830 II MK-BK DM50 FG H07RN-	3,350 lm	Distribution medium 50
912300024908	EDP770 LED50/830 II MK-BK DM50 FG SRG10	3,500 lm	Distribution medium 50	912300024915	EDP773 LED50/830 II MK-BK DM50 FG SRG10	3,350 lm	Distribution medium 50
912300024913	EDP769 LED50/722 II MK-WH DM50 FG SRG10	3,450 lm	Distribution medium 50	912300024907	EDP769 LED50/722 II MK-BK DX10 FG SRG10	3,200 lm	Distribution extra wide 10

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)	Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
912300024912	EDP768 LED50/830 II MK-WH DM50 FG SRG10	38 W	Surge protection level until 10 kV differential mode and 10 kV common mode	912300024906	EDP768 LED50/830 II MK-BK DM50 FG SRG10	38 W	Surge protection level until 10 kV differential mode and 10 kV common mode
912300024909	EDP771 LED50/730 II MK-BK DS50 FG H07RN-	31.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode	912300024908	EDP770 LED50/830 II MK-BK DM50 FG SRG10	38 W	Surge protection level until 10 kV differential mode and 10 kV common mode

Heritage LED retrofit kit

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
912300024913	EDP769 LED50/722 II MK-WH DM50 FG SRG10	41 W	Surge protection level until 10 kV differential mode and 10 kV common mode
912300024910	EDP772 LED50/830 II MK-BK DM50 FG H07RN-	38.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
912300024914	EDP772 LED50/727 II MK-BK DM50 FG SRG10	35 W	Surge protection level until 10 kV differential mode and 10 kV common mode




Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
912300024911	EDP773 LED50/830 II MK-BK DM50 FG H07RN-	38 W	Surge protection level until 6 kV differential mode and 8 kV common mode
912300024915	EDP773 LED50/830 II MK-BK DM50 FG SRG10	38 W	Surge protection level until 10 kV differential mode and 10 kV common mode
912300024907	EDP769 LED50/722 II MK-BK DX10 FG SRG10	41 W	Surge protection level until 10 kV differential mode and 10 kV common mode

Product Data

Order Code	Full Product Name	Product family code
912300024912	EDP768 LED50/830 II MK-WH DM50 FG SRG10	EDP768
912300024909	EDP771 LED50/730 II MK-BK DS50 FG H07RN-	EDP771
912300024906	EDP768 LED50/830 II MK-BK DM50 FG SRG10	EDP768
912300024908	EDP770 LED50/830 II MK-BK DM50 FG SRG10	EDP770
912300024913	EDP769 LED50/722 II MK-WH DM50 FG SRG10	EDP769

Order Code	Full Product Name	Product family code
912300024910	EDP772 LED50/830 II MK-BK DM50 FG H07RN-	EDP772
912300024914	EDP772 LED50/727 II MK-BK DM50 FG SRG10	EDP772
912300024911	EDP773 LED50/830 II MK-BK DM50 FG H07RN-	EDP773
912300024915	EDP773 LED50/830 II MK-BK DM50 FG SRG10	EDP773
912300024907	EDP769 LED50/722 II MK-BK DX10 FG SRG10	EDP769




Polar Wide Diagrams



Polar Normal (separate) - EDP768I - 912300024906

Polar Normal (separate) - EDP768I - 912300024907

Polar Normal (separate) - EDP768I - 912300024908




Polar Normal (separate) - EDP768I - 912300024909

Polar Normal (separate) - EDP768I - 912300024911


Polar Normal (separate) - EDP768I - 912300024910

Heritage LED retrofit kit


Polar Wide Diagrams




Polar Normal (separate) - EDP768I - 912300024913



Polar Normal (separate) - EDP768I - 912300024912



Polar Normal (separate) - EDP768I - 912300024914



Polar Normal (separate) - EDP768I - 912300024915

