



Powerful, Comprehensive and Reliable

GreenSpace Grid

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Grid product family offers a complete range of options with comprehensive control availability, optical solutions and powerful lumen outputs, meanwhile ensures the product reliability and quality within compact luminaire body.

Benefits

- Comprehensive offerings to meet various application requirements.
- Compact body while delivering powerful lumen outputs.
- Good glare control with color rendering performance.
- Ensured quality and reliability.

Features

- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- Tilttable & rotatable
- UGR19 & CRI90

Application



- Retail
- Hospitality
- Fashion

Versions



GreenUp Grid

Dimensional drawing



| Light Technical | |
|-------------------------------------|-----------------|
| Color rendering index (CRI) | >90 |
| Operating and Electrical | |
| Protection class IEC | Safety class II |
| Input Voltage | 200 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Mechanical and Housing | |
| Optical cover type | Acrylate |
| Housing Color | White |
| Mech. impact protection code | IK03 |
| Ingress protection code | IP20 |
| Approval and Application | |
| Ambient temperature range | -20 to +40 °C |
| CE mark | No |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |

| Light Technical | | Correlated Color | Luminous Efficacy | Luminous Flux |
|-----------------|---------------------------|-------------------|-------------------|---------------|
| Order Code | Full Product Name | Temperature (Nom) | (rated) (Nom) | |
| 911401511312 | GD309B 3*P20 930 PSU-E MB | 3000 K | 90 lm/W | 5,400 lm |
| 911401511412 | GD309B 3*P20 930 PSU-E WB | 3000 K | 94 lm/W | 5,640 lm |
| 911401512012 | GD309B 3*P20 940 PSU-E NB | 4000 K | 96 lm/W | 5,760 lm |
| 911401512312 | GD309B 3*P20 940 PSU-E | 4000 K | 80 lm/W | 4,800 lm |
| | VWB | | | |
| 911401528112 | GD309B 3*P24 940 PSU-E MB | 4000 K | 93 lm/W | 6,700 lm |
| 911401559312 | GD309B 3*P33 930 PSU-E MB | 3000 K | 86 lm/W | 8,510 lm |
| 911401560212 | GD309B 3*P33 940 PSU-E WB | 4000 K | 98 lm/W | 9,700 lm |
| 911401572012 | GD309B 3*P33 940 PSD-E NB | 4000 K | 95 lm/W | 9,410 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|--------------|----------------------------|-------------------|
| 911401511312 | GD309B 3*P20 930 PSU-E MB | 54 W |
| 911401511412 | GD309B 3*P20 930 PSU-E WB | 54 W |
| 911401512012 | GD309B 3*P20 940 PSU-E NB | 54 W |
| 911401512312 | GD309B 3*P20 940 PSU-E VWB | 54 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------|-------------------|
| 911401528112 | GD309B 3*P24 940 PSU-E MB | 64.8 W |
| 911401559312 | GD309B 3*P33 930 PSU-E MB | 108.9 W |
| 911401560212 | GD309B 3*P33 940 PSU-E WB | 108.9 W |
| 911401572012 | GD309B 3*P33 940 PSD-E NB | 108.9 W |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|----------------------------|----------|
| 911401511312 | GD309B 3*P20 930 PSU-E MB | No |
| 911401511412 | GD309B 3*P20 930 PSU-E WB | No |
| 911401512012 | GD309B 3*P20 940 PSU-E NB | No |
| 911401512312 | GD309B 3*P20 940 PSU-E VWB | No |

| Order Code | Full Product Name | Dimmable |
|--------------|---------------------------|----------|
| 911401528112 | GD309B 3*P24 940 PSU-E MB | No |
| 911401559312 | GD309B 3*P33 930 PSU-E MB | No |
| 911401560212 | GD309B 3*P33 940 PSU-E WB | No |
| 911401572012 | GD309B 3*P33 940 PSD-E NB | Yes |

