



The new classic light bulb

Halogen Classic A-shape

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Benefits

- Identical look and feel to standard lamp, with bright, sparkling halogen light
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Double the lifetime of a standard bulb and immediate light when switching on

Features

- Superior quality of light with excellent colour rendering ($R_{a} \geq 100$)
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

Application

- Accent and general lighting applications in homes, offices, shops, hotels and restaurants. Replacement for traditional bulb in classical luminaires


Halogen Classic A-shape

Versions



LPPR ECOCLAB 0007

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 105W B22 240V A55 FR 1CT/10	56 mm	95.5 mm
EcoClassic 140W B22 240V A55 FR 1CT/10	56 mm	95.5 mm

General Information

Cap-Base	B22
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL

Light Technical

Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100

Operating and Electrical

Warm-up time to 60% light	instant full light s
Voltage (Nom)	240 V
Starting Time (Nom)	0.0 s

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A55

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	18.9 lm/W	1,980 lm
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	20.3 lm/W	2,840 lm

Operating and Electrical

Halogen Classic A-shape

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	0.44 A	105 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	0.58 A	140 W

