



Instant heat exactly where and when needed

Infrared Lamps Industrial Use

Philips infrared incandescent reflector lamps are designed to work in the toughest environments, such as farms, bathrooms or kitchens and their nearest surrounding. They have a reinforced construction thanks to the use of hard glass. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. Philips infrared lamps provide direct, draught-free warmth to the animals, and also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Benefits

- 30% extra energy saving with PAR thanks to its unique reflector system
- Simple and safe heat source with no risk of broken glass
- 90% of energy is transmitted as infrared heat.

Features

- Robust and sturdy hard glass construction of entire range of infrared reflectors.
- Reflector shape allows concentrated heat to be applied to where it is needed.
- The design of PAR38 incorporates a completely sealed reflector and therefore high efficiency.
- More hassle free and handy replacement period thanks to long durability of infrared lamps
- Red-coloured lamps to reduce visual light emission and glare.

Infrared Lamps Industrial Use

Application

- Agricultural: breeding and rearing of pigs, poultry, calves, foals, dogs etc. as well as in veterinary clinics, zoos, pet shops.
- General radiant heating, e.g. hot food displays, cooker hoods, bathrooms, space heating etc.
- Industrial heating, e.g. drying, baking, carbonising, melting etc.

Versions



BR125 IR 150W E27 230-250V Red



LPPR IRPR38 0001



LPPR IRSG E27 R125 Clear




PAR38 IR E27 Red



BR125 IR 250W E27 230-250V Red



Dimensional drawing



Product	D	C (max)	C1 (max)
PAR38 IR 175W E27 230V CL 1CT/12	121 mm	136 mm	124 mm
PAR38 IR 175W E27 230V Red 1CT/12	121 mm	136 mm	124 mm

Infrared Lamps Industrial Use

Dimensional drawing



Product	D	C (max)
BR125 IR 150W E27 230-250V Red 1CT/10	125 mm	173 mm
BR125 IR 250W E27 230-250V CL 1CT/10	125 mm	173 mm
BR125 IR 250W E27 230-250V Red 1CT/10	125 mm	173 mm

Product	D	C (max)
R125 IR 375W E27 230-250V CL 1CT/10	125 mm	183 mm

General Information

Cap base	E27
Rated Lifetime (Hours)	5,000 h
Nominal lifetime	5,000 h

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb material	Hard Glass
---------------	------------

General Information

Order Code	Full Product Name	Operating position
923211843801	BR125 IR 150W E27 230-250V Red 1CT/10	H45
923801344209	PAR38 IR 175W E27 230V CL 1CT/12	UNIVERSAL
923212143801	BR125 IR 250W E27 230-250V CL 1CT/10	UNIVERSAL

Order Code	Full Product Name	Operating position
923223543807	R125 IR 375W E27 230-250V CL 1CT/10	UNIVERSAL
923801444210	PAR38 IR 175W E27 230V Red 1CT/12	H45
923212043801	BR125 IR 250W E27 230-250V Red 1CT/10	H45

Light Technical

Order Code	Full Product Name	Colour designation
923211843801	BR125 IR 150W E27 230-250V Red 1CT/10	-
923801344209	PAR38 IR 175W E27 230V CL 1CT/12	C
923212143801	BR125 IR 250W E27 230-250V CL 1CT/10	-

Order Code	Full Product Name	Colour designation
923223543807	R125 IR 375W E27 230-250V CL 1CT/10	-
923801444210	PAR38 IR 175W E27 230V Red 1CT/12	R
923212043801	BR125 IR 250W E27 230-250V Red 1CT/10	-

Operating and Electrical

Infrared Lamps Industrial Use

Order Code	Full Product Name	Voltage (nom.)	Power	
			Consumption	
923211843801	BR125 IR 150W E27 230-250V Red 1CT/10	230-250 V	150 W	
923801344209	PAR38 IR 175W E27 230V CL 1CT/12	230 V	175 W	
923212143801	BR125 IR 250W E27 230-250V CL 1CT/10	230-250 V	250 W	

Order Code	Full Product Name	Voltage (nom.)	Power	
			Consumption	
923223543807	R125 IR 375W E27 230-250V CL 1CT/10	230-250 V	375 W	
923801444210	PAR38 IR 175W E27 230V Red 1CT/12	230 V	175 W	
923212043801	BR125 IR 250W E27 230-250V Red 1CT/10	230-250 V	250 W	

Mechanical and Housing

Order Code	Full Product Name	Lamp Finish	Bulb shape
923211843801	BR125 IR 150W E27 230-250V Red 1CT/10	Red	BR125
923801344209	PAR38 IR 175W E27 230V CL 1CT/12	Clear	PAR38
923212143801	BR125 IR 250W E27 230-250V CL 1CT/10	Clear	BR125

Order Code	Full Product Name	Lamp Finish	Bulb shape
923223543807	R125 IR 375W E27 230-250V CL 1CT/10	Clear	R125
923801444210	PAR38 IR 175W E27 230V Red 1CT/12	Red	PAR38
923212043801	BR125 IR 250W E27 230-250V Red 1CT/10	Red	BR125

