

**PHILIPS**

**Lighting**



# Product Description

## Standard A-shape clear

Conventional pear-shaped incandescent lamps

### Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect

### Features

- Vacuum-filled (15W) or gas-filled (25W and above)

### Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare


### Versions



LED Lamps, CorePro LEDspotMV E27 R80

# Standard A-shape clear

## Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 220V A55 CL U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 60W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm

General Information	
Cap-Base	E27
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

## General Information

Order Code	Full Product Name	Rated Lifetime (Hours)
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	-
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	-

Order Code	Full Product Name	Rated Lifetime (Hours)
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	1,000 hour(s)

## Light Technical

Order Code	Full Product Name	Luminous Flux
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	710 lm
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	1,340 lm

Order Code	Full Product Name	Luminous Flux
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	710 lm

## Operating and Electrical

Order Code	Full Product Name	Power	
		Voltage (Nom)	Consumption
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	220-240 V	60 W
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	220 V	100 W

Order Code	Full Product Name	Power	
		Voltage (Nom)	Consumption
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	230 V	60 W

## Standard A-shape clear



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)  
2025, December 13 - data subject to change