



# Rough Service Incandescent Lamps

## Rough / Vibration Service

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

### Benefits

- An exceptionally strong filament resists shocks, bumps and vibrations.

### Features

- Rugged design resists vibration.
- Incandescent, vacuum or gas-filled lamp with clear or inside-frosted bulb.
- Single coil filament.
- Medium or mogul screw base.
- Available in 60W and 75W versions in clear and frosted. Also available in 100W TuffGuard version.

### Application

- Ideal for use in worklights and other fixtures subject to rough handling. Suited for Ships, engine rooms, mines, elevators public transport buses and trains and other industrial applications.


## Rough / Vibration Service

### Versions



LPPR I-A19 FR

### Dimensional drawing



A19

Product	D	C (max)
100A/2P/RS 12/2	2.375 inch	4.438 inch
50A/2P/RS 12/2 PK	2.375 inch	4.438 inch



## Rough / Vibration Service

### General Information

Cap-Base	E26
Rated Lifetime (Hours)	2.000 hour(s)
Operating Position	UNIVERSAL

### Operating and Electrical

Voltage (Nom)	130 V
---------------	-------

### Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A19

### Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
925278036104	50A/2P/RS 12/2 PK	50 W	925283534304	100A/2P/RS 12/2	100 W

