



LED Lamps – ideal for general lighting applications

LED Lamps

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Benefits

- Color temperature suitable for both functional lighting and to enhance atmosphere
- Color temperature suitable for both functional lighting and to enhance atmosphere
- Up to 80% energy savings compared with incandescent bulbs
- Up to 80% energy savings compared with incandescent bulbs
- Suitable for retrofit
- Suitable for retrofit
- Lower maintenance costs
- Lower maintenance costs

Features

- Long lifetime
- Long lifetime
- UV- and IR-free light for less heat and protection of heat-sensitive objects
- UV- and IR-free light for less heat and protection of heat-sensitive objects
- Instant start
- Instant start

LED Lamps

Application

- Homes, hotels, restaurants, cafes
- Homes, hotels, restaurants, cafes
- Bedroom, dining room, living room, study room
- Bedroom, dining room, living room, study room

Versions



CorePro LEDbulb 150W E27 827 FR
A80




LEDbulb CorePro 9.5-68W E27
Stick Frost 830 24D ND



27W E27 A67 FR




Dimensional drawing



Product	D	C
LEDBulb 19W E27 6500K 230VA80 1CT/6APR	80 mm	155 mm

LED Lamps

Dimensional drawing



Product	D	C
LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	68 mm	132 mm

Product	D	C
LEDStick 9.5W B22 3000K 1PF/6 AU	37.2 mm	113 mm
LEDStick 9.5W B22 6500K 1PF/6 AU	37.2 mm	113 mm

Product	D	C
LEDStick 9.5W E27 3000K 1PF/6 AU	37.2 mm	114.3 mm
LEDStick 9.5W E27 6500K 1PF/6 AU	37.2 mm	114.3 mm

LED Lamps

General Information	
Switching Cycle	50,000
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime	
			(Hours)	Nominal lifetime
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	E27	12,000 hour(s)	25,000 hour(s)
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	E27	15,000 hour(s)	15,000 hour(s)
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	E27	15,000 hour(s)	15,000 hour(s)
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	E27	12,000 hour(s)	25,000 hour(s)
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	B22	15,000 hour(s)	15,000 hour(s)
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	B22	15,000 hour(s)	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	150 degree(s)	6500 K	865	2,300 lm
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	200 degree(s)	3000 K	830	950 lm
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	200 degree(s)	6500 K	865	1,050 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	150 degree(s)	3000 K	830	1,650 lm
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	200 degree(s)	3000 K	830	950 lm
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	200 degree(s)	6500 K	865	1,050 lm

Operating and Electrical

Order Code	Full Product Name	Power	
		Consumption	Wattage Equivalent
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	19 W	160 W
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	9.5 W	68 W
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	9.5 W	75 W

Order Code	Full Product Name	Power	
		Consumption	Wattage Equivalent
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	14.5 W	120 W
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	9.5 W	68 W
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	9.5 W	75 W

Temperature

LED Lamps


Order Code	Full Product Name	T-Case Maximum (Nom)
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	90 °C
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	85 °C
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	85 °C
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	90 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	A80
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	Stick
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	Stick


Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	19 kWh
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	10 kWh
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	10 kWh
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	15 kWh
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	10 kWh
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	10 kWh



Order Code	Full Product Name	T-Case Maximum (Nom)
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	85 °C
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	85 °C

Order Code	Full Product Name	Bulb Shape
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	A67
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	Stick
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	Stick



LED Lamps

