



Guaranteed performance, thinking ahead

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- Freedom of (re-)positioning enables you to direct the light where needed
- Family of fixtures to create the desired atmosphere; wide variety of beam shapes to suit diversity of applications
- With up to 13-wire track, emergency lighting and third-party hardware can be integrated to declutter ceilings

Applications

- (Food) retail
- Industrial halls/areas
- Warehouses/distribution centers

Features


- Track system inside the trunk with up to 13 wires
- High uniformity and artefact-free light distributions
- Linear fixtures, non-linear fixtures and spots can be easily installed onto the trunk
- Eight optics, including (double) asymmetric distributions and a frosted cover
- IP54 optional, silicone-free
- StoreWise, Indoor Positioning and GreenWarehouse-ready

Versions



Maxos Fusion Panel-LL523X
 WB WH

Dimensional drawing



Maxos fusion Panel - 840 neutral white - Power supply unit with DALI interface - Wide beam - White

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Light Technical	
Luminous Flux	12,300 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	181 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Optic type	Wide beam
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	68 W
Suitable for random switching	Not applicable
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +35 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34. 0.35) SDCM <3

Product Data

Product family code	LL523X [Maxos fusion Panel]
---------------------	-----------------------------

Polar normal diagrams



LL500XI - 910925867816

