



New standard in trunking

Maxos unify

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with an optimal number of linear panels and a solution for retrofitting old installations – Bringing your application right up to date with the latest lighting possibilities. Now and in the future.

Benefits

- Simple retrofit of 'old' Maxos and TTX400 electrical units with significant energy savings using the UE portfolio
- Upgrade to Interact systems to unlock greater savings
- Flexible trunking infrastructure with a solution for all electrical scenarios and more
- Reliable and long-lasting performance across the full offer

Features

- Simplified panel offer → 1.5 m and 2.25 m constructed from modular components.
- High efficacy up to 200 lm/W in UE range
- Lumen maintenance L85 100,000 hrs across the range
- Dedicated sensor units to upgrade to Interact system propositions

Application

- Food and large retailers
- Manufacturing
- Warehouses

Maxos unify

Versions



Maxos unify panel for 4MX656
trunk white






Maxos unify panel 2215mm for
track white



Maxos unify panel for track black

Dimensional drawing



Maxos unify

Product details



Maxos unify optical design

General Information					
Driver included					Yes
Number of gear units					Unit
Light Technical					
Order Code	Full Product Name		Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
95516500	LL553X 40S/840 UE DIA WB WH		195 lm/W	4,000 lm	Wide beam
95519600	LL553X 105S/840 UE DIA NB WH		191 lm/W	10,500 lm	Narrow beam
95506600	LL552X 160S/840 UE DIA NB WH		191 lm/W	16,000 lm	Narrow beam
95509700	LL552X 62S/840 UE SIA WB WH		197 lm/W	6,200 lm	Wide beam
95499100	LL551X 40S/840 UE DIA WB BK		195 lm/W	4,000 lm	Wide beam
95502800	LL551X 105S/840 UE DIA NB BK		191 lm/W	10,500 lm	Narrow beam
Operating and Electrical					
Protection class IEC	Safety class I				
Input Voltage	220-240 V				
Line Frequency	50 to 60 Hz				
Suitable for random switching	Not applicable				
Controls and Dimming					
Dimmable	Yes				
Maximum dim level	1%				
Mechanical and Housing					
Mech. impact protection code	IK02				
Ingress protection code	IP20				
Emergency Operation					
Central Emergency	No				
Approval and Application					
Ambient temperature range	-20 to +35 °C				
CE mark	Yes				
ENEC mark	ENEC mark				
Flammability mark	For mounting on normally flammable surfaces				
Glow-wire test	Temperature 850 °C, duration 30 s				
Initial Performance (IEC Compliant)					
Initial chromaticity	(0.34. 0.35) SDCM				
	<3				
Luminous flux tolerance	+/-7%				

Operating and Electrical

Order Code	Full Product Name	Power Consumption
95516500	LL553X 40S/840 UE DIA WB WH	20.5 W
95519600	LL553X 105S/840 UE DIA NB WH	55 W
95506600	LL552X 160S/840 UE DIA NB WH	84 W

Order Code	Full Product Name	Power Consumption
95509700	LL552X 62S/840 UE SIA WB WH	31.5 W
95499100	LL551X 40S/840 UE DIA WB BK	20.5 W
95502800	LL551X 105S/840 UE DIA NB BK	55 W

Mechanical and Housing

Order Code	Full Product Name	Housing Colour
95516500	LL553X 40S/840 UE DIA WB WH	White
95519600	LL553X 105S/840 UE DIA NB WH	White
95506600	LL552X 160S/840 UE DIA NB WH	White


Order Code	Full Product Name	Housing Colour
95509700	LL552X 62S/840 UE SIA WB WH	White
95499100	LL551X 40S/840 UE DIA WB BK	Black
95502800	LL551X 105S/840 UE DIA NB BK	Black

Product Data


Order Code	Full Product Name	Product family code
95516500	LL553X 40S/840 UE DIA WB WH	LL553X
95519600	LL553X 105S/840 UE DIA NB WH	LL553X
95506600	LL552X 160S/840 UE DIA NB WH	LL552X

Order Code	Full Product Name	Product family code
95509700	LL552X 62S/840 UE SIA WB WH	LL552X
95499100	LL551X 40S/840 UE DIA WB BK	LL551X
95502800	LL551X 105S/840 UE DIA NB BK	LL551X


Polar Wide Diagrams




Polar Normal (separate) - LL550XI -
910925870856




Polar Normal (separate) - LL550XI -
910925870849




Polar Normal (separate) - LL550XI -
910925870853



Polar Normal (separate) - LL550XI -
910925870846



Polar Normal (separate) - LL550XI -
910925870866



Polar Normal (separate) - LL550XI -
910925870863

