



# MASTER LEDspot LV - The ideal solution for spot lighting

## MASTER VALUE LED spot LV

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Benefits

- Up to 80% energy saving compared with halogen lamp
- Broad compatibility with transformers
- Retrofittable with low-voltage MR16 halogen lamps with GU5.3 socket

### Features

- dimmable (the 7-35W and 10-50W versions)
- patented intelligent driver
- air movement mechanism (active fan cooling) with very low sound levels
- lifetime of 25,000 to 45,000 hours
- CRI90 (MR11 only)

### Application

- Ideal for accent lighting in hotels, hospitals, shops and museums (e.g. floors, elevators, displays)

# MASTER VALUE LED spot LV

## Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

## Versions





MASTER LED 5.5-50W MR16 GU5.3



LEDspots MAS SLR 2 MR11 GU4

## Dimensional drawing





Product	D	C
MASTER LED 5.5-50W 2700K MR16 36D	50.2 mm	49 mm

Product	D	C
MAS LED SPOT VLE D 7.5-50W MR16 927 36D	50.5 mm	45.5 mm
MAS LED SPOT VLE D 7.5-50W MR16 927 60D	50.5 mm	45.5 mm
MAS LED SPOT VLE D 7.5-50W MR16 930 36D	50.5 mm	45.5 mm
MAS LED SPOT VLE D 7.5-50W MR16 930 60D	50.5 mm	45.5 mm
MAS LED SPOT VLE D 7.5-50W MR16 940 36D	50.5 mm	45.5 mm
MAS LED SPOT VLE D 7.5-50W MR16 940 60D	50.5 mm	45.5 mm
MAS LED spot VLE D 5.8-35W MR16 927 36D	50.5 mm	45.5 mm

# MASTER VALUE LED spot LV

## Dimensional drawing



Product	D	C
MAS LEDspotLV 3.5-20W 827 MR11 24D	35.1 mm	39.5 mm

Product	D	C
MASTER LED 3.9-35W 2700K MR16 24D	50.5 mm	50 mm
MASTER LED 3.9-35W 2700K MR16 36D	50.5 mm	50 mm
MASTER LED 3.9-35W 3000K MR16 24D	50.5 mm	50 mm
MASTER LED 3.9-35W 3000K MR16 36D	50.5 mm	50 mm
MASTER LED 4.9-50W 2700K MR16 24D	50.5 mm	50 mm
MASTER LED 4.9-50W 2700K MR16 36D	50.5 mm	50 mm
MASTER LED 4.9-50W 3000K MR16 24D	50.5 mm	50 mm
MASTER LED 4.9-50W 3000K MR16 36D	50.5 mm	50 mm
MASTER LED 4.9-50W 4000K MR16 24D	50.5 mm	50 mm
MASTER LED 4.9-50W 4000K MR16 36D	50.5 mm	50 mm

### General Information

Switching Cycle 50,000

### Light Technical

LLMF At End Of Nominal Lifetime (Nom) 70 %

### Operating and Electrical

Input Frequency - Hz  
Starting Time (Nom) 0.5 s

## General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	GU5.3	25,000 hour(s)
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	GU5.3	25,000 hour(s)
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	GU5.3	25,000 hour(s)
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	GU5.3	25,000 hour(s)
47603100	MASTER LED 5.5-50W 2700K MR16 36D	GU5.3	25,000 hour(s)
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	GU4	40,000 hour(s)
17446700	MASTER LED 3.9-35W 2700K MR16 24D	GU5.3	25,000 hour(s)
17448100	MASTER LED 3.9-35W 3000K MR16 24D	GU5.3	25,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
17450400	MASTER LED 3.9-35W 2700K MR16 36D	GU5.3	25,000 hour(s)
17452800	MASTER LED 3.9-35W 3000K MR16 36D	GU5.3	25,000 hour(s)
17454200	MASTER LED 4.9-50W 2700K MR16 24D	GU5.3	25,000 hour(s)
17456600	MASTER LED 4.9-50W 3000K MR16 24D	GU5.3	25,000 hour(s)
17458000	MASTER LED 4.9-50W 4000K MR16 24D	GU5.3	25,000 hour(s)
17460300	MASTER LED 4.9-50W 2700K MR16 36D	GU5.3	25,000 hour(s)
17462700	MASTER LED 4.9-50W 3000K MR16 36D	GU5.3	25,000 hour(s)
17464100	MASTER LED 4.9-50W 4000K MR16 36D	GU5.3	25,000 hour(s)
30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	GU5.3	25,000 hour(s)
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	GU5.3	25,000 hour(s)

# MASTER VALUE LED spot LV

Order Code	Full Product Name	Cap-Base	Nominal lifetime
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	GU5.3	25,000 hour(s)

## Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color rendering		Luminous Intensity	
			Temperature (Nom)	index (CRI)	Color Code	Luminous Flux (Nom)		
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	36 degree(s)	2700 K	90	927	450 lm	1,300 cd	
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	36 degree(s)	2700 K	90	927	621 lm	1,600 cd	
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	36 degree(s)	3000 K	90	930	630 lm	1,600 cd	
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	36 degree(s)	4000 K	90	940	660 lm	1,500 cd	
47603100	MASTER LED 5.5-50W 2700K MR16 36D	36 degree(s)	2700 K	80	827	415 lm	1,000 cd	
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	24 degree(s)	2700 K	80	827	200 lm	1,000 cd	
17446700	MASTER LED 3.9-35W 2700K MR16 24D	24 degree(s)	2700 K	90	927	270 lm	1,000 cd	
17448100	MASTER LED 3.9-35W 3000K MR16 24D	24 degree(s)	3000 K	90	930	280 lm	1,000 cd	
17450400	MASTER LED 3.9-35W 2700K MR16 36D	36 degree(s)	2700 K	90	927	270 lm	600 cd	
17452800	MASTER LED 3.9-35W 3000K MR16 36D	36 degree(s)	3000 K	90	930	280 lm	600 cd	
17454200	MASTER LED 4.9-50W 2700K MR16 24D	24 degree(s)	2700 K	90	927	415 lm	1,600 cd	
17456600	MASTER LED 4.9-50W 3000K MR16 24D	24 degree(s)	3000 K	90	930	425 lm	1,700 cd	
17458000	MASTER LED 4.9-50W 4000K MR16 24D	24 degree(s)	4000 K	90	940	430 lm	1,700 cd	
17460300	MASTER LED 4.9-50W 2700K MR16 36D	36 degree(s)	2700 K	90	927	415 lm	900 cd	
17462700	MASTER LED 4.9-50W 3000K MR16 36D	36 degree(s)	3000 K	90	930	425 lm	950 cd	
17464100	MASTER LED 4.9-50W 4000K MR16 36D	36 degree(s)	4000 K	90	940	430 lm	950 cd	
30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	60 degree(s)	2700 K	90	927	621 lm	750 cd	
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	60 degree(s)	3000 K	90	930	630 lm	800 cd	
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	60 degree(s)	4000 K	90	940	660 lm	770 cd	

## Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	- Hz	5.8 W	35 W	17450400	MASTER LED 3.9-35W 2700K MR16 36D	-	3.9 W	35 W
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	- Hz	7.5 W	50 W	17452800	MASTER LED 3.9-35W 3000K MR16 36D	-	3.9 W	35 W
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	- Hz	7.5 W	50 W	17454200	MASTER LED 4.9-50W 2700K MR16 24D	-	4.9 W	50 W
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	- Hz	7.5 W	50 W	17456600	MASTER LED 4.9-50W 3000K MR16 24D	-	4.9 W	50 W
47603100	MASTER LED 5.5-50W 2700K MR16 36D	- Hz	5.5 W	50 W	17458000	MASTER LED 4.9-50W 4000K MR16 24D	-	4.9 W	50 W
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	- Hz	3.5 W	20 W	17460300	MASTER LED 4.9-50W 2700K MR16 36D	-	4.9 W	50 W
17446700	MASTER LED 3.9-35W 2700K MR16 24D	-	3.9 W	35 W	17462700	MASTER LED 4.9-50W 3000K MR16 36D	-	4.9 W	50 W
17448100	MASTER LED 3.9-35W 3000K MR16 24D	-	3.9 W	35 W	17464100	MASTER LED 4.9-50W 4000K MR16 36D	-	4.9 W	50 W
					30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	- Hz	7.5 W	50 W

## MASTER VALUE LED spot LV

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	- Hz	7.5 W	50 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	- Hz	7.5 W	50 W

### Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	85 °C
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	95 °C
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	95 °C
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	95 °C
47603100	MASTER LED 5.5-50W 2700K MR16 36D	95 °C
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	85 °C
17446700	MASTER LED 3.9-35W 2700K MR16 24D	68 °C
17448100	MASTER LED 3.9-35W 3000K MR16 24D	68 °C
17450400	MASTER LED 3.9-35W 2700K MR16 36D	68 °C
17452800	MASTER LED 3.9-35W 3000K MR16 36D	68 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
17454200	MASTER LED 4.9-50W 2700K MR16 24D	72 °C
17456600	MASTER LED 4.9-50W 3000K MR16 24D	72 °C
17458000	MASTER LED 4.9-50W 4000K MR16 24D	72 °C
17460300	MASTER LED 4.9-50W 2700K MR16 36D	72 °C
17462700	MASTER LED 4.9-50W 3000K MR16 36D	72 °C
17464100	MASTER LED 4.9-50W 4000K MR16 36D	72 °C
30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	95 °C
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	95 °C
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	95 °C

### Controls and Dimming

Order Code	Full Product Name	Dimmable
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	Only with specific dimmers
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	Only with specific dimmers
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	Only with specific dimmers
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	Only with specific dimmers
47603100	MASTER LED 5.5-50W 2700K MR16 36D	No
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	No
17446700	MASTER LED 3.9-35W 2700K MR16 24D	No
17448100	MASTER LED 3.9-35W 3000K MR16 24D	No
17450400	MASTER LED 3.9-35W 2700K MR16 36D	No

Order Code	Full Product Name	Dimmable
17452800	MASTER LED 3.9-35W 3000K MR16 36D	No
17454200	MASTER LED 4.9-50W 2700K MR16 24D	No
17456600	MASTER LED 4.9-50W 3000K MR16 24D	No
17458000	MASTER LED 4.9-50W 4000K MR16 24D	No
17460300	MASTER LED 4.9-50W 2700K MR16 36D	No
17462700	MASTER LED 4.9-50W 3000K MR16 36D	No
17464100	MASTER LED 4.9-50W 4000K MR16 36D	No
30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	Only with specific dimmers
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	Only with specific dimmers
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	Only with specific dimmers

### Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	Clear	MR16
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	Clear	MR16
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	Clear	MR16
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	Clear	MR16
47603100	MASTER LED 5.5-50W 2700K MR16 36D	-	MR16
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	Clear	MR11
17446700	MASTER LED 3.9-35W 2700K MR16 24D	Clear	MR16
17448100	MASTER LED 3.9-35W 3000K MR16 24D	Clear	MR16

Order Code	Full Product Name	Bulb Finish	Bulb Shape
17450400	MASTER LED 3.9-35W 2700K MR16 36D	Clear	MR16
17452800	MASTER LED 3.9-35W 3000K MR16 36D	Clear	MR16
17454200	MASTER LED 4.9-50W 2700K MR16 24D	Clear	MR16
17456600	MASTER LED 4.9-50W 3000K MR16 24D	Clear	MR16
17458000	MASTER LED 4.9-50W 4000K MR16 24D	Clear	MR16
17460300	MASTER LED 4.9-50W 2700K MR16 36D	Clear	MR16
17462700	MASTER LED 4.9-50W 3000K MR16 36D	Clear	MR16
17464100	MASTER LED 4.9-50W 4000K MR16 36D	Clear	MR16
30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	Clear	MR16





# MASTER VALUE LED spot LV

Order Code	Full Product Name	Bulb Finish	Bulb Shape
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	Clear	MR16











Order Code	Full Product Name	Bulb Finish	Bulb Shape
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	Clear	MR16

## Approval and Application






Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
30718600	MASTER LED spot VLE D 5.8-35W MR16 927 36D	-20 to +40 °C	6 kWh
30732200	MASTER LED SPOT VLE D 7.5-50W MR16 927 36D	-20 to +40 °C	8 kWh
30734600	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D	-20 to +40 °C	8 kWh
30736000	MASTER LED SPOT VLE D 7.5-50W MR16 940 36D	-20 to +40 °C	8 kWh
47603100	MASTER LED 5.5-50W 2700K MR16 36D	-20 to +45 °C	-
35990100	MASTER LEDspotLV 3.5-20W 827 MR11 24D	-20 to +45 °C	4 kWh
17446700	MASTER LED 3.9-35W 2700K MR16 24D	-20 to +45 °C	-
17448100	MASTER LED 3.9-35W 3000K MR16 24D	-20 to +45 °C	-
17450400	MASTER LED 3.9-35W 2700K MR16 36D	-20 to +45 °C	-
17452800	MASTER LED 3.9-35W 3000K MR16 36D	-20 to +45 °C	-
17454200	MASTER LED 4.9-50W 2700K MR16 24D	-20 to +45 °C	-
17456600	MASTER LED 4.9-50W 3000K 20 to +45 °C MR16 24D	-20 to +45 °C	-
17458000	MASTER LED 4.9-50W 4000K MR16 24D	-20 to +45 °C	-
17460300	MASTER LED 4.9-50W 2700K MR16 36D	-20 to +45 °C	-
17462700	MASTER LED 4.9-50W 3000K MR16 36D	-20 to +45 °C	-
17464100	MASTER LED 4.9-50W 4000K MR16 36D	-20 to +45 °C	-
30738400	MASTER LED SPOT VLE D 7.5-50W MR16 927 60D	-20 to +40 °C	8 kWh
30740700	MASTER LED SPOT VLE D 7.5-50W MR16 930 60D	-20 to +40 °C	8 kWh
30742100	MASTER LED SPOT VLE D 7.5-50W MR16 940 60D	-20 to +40 °C	8 kWh






# MASTER VALUE LED spot LV



# MASTER VALUE LED spot LV



## Accent Diagrams




Accent Diagram - MASTER LED 4.9-50W 2700K MR16 36D

Accent Diagram - MASTER LED 4.9-50W 2700K MR16 24D


Accent Diagram - MASTER LED 4.9-50W 3000K MR16 36D

# MASTER VALUE LED spot LV


## Accent Diagrams




Accent Diagram - MAS LED SPOT VLE D  
7.5-50W MR16 927 60D




Accent Diagram - MASTER LED 5.5-50W 2700K  
MR16 36D




Accent Diagram - MASTER LED 3.9-35W 2700K  
MR16 24D




Accent Diagram - MAS LED SPOT VLE D  
7.5-50W MR16 930 36D




Accent Diagram - MASTER LED 3.9-35W 3000K  
MR16 24D




Accent Diagram - MAS LED SPOT VLE D  
7.5-50W MR16 940 36D



Accent Diagram - MASTER LED 3.9-35W 3000K  
MR16 36D




Accent Diagram - MASTER LED 3.9-35W 2700K  
MR16 36D




Accent Diagram - MAS LED spot VLE D 5.8-35W  
MR16 927 36D

# MASTER VALUE LED spot LV


## Accent Diagrams




Accent Diagram - MASTER LED 4.9-50W  
4000K MR16 24D




Accent Diagram - MAS LEDspotLV 3.5-20W 827  
MR11 24D




Accent Diagram - MAS LED SPOT VLE D  
7.5-50W MR16 930 60D




Accent Diagram - MASTER LED 4.9-50W  
4000K MR16 36D



Accent Diagram - MASTER LED 4.9-50W  
3000K MR16 24D




Accent Diagram - MAS LED SPOT VLE D  
7.5-50W MR16 940 60D




Accent Diagram - MAS LED SPOT VLE D  
7.5-50W MR16 927 36D

# MASTER VALUE LED spot LV


## Beam Diagrams




Beam diagram - MAS LED SPOT VLE D 7.5-50W MR16 927 36D




Beam diagram - MASTER LED 4.9-50W 3000K MR16 24D




Beam diagram - MASTER LED 5.5-50W 2700K MR16 36D




Beam diagram - MASTER LED 4.9-50W 4000K MR16 24D




Beam diagram - MASTER LED 3.9-35W 3000K MR16 24D




Beam diagram - MAS LED SPOT VLE D 7.5-50W MR16 940 60D



Beam diagram - MASTER LED 4.9-50W 4000K MR16 36D




Beam diagram - MASTER LED 4.9-50W 3000K MR16 36D




Beam diagram - MASTER LED 3.9-35W 3000K MR16 36D


## Beam Diagrams




Beam diagram - MASTER LED 4.9-50W 2700K MR16 36D




Beam diagram - MAS LED SPOT VLE D 7.5-50W MR16 940 36D




Beam diagram - MASTER LED 3.9-35W 2700K MR16 36D




Beam diagram - MASTER LED 3.9-35W 2700K MR16 24D




Beam diagram - MAS LED SPOT VLE D 7.5-50W MR16 927 60D




Beam diagram - MASTER LED 4.9-50W 2700K MR16 24D



Beam diagram - MAS LEDspotLV 3.5-20W 827 MR11 24D




Beam diagram - MAS LED SPOT VLE D 7.5-50W MR16 930 60D



Beam diagram - MAS LED SPOT VLE D 7.5-50W MR16 930 36D

# MASTER VALUE LED spot LV

## Beam Diagrams



Beam diagram - MAS LED spot VLE D 5.8-35W  
MR16 927 36D

