



A small and sustainable pendant in a sleek, subtle design

GreenSpace Evo Mini Pendant

GreenSpace Evo Mini Pendant is a sustainable lighting pendant that comes with a sleek and subtle design. This makes the pendant an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini pendant a sustainable choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customisation of colours and textures is possible via Philips MyCreation

Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Pendant

Features

- Easy access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down

Versions



PT332B GreenSpace Evo Mini
Pendant Recessed - White



PT332C GreenSpace Evo Mini
Pendant Surface mount - Black



PT332B GreenSpace Evo Mini
Pendant Recessed - Black



PT332T GreenSpace Evo Mini
Pendant Track - White

GreenSpace Evo Mini Pendant

Versions






PT332B GreenSpace Evo Mini
Pendant Recessed - Black with
White canopy



PT332C GreenSpace Evo Mini
Pendant Surface mount - White

Dimensional drawing



GreenSpace Evo Mini Pendant

General Information

Driver included	Yes
Number of gear units	Unit

Light Technical

Colour rendering index (CRI)	>90
------------------------------	-----

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Controls and Dimming

Embedded control	-
------------------	---

Mechanical and Housing

Explosion hazard class	-
Mech. impact protection code	IK02
Ingress protection code	IP20

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM)	1

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Correlated				Optic type
		Colour Temperature (Nom)	Luminous efficacy (rated) (nom.)	Luminous Flux		
910505104926	PT332T 12S/PW940 PSU HWB BK	4000 K	124 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees	
910505104929	PT332T 17S/PW930 DIA HVWB BK	3000 K	128 lm/W	1,700 lm	High-reflective metal reflector very wide beam >80 degrees	
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	4000 K	135 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees	
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	3000 K	143 lm/W	1,700 lm	High-reflective metal reflector very wide beam >80 degrees	
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	3000 K	143 lm/W	1,700 lm	High-reflective metal reflector very wide beam >80 degrees	
910505104932	PT332T 27S/PW940 WIA HWB WH	4000 K	122 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees	
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	4000 K	121 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees	
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	3000 K	121 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees	
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	4000 K	135 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees	

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505104926	PT332T 12S/PW940 PSU HWB BK	9.7 W
910505104929	PT332T 17S/PW930 DIA HVWB BK	13.3 W
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	20 W
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	11.9 W
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	11.9 W

Order Code	Full Product Name	Power Consumption
910505104932	PT332T 27S/PW940 WIA HWB WH	22.2 W
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	9.9 W
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	9.9 W
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	20 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104926	PT332T 12S/PW940 PSU HWB BK	No
910505104929	PT332T 17S/PW930 DIA HVWB BK	Yes
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	Yes
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	Yes
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	Yes

Order Code	Full Product Name	Dimmable
910505104932	PT332T 27S/PW940 WIA HWB WH	Yes
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	No
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	No
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	Yes

GreenSpace Evo Mini Pendant

Mechanical and Housing

Order Code	Full Product Name	Housing Colour
910505104926	PT332T 12S/PW940 PSU HWB BK	Black
910505104929	PT332T 17S/PW930 DIA HVWB BK	Black
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	White
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	Black
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	Black

Order Code	Full Product Name	Housing Colour
910505104932	PT332T 27S/PW940 WIA HWB WH	White
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	Black
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	White
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	White

Approval and Application

Order Code	Full Product Name	Stroboscopic effect
910505104926	PT332T 12S/PW940 PSU HWB BK	0.4
910505104929	PT332T 17S/PW930 DIA HVWB BK	0.4
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	0.5
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	0.4
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	0.4

Order Code	Full Product Name	Stroboscopic effect
910505104932	PT332T 27S/PW940 WIA HWB WH	0.4
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	0.4
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	0.4
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	0.5

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104926	PT332T 12S/PW940 PSU HWB BK	(0.374, 0.364)
910505104929	PT332T 17S/PW930 DIA HVWB BK	(0.422, 0.386)
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	(0.374, 0.364)
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	(0.422, 0.386)
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	(0.422, 0.386)


Order Code	Full Product Name	Initial chromaticity
910505104932	PT332T 27S/PW940 WIA HWB WH	(0.374, 0.364)
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	(0.374, 0.364)
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	(0.422, 0.386)
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	(0.374, 0.364)

Product Data


Order Code	Full Product Name	Product family code
910505104926	PT332T 12S/PW940 PSU HWB BK	PT332T
910505104929	PT332T 17S/PW930 DIA HVWB BK	PT332T
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	PT332B
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	PT332C
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	PT332B

Order Code	Full Product Name	Product family code
910505104932	PT332T 27S/PW940 WIA HWB WH	PT332T
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	PT332B
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	PT332C
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	PT332C


Polar Wide Diagrams



Polar Normal (separate) - PT332TI -
910505104926




Polar Normal (separate) - PT332TI -
910505104950




Polar Normal (separate) - PT332TI -
910505104932

GreenSpace Evo Mini Pendant


Polar Wide Diagrams




Polar Normal (separate) - PT332TI -
910505104929




Polar Normal (separate) - PT332TI -
910505104938




Polar Normal (separate) - PT332TI -
910505104947



Polar Normal (separate) - PT332TI -
910505104944



Polar Normal (separate) - PT332TI -
910505104934



Polar Normal (separate) - PT332TI -
910505104941

