



Ledinaire RC065B, panel – egyszerűen nagyszerű LED

A Ledinaire termékcsalád egyszerűen megvásárolható, népszerű LED-es termékeket tartalmaz, melyek kimagasló Philips minőségben kaphatók, versenyképes áron, különböző alkalmazási területekre. Megbízható, energiatakarékos és megfizethető – pontosan azt tudja, amire szüksége van.

Előnyök

- Philips minőség és megbízhatóság
- Magas energiamegtakarítás
- Kellemes szórt fény

Applications

- Irodák
- Egészségügy

- Oktatás
- Önkormányzati épületek
- Üzletek


Szolgáltatások

- Kaphatók gipszkartonba-, felületre és függesztett szereléshez való tartozékok
- Modern, diszkrét forma

Versions


	Ledinaire Panel PSD All-in 830_835_840 W60L60 OC		Ledinaire panel G5 60x120
	Ledinaire Panel PSU All-in 830_835_840 W60L60 OC		Ledinaire Panel All-in PSU 60x60
	Ledinaire panel G5 60x60		Ledinaire Panel G5 All in W30L120 RTP

Méretezett rajza




RC065B G5 34_36S/830_40 PSU W60L60 OC SC



RC065B G5 34S/840 PSU W60L60 NOC SC



RC065B G5 34_36S/830_40 PSU 60x60 NOC SC




RC065B G5 41S/840 PSU W60L60 NOC CFW CL




RC065B G5 34S/840 PSU W60L60 OC SC


RC065B G5 34S/840 PSD W60L60 OC SC



RC065B G5 34S/840 PSU W60L60 OC CFW CL



RC065B G5 34_36S/830_40 PSD W60L60 OC SC



RC065B G5 34S/840 PSD W60L60 OC CFW



RC065B G5 60S/840 PSU 60x120 NOC TPb CFW



RC065B G5 34_36S/830_40 PSU 30x120 OC SC


Termék részletei



Ledinaire Panel G5 All in CCT
Switch 3000K



Ledinaire Panel G5 Back
housing PSU Flywire (CFW)



White Quick connector-closed



Panel flywires CFW + backside panel




Ledinaire Panel G5 All in CCT Switch PSU ON OFF Driver Open connector



Ledinaire Panel G5 PSD DALI Driver Open connector




Ledinaire Panel G5 All in CCT Switch PSD ON OFF Driver Closed connector



Ledinaire Panel G5 PSD DALI Driver Closed connector




Ledinaire panel G5 frame and optical area 60x120



White Quick connector+wire-closed



Ledinaire Panel Gen 5-RC065B W60L120-backside




White Quick connector +wire-open



White Quick connector-open



Ledinaire Panel G5 All in CCT
Switch PSD ON OFF Driver
Open connector



Ledinaire Panel RC065B G5
30x120 Packaging



Panel flywires CFW



Ledinaire Panel G5 Back
housing PSU Connector



Ledinaire Panel RC065B
Square backside




Ledinaire Panel Gen 5-
RC065B_RC066B Square-
backside-PSU driver and
connector



Ledinaire Panel Gen 5-
RC065B_RC066B Square-
backside



Ledinaire Panel RC065B G5
PSU 30x120 Backside



Ledinaire Panel G5 All in CCT
Switch PSU ON OFF Driver
Closed connector



Ledinaire Panel G5 All in CCT
Switch 3500K



Ledinaire Panel G5 All in CCT
Switch 4000K



Ledinaire Panel Gen 5-RC065B W60L120-backside-PSU driver and Flywire



Ledinaire Panel Gen 5-RC065B_RC066B Square-backside-PSU driver and connector

Általános információ

Előtetegységek száma	1 egység
Előtét mellékelve	Igen
Szervizcímke	Nem

Technikai adatok

Fényhasznosítás (névleges) (névleges)	120 lm/W
Színvisszaadási index (CRI)	80
Univerzális típus	All-in, Multi Color Temperature

Működtetés és elektronika

Bemeneti feszültség	220–240 V
Hálózati frekvencia	50 or 60 Hz
Véletlenszerű váltásra alkalmas	Nem alkalmazható
IEC védelmi osztály	II. biztonsági osztály

Mechanika és tokozás

Ház színe	Fehér – RAL 9003
Por és víz elleni védelem kódja	IP20/40 [Ujjak behatolása ellen védett, kibocsátó felület]
Mech. behatások elleni védelem kódja	IK02 [0,2 J standard]

Vészhelyzeti működés

Központi vészvilágítás	Nem
------------------------	-----

Tanúsítvány és alkalmazási területek

Izzóhuzalos teszt	Hőmérséklet: 650 °C, időtartam: 30 s
Gyúlékonysági jelzés	Normál gyúlékonyságú felületekre szereléshez
CE jelölés	Igen
ENEC jel	-
Villogás (PstLM)	1
Környezeti hőmérséklet-tartomány	-10 – +35 °C

Kezdeti teljesítmény (IEC-szabványnak megfelelően)

Fényáram-tolerancia -10%,+15%

Technikai adatok

Order Code	Full Product Name	Fényáram	Korrelált színhőmérséklet (névleges)	A fényforrás sugárzási szöge	Az optika típusa
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	3 400 lm 3 600 lm	Selectable	90 fok	Sugárzási szög 90°
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	6 000 lm	4000 K	120 fok	Sugárzási szög 120°
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	3 400 lm 3 600 lm	Selectable	90 fok	Sugárzási szög 90°
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	3 400 lm 3 600 lm	Selectable	120 fok	Sugárzási szög 120°
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	3 400 lm	4000 K	90 fok	Sugárzási szög 90°
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	3 400 lm	4000 K	90 fok	Sugárzási szög 90°
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	3 400 lm	6500 K	90 fok	Sugárzási szög 90°
51654099	RC065B G5 34S/840 PSU W60L60 NOC CFW	3 400 lm	4000 K	120 fok	Sugárzási szög 120°
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	3 400 lm	4000 K	120 fok	Sugárzási szög 120°
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	3 400 lm	6500 K	120 fok	Sugárzási szög 120°
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	3 400 lm	4000 K	90 fok	Sugárzási szög 90°
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	3 400 lm	4000 K	90 fok	Sugárzási szög 90°
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	4 100 lm	4000 K	120 fok	Sugárzási szög 120°
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	4 100 lm	4000 K	90 fok	Sugárzási szög 90°
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	4 100 lm	4000 K	120 fok	Sugárzási szög 120°
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	4 100 lm	4000 K	90 fok	Sugárzási szög 90°
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	3 400 lm	4000 K	120 fok	Sugárzási szög 120°
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	3 400 lm	4000 K	90 fok	Sugárzási szög 90°
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	3 400 lm 3 600 lm	Selectable	90 fok	Sugárzási szög 90°

Működtetés és elektronika

Order Code	Full Product Name	Teljesítményfelvétel
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	28 W
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	50 W
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	30 W
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	30 W
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	28 W
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	28 W
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	28 W
51654099	RC065B G5 34S/840 PSU W60L60 NOC CFW	28 W
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	28 W

Order Code	Full Product Name	Teljesítményfelvétel
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	28 W
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	28 W
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	28 W
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	34 W
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	34 W
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	34 W
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	34 W
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	28 W
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	28 W
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	30 W

Vezérlők és fényerő-szabályozás

Order Code	Full Product Name	Szabályozható	Maximális szabályozási szint
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	Igen	1%
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	Nem	Nem alkalmazható
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	Nem	Nem alkalmazható
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	Nem	Nem alkalmazható
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	Nem	Nem alkalmazható
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	Nem	Nem alkalmazható
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	Nem	Nem alkalmazható
51654099	RC065B G5 34S/840 PSU W60L60 NOC CFW	Nem	Nem alkalmazható
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	Nem	Nem alkalmazható
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	Nem	Nem alkalmazható
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	Igen	1%
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	Igen	1%
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	Nem	Nem alkalmazható
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	Nem	Nem alkalmazható
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	Nem	Nem alkalmazható
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	Nem	Nem alkalmazható
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	Nem	Nem alkalmazható
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	Nem	Nem alkalmazható
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	Nem	Nem alkalmazható

Kezdeti teljesítmény (IEC-szabványnak megfelelően)

Order Code	Full Product Name	Kezdeti színérték
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	(0.38, 0.38) SDCM ≤5
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	(0.38, 0.38) SDCM ≤5

Order Code	Full Product Name	Kezdeti színérték
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	(0.38, 0.38) SDCM ≤5
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	(0.31, 0.33) SDCM ≤5
51654099	RC065B G5 34S/840 PSU W60L60 NOC CFW	(0.38, 0.38) SDCM ≤5
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	(0.38, 0.38) SDCM ≤5
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	(0.31, 0.33) SDCM ≤5
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	(0.38, 0.38) SDCM ≤5
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	(0.38, 0.38) SDCM ≤5
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	(0.38, 0.38) SDCM ≤5
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	(0.38, 0.38) SDCM ≤5
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	(0.38, 0.38) SDCM ≤5
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	(0.38, 0.38) SDCM ≤5
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	(0.38, 0.38) SDCM ≤5
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	(0.38, 0.38) SDCM ≤5
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5