



SlimBlend gen2: high performance, advanced control

SlimBlend Gen2

Offices are looking for high-performance lighting that enhances performance, comfort, well-being, and sustainability. That's why 'surface of light' solutions that deliver excellent quality of light with great functionality and connectivity are in such demand. Like Philips SlimBlend Gen2 – a complete family of slim luminaires designed for enhanced well-being and circularity. SlimBlend Gen2 luminaires offer state-of-the-art efficacy and excellent light quality (CRI>90) with upgradability features and repairability that promise a long lifetime. They are also designed for recyclability, making them a truly circular, green choice. But it's the high-quality light that makes SlimBlend Gen2 luminaires really stand out. The special Micro Hexagonal Optics (MXO) provides glare-free comfort & also infuses the homogeneous light with sparkles, creating a lively surface of light that enhances interiors and offers full Office compliance. SlimBlend Gen 2 is a minimalist solution with superior lighting specifications combined with a best-in-class connectivity using Interact Pro – all with a sustainable approach to high-performance office lighting.

Benefits

- Highly efficient LED luminaire with choice of mounting options (recessed, suspended, surface mounted)
- Comfortable, glare-free Office-compliant
- Competitive solution with good lighting specifications
- Sustainable and best-in-class connected offer

SlimBlend Gen2

Features

- Best-in-class efficacy up to 140lm/W supports green building design and energy saving subsidy criteria
- CRI90 with Tunable White option
- Office-compliant lighting using both MXO optics and Opal cover
- Long lifetime up to 50,000 hours @L90
- Quick connector or Wieland connector for simpler, faster installation
- Prepared for circularity (no glue, replaceable electronics, upgradable system, efficient and long lifetime) plus supporting Environmental Product Declaration (EPD) guide
- Connected system ready with Interact Pro scalable platform using integrated sensors and/or wireless drivers for data collection, occupancy, daylight regulation and wayfinding

Application

- Offices
- Healthcare
- Education

Versions





SlimBlendGen2 RecessMouted
RC330V W62L62 MXO IA5 SPP




SlimBlendGen2 RecessMouted
RC330V W60L60 MXO IA5 SPP

Dimensional drawing



Dimensional drawing



Product details

SlimBlendGen2 Backview _DPP




SlimBlendGen2_IA5 Sensor with MXO



SlimBlendGen2_IA5 Sensor_with OC



SlimBlendGen2 with CPC accessory DPP01



SlimBlend Gen2

Product details



SlimBlendGen2_Suspended with
sensor_W30L120



Connector- Wieland DPP01



SlimBlendGen2_Suspended with
sensor_W60L60



RC330V W60L60 sensor with
Surface mounted accessories



RC330V W30L120 with Surface
mounted accessories



RC330V W30L120 sensor with
Surface mounted accessories



RC330V W60L60 with Surface
mounted accessories



SlimBlendGen2 with CPC
accessory DPP02



PIP connector DPP02

SlimBlend Gen2

Product details


SlimBlend Gen2
RC330Z_SMB_W30L120



Connector- Wieland DPP02



PIP connector DPP03



Safety cable



SlimBlendGen2_IA4 Sensor with
MXO



SlimBlendGen2 MXO-optics



SlimBlend Gen2
RC330Z_SMB_W60L60



SlimBlendGen2 Backview with IA4
sensor



SlimBlendGen2_Suspended
without sensor_W60L60



SlimBlend Gen2

Product details



SlimBlend Gen2_Backview with EL
& Sensor_DPP



SlimBlendGen2_Suspended
without sensor_W30L120



PIP connector DPP01

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90
Optic type	-
Upward light output ratio	0
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	White
Mech. impact protection code	IK03
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	36S
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	36S
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	42S
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	42S
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	36S
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	36S
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	42S
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	42S
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	36S
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	36S
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	36S
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	36S
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	42S
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	42S
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	42S
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	36S
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	36S
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	42S
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	42S
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	42S
910505102469	RC330V 36S/940 PSD W30L120 MXO	36S
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	36S
910505102471	RC330V 42S/940 PSD W30L120 MXO	42S
910505102472	RC330V 42S/930 PSD W30L120 MXO	42S
910505102473	RC330V 36S/940 WIA W30L120 MXO	36S
910505102474	RC330V 42S/940 WIA W30L120 MXO	42S
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	36S
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	36S
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	36S
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	42S
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	42S
910505102445	RC330V 36S/940 PSD W60L60 MXO	36S
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	36S
910505102447	RC330V 42S/940 PSD W60L60 MXO	42S
910505102448	RC330V 42S/930 PSD W60L60 MXO	42S
910505102449	RC330V 36S/940 WIA W60L60 MXO	36S
910505102455	RC332V 36S/930 PSD W62L62 MXO	36S
910505102456	RC332V 36S/940 PSD W62L62 MXO	36S
910505102457	RC332V 42S/930 PSD W62L62 MXO	42S
910505102458	RC332V 42S/940 PSD W62L62 MXO	42S
910505102459	RC332V 36S/940 DEIA W62L62 MXO	36S
910505102460	RC332V 36S/930 WIA W62L62 MXO	36S
910505102461	RC332V 36S/940 WIA W62L62 MXO	36S
910505102462	RC332V 42S/930 WIA W62L62 MXO	42S
910505102463	RC332V 42S/940 WIA W62L62 MXO	42S
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	36S
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	36S
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	42S
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	36S

Light Technical

SlimBlend Gen2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	3000 K	127 lm/W	3,400 lm
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	4000 K	133 lm/W	3,600 lm
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	3000 K	127 lm/W	4,000 lm
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	4000 K	133 lm/W	4,200 lm
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	4000 K	133 lm/W	3,600 lm
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	4000 K	136 lm/W	3,600 lm
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	3000 K	129 lm/W	4,000 lm
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	4000 K	135 lm/W	4,200 lm
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	4000 K	136 lm/W	3,600 lm
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	3000 K	129 lm/W	3,400 lm
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	4000 K	133 lm/W	3,600 lm
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	4000 K	133 lm/W	3,600 lm
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	3000 K	127 lm/W	4,000 lm
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	4000 K	133 lm/W	4,200 lm
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	4000 K	127 lm/W	3,400 lm
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	4000 K	133 lm/W	3,600 lm
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	4000 K	133 lm/W	3,600 lm
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	3000 K	127 lm/W	4,000 lm
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	4000 K	133 lm/W	4,200 lm
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	4000 K	133 lm/W	4,200 lm
910505102469	RC330V 36S/940 PSD W30L120 MXO	4000 K	136 lm/W	3,600 lm
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	4000 K	136 lm/W	3,600 lm
910505102471	RC330V 42S/940 PSD W30L120 MXO	4000 K	135 lm/W	4,200 lm
910505102472	RC330V 42S/930 PSD W30L120 MXO	3000 K	129 lm/W	4,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102473	RC330V 36S/940 WIA W30L120 MXO	4000 K	136 lm/W	3,600 lm
910505102474	RC330V 42S/940 WIA W30L120 MXO	4000 K	135 lm/W	4,200 lm
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	4000 K	136 lm/W	3,600 lm
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	4000 K	136 lm/W	3,600 lm
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	3000 K	129 lm/W	3,400 lm
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	4000 K	135 lm/W	4,200 lm
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	3000 K	129 lm/W	4,000 lm
910505102445	RC330V 36S/940 PSD W60L60 MXO	4000 K	133 lm/W	3,600 lm
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	4000 K	133 lm/W	3,600 lm
910505102447	RC330V 42S/940 PSD W60L60 MXO	4000 K	133 lm/W	4,200 lm
910505102448	RC330V 42S/930 PSD W60L60 MXO	3000 K	127 lm/W	4,000 lm
910505102449	RC330V 36S/940 WIA W60L60 MXO	4000 K	133 lm/W	3,600 lm
910505102455	RC332V 36S/930 PSD W62L62 MXO	3000 K	133 lm/W	3,600 lm
910505102456	RC332V 36S/940 PSD W62L62 MXO	4000 K	133 lm/W	3,600 lm
910505102457	RC332V 42S/930 PSD W62L62 MXO	3000 K	127 lm/W	4,000 lm
910505102458	RC332V 42S/940 PSD W62L62 MXO	4000 K	133 lm/W	4,200 lm
910505102459	RC332V 36S/940 DEIA W62L62 MXO	4000 K	133 lm/W	3,600 lm
910505102460	RC332V 36S/930 WIA W62L62 MXO	3000 K	127 lm/W	3,400 lm
910505102461	RC332V 36S/940 WIA W62L62 MXO	4000 K	133 lm/W	3,600 lm
910505102462	RC332V 42S/930 WIA W62L62 MXO	3000 K	127 lm/W	4,000 lm
910505102463	RC332V 42S/940 WIA W62L62 MXO	4000 K	133 lm/W	4,200 lm
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	4000 K	133 lm/W	3,600 lm
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	3000 K	127 lm/W	3,400 lm
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	4000 K	133 lm/W	4,200 lm

SlimBlend Gen2

Order Code	Full Product Name	Correlated	Luminous	Luminous
		Color Temperature (Nom)	Efficacy (rated) (Nom)	Flux
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	4000 K	133 lm/W	3,600 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	27 W
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	27 W
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	31.5 W
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	31.5 W
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	27 W
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	26.5 W
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	31 W
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	31 W
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	26.5 W
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	26.5 W
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	27 W
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	27 W
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	31.5 W
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	31.5 W
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	31.5 W
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	27 W
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	27 W
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	31.5 W
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	31.5 W
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	31.5 W
910505102469	RC330V 36S/940 PSD W30L120 MXO	26.5 W
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	26.5 W
910505102471	RC330V 42S/940 PSD W30L120 MXO	31 W
910505102472	RC330V 42S/930 PSD W30L120 MXO	31 W
910505102473	RC330V 36S/940 WIA W30L120 MXO	26.5 W

Order Code	Full Product Name	Power Consumption
910505102474	RC330V 42S/940 WIA W30L120 MXO	31 W
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	26.5 W
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	26.5 W
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	26.5 W
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	31 W
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	31 W
910505102445	RC330V 36S/940 PSD W60L60 MXO	27 W
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	27 W
910505102447	RC330V 42S/940 PSD W60L60 MXO	31.5 W
910505102448	RC330V 42S/930 PSD W60L60 MXO	31.5 W
910505102449	RC330V 36S/940 WIA W60L60 MXO	27 W
910505102455	RC332V 36S/930 PSD W62L62 MXO	27 W
910505102456	RC332V 36S/940 PSD W62L62 MXO	27 W
910505102457	RC332V 42S/930 PSD W62L62 MXO	31.5 W
910505102458	RC332V 42S/940 PSD W62L62 MXO	31.5 W
910505102459	RC332V 36S/940 DEIA W62L62 MXO	27 W
910505102460	RC332V 36S/930 WIA W62L62 MXO	27 W
910505102461	RC332V 36S/940 WIA W62L62 MXO	27 W
910505102462	RC332V 42S/930 WIA W62L62 MXO	31.5 W
910505102463	RC332V 42S/940 WIA W62L62 MXO	31.5 W
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	27 W
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	27 W
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	31.5 W
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	27 W

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	IP20
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	IP20
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	IP20
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	IP20
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	IP20
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	IP20
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	IP20
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	IP20
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	IP20
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	IP20
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	IP20
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	IP20

Order Code	Full Product Name	Ingress protection code
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	IP20
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	IP20
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	IP20
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	IP20
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	IP20
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	IP20
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	IP20
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	IP20
910505102469	RC330V 36S/940 PSD W30L120 MXO	IP20/44
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	IP20/44
910505102471	RC330V 42S/940 PSD W30L120 MXO	IP20/44
910505102472	RC330V 42S/930 PSD W30L120 MXO	IP20/44

Order Code	Full Product Name	Ingress protection code
910505102473	RC330V 36S/940 WIA W30L120 MXO	IP20/44
910505102474	RC330V 42S/940 WIA W30L120 MXO	IP20/44
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	IP20
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	IP20/44
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	IP20/44
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	IP20/44
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	IP20/44
910505102445	RC330V 36S/940 PSD W60L60 MXO	IP20/44
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	IP20/44
910505102447	RC330V 42S/940 PSD W60L60 MXO	IP20/44
910505102448	RC330V 42S/930 PSD W60L60 MXO	IP20/44
910505102449	RC330V 36S/940 WIA W60L60 MXO	IP20/44
910505102455	RC332V 36S/930 PSD W62L62 MXO	IP20/44

Order Code	Full Product Name	Ingress protection code
910505102456	RC332V 36S/940 PSD W62L62 MXO	IP20/44
910505102457	RC332V 42S/930 PSD W62L62 MXO	IP20/44
910505102458	RC332V 42S/940 PSD W62L62 MXO	IP20/44
910505102459	RC332V 36S/940 DEIA W62L62 MXO	IP20/44
910505102460	RC332V 36S/930 WIA W62L62 MXO	IP20/44
910505102461	RC332V 36S/940 WIA W62L62 MXO	IP20/44
910505102462	RC332V 42S/930 WIA W62L62 MXO	IP20/44
910505102463	RC332V 42S/940 WIA W62L62 MXO	IP20/44
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	IP20/44
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	IP20/44
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	IP20/44
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	IP20/44

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	Yes	DC operated central emergency lighting	-	-
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	Yes	DC operated central emergency lighting	-	-
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	Yes	DC operated central emergency lighting	-	-
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	Yes	DC operated central emergency lighting	-	-
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	Yes	DC operated central emergency lighting	-	-
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	Yes	DC operated central emergency lighting	-	-

SlimBlend Gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	Yes	Emergency lighting 3 hours duration with Wireless Interface	270 lm	3 hour(s)
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	Yes	DC operated central emergency lighting	-	-
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	Yes	DC operated central emergency lighting	-	-
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	Yes	DC operated central emergency lighting	-	-
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	Yes	DC operated central emergency lighting	-	-
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	Yes	Emergency lighting 3 hours duration with Wireless Interface	270 lm	3 hour(s)
910505102469	RC330V 36S/940 PSD W30L120 MXO	-	-	-	-
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	-	-	-	-
910505102471	RC330V 42S/940 PSD W30L120 MXO	-	-	-	-
910505102472	RC330V 42S/930 PSD W30L120 MXO	-	-	-	-
910505102473	RC330V 36S/940 WIA W30L120 MXO	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
910505102474	RC330V 42S/940 WIA W30L120 MXO	-	-	-	-
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	Yes	DC operated central emergency lighting	-	-
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	-	-	-	-
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	-	-	-	-
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	-	-	-	-
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	-	-	-	-
910505102445	RC330V 36S/940 PSD W60L60 MXO	-	-	-	-
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	-	-	-	-
910505102447	RC330V 42S/940 PSD W60L60 MXO	-	-	-	-
910505102448	RC330V 42S/930 PSD W60L60 MXO	-	-	-	-
910505102449	RC330V 36S/940 WIA W60L60 MXO	-	-	-	-
910505102455	RC332V 36S/930 PSD W62L62 MXO	-	-	-	-
910505102456	RC332V 36S/940 PSD W62L62 MXO	-	-	-	-

SlimBlend Gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
910505102457	RC332V 42S/930 PSD W62L62 MXO	-	-	-	-
910505102458	RC332V 42S/940 PSD W62L62 MXO	-	-	-	-
910505102459	RC332V 36S/940 DEIA W62L62 MXO	Yes	DC operated central emergency lighting	-	-
910505102460	RC332V 36S/930 WIA W62L62 MXO	-	-	-	-
910505102461	RC332V 36S/940 WIA W62L62 MXO	-	-	-	-
910505102462	RC332V 42S/930 WIA W62L62 MXO	-	-	-	-

Approval and Application

Order Code	Full Product Name	Glow-wire test
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	Temperature 650 °C, duration 30 s
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	Temperature 650 °C, duration 30 s
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	Temperature 650 °C, duration 30 s
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	Temperature 650 °C, duration 30 s
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
910505102463	RC332V 42S/940 WIA W62L62 MXO	-	-	-	-
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	-	-	-	-
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	-	-	-	-
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	-	-	-	-
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	-	-	-	-

Order Code	Full Product Name	Glow-wire test
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	Temperature 650 °C, duration 30 s
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	Temperature 650 °C, duration 30 s
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	Temperature 650 °C, duration 30 s
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	Temperature 850 °C, duration 30 s
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	Temperature 650 °C, duration 30 s
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	Temperature 850 °C, duration 30 s
910505102469	RC330V 36S/940 PSD W30L120 MXO	Temperature 650 °C, duration 30 s
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910505102471	RC330V 42S/940 PSD W30L120 MXO	Temperature 650 °C, duration 30 s
910505102472	RC330V 42S/930 PSD W30L120 MXO	Temperature 650 °C, duration 30 s
910505102473	RC330V 36S/940 WIA W30L120 MXO	Temperature 650 °C, duration 30 s
910505102474	RC330V 42S/940 WIA W30L120 MXO	Temperature 650 °C, duration 30 s
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	Temperature 650 °C, duration 30 s
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102445	RC330V 36S/940 PSD W60L60 MXO	Temperature 650 °C, duration 30 s
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	Temperature 650 °C, duration 30 s
910505102447	RC330V 42S/940 PSD W60L60 MXO	Temperature 650 °C, duration 30 s
910505102448	RC330V 42S/930 PSD W60L60 MXO	Temperature 650 °C, duration 30 s
910505102449	RC330V 36S/940 WIA W60L60 MXO	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	(0.38, 0.38) SDCM <3
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	(0.43, 0.40) SDCM<3
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	(0.38, 0.38) SDCM <3
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	(0.43, 0.40) SDCM<3
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	(0.43, 0.40) SDCM<3
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	(0.43, 0.40) SDCM<3
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	(0.38, 0.38) SDCM <3
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	(0.43, 0.40) SDCM<3
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	(0.43, 0.40) SDCM<3
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	(0.38, 0.38) SDCM <3
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	(0.43, 0.40) SDCM<3
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	(0.43, 0.40) SDCM<3
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	(0.38, 0.38) SDCM <3
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	(0.43, 0.40) SDCM<3
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	(0.43, 0.40) SDCM<3
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	(0.43, 0.40) SDCM<3
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	(0.43, 0.40) SDCM<3
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	(0.38, 0.38) SDCM <3
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	(0.43, 0.40) SDCM<3

Order Code	Full Product Name	Glow-wire test
910505102455	RC332V 36S/930 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102456	RC332V 36S/940 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102457	RC332V 42S/930 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102458	RC332V 42S/940 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102459	RC332V 36S/940 DEIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102460	RC332V 36S/930 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102461	RC332V 36S/940 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102462	RC332V 42S/930 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102463	RC332V 42S/940 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	Temperature 650 °C, duration 30 s
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	Temperature 650 °C, duration 30 s
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	Temperature 650 °C, duration 30 s
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Initial chromaticity
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	(0.43, 0.40) SDCM<3
910505102469	RC330V 36S/940 PSD W30L120 MXO	(0.43, 0.40) SDCM<3
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	(0.43, 0.40) SDCM<3
910505102471	RC330V 42S/940 PSD W30L120 MXO	(0.43, 0.40) SDCM<3
910505102472	RC330V 42S/930 PSD W30L120 MXO	(0.38, 0.38) SDCM <3
910505102473	RC330V 36S/940 WIA W30L120 MXO	(0.43, 0.40) SDCM<3
910505102474	RC330V 42S/940 WIA W30L120 MXO	(0.43, 0.40) SDCM<3
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	(0.43, 0.40) SDCM<3
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	(0.43, 0.40) SDCM<3
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	(0.38, 0.38) SDCM <3
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	(0.43, 0.40) SDCM<3
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	(0.38, 0.38) SDCM <3
910505102445	RC330V 36S/940 PSD W60L60 MXO	(0.43, 0.40) SDCM<3
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	(0.43, 0.40) SDCM<3
910505102447	RC330V 42S/940 PSD W60L60 MXO	(0.43, 0.40) SDCM<3
910505102448	RC330V 42S/930 PSD W60L60 MXO	(0.38, 0.38) SDCM <3
910505102449	RC330V 36S/940 WIA W60L60 MXO	(0.43, 0.40) SDCM<3
910505102455	RC332V 36S/930 PSD W62L62 MXO	(0.38, 0.38) SDCM <3
910505102456	RC332V 36S/940 PSD W62L62 MXO	(0.43, 0.40) SDCM<3

Order Code	Full Product Name	Initial chromaticity
910505102457	RC332V 42S/930 PSD W62L62 MXO	(0.38, 0.38) SDCM <3
910505102458	RC332V 42S/940 PSD W62L62 MXO	(0.43, 0.40) SDCM<3
910505102459	RC332V 36S/940 DEIA W62L62 MXO	(0.43, 0.40) SDCM<3
910505102460	RC332V 36S/930 WIA W62L62 MXO	(0.38, 0.38) SDCM <3
910505102461	RC332V 36S/940 WIA W62L62 MXO	(0.43, 0.40) SDCM<3
910505102462	RC332V 42S/930 WIA W62L62 MXO	(0.38, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910505102463	RC332V 42S/940 WIA W62L62 MXO	(0.43, 0.40) SDCM<3
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	(0.43, 0.40) SDCM<3
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	(0.38, 0.38) SDCM <3
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	(0.43, 0.40) SDCM<3
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	(0.43, 0.40) SDCM<3

Product Data


Order Code	Full Product Name	Product family code
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	RC332V
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	RC332V
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	RC332V
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	RC330V
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	RC332V
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	RC330V
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	RC330V
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	RC330V
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	RC330V
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	RC330V
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	RC330V
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	RC330V
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	RC330V
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	RC330V
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	RC330V
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	RC330V
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	RC330V
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	RC330V
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	RC330V
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	RC330V
910505102469	RC330V 36S/940 PSD W30L120 MXO	RC330V
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	RC330V
910505102471	RC330V 42S/940 PSD W30L120 MXO	RC330V
910505102472	RC330V 42S/930 PSD W30L120 MXO	RC330V
910505102473	RC330V 36S/940 WIA W30L120 MXO	RC330V

Order Code	Full Product Name	Product family code
910505102474	RC330V 42S/940 WIA W30L120 MXO	RC330V
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	RC330V
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	RC330V
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	RC330V
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	RC330V
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	RC330V
910505102445	RC330V 36S/940 PSD W60L60 MXO	RC330V
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	RC330V
910505102447	RC330V 42S/940 PSD W60L60 MXO	RC330V
910505102448	RC330V 42S/930 PSD W60L60 MXO	RC330V
910505102449	RC330V 36S/940 WIA W60L60 MXO	RC330V
910505102455	RC332V 36S/930 PSD W62L62 MXO	RC332V
910505102456	RC332V 36S/940 PSD W62L62 MXO	RC332V
910505102457	RC332V 42S/930 PSD W62L62 MXO	RC332V
910505102458	RC332V 42S/940 PSD W62L62 MXO	RC332V
910505102459	RC332V 36S/940 DEIA W62L62 MXO	RC332V
910505102460	RC332V 36S/930 WIA W62L62 MXO	RC332V
910505102461	RC332V 36S/940 WIA W62L62 MXO	RC332V
910505102462	RC332V 42S/930 WIA W62L62 MXO	RC332V
910505102463	RC332V 42S/940 WIA W62L62 MXO	RC332V
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	RC330V
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	RC330V
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	RC330V
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	RC330V


Polar Wide Diagrams



Polar Normal (separate) - RC330VI - 910505102491




Polar Normal (separate) - RC330VI - 910505102445




Polar Normal (separate) - RC330VI - 910505102447


Polar Wide Diagrams




Polar Normal (separate) - RC330VI - 910505102475




Polar Normal (separate) - RC330VI - 910505102476




Polar Normal (separate) - RC330VI - 910505102497




Polar Normal (separate) - RC330VI - 910505102446




Polar Normal (separate) - RC330VI - 910505102495




Polar Normal (separate) - RC330VI - 910505102448



Polar Normal (separate) - RC330VI - 910505102477






Polar Normal (separate) - RC330VI - 910505102485



Polar Normal (separate) - RC330VI - 910505102468




Polar Wide Diagrams



Polar Normal (separate) - RC330VI - 910505102498

Polar Normal (separate) - RC330VI - 910505102450




Polar Normal (separate) - RC330VI - 910505102449



Polar Normal (separate) - RC330VI - 910505102474

Polar Normal (separate) - RC330VI - 910505102486

Polar Normal (separate) - RC330VI - 910505102494






Polar Normal (separate) - RC330VI - 910505102452

Polar Normal (separate) - RC330VI - 910505102478

Polar Normal (separate) - RC330VI - 910505102455




Polar Wide Diagrams



Polar Normal (separate) - RC330VI - 910505102490

Polar Normal (separate) - RC330VI - 910505102454




Polar Normal (separate) - RC330VI - 910505102484



Polar Normal (separate) - RC330VI - 910505102458

Polar Normal (separate) - RC330VI - 910505102464

Polar Normal (separate) - RC330VI - 910505102456




Polar Normal (separate) - RC330VI - 910505102470


Polar Normal (separate) - RC330VI - 910505102488

Polar Normal (separate) - RC330VI - 910505102487


Polar Wide Diagrams




Polar Normal (separate) - RC330VI - 910505102467




Polar Normal (separate) - RC330VI - 910505102457




Polar Normal (separate) - RC330VI - 910505102469




Polar Normal (separate) - RC330VI - 910505102496




Polar Normal (separate) - RC330VI - 910505102461




Polar Normal (separate) - RC330VI - 910505102492



Polar Normal (separate) - RC330VI - 910505102459




Polar Normal (separate) - RC330VI - 910505102460




Polar Normal (separate) - RC330VI - 910505102465


Polar Wide Diagrams




Polar Normal (separate) - RC330VI - 910505102463




Polar Normal (separate) - RC330VI - 910505102472




Polar Normal (separate) - RC330VI - 910505102462




Polar Normal (separate) - RC330VI - 910505102493




Polar Normal (separate) - RC330VI - 910505102466




Polar Normal (separate) - RC330VI - 910505102453



Polar Normal (separate) - RC330VI - 910505102473




Polar Normal (separate) - RC330VI - 910505102451



Polar Normal (separate) - RC330VI - 910505102471

Polar Wide Diagrams



Polar Normal (separate) - RC330VI -
910505102489

