

FlexBlend - Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application

- Offices
- Education
- Healthcare
- Banks

Versions

Upgradable sensor



0 FlexBlend Recessed-RC340B
W30L120 MLO VPC




FlexBlend Recessed RC342B
W62L62 MLO VPC



FlexBlend Recessed

Dimensional drawing



FlexBlend Recessed

Product details

O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC




FlexBlend Recessed-
RC340B_MLO_DPP



FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C




FlexBlend Recessed-
RC340B_W60L60_CPC brackets



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP



O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed


Product details



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90
Optic type	Wide beam

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02

Approval and Application

Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	4000 K	95 lm/W	3,600 lm
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	4000 K	95 lm/W	3,600 lm
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	4000 K	93 lm/W	4,200 lm
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	4000 K	93 lm/W	4,200 lm
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	4000 K	95 lm/W	3,600 lm
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	4000 K	93 lm/W	4,200 lm
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	4000 K	95 lm/W	3,600 lm
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	4000 K	93 lm/W	4,200 lm
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	4000 K	95 lm/W	3,600 lm
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	4000 K	95 lm/W	3,600 lm
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	4000 K	95 lm/W	3,600 lm
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	4000 K	93 lm/W	4,200 lm
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	4000 K	93 lm/W	4,200 lm
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	3000 K	93 lm/W	4,200 lm
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	3000 K	93 lm/W	4,200 lm
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	4000 K	138 lm/W	4,200 lm
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	4000 K	138 lm/W	4,200 lm
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	3000 K	138 lm/W	4,200 lm
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	4000 K	140 lm/W	4,200 lm
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	4000 K	126 lm/W	3,600 lm
10263700	RC340B 42S/940 PSE W60L60 VPC O	4000 K	125 lm/W	4,200 lm
10264400	RC340B 42S/940 DEIA W60L60 VPC O	4000 K	125 lm/W	4,200 lm
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	4000 K	125 lm/W	4,200 lm
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	4000 K	125 lm/W	4,200 lm
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	4000 K	126 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	4000 K	126 lm/W	3,600 lm
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	4000 K	95 lm/W	3,600 lm
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	3000 K	93 lm/W	4,200 lm
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	4000 K	93 lm/W	4,200 lm
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	4000 K	138 lm/W	4,200 lm
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	3000 K	138 lm/W	4,200 lm
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	4000 K	95 lm/W	3,600 lm
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	4000 K	93 lm/W	4,200 lm
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	4000 K	93 lm/W	4,200 lm
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	3000 K	138 lm/W	4,200 lm
10230900	RC340B 36S/940 DEIA W60L60 VPC O	4000 K	126 lm/W	3,600 lm
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	4000 K	138 lm/W	3,600 lm
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	4000 K	138 lm/W	3,600 lm
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	4000 K	95 lm/W	3,600 lm
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	4000 K	138 lm/W	3,600 lm
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	4000 K	138 lm/W	3,600 lm
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	4000 K	138 lm/W	4,200 lm
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	4000 K	138 lm/W	4,200 lm
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	4000 K	138 lm/W	4,200 lm
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	3000 K	138 lm/W	4,200 lm
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	4000 K	138 lm/W	4,200 lm
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	4000 K	138 lm/W	3,600 lm
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	4000 K	138 lm/W	3,600 lm
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	4000 K	138 lm/W	4,200 lm
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	4000 K	138 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	4000 K	138 lm/W	3,600 lm
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	4000 K	138 lm/W	3,600 lm
10229300	RC340B 36S/940 PSE W60L60 VPC O	4000 K	126 lm/W	3,600 lm
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	4000 K	95 lm/W	3,600 lm
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	4000 K	95 lm/W	3,600 lm
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	4000 K	126 lm/W	3,600 lm
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	4000 K	95 lm/W	3,600 lm
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	4000 K	93 lm/W	4,200 lm
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	4000 K	93 lm/W	4,200 lm
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	3000 K	93 lm/W	4,200 lm
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	4000 K	93 lm/W	4,200 lm
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	4000 K	93 lm/W	4,200 lm
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	4000 K	95 lm/W	3,600 lm
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	4000 K	95 lm/W	3,600 lm
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	4000 K	138 lm/W	4,200 lm
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	3000 K	93 lm/W	4,200 lm
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	4000 K	93 lm/W	4,200 lm
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	4000 K	138 lm/W	4,200 lm
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	3000 K	138 lm/W	4,200 lm
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	4000 K	138 lm/W	3,600 lm
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	4000 K	95 lm/W	3,600 lm
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	4000 K	95 lm/W	3,600 lm
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	4000 K	95 lm/W	3,600 lm
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	4000 K	144 lm/W	3,600 lm

Operating and Electrical

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	38 W	Yes
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	38 W	Yes
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	45 W	Yes
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	45 W	Yes
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	38 W	Yes
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	45 W	Yes
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	38 W	Yes
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	45 W	Yes
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	38 W	Yes
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	37 W	Yes
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	38 W	Yes
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	45 W	Yes
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	45 W	Yes
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	45 W	Yes
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	45 W	Yes
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	30.5 W	Yes
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	30.5 W	Yes
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	30.5 W	Yes
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	30 W	No
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	28.5 W	Yes
10263700	RC340B 42S/940 PSE W60L60 VPC O	33.5 W	Yes
10264400	RC340B 42S/940 DEIA W60L60 VPC O	33.5 W	Yes
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	33.5 W	Yes
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	33.5 W	Yes
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	28.5 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	28.5 W	Yes
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	38 W	Yes
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	45 W	Yes
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	45 W	Yes
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	30.5 W	Yes
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	30.5 W	Yes
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	38 W	Yes
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	45 W	Yes
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	45 W	Yes
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	30.5 W	Yes
10230900	RC340B 36S/940 DEIA W60L60 VPC O	28.5 W	Yes
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	26 W	Yes
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	26 W	Yes
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	38 W	Yes
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	26 W	Yes
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	26 W	Yes
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	30.5 W	Yes
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	30.5 W	Yes
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	30.5 W	Yes
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	30.5 W	Yes
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	30.5 W	Yes
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	26 W	Yes
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	26 W	Yes
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	30.5 W	Yes
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	30.5 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	26 W	Yes
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	26 W	Yes
10229300	RC340B 36S/940 PSE W60L60 VPC O	28.5 W	Yes
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	37 W	Yes
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	38 W	Yes
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	28.5 W	Yes
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	38 W	Yes
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	45 W	Yes
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	45 W	Yes
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	45 W	Yes
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	45 W	Yes
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	45 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	38 W	Yes
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	38 W	Yes
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	30.5 W	Yes
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	45 W	Yes
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	45 W	Yes
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	30.5 W	Yes
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	30.5 W	Yes
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	26 W	Yes
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	38 W	Yes
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	38 W	Yes
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	38 W	Yes
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	25 W	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	No	-
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	-
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	No	-
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	-
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes	-
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes	-
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes	-
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes	-
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	-
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	No	-
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	-
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	-
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	-
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	-
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	-
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	-
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	-
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	No	Upgradable sensor slot with SC200 sensor
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes	-
10263700	RC340B 42S/940 PSE W60L60 VPC O	No	-
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Yes	-
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes	-
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes	-
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	No	-
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	-
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	-
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	-

FlexBlend Recessed

Order Code	Full Product Name	Embedded	
		Dimmable	control
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	-
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	-
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	-
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	No	-
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	No	-
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	-
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	-
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Yes	-
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	No	-
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	-
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	-
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes	-
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes	-
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	No	-
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	-
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes	-
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	-
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	-
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No	-
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	-
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	No	-
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	-
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	No	-
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	-

Order Code	Full Product Name	Embedded	
		Dimmable	control
10229300	RC340B 36S/940 PSE W60L60 VPC O	No	-
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	No	-
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes	-
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes	-
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes	-
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	-
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes	-
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	-
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	-
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	No	-
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	No	-
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	-
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes	-
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	-
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	-
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	-
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	-
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	-
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No	-
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	-
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	-
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Ingress protection
		code
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	IP20/40
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	IP20/40
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	IP20/40
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	IP20/40
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IP20
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IP20
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IP20
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IP20
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	IP20/40
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	IP20/40
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	IP20/40
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	IP20/40

Order Code	Full Product Name	Ingress protection
		code
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	IP20/40
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	IP20/40
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	IP20/40
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	IP20/54
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	IP20/54
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	IP20/54
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	IP20/54
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	IP54
10263700	RC340B 42S/940 PSE W60L60 VPC O	IP20/54
10264400	RC340B 42S/940 DEIA W60L60 VPC O	IP20/54
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	IP20/54
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	IP54

FlexBlend Recessed

Order Code	Full Product Name	Ingress protection code
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	IP20/54
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	IP20/54
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	IP20/40
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	IP20/40
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	IP20/40
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	IP20/54
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	IP20/54
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	IP20/40
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	IP20/40
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	IP20/40
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	IP20/54
10230900	RC340B 36S/940 DEIA W60L60 VPC O	IP20/54
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	IP20/54
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	IP20/54
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	IP20/40
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IP20/54
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IP20/54
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	IP20/54
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	IP20/54
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IP20/54
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	IP20/54
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	IP20/54
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IP20/54
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	IP20/54
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	IP20/54

Order Code	Full Product Name	Ingress protection code
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	IP20/54
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	IP20/54
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IP20/54
10229300	RC340B 36S/940 PSE W60L60 VPC O	IP20/54
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	IP20/40
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IP20/54
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	IP54
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IP20/54
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	IP20/40
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IP20
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	IP20/40
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	IP20/40
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	IP20/40
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	IP20/40
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IP20/40
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IP20/54
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	IP20/40
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	IP20/40
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	IP20/54
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	IP20/54
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	IP20/54
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IP20/40
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	IP20/40
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	IP20/40
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	IP20/54

Emergency Operation

Order Code	Full Product Name	Central		Rated duration of the emergency lighting (when fully charged)
		Emergency	Emergency lighting	
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	-	-	-
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting	-
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	-	-	-
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting	-
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)

Order Code	Full Product Name	Central		Rated duration of the emergency lighting (when fully charged)
		Emergency	Emergency lighting	
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting	-
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	-	-	-
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting	-

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Yes	DC operated central emergency lighting	-
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10263700	RC340B 42S/940 PSE W60L60 VPC O	-	-	-
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting	-
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	-	-	-
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting	-
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	-	-	-
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	-	-	-
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting	-
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting	-
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	-	-	-
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting	-
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting	-
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	-	-	-
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting	-

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-	-
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting	-
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	-	-	-
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting	-
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-	-
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting	-
10229300	RC340B 36S/940 PSE W60L60 VPC O	-	-	-
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	-	-	-
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting	-
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	-	-	-
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-	-
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting	-
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting	-
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting	-
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting	-
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting	-
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	DC operated central emergency lighting	-
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-	-
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting	-
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting	-
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-

Approval and Application

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10263700	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
10229300	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	Temperature 850 °C, duration 30 s
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	(0.43, 0.40) SDCM <3
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	(0.43, 0.40) SDCM <3
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	(0.43, 0.40) SDCM <3
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	(0.38, 0.37) SDCM ≤3
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
10263700	RC340B 42S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10264400	RC340B 42S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	(0.43, 0.40) SDCM <3

Order Code	Full Product Name	Initial chromaticity
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	(0.43, 0.40) SDCM <3
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	(0.43, 0.40) SDCM <3
10230900	RC340B 36S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	(0.43, 0.40) SDCM <3
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	(0.38, 0.37) SDCM ≤3
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
10229300	RC340B 36S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3

FlexBlend Recessed

Order Code	Full Product Name	Initial chromaticity
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM \leq 3
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM \leq 3
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM \leq 3
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	(0.43, 0.40) SDCM <3
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	(0.38, 0.37) SDCM \leq 3
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	(0.38, 0.37) SDCM \leq 3
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	(0.38, 0.37) SDCM \leq 3
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	(0.38, 0.37) SDCM \leq 3
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM \leq 3

Order Code	Full Product Name	Initial chromaticity
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	(0.43, 0.40) SDCM <3
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	(0.38, 0.37) SDCM \leq 3
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	(0.38, 0.37) SDCM \leq 3
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	(0.43, 0.40) SDCM <3
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	(0.38, 0.37) SDCM \leq 3
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	(0.38, 0.37) SDCM \leq 3
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	(0.38, 0.37) SDCM \leq 3
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	(0.38, 0.37) SDCM \leq 3
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM \leq 3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	0.01 %
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	0.01 %
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	0.01 %
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	0.01 %
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	0.01 %
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	0.01 %
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	0.01 %
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	0.01 %
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	0.01 %
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	0.01 %
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	0.01 %
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	0.01 %
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	0.01 %
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	0.01 %
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	0.01 %
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	0.01 %
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	0.01 %
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	0.01 %
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	-
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	0.01 %
10263700	RC340B 42S/940 PSE W60L60 VPC O	0.01 %
10264400	RC340B 42S/940 DEIA W60L60 VPC O	0.01 %
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	0.01 %
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	0.01 %
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	0.01 %
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	0.01 %
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	0.01 %
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	0.01 %
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	0.01 %
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	0.01 %
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	0.01 %
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	0.01 %
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	0.01 %
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	0.01 %
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	0.01 %
10230900	RC340B 36S/940 DEIA W60L60 VPC O	0.01 %
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	0.01 %
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	0.01 %
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	0.01 %
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	0.01 %
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	0.01 %
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	0.01 %
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	0.01 %
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	0.01 %
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	0.01 %
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	0.01 %
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	0.01 %
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	0.01 %
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	0.01 %
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	0.01 %
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	0.01 %
10229300	RC340B 36S/940 PSE W60L60 VPC O	0.01 %
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	0.01 %
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	0.01 %
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	0.01 %
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	0.01 %
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	0.01 %
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	0.01 %
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	0.01 %
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	0.01 %
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	0.01 %
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	0.01 %
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	0.01 %
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	0.01 %
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	0.01 %
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	0.01 %
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	0.01 %
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	0.01 %
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	-
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	0.01 %
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	0.01 %
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	0.01 %
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	-


FlexBlend Recessed

Product Data


Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B	10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B	10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B	10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B	10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B	10265100	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B	10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B	10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B	10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	RC340B
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B	10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	RC340B
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B	10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B	10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	RC340B	10311500	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	RC340B	10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	RC340B	10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	RC340B	10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	RC340B	10229300	RC340B 36S/940 PSE W60L60 VPC O	RC340B
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	RC340B	10243900	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	RC340B	10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	RC340B	10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B	10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
10263700	RC340B 42S/940 PSE W60L60 VPC O	RC340B	10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
10264400	RC340B 42S/940 DEIA W60L60 VPC O	RC340B	10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B	10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	RC340B
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B	10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	RC340B
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B	10305400	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B	10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B	10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	RC340B	10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	RC340B	10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	RC340B
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	RC340B	10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	RC340B
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	RC340B	10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	RC340B
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B	10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	RC340B
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B	10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	RC340B
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B	10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	RC340B	10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
10230900	RC340B 36S/940 DEIA W60L60 VPC O	RC340B	10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B	10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866978




Polar Normal (separate) - RC340BI - 910925866989




Polar Normal (separate) - RC340BI - 910925867030




Polar Normal (separate) - RC340BI - 910925867031




Polar Normal (separate) - RC340BI - 910925866987




Polar Normal (separate) - RC340BI - 910925868920



Polar Normal (separate) - RC340BI - 910925866969




Polar Normal (separate) - RC340BI - 910925866968




Polar Normal (separate) - RC340BI - 910925866979

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866981




Polar Normal (separate) - RC340BI - 910925867038




Polar Normal (separate) - RC340BI - 910925867040




Polar Normal (separate) - RC340BI - 910925867050




Polar Normal (separate) - RC340BI - 910925866973




Polar Normal (separate) - RC340BI - 910925866991



Polar Normal (separate) - RC340BI - 910925866993




Polar Normal (separate) - RC340BI - 910925867002




Polar Normal (separate) - RC340BI - 910925867003

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866977




Polar Normal (separate) - RC340BI - 910925866995




Polar Normal (separate) - RC340BI - 910925867012




Polar Normal (separate) - RC340BI - 910925867017




Polar Normal (separate) - RC340BI - 910925867033




Polar Normal (separate) - RC340BI - 910925867024



Polar Normal (separate) - RC340BI - 910925867043




Polar Normal (separate) - RC340BI - 910925867049




Polar Normal (separate) - RC340BI - 910925866967

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867010




Polar Normal (separate) - RC340BI - 910925867013




Polar Normal (separate) - RC340BI - 910925867022




Polar Normal (separate) - RC340BI - 910925867034




Polar Normal (separate) - RC340BI - 910925867039




Polar Normal (separate) - RC340BI - 910925867032



Polar Normal (separate) - RC340BI - 910925867064




Polar Normal (separate) - RC340BI - 910925866980




Polar Normal (separate) - RC340BI - 910925866982

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866983




Polar Normal (separate) - RC340BI - 910925866997




Polar Normal (separate) - RC340BI - 910925867009




Polar Normal (separate) - RC340BI - 910925867047




Polar Normal (separate) - RC340BI - 910925867062




Polar Normal (separate) - RC340BI - 910925867063



Polar Normal (separate) - RC340BI - 910925866966




Polar Normal (separate) - RC340BI - 910925867018




Polar Normal (separate) - RC340BI - 910925867016

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867025




Polar Normal (separate) - RC340BI - 910925867028




Polar Normal (separate) - RC340BI - 910925867014




Polar Normal (separate) - RC340BI - 910925867020




Polar Normal (separate) - RC340BI - 910925867026




Polar Normal (separate) - RC340BI - 910925867035



Polar Normal (separate) - RC340BI - 910925867036




Polar Normal (separate) - RC340BI - 910925867044




Polar Normal (separate) - RC340BI - 910925867045

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867007




Polar Normal (separate) - RC340BI - 910925867015




Polar Normal (separate) - RC340BI - 910925867023




Polar Normal (separate) - RC340BI - 910925867027




Polar Normal (separate) - RC340BI - 910925867029




Polar Normal (separate) - RC340BI - 910925867037



Polar Normal (separate) - RC340BI - 910925867046




Polar Normal (separate) - RC340BI - 910925867042




Polar Normal (separate) - RC340BI - 910925867061

FlexBlend Recessed

Polar Wide Diagrams



Polar Normal (separate) - RC340BI - 910925867068



Polar Normal (separate) - RC340BI - 910925867168

