



PowerBalance Gen2: sustainable performance

When it comes to lighting office spaces with LED luminaires, businesses are willing to invest in sustainability, provided they get a payback on their investment. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. Philips PowerBalance Gen2 is our most energy-efficient, office-compliant LED luminaire. Designed for circularity and enhanced wellbeing, this office luminaire also promises future-proof connectivity. State-of-the-art efficacy (at CRI >90), upgradability features, a long lifetime, repairability, and design for recyclability make PowerBalance Gen2 a true 'green choice'. One that also delivers significantly lower operational costs to ensure an attractive payback that meets the needs of businesses and the specification market. The Gen2 architecture in the latest PowerBalance range has enabled us to create a range of highly-versatile modular and semi-modular luminaires. These LED luminaires can be easily mounted in ceilings with an exposed T-bar or concealed T-bar, as well as plaster ceilings and bandraster-type ceilings. PowerBalance is a solution with superior lighting specifications combined with a best-in-class connectivity designed for Circularity & enhanced Wellbeing using Interact Pro - all with a sustainable approach to high-performance office lighting.

Benefits

- Extremely-efficient LED luminaire with upto 174 lm/W
- Complies with office norms
- Comfortable, glare-free light
- Significantly reduces operational costs for an attractive payback time
- Sustainable and best-in-class connected offer

Applications

- Offices
- Education
- Healthcare

Features

- Best-in-class efficacy up to 174lm/W supports green building design and energy saving subsidy criteria
- 3000K, 4000K, Tunable White options with CRI >90
- Long lifetime 50,000 hours @L90
- Prepared for circularity (no glue, replaceable electronics, upgradable system, efficient and long lifetime)

- Environmental Product Declaration (EPD) guide
- Connected system ready with Interact Pro scalable platform using integrated sensors and/or wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- The product is IP20 and, as such, is not protected against water ingress. Therefore we strongly recommend that the environment in which the luminaire is to be installed should be suitably checked
- If the advice above is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

Versions



PowerBalance RC463B
W31L125 CWL




PowerBalance Rectangle-
16cup




PowerBalance Square- 16cup




PowerBalance RC461B
W60L60 CWL U4




IPPR RC460Bi 0025




IPPR_RC460Bi_0027-Product
photo




IPPR_RC460Bi_0043-Product photo




IPPR_RC460Bi_0049-Product photo




IPPR_RC460Bi_0053-Product photo



IPPR RC460Bi 0047



IPPR RC460Bi 0069



IPPR_RC460Bi_0065-Product photo



PowerBalance RC461B W60L60 CWL



PowerBalance RC461B W30L120 CWL U4



PowerBalance RC463B W62L62 CWL CPC



PowerBalance RC463B W62L62 CWL CPC U4



PowerBalance RC463B
W62L62 CWL VPC



PowerBalance RC461B
W30L120 CWL




PowerBalance RC463B
W31L125 CWL U4




PowerBalance RC463B
W62L62 CWL VPC U4


Dimensional drawing




PowerBalance recessed - 840 neutral white - Power supply unit with DALI interface - Push-in connector and pull relief - -




PowerBalance recessed - 840 neutral white - Power supply unit with DALI interface - Push-in connector and pull relief - -




PowerBalance recessed - 940 neutral white - Power supply unit with DALI and SystemReady interface, InterAct ready - Push-in connector and pull relief - -




PowerBalance recessed - 840 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible - -




RC461B 345/940 DEIA W60L60 CPC W3W2



PowerBalance recessed - 940 neutral white - Power supply unit with DALI interface - Push-in connector and pull relief - -



PowerBalance recessed - Tunable White Bio-up Cyan Enhanced Spectrum CRI90 - Sensor ready driver InterAct System ready - Push-in connector and pull relief



PowerBalance recessed - Generation 2 - LED Module, system flux 4000 lm - 940 neutral white - Power supply unit with DALI interface - Width 0.31 m, length 1.25 m - Concealed profile ceiling version - Push-in connector and pull relief - -

Product details



IPDP_RC460Bi_0153-Detail photo



Upgradable sensor




IPDP_RC460Bi_0039-Detail photo



IPDP_RC460Bi_0041-Detail photo



IPDP_RC460Bi_0043-Detail photo




IPDP_RC460Bi_0045-Detail photo



IPDP_RC460Bi_0047-Detail photo



IPDP_RC460Bi_0049-Detail photo



IPDP_RC460Bi_0051-Detail photo



IPDP_RC460Bi_0053-Detail photo



IPDP_RC460Bi_0054-Detail photo



IPDP_RC460Bi_0055-Detail photo



IPDP_RC460Bi_0073-Detail photo



IPDP_RC460Bi_0081-Detail photo



IPDP_RC460Bi_0103-Detail photo



PowerBalance LEAF DP



PowerBalance_RC461_W31L1 25_IA4-DPP



PowerBalance SC200 DPP



PowerBalance SC200 DPP



PowerBalance SC200 DPP

PowerBalance CPC DP



PowerBalance SC200 DPP



General Information

Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Service tag	Yes

Light Technical

Number of light sources	1
Beam angle of light source	120 degree(s)
Optic type	Wide beam office compliant

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK03 [0.35 J reinforced]
Explosion hazard class	-
Optical cover type	Polycarbonate bowl/cover

Emergency Operation

Emergency flux	300 lm
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Type of emergency lighting battery	Lithium

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Lamp family code
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	-
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	-
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	-
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	-
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	-
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	-
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	-
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	-
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	-
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	-
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	-
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	-
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	-
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	-
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	-
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	-
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	-
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	-
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	-
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	-
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	-
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	-
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	-

Order Code	Full Product Name	Lamp family code
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	-
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	-
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	-
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	-
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	-
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	-
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	-
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	-
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	-
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	-
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	-
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	-
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	-
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	-
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	-
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	-
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	-
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	-
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	-
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	LED34S
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	LED34S
910505100425	RC463B 34S/940 DEIA W62L62 CPC	-
910505100426	RC463B 40S/940 DEIA W62L62 CPC	-
910505100489	RC463B 34S/930 DEIA W62L62 CPC	-
910505100490	RC463B 40S/930 DEIA W62L62 CPC	-
910505100277	RC461B 34S/940 DEIA W60L60 PCV	LED34S
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	LED28S
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	LED34S
910505100278	RC463B 40S/940 DEIA W62L62 VPC	LED40S
910505100416	RC463B 28S/940 DEIA W62L62 VPC	-
910505100417	RC463B 34S/940 DEIA W62L62 VPC	-
910505100418	RC463B 34S/930 DEIA W62L62 VPC	-
910505100488	RC463B 28S/930 DEIA W62L62 VPC	-
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	-
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	-
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	-
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	-
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	-
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	-

Order Code	Full Product Name	Lamp family code
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	-
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	-
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	-
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	-
910505100419	RC463B 40S/930 DEIA W62L62 VPC	-
910505100245	RC461B 34S/940 DEIA W60L60 VPC	LED34S
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	LED40S
910505100250	RC461B 40S/940 DEIA W60L60 VPC	LED40S
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	LED40S
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	LED34S
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	LED40S
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	LED40S
910505100269	RC461B 34S/930 PSE W60L60 VPC	LED34S
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	LED34S
910505100595	RC461B 40S/930 DEIA W60L60 VPC	-
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	-
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	-
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	-
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	-
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	-
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	-
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	-
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	-
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	-
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	-
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	-
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	-
910505100236	RC463B 40S/940 DEIA W31L125 CPC	LED40S
910505100422	RC463B 34S/930 DEIA W31L125 VPC	-
910505100423	RC463B 40S/940 DEIA W31L125 VPC	-
910505100424	RC463B 40S/930 DEIA W31L125 VPC	-
910505100427	RC463B 34S/940 DEIA W31L125 CPC	-
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	-
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	-
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	-
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	-
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	-
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	-
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	LED34S
910505100234	RC461B 34S/930 DEIA W30L120 VPC	LED34S
910505100235	RC461B 40S/940 DEIA W30L120 VPC	LED40S
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	LED40S

Order Code	Full Product Name	Lamp family code
910505100241	RC461B 34S/940 DEIA W30L120 VPC	LED34S
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	-
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	-
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	-
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	-
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	-
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	-
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	-
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	-
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	-
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	-
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	-
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	-
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	-
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	-
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	-
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	-

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	4,000 lm	4000 K	146 lm/W	>90
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	3,400 lm	4000 K	172 lm/W	>80
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	3,400 lm	4000 K	139 lm/W	>90
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	3,400 lm	4000 K	139 lm/W	>90
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	4,000 lm	4000 K	138 lm/W	>90
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	6,000 lm	4000 K	130 lm/W	>90
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	3,400 lm	4000 K	139 lm/W	>90

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	8,000 lm	Tunable white 2700-5000 K	125 lm/W	>90
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	8,000 lm	Tunable white 2700-5000 K	125 lm/W	>90
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	8,000 lm	Tunable white 2700-5000 K	125 lm/W	>90
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	3,400 lm	4000 K	172 lm/W	>80
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	3,400 lm	4000 K	172 lm/W	>80
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	4,000 lm	4000 K	174 lm/W	>80
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	4,000 lm	4000 K	174 lm/W	>80
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	3,400 lm	4000 K	172 lm/W	>80
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	4,000 lm	4000 K	174 lm/W	>80
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	3,400 lm	3000 K	131 lm/W	>90
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	3,400 lm	4000 K	139 lm/W	>90
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	4,000 lm	4000 K	138 lm/W	>90
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	2,800 lm	4000 K	137 lm/W	>90
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	3,400 lm	4000 K	139 lm/W	>90
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	4,000 lm	4000 K	138 lm/W	>90
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	6,000 lm	4000 K	144 lm/W	>90
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	3,400 lm	3000 K	131 lm/W	>90
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	3,400 lm	4000 K	139 lm/W	>90
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	3,400 lm	3000 K	131 lm/W	>90
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	3,400 lm	4000 K	139 lm/W	>90
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	3,400 lm	4000 K	139 lm/W	>90
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	4,000 lm	4000 K	138 lm/W	>90
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	8,000 lm	Tunable white 2700-5000 K	125 lm/W	>90
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	8,000 lm	Tunable white 2700-5000 K	125 lm/W	>90
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	8,000 lm	Tunable white 2700-5000 K	125 lm/W	>90
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	3,400 lm	4000 K	172 lm/W	>80
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	3,400 lm	4000 K	172 lm/W	>80
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	4,000 lm	4000 K	174 lm/W	>80

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	4,000 lm	4000 K	174 lm/W	>80
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	3,400 lm	4000 K	172 lm/W	>80
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	4,000 lm	4000 K	174 lm/W	>80
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	8,000 lm	Tunable white 2700-5000 K	131 lm/W	≥80
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	7,800 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	3,400 lm	4000 K	142 lm/W	>90
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	3,400 lm	4000 K	142 lm/W	>90
910505100425	RC463B 34S/940 DEIA W62L62 CPC	3,400 lm	4000 K	142 lm/W	>90
910505100426	RC463B 40S/940 DEIA W62L62 CPC	4,000 lm	4000 K	146 lm/W	>90
910505100489	RC463B 34S/930 DEIA W62L62 CPC	3,400 lm	3000 K	133 lm/W	>90
910505100490	RC463B 40S/930 DEIA W62L62 CPC	4,000 lm	3000 K	133 lm/W	>90
910505100277	RC461B 34S/940 DEIA W60L60 PCV	3,400 lm	4000 K	142 lm/W	>90
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	2,800 lm	4000 K	141 lm/W	>90
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	3,400 lm	4000 K	142 lm/W	>90
910505100278	RC463B 40S/940 DEIA W62L62 VPC	4,000 lm	4000 K	146 lm/W	>90
910505100416	RC463B 28S/940 DEIA W62L62 VPC	2,800 lm	4000 K	141 lm/W	>90
910505100417	RC463B 34S/940 DEIA W62L62 VPC	3,400 lm	4000 K	142 lm/W	>90
910505100418	RC463B 34S/930 DEIA W62L62 VPC	3,400 lm	3000 K	133 lm/W	>90
910505100488	RC463B 28S/930 DEIA W62L62 VPC	2,800 lm	3000 K	133 lm/W	>90
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	2,800 lm	4000 K	129 lm/W	>80
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	2,800 lm	4000 K	129 lm/W	>80
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	4,000 lm	4000 K	124 lm/W	>80
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	4,000 lm	4000 K	124 lm/W	>80
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	2,800 lm	4000 K	173 lm/W	>80
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	3,400 lm	4000 K	172 lm/W	>80
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	4,000 lm	4000 K	174 lm/W	>80
910505100419	RC463B 40S/930 DEIA W62L62 VPC	4,000 lm	3000 K	133 lm/W	>90
910505100245	RC461B 34S/940 DEIA W60L60 VPC	3,400 lm	4000 K	142 lm/W	>90
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	4,000 lm	4000 K	140 lm/W	>90
910505100250	RC461B 40S/940 DEIA W60L60 VPC	4,000 lm	4000 K	146 lm/W	>90
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	4,000 lm	4000 K	140 lm/W	>90
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	3,400 lm	4000 K	142 lm/W	>90
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	4,000 lm	3000 K	133 lm/W	>90
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	4,000 lm	4000 K	140 lm/W	>90

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505100269	RC461B 34S/930 PSE W60L60 VPC	3,400 lm	3000 K	136 lm/W	>90
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	3,400 lm	4000 K	142 lm/W	>90
910505100595	RC461B 40S/930 DEIA W60L60 VPC	4,000 lm	3000 K	133 lm/W	>90
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	2,800 lm	4000 K	129 lm/W	>80
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	2,800 lm	4000 K	129 lm/W	>80
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	4,000 lm	4000 K	124 lm/W	>80
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	4,000 lm	4000 K	124 lm/W	>80
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	2,800 lm	4000 K	173 lm/W	>80
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	2,800 lm	4000 K	173 lm/W	>80
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	3,400 lm	4000 K	172 lm/W	>80
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	3,400 lm	4000 K	172 lm/W	>80
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	4,000 lm	4000 K	174 lm/W	>80
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	4,000 lm	4000 K	174 lm/W	>80
910505100236	RC463B 40S/940 DEIA W31L125 CPC	4,000 lm	4000 K	140 lm/W	>90
910505100422	RC463B 34S/930 DEIA W31L125 VPC	3,400 lm	3000 K	133 lm/W	>90
910505100423	RC463B 40S/940 DEIA W31L125 VPC	4,000 lm	4000 K	146 lm/W	>90
910505100424	RC463B 40S/930 DEIA W31L125 VPC	4,000 lm	3000 K	133 lm/W	>90
910505100427	RC463B 34S/940 DEIA W31L125 CPC	3,400 lm	4000 K	142 lm/W	>90
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	2,800 lm	4000 K	129 lm/W	>80
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	2,800 lm	4000 K	129 lm/W	>80
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	3,400 lm	4000 K	172 lm/W	>80
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	4,000 lm	4000 K	174 lm/W	>80
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	3,400 lm	4000 K	142 lm/W	>90
910505100234	RC461B 34S/930 DEIA W30L120 VPC	3,400 lm	3000 K	133 lm/W	>90
910505100235	RC461B 40S/940 DEIA W30L120 VPC	4,000 lm	4000 K	146 lm/W	>90
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	4,000 lm	4000 K	140 lm/W	>90
910505100241	RC461B 34S/940 DEIA W30L120 VPC	3,400 lm	4000 K	142 lm/W	>90
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	8,000 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	2,800 lm	4000 K	129 lm/W	>80
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	2,800 lm	4000 K	129 lm/W	>80
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	2,800 lm	4000 K	129 lm/W	>80
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	2,800 lm	4000 K	129 lm/W	>80
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	2,800 lm	4000 K	169 lm/W	>80

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	2,800 lm	4000 K	173 lm/W	>80
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	3,400 lm	4000 K	172 lm/W	>80
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	3,400 lm	4000 K	172 lm/W	>80
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	4,000 lm	4000 K	174 lm/W	>80
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	4,000 lm	4000 K	174 lm/W	>80
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	4,000 lm	3000 K	138 lm/W	>90
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	4,000 lm	4000 K	167 lm/W	>80
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	7,800 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	3,400 lm	4000 K	148 lm/W	>90
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	4,000 lm	4000 K	146 lm/W	>90
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	3,400 lm	4000 K	172 lm/W	>80
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	4,000 lm	4000 K	138 lm/W	>90
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	3,400 lm	4000 K	172 lm/W	>80
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	3,400 lm	4000 K	148 lm/W	>90
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	4,000 lm	4000 K	146 lm/W	>90
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	3,400 lm	4000 K	172 lm/W	>80
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	4,000 lm	4000 K	167 lm/W	>80
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	2,800 lm	4000 K	169 lm/W	>80
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	4,000 lm	4000 K	138 lm/W	>90
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	4,000 lm	4000 K	138 lm/W	>90
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	7,800 lm	Tunable white 2700-6500 K	122 lm/W	>90
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	3,400 lm	4000 K	172 lm/W	>80

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	29 W	No
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	24 W	No
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	45 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	21 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	45 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	24 W	No
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	24 W	No
910505100425	RC463B 34S/940 DEIA W62L62 CPC	24 W	No
910505100426	RC463B 40S/940 DEIA W62L62 CPC	29 W	No
910505100489	RC463B 34S/930 DEIA W62L62 CPC	26 W	No
910505100490	RC463B 40S/930 DEIA W62L62 CPC	30 W	No
910505100277	RC461B 34S/940 DEIA W60L60 PCV	24 W	No
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	20 W	No
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	24 W	No
910505100278	RC463B 40S/940 DEIA W62L62 VPC	29 W	No
910505100416	RC463B 28S/940 DEIA W62L62 VPC	20 W	No
910505100417	RC463B 34S/940 DEIA W62L62 VPC	24 W	No
910505100418	RC463B 34S/930 DEIA W62L62 VPC	26 W	No
910505100488	RC463B 28S/930 DEIA W62L62 VPC	21 W	No
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	64 W	No
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	64 W	No
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	23 W	No
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	23 W	No
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	64 W	No
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	64 W	No
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	33 W	No
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	33 W	No
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	16 W	No
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	20 W	No
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	23 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505100419	RC463B 40S/930 DEIA W62L62 VPC	30 W	No
910505100245	RC461B 34S/940 DEIA W60L60 VPC	24 W	No
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	29 W	No
910505100250	RC461B 40S/940 DEIA W60L60 VPC	29 W	No
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	29 W	No
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	24 W	No
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	30 W	No
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	29 W	No
910505100269	RC461B 34S/930 PSE W60L60 VPC	25 W	No
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	24 W	No
910505100595	RC461B 40S/930 DEIA W60L60 VPC	30 W	No
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	64 W	No
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	64 W	No
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	23 W	No
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	23 W	No
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	33 W	No
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	33 W	No
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	16 W	No
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	16 W	No
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	20 W	No
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	20 W	No
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	23 W	No
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	23 W	No
910505100236	RC463B 40S/940 DEIA W31L125 CPC	29 W	No
910505100422	RC463B 34S/930 DEIA W31L125 VPC	26 W	No
910505100423	RC463B 40S/940 DEIA W31L125 VPC	29 W	No
910505100424	RC463B 40S/930 DEIA W31L125 VPC	30 W	No
910505100427	RC463B 34S/940 DEIA W31L125 CPC	24 W	No
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	64 W	No
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	23 W	No
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	64 W	No
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	23 W	No
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	20 W	No
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	23 W	No
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	24 W	No
910505100234	RC461B 34S/930 DEIA W30L120 VPC	26 W	No
910505100235	RC461B 40S/940 DEIA W30L120 VPC	29 W	No
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	29 W	No
910505100241	RC461B 34S/940 DEIA W30L120 VPC	24 W	No
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	64 W	No
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	64 W	No
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	23 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	23 W	No
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	23 W	No
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	23 W	No
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	16 W	No
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	16 W	No
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	20 W	No
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	20 W	No
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	23 W	No
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	23 W	No
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	29 W	No
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	23 W	No
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	23 W	No
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	28 W	No
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	20 W	No
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	23 W	No
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	28 W	No
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	20 W	No
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	21 W	No
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	28 W	No
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	24 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	20 W	Yes (relates to presence/ movement detection and daylight harvesting)

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level	Embedded control
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	Yes	1%	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	Yes	1%	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	Yes	1%	Interact SC200 sensor
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	Yes	1%	Interact SC200 sensor
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	Yes	1%	Interact SC200 sensor
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	Yes	1%	Interact SC200 sensor
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	Yes	1%	Interact SC200 sensor

Order Code	Full Product Name	Dimmable	Maximum dim level	Embedded control
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Yes	1%	Interact SC200 sensor
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Yes	1%	Interact SC200 sensor
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Yes	1%	Interact SC200 sensor
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Yes	1%	Interact SC200 sensor
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Yes	1%	Interact SC200 sensor
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Yes	1%	Interact SC200 sensor
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	Yes	1%	Interact SC200 sensor
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	Yes	1%	Interact SC200 sensor
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	Yes	1%	Interact SC200 sensor
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	Yes	1%	Interact SC200 sensor
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	Yes	1%	Interact SC200 sensor
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	Yes	1%	Interact SC200 sensor
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	Yes	1%	Upgradable sensor slot with SC200 sensor
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	Yes	1%	Upgradable sensor slot with SC200 sensor
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	Yes	1%	Upgradable sensor slot with SC200 sensor
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Yes	1%	-
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Yes	1%	-
910505100425	RC463B 34S/940 DEIA W62L62 CPC	Yes	1%	-

Order Code	Full Product Name	Dimmable	Maximum dim level	Embedded control
910505100426	RC463B 40S/940 DEIA W62L62 CPC	Yes	1%	-
910505100489	RC463B 34S/930 DEIA W62L62 CPC	Yes	1%	-
910505100490	RC463B 40S/930 DEIA W62L62 CPC	Yes	1%	-
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Yes	1%	-
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Yes	1%	-
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Yes	1%	-
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Yes	1%	-
910505100416	RC463B 28S/940 DEIA W62L62 VPC	Yes	1%	-
910505100417	RC463B 34S/940 DEIA W62L62 VPC	Yes	1%	-
910505100418	RC463B 34S/930 DEIA W62L62 VPC	Yes	1%	-
910505100488	RC463B 28S/930 DEIA W62L62 VPC	Yes	1%	-
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	Yes	1%	-
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	Yes	1%	-
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	Yes	1%	-
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	Yes	1%	-
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	Yes	1%	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	Yes	1%	-
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	Yes	1%	-
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	Yes	1%	-
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	Yes	1%	-
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	Yes	1%	-
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	Yes	1%	-
910505100419	RC463B 40S/930 DEIA W62L62 VPC	Yes	1%	-
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Yes	1%	-
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Yes	1%	-
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Yes	1%	-
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	Yes	1% (no dimming in emergency mode)	-
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Yes	1%	-
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Yes	1%	-
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Yes	1%	-
910505100269	RC461B 34S/930 PSE W60L60 VPC	No	Not applicable	-
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Yes	1%	-
910505100595	RC461B 40S/930 DEIA W60L60 VPC	Yes	1%	-
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	Yes	1%	-
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	Yes	1%	-
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	Yes	1%	-
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	Yes	1%	-
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	Yes	1%	-
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	Yes	1%	-
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	Yes	1%	-
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	Yes	1%	-
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	Yes	1%	-

Order Code	Full Product Name	Dimmable	Maximum dim level	Embedded control
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	Yes	1%	-
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	Yes	1%	-
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	Yes	1%	-
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Yes	1%	-
910505100422	RC463B 34S/930 DEIA W31L125 VPC	Yes	1%	-
910505100423	RC463B 40S/940 DEIA W31L125 VPC	Yes	1%	-
910505100424	RC463B 40S/930 DEIA W31L125 VPC	Yes	1%	-
910505100427	RC463B 34S/940 DEIA W31L125 CPC	Yes	1%	-
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	Yes	1%	-
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	Yes	1%	-
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	Yes	1%	-
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	Yes	1%	-
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	Yes	1%	-
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	Yes	1%	-
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Yes	1%	-
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Yes	1%	-
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Yes	1%	-
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Yes	1%	-
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Yes	1%	-
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	Yes	1%	-
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	Yes	1%	-
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	Yes	1%	-
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	Yes	1%	-
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	Yes	1%	-
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	Yes	1%	-
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	Yes	1%	-
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	Yes	1%	-
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	Yes	1%	-
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	Yes	1%	-
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	Yes	1%	-
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	Yes	1%	-
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	Yes	1%	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	Yes	1%	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Yes	1%	Interact SC200 sensor
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	Yes	1%	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	Yes	1%	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	Yes	1%	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	Yes	1%	Interact SC200 sensor
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	Yes	1%	Interact SC200 sensor
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	Yes	1%	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	Yes	1%	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	Yes	1%	-

Order Code	Full Product Name	Dimmable	Maximum dim level	Embedded control
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	Yes	1%	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	Yes	1%	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	Yes	1%	Interact SC200 sensor
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Yes	1%	Upgradable sensor slot with SC200 sensor
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	Yes	1%	Upgradable sensor slot with SC200 sensor

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	Yes	DC operated central emergency lighting
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	Yes	DC operated central emergency lighting
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	Yes	DC operated central emergency lighting
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	Yes	DC operated central emergency lighting
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Yes	DC operated central emergency lighting
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Yes	DC operated central emergency lighting
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Yes	DC operated central emergency lighting
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Yes	DC operated central emergency lighting
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	Yes	DC operated central emergency lighting
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	Yes	DC operated central emergency lighting
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	Yes	DC operated central emergency lighting
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	Yes	DC operated central emergency lighting
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	Yes	DC operated central emergency lighting
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	Yes	DC operated central emergency lighting
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	Yes	DC operated central emergency lighting
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	Yes	DC operated central emergency lighting
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	Yes	DC operated central emergency lighting
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	Yes	DC operated central emergency lighting
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	Yes	DC operated central emergency lighting
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	Yes	DC operated central emergency lighting
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	Yes	DC operated central emergency lighting
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	Yes	DC operated central emergency lighting
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	Yes	DC operated central emergency lighting
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	Yes	DC operated central emergency lighting
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	Yes	DC operated central emergency lighting
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Yes	DC operated central emergency lighting
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Yes	DC operated central emergency lighting
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Yes	DC operated central emergency lighting
910505100425	RC463B 34S/940 DEIA W62L62 CPC	Yes	DC operated central emergency lighting
910505100426	RC463B 40S/940 DEIA W62L62 CPC	Yes	DC operated central emergency lighting
910505100489	RC463B 34S/930 DEIA W62L62 CPC	Yes	DC operated central emergency lighting
910505100490	RC463B 40S/930 DEIA W62L62 CPC	Yes	DC operated central emergency lighting
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Yes	DC operated central emergency lighting
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Yes	DC operated central emergency lighting
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Yes	DC operated central emergency lighting
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505100416	RC463B 28S/940 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505100417	RC463B 34S/940 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505100418	RC463B 34S/930 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505100488	RC463B 28S/930 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	No	-
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	No	-
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	Yes	DC operated central emergency lighting
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	No	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	No	-
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	Yes	DC operated central emergency lighting
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	Yes	DC operated central emergency lighting
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	Yes	DC operated central emergency lighting
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	Yes	DC operated central emergency lighting
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	Yes	DC operated central emergency lighting
910505100419	RC463B 40S/930 DEIA W62L62 VPC	Yes	DC operated central emergency lighting
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Yes	DC operated central emergency lighting
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Yes	DC operated central emergency lighting
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	No	Emergency lighting 3 hours duration with DALI interface
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Yes	DC operated central emergency lighting
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Yes	DC operated central emergency lighting
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Yes	DC operated central emergency lighting
910505100269	RC461B 34S/930 PSE W60L60 VPC	No	-
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Yes	DC operated central emergency lighting
910505100595	RC461B 40S/930 DEIA W60L60 VPC	Yes	DC operated central emergency lighting
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	No	Emergency lighting 3 hours duration with DALI interface
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	No	-
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	Yes	DC operated central emergency lighting
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	Yes	DC operated central emergency lighting
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	Yes	DC operated central emergency lighting
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	Yes	DC operated central emergency lighting
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	Yes	DC operated central emergency lighting
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	Yes	DC operated central emergency lighting
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	Yes	DC operated central emergency lighting
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	Yes	DC operated central emergency lighting
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	Yes	DC operated central emergency lighting
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	Yes	DC operated central emergency lighting
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Yes	DC operated central emergency lighting
910505100422	RC463B 34S/930 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505100423	RC463B 40S/940 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505100424	RC463B 40S/930 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505100427	RC463B 34S/940 DEIA W31L125 CPC	Yes	DC operated central emergency lighting
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	Yes	DC operated central emergency lighting
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	Yes	DC operated central emergency lighting
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	Yes	DC operated central emergency lighting
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Yes	DC operated central emergency lighting
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Yes	DC operated central emergency lighting
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	Yes	DC operated central emergency lighting
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	Yes	DC operated central emergency lighting
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	Yes	DC operated central emergency lighting
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	Yes	DC operated central emergency lighting
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Yes	DC operated central emergency lighting
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	Yes	DC operated central emergency lighting
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	Yes	DC operated central emergency lighting
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	Yes	DC operated central emergency lighting
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	Yes	DC operated central emergency lighting
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	Yes	DC operated central emergency lighting
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	Yes	DC operated central emergency lighting
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	Yes	DC operated central emergency lighting
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	Yes	DC operated central emergency lighting
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	Yes	DC operated central emergency lighting
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	Yes	DC operated central emergency lighting
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	Yes	DC operated central emergency lighting
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	Yes	DC operated central emergency lighting
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Yes	DC operated central emergency lighting
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	Temperature 650 °C, duration 30 s
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	Temperature 650 °C, duration 30 s
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	Temperature 650 °C, duration 30 s
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	Temperature 650 °C, duration 30 s
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Temperature 650 °C, duration 30 s
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Temperature 650 °C, duration 30 s
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Temperature 650 °C, duration 30 s
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Temperature 650 °C, duration 30 s
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	Temperature 650 °C, duration 30 s
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	Temperature 650 °C, duration 30 s
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	Temperature 650 °C, duration 30 s
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	Temperature 650 °C, duration 30 s
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	Temperature 650 °C, duration 30 s
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	Temperature 650 °C, duration 30 s
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	Temperature 650 °C, duration 30 s
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	Temperature 650 °C, duration 30 s
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	Temperature 650 °C, duration 30 s
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	Temperature 650 °C, duration 30 s
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	Temperature 650 °C, duration 30 s
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	Temperature 650 °C, duration 30 s
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	Temperature 650 °C, duration 30 s
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	Temperature 650 °C, duration 30 s
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	Temperature 650 °C, duration 30 s
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	Temperature 650 °C, duration 30 s
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Temperature 650 °C, duration 30 s
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Temperature 650 °C, duration 30 s
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Temperature 650 °C, duration 30 s
910505100425	RC463B 34S/940 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s
910505100426	RC463B 40S/940 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s
910505100489	RC463B 34S/930 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s
910505100490	RC463B 40S/930 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Temperature 650 °C, duration 30 s
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Temperature 650 °C, duration 30 s
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Temperature 650 °C, duration 30 s
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505100416	RC463B 28S/940 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505100417	RC463B 34S/940 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505100418	RC463B 34S/930 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910505100488	RC463B 28S/930 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	Temperature 650 °C, duration 30 s
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	Temperature 650 °C, duration 30 s
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	Temperature 650 °C, duration 30 s
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	Temperature 650 °C, duration 30 s
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	Temperature 650 °C, duration 30 s
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	Temperature 650 °C, duration 30 s
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	Temperature 650 °C, duration 30 s
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	Temperature 650 °C, duration 30 s
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	Temperature 650 °C, duration 30 s
910505100419	RC463B 40S/930 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Temperature 650 °C, duration 30 s
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	Temperature 850 °C, duration 30 s
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Temperature 650 °C, duration 30 s
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Temperature 650 °C, duration 30 s
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Temperature 650 °C, duration 30 s
910505100269	RC461B 34S/930 PSE W60L60 VPC	Temperature 650 °C, duration 30 s
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Temperature 650 °C, duration 30 s
910505100595	RC461B 40S/930 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	Temperature 650 °C, duration 30 s
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	Temperature 650 °C, duration 30 s
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	Temperature 650 °C, duration 30 s
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	Temperature 650 °C, duration 30 s
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	Temperature 650 °C, duration 30 s
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	Temperature 650 °C, duration 30 s
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	Temperature 650 °C, duration 30 s
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	Temperature 650 °C, duration 30 s
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	Temperature 650 °C, duration 30 s
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	Temperature 650 °C, duration 30 s
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	Temperature 650 °C, duration 30 s
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s
910505100422	RC463B 34S/930 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s
910505100423	RC463B 40S/940 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s
910505100424	RC463B 40S/930 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s
910505100427	RC463B 34S/940 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Temperature 650 °C, duration 30 s
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Temperature 650 °C, duration 30 s
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	Temperature 650 °C, duration 30 s
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	Temperature 650 °C, duration 30 s
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	Temperature 650 °C, duration 30 s
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	Temperature 650 °C, duration 30 s
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Temperature 650 °C, duration 30 s
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	Temperature 650 °C, duration 30 s
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	Temperature 650 °C, duration 30 s
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	Temperature 650 °C, duration 30 s
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	Temperature 650 °C, duration 30 s
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	Temperature 650 °C, duration 30 s
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	Temperature 650 °C, duration 30 s
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	Temperature 650 °C, duration 30 s
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	Temperature 650 °C, duration 30 s
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	Temperature 650 °C, duration 30 s
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	Temperature 650 °C, duration 30 s
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	Temperature 650 °C, duration 30 s
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	Temperature 650 °C, duration 30 s
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Temperature 650 °C, duration 30 s
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	(0.38, 0.38) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	(0.38, 0.38) SDCM ≤ 3
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	(0.38, 0.38) SDCM ≤ 3
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	(0.38, 0.38) SDCM ≤ 3
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Tunable, SDCM ≤ 3
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Tunable, SDCM ≤ 3
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Tunable, SDCM ≤ 3
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Tunable, SDCM ≤ 3
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Tunable, SDCM ≤ 3
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Tunable, SDCM ≤ 3
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	(0.38, 0.38) SDCM ≤ 3
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	(0.38, 0.38) SDCM ≤ 3
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	(0.43, 0.40) SDCM ≤ 3
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	(0.38, 0.38) SDCM ≤ 3
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	(0.38, 0.38) SDCM ≤ 3
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	(0.43, 0.40) SDCM ≤ 3
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	(0.38, 0.38) SDCM ≤ 3
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	(0.43, 0.40) SDCM ≤ 3
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	(0.38, 0.38) SDCM ≤ 3
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	(0.38, 0.38) SDCM ≤ 3
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	(0.38, 0.38) SDCM ≤ 3
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Tunable, SDCM ≤ 3
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Tunable, SDCM ≤ 3
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Tunable, SDCM ≤ 3
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Tunable, SDCM ≤ 3
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Tunable, SDCM ≤ 3
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Tunable, SDCM ≤ 3
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	(0.38, 0.38) SDCM ≤ 3
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	(0.38, 0.38) SDCM ≤ 3
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	(0.38, 0.38) SDCM ≤ 3

Order Code	Full Product Name	Initial chromaticity
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505100425	RC463B 34S/940 DEIA W62L62 CPC	(0.38, 0.38) SDCM ≤3
910505100426	RC463B 40S/940 DEIA W62L62 CPC	(0.38, 0.38) SDCM ≤3
910505100489	RC463B 34S/930 DEIA W62L62 CPC	(0.43, 0.40) SDCM ≤3
910505100490	RC463B 40S/930 DEIA W62L62 CPC	(0.43, 0.40) SDCM ≤3
910505100277	RC461B 34S/940 DEIA W60L60 PCV	(0.38, 0.38) SDCM ≤3
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100278	RC463B 40S/940 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505100416	RC463B 28S/940 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505100417	RC463B 34S/940 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505100418	RC463B 34S/930 DEIA W62L62 VPC	(0.43, 0.40) SDCM ≤3
910505100488	RC463B 28S/930 DEIA W62L62 VPC	(0.43, 0.40) SDCM ≤3
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	(0.38, 0.38) SDCM ≤3
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	(0.38, 0.38) SDCM ≤3
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	(0.38, 0.38) SDCM ≤3
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	(0.38, 0.38) SDCM ≤3
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	(0.38, 0.38) SDCM ≤3
910505100419	RC463B 40S/930 DEIA W62L62 VPC	(0.43, 0.40) SDCM ≤3
910505100245	RC461B 34S/940 DEIA W60L60 VPC	(0.38, 0.38) SDCM ≤3
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100250	RC461B 40S/940 DEIA W60L60 VPC	(0.38, 0.38) SDCM ≤3
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	(0.38, 0.38) SDCM ≤3
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	(0.43, 0.40) SDCM ≤3
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	(0.38, 0.38) SDCM ≤3
910505100269	RC461B 34S/930 PSE W60L60 VPC	(0.43, 0.40) SDCM ≤3
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	(0.38, 0.38) SDCM ≤3
910505100595	RC461B 40S/930 DEIA W60L60 VPC	(0.43, 0.40) SDCM ≤3
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	(0.38, 0.38) SDCM ≤3
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	(0.38, 0.38) SDCM ≤3
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	(0.38, 0.38) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	(0.38, 0.38) SDCM ≤3
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	(0.38, 0.38) SDCM ≤3
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	(0.38, 0.38) SDCM ≤3
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	(0.38, 0.38) SDCM ≤3
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	(0.38, 0.38) SDCM ≤3
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	(0.38, 0.38) SDCM ≤3
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	(0.38, 0.38) SDCM ≤3
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	(0.38, 0.38) SDCM ≤3
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	(0.38, 0.38) SDCM ≤3
910505100236	RC463B 40S/940 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505100422	RC463B 34S/930 DEIA W31L125 VPC	(0.43, 0.40) SDCM ≤3
910505100423	RC463B 40S/940 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505100424	RC463B 40S/930 DEIA W31L125 VPC	(0.43, 0.40) SDCM ≤3
910505100427	RC463B 34S/940 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100234	RC461B 34S/930 DEIA W30L120 VPC	(0.43, 0.40) SDCM ≤3
910505100235	RC461B 40S/940 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100241	RC461B 34S/940 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	(0.38, 0.38) SDCM ≤3
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	(0.38, 0.38) SDCM ≤3
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	(0.43, 0.40) SDCM ≤3
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	(0.38, 0.38) SDCM ≤3
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	(0.38, 0.38) SDCM ≤3
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	(0.38, 0.38) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	(0.38, 0.38) SDCM ≤3
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	(0.38, 0.38) SDCM ≤3
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	(0.38, 0.38) SDCM ≤3
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	(0.38, 0.38) SDCM ≤3
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	(0.38, 0.38) SDCM ≤3
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	(0.38, 0.38) SDCM ≤3
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	(0.38, 0.38) SDCM ≤3
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	(0.38, 0.38) SDCM ≤3
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	(0.38, 0.38) SDCM ≤3
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	(0.38, 0.38) SDCM ≤3
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	(0.38, 0.38) SDCM ≤3

Product Data


Order Code	Full Product Name	Product family code
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	RC463B
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	RC463B
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	RC461B
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	RC463B
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	RC463B
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	RC463B
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	RC461B
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	RC461B
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	RC461B
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	RC463B
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	RC461B
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	RC461B
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	RC463B
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	RC461B
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	RC461B
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	RC461B
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	RC461B
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	RC461B
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	RC461B
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	RC461B
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	RC461B
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	RC461B
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	RC463B
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	RC463B
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	RC463B
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	RC463B
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	RC461B

Order Code	Full Product Name	Product family code
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	RC461B
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	RC461B
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	RC461B
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	RC461B
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	RC461B
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	RC461B
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	RC461B
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	RC463B
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	RC468B
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	RC461B
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	RC463B
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	RC461B
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	RC461B
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	RC461B
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	RC461B
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	RC461B
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	RC461B
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	RC461B
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	RC461B
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	RC461B
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	RC463B
910505100425	RC463B 34S/940 DEIA W62L62 CPC	RC463B
910505100426	RC463B 40S/940 DEIA W62L62 CPC	RC463B
910505100489	RC463B 34S/930 DEIA W62L62 CPC	RC463B
910505100490	RC463B 40S/930 DEIA W62L62 CPC	RC463B
910505100277	RC461B 34S/940 DEIA W60L60 PCV	RC461B
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	RC463B
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	RC463B
910505100278	RC463B 40S/940 DEIA W62L62 VPC	RC463B
910505100416	RC463B 28S/940 DEIA W62L62 VPC	RC463B
910505100417	RC463B 34S/940 DEIA W62L62 VPC	RC463B
910505100418	RC463B 34S/930 DEIA W62L62 VPC	RC463B
910505100488	RC463B 28S/930 DEIA W62L62 VPC	RC463B
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	RC463B
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	RC468B
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	RC463B
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	RC468B
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	RC463B
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	RC468B
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	RC463B
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	RC468B
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	RC463B


Order Code	Full Product Name	Product family code
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	RC461B
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	RC461B
910505100419	RC463B 40S/930 DEIA W62L62 VPC	RC463B
910505100245	RC461B 34S/940 DEIA W60L60 VPC	RC461B
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	RC461B
910505100250	RC461B 40S/940 DEIA W60L60 VPC	RC461B
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	RC461B
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	RC461B
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	RC461B
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	RC461B
910505100269	RC461B 34S/930 PSE W60L60 VPC	RC461B
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	RC461B
910505100595	RC461B 40S/930 DEIA W60L60 VPC	RC461B
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	RC461B
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	RC461B
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	RC461B
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	RC461B
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	RC461B
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	RC461B
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	RC461B
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	RC461B
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	RC461B
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	RC461B
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	RC461B
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	RC461B
910505100236	RC463B 40S/940 DEIA W31L125 CPC	RC463B
910505100422	RC463B 34S/930 DEIA W31L125 VPC	RC463B
910505100423	RC463B 40S/940 DEIA W31L125 VPC	RC463B
910505100424	RC463B 40S/930 DEIA W31L125 VPC	RC463B
910505100427	RC463B 34S/940 DEIA W31L125 CPC	RC463B
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	RC463B
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	RC463B
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	RC463B
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	RC463B
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	RC461B
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	RC461B
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	RC461B
910505100234	RC461B 34S/930 DEIA W30L120 VPC	RC461B
910505100235	RC461B 40S/940 DEIA W30L120 VPC	RC461B
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	RC461B
910505100241	RC461B 34S/940 DEIA W30L120 VPC	RC461B
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	RC461B

Order Code	Full Product Name	Product family code
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	RC461B
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	RC461B
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	RC461B
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	RC461B
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	RC461B
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	RC461B
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	RC461B
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	RC461B
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	RC461B
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	RC461B
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	RC461B
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	RC461B
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	RC461B
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	RC461B
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	RC463B
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	RC463B
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	RC463B
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	RC463B
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	RC463B
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	RC463B
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	RC463B
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	RC463B
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	RC461B
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	RC461B
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	RC463B
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	RC463B
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	RC463B
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	RC463B


Polar normal diagrams




RC460BN - 910505101692




RC460BP - 910505101671




RC460BN - 910505100270




RC460BP - 910505100235




RC460BN - 910505100251




RC460BN - 910505100259




RC460BN - 910505100416




RC460BN - 910505100271




RC460BP - 910505100427




RC460BN - 910505100425




RC460BN - 910505100266




RC460BN - 910505100269




RC460BN - 910505100256




RC460BN - 910505100426




RC460BN - 910505100261




RC460BN - 910505100265




RC460BP - 910505100422




RC460BN - 910505100418




RC460BN - 910505100417




RC460BN - 910505100245




RC460BN - 910505100489




RC460BP - 910505100423




RC460BP - 910505100241




RC460BN - 910505100419




RC460BN - 910505100250




RC460BP - 910505100424




RC460BP - 910505100238




RC460BP - 910505101674




RC460BN - 910505101716




RC460BN - 910505101680




RC460BN - 910505101718




RC460BN - 910505100490




RC460BN - 910505101683




RC460BN - 910505101719




RC460BN - 910505101722




RC460BN - 910505101715




RC460BN - 910505101712




RC460BP - 910505101728




RC460BP - 910505101667




RC460BN - 910505101713




RC460BN - 910505100277




RC460BN - 910505101720




RC460BN - 910505101682




RC460BN - 910505101689




RC460BP - 910505101675




RC460BP - 910505101670




RC460BN - 910505101693




RC460BN - 910505100488




RC460BP - 910505101676




RC460BN - 910505101688




RC460BN - 910505101679




RC460BP - 910505101730




RC460BN - 910505101690




RC460BN - 910505101714




RC460BN - 910505103390




RC460BN - 910505101691




RC460BN - 910505100595




RC460BP - 910505100236




RC460BN - 910505101717




RC460BN - 910505101721




RC460BP - 910505100234




RC460BN - 910505101710




RC460BN - 910505101681




RC460BN - 910505101684




RC460BP - 910505101729




RC460BP - 910505101731




RC460BP - 910505101727




RC460BP - 910505101668




RC460BP - 910505101669




RC460BP - 910505101666




RC460BP - 910505101677




RC460BN - 910505101678




RC460BN - 910505101685




RC460BN - 910505101711




RC460BP - 910505103619




RC460BN - 910505103620




RC460BP - 910505103623




RC460BN - 910505103622




RC460BP - 910505103621




RC460BN - 910505103624




RC460BP - 910505103625




RC460BN - 910505103628




RC460BP - 910505103627




RC460BN - 910505103626




RC460BN - 910505103630




RC460BN - 910505103632




RC460BP - 910505103633




RC460BP - 910505103629




RC460BP - 910505103631




RC460BP - 910505103635




RC460BN - 910505103634




RC460BN - 910505103636




RC460BP - 910505103637




RC460BN - 910505103638




RC460BN - 910505103642




RC460BN - 910505103639




RC460BN - 910505103641




RC460BN - 910505103643




RC460BN - 910505103640




RC460BP - 910505103644




RC460BP - 910505103645




RC460BP - 910505103647




RC460BP - 910505103646




RC460BP - 910505103384




RC460BN - 910505103383




RC460BN - 910505103385




RC460BN - 910505103386




RC460BP - 910505103388




RC460BP - 910505103387




RC460BN - 910505103393




RC460BP - 910505103394




RC460BN - 910505103392




RC460BP - 910505103391




RC460BP - 910505103395




RC460BN - 910505100252




RC460BP - 910505100232




RC460BN - 910505100249




RC460BN - 910505100278




910505105870




910505105878




910505105871




910505105876




910505105883




910505105873




910505105888




910505105890




910505105886




910505105884




910505105880




910505105875




910505105882




910505105881




910505105885




910505105872




910505105889




910505105874



910505105877



910505105887



910505105879

