



PowerBalance Gen2: sustainable performance

PowerBalance gen2

When it comes to lighting office spaces with LED luminaires, businesses are willing to invest in sustainability, provided they get a payback on their investment. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. Philips PowerBalance Gen2 is our most energy-efficient, office-compliant LED luminaire. Designed for circularity and enhanced wellbeing, this office luminaire also promises future-proof connectivity. State-of-the-art efficacy (at CRI >90), upgradability features, a long lifetime, reparability, and design for recyclability make PowerBalance Gen2 a true 'green choice'. One that also delivers significantly lower operational costs to ensure an attractive payback that meets the needs of businesses and the specification market. The Gen2 architecture in the latest PowerBalance range has enabled us to create a range of highly-versatile modular and semi-modular luminaires. These LED luminaires can be easily mounted in ceilings with an exposed T-bar or concealed T-bar, as well as plaster ceilings and bandraaster-type ceilings. PowerBalance is a solution with superior lighting specifications combined with a best-in-class connectivity designed for Circularity & enhanced Wellbeing using Interact Pro - all with a sustainable approach to high-performance office lighting.

Benefits

- Extremely-efficient LED luminaire with upto 174 lm/W
- Complies with office norms
- Comfortable, glare-free light
- Significantly reduces operational costs for an attractive payback time
- Sustainable and best-in-class connected offer

PowerBalance gen2

Features

- Best-in-class efficacy up to 174lm/W supports green building design and energy saving subsidy criteria
- 3000K, 4000K, Tunable White options with CRI >90
- Long lifetime 50,000 hours @L90
- Prepared for circularity (no glue, replaceable electronics, upgradable system, efficient and long lifetime)
- Environmental Product Declaration (EPD) guide
- Connected system ready with Interact Pro scalable platform using integrated sensors and/or wireless drivers for data collection, occupancy, daylight regulation and wayfinding

Application

- Offices
- Education
- Healthcare

Warnings and Safety

- The product is IP20 and, as such, is not protected against water ingress. Therefore we strongly recommend that the environment in which the luminaire is to be installed should be suitably checked
- If the advice above is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void


Versions




PowerBalance RC463B W31L125 CWL



IPPR RC460Bi 0025



IPPR_RC460Bi_0043-Product photo



IPPR_RC460Bi_0053-Product photo



PowerBalance RC461B W30L120 CWL U4



PowerBalance RC463B W62L62 CWL CPC




PowerBalance RC463B W62L62 CWL CPC U4



PowerBalance RC463B W31L125 CWL U4

Dimensional drawing



PowerBalance gen2

Product details



IPDP_RC460Bi_0153-Detail photo



Upgradable sensor



IPDP_RC460Bi_0039-Detail photo



IPDP_RC460Bi_0041-Detail photo



IPDP_RC460Bi_0043-Detail photo



IPDP_RC460Bi_0045-Detail photo




IPDP_RC460Bi_0047-Detail photo



IPDP_RC460Bi_0049-Detail photo

PowerBalance gen2

Product details



IPDP_RC460Bi_0051-Detail photo



IPDP_RC460Bi_0053-Detail photo



IPDP_RC460Bi_0054-Detail photo



IPDP_RC460Bi_0055-Detail photo



IPDP_RC460Bi_0073-Detail photo



IPDP_RC460Bi_0081-Detail photo



IPDP_RC460Bi_0103-Detail photo



PowerBalance LEAF DP

PowerBalance gen2

Product details



PowerBalance_RC461_W31L125_I
A4-DPP



PowerBalance SC200 DPP



PowerBalance SC200 DPP



PowerBalance SC200 DPP



PowerBalance CPC DP



PowerBalance SC200 DPP

General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Beam angle of light source	120 degree(s)
Optic type	Wide beam office compliant
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Explosion hazard class	-
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20/40
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable	Service tag
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	-	-	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	-	-	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	-	No	Yes
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	-	No	Yes
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	-	No	Yes
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	-	No	Yes
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	-	No	Yes
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	-	No	Yes
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	-	No	Yes
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	-	No	Yes
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	-	No	Yes
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	-	No	Yes
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	-	No	Yes
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	-	No	Yes
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	-	No	Yes
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	-	No	Yes
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	-	No	Yes
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	-	No	Yes
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	-	No	Yes
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	-	No	Yes
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	-	No	Yes
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	-	No	Yes
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	-	No	Yes
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	-	No	Yes
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	-	No	Yes
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	-	No	Yes
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	-	No	Yes
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	-	No	Yes
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	-	No	Yes
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	-	No	Yes
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	-	No	Yes
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	-	No	Yes
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	-	No	Yes
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	-	No	Yes
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	-	No	Yes
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	-	No	Yes
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	-	No	Yes
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	-	No	Yes
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	-	No	Yes
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	-	No	Yes
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	-	No	Yes
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	-	No	Yes
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	-	No	Yes
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	-	No	Yes
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	-	-	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-	-	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	LED34S	No	Yes
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	LED34S	No	Yes
910505100425	RC463B 34S/940 DEIA W62L62 CPC	-	No	Yes
910505100426	RC463B 40S/940 DEIA W62L62 CPC	-	No	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Service tag
910505100489	RC463B 34S/930 DEIA W62L62 CPC	-	No	Yes
910505100490	RC463B 40S/930 DEIA W62L62 CPC	-	No	Yes
910505100277	RC461B 34S/940 DEIA W60L60 PCV	LED34S	No	Yes
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	LED28S	No	Yes
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	LED34S	No	Yes
910505100278	RC463B 40S/940 DEIA W62L62 VPC	LED40S	No	Yes
910505100416	RC463B 28S/940 DEIA W62L62 VPC	-	No	Yes
910505100417	RC463B 34S/940 DEIA W62L62 VPC	-	No	Yes
910505100418	RC463B 34S/930 DEIA W62L62 VPC	-	No	Yes
910505100488	RC463B 28S/930 DEIA W62L62 VPC	-	No	Yes
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	-	No	Yes
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	-	No	Yes
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	-	No	Yes
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	-	No	Yes
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	-	No	Yes
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	-	No	Yes
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	-	No	Yes
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	-	No	Yes
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	-	No	Yes
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	-	No	Yes
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	-	No	Yes
910505100419	RC463B 40S/930 DEIA W62L62 VPC	-	No	Yes
910505100245	RC461B 34S/940 DEIA W60L60 VPC	LED34S	No	Yes
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	LED40S	No	Yes
910505100250	RC461B 40S/940 DEIA W60L60 VPC	LED40S	No	Yes
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	LED40S	No	Yes
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	LED34S	No	Yes
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	LED40S	No	Yes
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	LED40S	No	Yes
910505100269	RC461B 34S/930 PSE W60L60 VPC	LED34S	No	Yes
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	LED34S	No	Yes
910505100595	RC461B 40S/930 DEIA W60L60 VPC	-	No	Yes
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	-	No	Yes
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	-	No	Yes
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	-	No	Yes
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	-	No	Yes
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	-	No	Yes
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	-	No	Yes
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	-	No	Yes
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	-	No	Yes
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	-	No	Yes
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	-	No	Yes
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	-	No	Yes
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	-	No	Yes
910505100236	RC463B 40S/940 DEIA W31L125 CPC	LED40S	No	Yes
910505100422	RC463B 34S/930 DEIA W31L125 VPC	-	No	Yes
910505100423	RC463B 40S/940 DEIA W31L125 VPC	-	No	Yes
910505100424	RC463B 40S/930 DEIA W31L125 VPC	-	No	Yes
910505100427	RC463B 34S/940 DEIA W31L125 CPC	-	No	Yes
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	-	No	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Service tag
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	-	No	Yes
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	-	No	Yes
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	-	No	Yes
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	-	No	Yes
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	-	No	Yes
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	LED34S	No	Yes
910505100234	RC461B 34S/930 DEIA W30L120 VPC	LED34S	No	Yes
910505100235	RC461B 40S/940 DEIA W30L120 VPC	LED40S	No	Yes
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	LED40S	No	Yes
910505100241	RC461B 34S/940 DEIA W30L120 VPC	LED34S	No	Yes
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	-	No	Yes
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	-	No	Yes
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	-	No	Yes
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	-	No	Yes
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	-	No	Yes
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	-	No	Yes
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	-	No	Yes
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	-	No	Yes
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	-	No	Yes
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	-	No	Yes
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	-	No	Yes
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	-	No	Yes
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	-	-	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	-	-	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-	-	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	-	-	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	-	-	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	-	-	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	-	-	-
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	-	-	-
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	-	-	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	-	-	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	-	-	-
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	-	-	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	-	-	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	-	-	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	-	-	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-	-	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	-	-	-

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	4000 K	>90	146 lm/W	4,000 lm	910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	4000 K	>80	172 lm/W	3,400 lm

PowerBalance gen2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	4000 K	>90	139 lm/W	3,400 lm
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	4000 K	>90	139 lm/W	3,400 lm
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	4000 K	>90	138 lm/W	4,000 lm
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	4000 K	>90	130 lm/W	6,000 lm
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	4000 K	>90	139 lm/W	3,400 lm
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Tunable white 2700-5000 K	>90	125 lm/W	8,000 lm
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Tunable white 2700-5000 K	>90	125 lm/W	8,000 lm
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Tunable white 2700-5000 K	>90	125 lm/W	8,000 lm
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	4000 K	>80	172 lm/W	3,400 lm
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	4000 K	>80	172 lm/W	3,400 lm
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	4000 K	>80	174 lm/W	4,000 lm
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	4000 K	>80	174 lm/W	4,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	4000 K	>80	172 lm/W	3,400 lm
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	4000 K	>80	174 lm/W	4,000 lm
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	3000 K	>90	131 lm/W	3,400 lm
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	4000 K	>90	139 lm/W	3,400 lm
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	4000 K	>90	138 lm/W	4,000 lm
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	4000 K	>90	137 lm/W	2,800 lm
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	4000 K	>90	139 lm/W	3,400 lm
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	4000 K	>90	138 lm/W	4,000 lm
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	4000 K	>90	144 lm/W	6,000 lm
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	3000 K	>90	131 lm/W	3,400 lm
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	4000 K	>90	139 lm/W	3,400 lm
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	3000 K	>90	131 lm/W	3,400 lm
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	4000 K	>90	139 lm/W	3,400 lm
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	4000 K	>90	139 lm/W	3,400 lm
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	4000 K	>90	138 lm/W	4,000 lm
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm

PowerBalance gen2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505103390	RC461B 80S/TWBW SEIA W60L60 VPC U4	Tunable white 2700-5000 K	>90	125 lm/W	8,000 lm
910505103392	RC461B 80S/TWBW SEIA W60L60 VPC U4 SC	Tunable white 2700-5000 K	>90	125 lm/W	8,000 lm
910505103393	RC463B 80S/TWBW SEIA W62L62 VPC U4	Tunable white 2700-5000 K	>90	125 lm/W	8,000 lm
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	4000 K	>80	172 lm/W	3,400 lm
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	4000 K	>80	172 lm/W	3,400 lm
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	4000 K	>80	174 lm/W	4,000 lm
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	4000 K	>80	174 lm/W	4,000 lm
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	4000 K	>80	172 lm/W	3,400 lm
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	4000 K	>80	174 lm/W	4,000 lm
910505105877	RC461B 80S/TWBW SEIA W60L60 CWLVPC U4SC	Tunable white 2700-5000 K	≥80	131 lm/W	8,000 lm
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Tunable white 2700-6500 K	>90	122 lm/W	7,800 lm
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	4000 K	>90	142 lm/W	3,400 lm
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	4000 K	>90	142 lm/W	3,400 lm
910505100425	RC463B 34S/940 DEIA W62L62 CPC	4000 K	>90	142 lm/W	3,400 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505100426	RC463B 40S/940 DEIA W62L62 CPC	4000 K	>90	146 lm/W	4,000 lm
910505100489	RC463B 34S/930 DEIA W62L62 CPC	3000 K	>90	133 lm/W	3,400 lm
910505100490	RC463B 40S/930 DEIA W62L62 CPC	3000 K	>90	133 lm/W	4,000 lm
910505100277	RC461B 34S/940 DEIA W60L60 PCV	4000 K	>90	142 lm/W	3,400 lm
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	4000 K	>90	141 lm/W	2,800 lm
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	4000 K	>90	142 lm/W	3,400 lm
910505100278	RC463B 40S/940 DEIA W62L62 VPC	4000 K	>90	146 lm/W	4,000 lm
910505100416	RC463B 28S/940 DEIA W62L62 VPC	4000 K	>90	141 lm/W	2,800 lm
910505100417	RC463B 34S/940 DEIA W62L62 VPC	4000 K	>90	142 lm/W	3,400 lm
910505100418	RC463B 34S/930 DEIA W62L62 VPC	3000 K	>90	133 lm/W	3,400 lm
910505100488	RC463B 28S/930 DEIA W62L62 VPC	3000 K	>90	133 lm/W	2,800 lm
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	4000 K	>80	129 lm/W	2,800 lm
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	4000 K	>80	129 lm/W	2,800 lm
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	4000 K	>80	124 lm/W	4,000 lm
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	4000 K	>80	124 lm/W	4,000 lm

PowerBalance gen2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	4000 K	>80	173 lm/W	2,800 lm
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	4000 K	>80	172 lm/W	3,400 lm
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	4000 K	>80	174 lm/W	4,000 lm
910505100419	RC463B 40S/930 DEIA W62L62 VPC	3000 K	>90	133 lm/W	4,000 lm
910505100245	RC461B 34S/940 DEIA W60L60 VPC	4000 K	>90	142 lm/W	3,400 lm
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	4000 K	>90	140 lm/W	4,000 lm
910505100250	RC461B 40S/940 DEIA W60L60 VPC	4000 K	>90	146 lm/W	4,000 lm
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	4000 K	>90	140 lm/W	4,000 lm
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	4000 K	>90	142 lm/W	3,400 lm
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	3000 K	>90	133 lm/W	4,000 lm
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	4000 K	>90	140 lm/W	4,000 lm
910505100269	RC461B 34S/930 PSE W60L60 VPC	3000 K	>90	136 lm/W	3,400 lm
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	4000 K	>90	142 lm/W	3,400 lm
910505100595	RC461B 40S/930 DEIA W60L60 VPC	3000 K	>90	133 lm/W	4,000 lm
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101682	RC461B 28S/ BU840 DEIA W60L60 VPC	4000 K	>80	129 lm/W	2,800 lm
910505101683	RC461B 28S/ BU840 DEIA W60L60 VPC SC	4000 K	>80	129 lm/W	2,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101690	RC461B 40S/ BU840 DEIA W60L60 PCV W3W2	4000 K	>80	124 lm/W	4,000 lm
910505101691	RC461B 40S/ BU840 DEIA W60L60 PCV W3W2 SC	4000 K	>80	124 lm/W	4,000 lm
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	4000 K	>80	173 lm/W	2,800 lm
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	4000 K	>80	173 lm/W	2,800 lm
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	4000 K	>80	172 lm/W	3,400 lm
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	4000 K	>80	172 lm/W	3,400 lm
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	4000 K	>80	174 lm/W	4,000 lm
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	4000 K	>80	174 lm/W	4,000 lm
910505100236	RC463B 40S/940 DEIA W31L125 CPC	4000 K	>90	140 lm/W	4,000 lm
910505100422	RC463B 34S/930 DEIA W31L125 VPC	3000 K	>90	133 lm/W	3,400 lm
910505100423	RC463B 40S/940 DEIA W31L125 VPC	4000 K	>90	146 lm/W	4,000 lm
910505100424	RC463B 40S/930 DEIA W31L125 VPC	3000 K	>90	133 lm/W	4,000 lm
910505100427	RC463B 34S/940 DEIA W31L125 CPC	4000 K	>90	142 lm/W	3,400 lm
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101671	RC463B 28S/ BU840 DEIA W31L125 VPC	4000 K	>80	129 lm/W	2,800 lm
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101677	RC463B 28S/ BU840 DEIA W31L125 CPC	4000 K	>80	129 lm/W	2,800 lm
910505103644	RC463B 34S/ UE840 DEIA W31L125 VPC	4000 K	>80	172 lm/W	3,400 lm

PowerBalance gen2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103646	RC463B 40S/ UE840 DEIA W31L125 VPC	4000 K	>80	174 lm/W	4,000 lm
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	4000 K	>90	142 lm/W	3,400 lm
910505100234	RC461B 34S/930 DEIA W30L120 VPC	3000 K	>90	133 lm/W	3,400 lm
910505100235	RC461B 40S/940 DEIA W30L120 VPC	4000 K	>90	146 lm/W	4,000 lm
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	4000 K	>90	140 lm/W	4,000 lm
910505100241	RC461B 34S/940 DEIA W30L120 VPC	4000 K	>90	142 lm/W	3,400 lm
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	Tunable white 2700-6500 K	>90	122 lm/W	8,000 lm
910505101669	RC461B 28S/ BU840 DEIA W30L120 VPC	4000 K	>80	129 lm/W	2,800 lm
910505101670	RC461B 28S/ BU840 DEIA W30L120 VPC SC	4000 K	>80	129 lm/W	2,800 lm
910505101675	RC461B 28S/ BU840 DEIA W30L120 PCV	4000 K	>80	129 lm/W	2,800 lm
910505101676	RC461B 28S/ BU840 DEIA W30L120 PCV SC	4000 K	>80	129 lm/W	2,800 lm
910505103619	RC461B 28S/ UE840 DEIA W30L120 VPC	4000 K	>80	169 lm/W	2,800 lm
910505103621	RC461B 28S/ UE840 DEIA W30L120 VPC SC	4000 K	>80	173 lm/W	2,800 lm
910505103623	RC461B 34S/ UE840 DEIA W30L120 VPC	4000 K	>80	172 lm/W	3,400 lm
910505103627	RC461B 34S/ UE840 DEIA W30L120 VPC SC	4000 K	>80	172 lm/W	3,400 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103631	RC461B 40S/ UE840 DEIA W30L120 VPC	4000 K	>80	174 lm/W	4,000 lm
910505103635	RC461B 40S/ UE840 DEIA W30L120 VPC SC	4000 K	>80	174 lm/W	4,000 lm
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	3000 K	>90	138 lm/W	4,000 lm
910505105879	RC461B 40S/ UE840 DEIA W60L60 CWL VPC	4000 K	>80	167 lm/W	4,000 lm
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Tunable white 2700-6500 K	>90	122 lm/W	7,800 lm
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	4000 K	>90	148 lm/W	3,400 lm
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	4000 K	>90	146 lm/W	4,000 lm
910505105889	RC463B 34S/ UE840 DEIA W62L62 CPC CWL	4000 K	>80	172 lm/W	3,400 lm
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	4000 K	>90	138 lm/W	4,000 lm
910505105890	RC463B 34S/ UE840 SEIA W62L62 CPC CWL IA4	4000 K	>80	172 lm/W	3,400 lm
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	4000 K	>90	148 lm/W	3,400 lm
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	4000 K	>90	146 lm/W	4,000 lm
910505105887	RC463B 34S/ UE840 DEIA W62L62 VPC CWL	4000 K	>80	172 lm/W	3,400 lm
910505105871	RC461B 40S/ UE840 DEIA W30L120 VPC CWL SC	4000 K	>80	167 lm/W	4,000 lm
910505105872	RC461B 28S/ UE840 DEIA W30L120 VPC CWL	4000 K	>80	169 lm/W	2,800 lm

PowerBalance gen2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	4000 K	>90	138 lm/W	4,000 lm
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	4000 K	>90	138 lm/W	4,000 lm
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Tunable white 2700-6500 K	>90	122 lm/W	7,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505105888	RC463B 34S/ UE840 SEIA W62L62 VPC CWL U4	4000 K	>80	172 lm/W	3,400 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	-
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	-
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	-
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	-
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	-
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	-
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	-
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	-
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	-
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	-
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	-
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	-
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	-
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	-
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	-
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	-
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	-
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	-
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	-
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	-
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	-
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	-
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	-
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	-
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	-
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	-
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	-
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	-
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	-
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	-
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	-
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	-
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	-

Order Code	Full Product Name	Number of light sources
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	-
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	-
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	-
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	-
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	-
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	-
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	-
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	-
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	-
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	1
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	1
910505100425	RC463B 34S/940 DEIA W62L62 CPC	-
910505100426	RC463B 40S/940 DEIA W62L62 CPC	-
910505100489	RC463B 34S/930 DEIA W62L62 CPC	-
910505100490	RC463B 40S/930 DEIA W62L62 CPC	-
910505100277	RC461B 34S/940 DEIA W60L60 PCV	1
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	1
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	1
910505100278	RC463B 40S/940 DEIA W62L62 VPC	1
910505100416	RC463B 28S/940 DEIA W62L62 VPC	-
910505100417	RC463B 34S/940 DEIA W62L62 VPC	-
910505100418	RC463B 34S/930 DEIA W62L62 VPC	-
910505100488	RC463B 28S/930 DEIA W62L62 VPC	-
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	-
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	-
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	-
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	-
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	-
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	-
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	-
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	-
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	-

PowerBalance gen2

Order Code	Full Product Name	Number of light sources
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	-
910505100419	RC463B 40S/930 DEIA W62L62 VPC	-
910505100245	RC461B 34S/940 DEIA W60L60 VPC	1
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	1
910505100250	RC461B 40S/940 DEIA W60L60 VPC	1
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	1
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	1
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	1
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	1
910505100269	RC461B 34S/930 PSE W60L60 VPC	1
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	1
910505100595	RC461B 40S/930 DEIA W60L60 VPC	-
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	-
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	-
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	-
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	-
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	-
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	-
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	-
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	-
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	-
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	-
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	-
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	-
910505100236	RC463B 40S/940 DEIA W31L125 CPC	1
910505100422	RC463B 34S/930 DEIA W31L125 VPC	-
910505100423	RC463B 40S/940 DEIA W31L125 VPC	-
910505100424	RC463B 40S/930 DEIA W31L125 VPC	-
910505100427	RC463B 34S/940 DEIA W31L125 CPC	-
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	-
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	-
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	-
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	-
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	-
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	-

Order Code	Full Product Name	Number of light sources
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	1
910505100234	RC461B 34S/930 DEIA W30L120 VPC	1
910505100235	RC461B 40S/940 DEIA W30L120 VPC	1
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	1
910505100241	RC461B 34S/940 DEIA W30L120 VPC	1
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	-
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	-
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	-
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	-
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	-
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	-
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	-
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	-
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	-
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	-
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	-
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	-
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	-
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	-
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	-
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	29 W	No
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	24 W	No
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	25 W	Yes (relates to presence/movement detection and daylight harvesting)
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	25 W	Yes (relates to presence/

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	29 W	Yes (relates to presence/movement detection and daylight harvesting)
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	45 W	Yes (relates to presence/movement

PowerBalance gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching	Order Code	Full Product Name	Power Consumption	Suitable for random switching
			detection and daylight harvesting)				detection and daylight harvesting)
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	25 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	21 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	23 W	Yes (relates to presence/ movement	910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	45 W	Yes (relates to presence/ movement

PowerBalance gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching	Order Code	Full Product Name	Power Consumption	Suitable for random switching
			detection and daylight harvesting)				detection and daylight harvesting)
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	26 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	25 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	26 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	25 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	25 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	29 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	20 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	23 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	64 W	Yes (relates to presence/ movement detection and daylight harvesting)	910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	64 W	Yes (relates to presence/ movement)	910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	64 W	Yes (relates to presence/ movement)

PowerBalance gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
			detection and daylight harvesting)
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	24 W	No
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	24 W	No
910505100425	RC463B 34S/940 DEIA W62L62 CPC	24 W	No
910505100426	RC463B 40S/940 DEIA W62L62 CPC	29 W	No
910505100489	RC463B 34S/930 DEIA W62L62 CPC	26 W	No
910505100490	RC463B 40S/930 DEIA W62L62 CPC	30 W	No
910505100277	RC461B 34S/940 DEIA W60L60 PCV	24 W	No
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	20 W	No
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	24 W	No
910505100278	RC463B 40S/940 DEIA W62L62 VPC	29 W	No
910505100416	RC463B 28S/940 DEIA W62L62 VPC	20 W	No
910505100417	RC463B 34S/940 DEIA W62L62 VPC	24 W	No
910505100418	RC463B 34S/930 DEIA W62L62 VPC	26 W	No
910505100488	RC463B 28S/930 DEIA W62L62 VPC	21 W	No
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	64 W	No
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	64 W	No
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	23 W	No
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	23 W	No
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	64 W	No
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	64 W	No
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	33 W	No
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	33 W	No
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	16 W	No
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	20 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	23 W	No
910505100419	RC463B 40S/930 DEIA W62L62 VPC	30 W	No
910505100245	RC461B 34S/940 DEIA W60L60 VPC	24 W	No
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	29 W	No
910505100250	RC461B 40S/940 DEIA W60L60 VPC	29 W	No
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	29 W	No
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	24 W	No
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	30 W	No
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	29 W	No
910505100269	RC461B 34S/930 PSE W60L60 VPC	25 W	No
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	24 W	No
910505100595	RC461B 40S/930 DEIA W60L60 VPC	30 W	No
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	64 W	No
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	64 W	No
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	23 W	No
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	23 W	No
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	33 W	No
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	33 W	No
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	16 W	No
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	16 W	No
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	20 W	No
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	20 W	No
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	23 W	No
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	23 W	No
910505100236	RC463B 40S/940 DEIA W31L125 CPC	29 W	No

PowerBalance gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505100422	RC463B 34S/930 DEIA W31L125 VPC	26 W	No
910505100423	RC463B 40S/940 DEIA W31L125 VPC	29 W	No
910505100424	RC463B 40S/930 DEIA W31L125 VPC	30 W	No
910505100427	RC463B 34S/940 DEIA W31L125 CPC	24 W	No
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	64 W	No
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	23 W	No
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	64 W	No
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	23 W	No
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	20 W	No
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	23 W	No
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	24 W	No
910505100234	RC461B 34S/930 DEIA W30L120 VPC	26 W	No
910505100235	RC461B 40S/940 DEIA W30L120 VPC	29 W	No
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	29 W	No
910505100241	RC461B 34S/940 DEIA W30L120 VPC	24 W	No
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	64 W	No
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	64 W	No
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	23 W	No
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	23 W	No
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	23 W	No
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	23 W	No
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	16 W	No
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	16 W	No
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	20 W	No
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	20 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	23 W	No
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	23 W	No
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	29 W	No
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	23 W	No
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	64 W	Yes (relates to presence/movement detection and daylight harvesting)
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	23 W	No
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	28 W	No
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	20 W	No
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	23 W	Yes (relates to presence/movement detection and daylight harvesting)
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	29 W	Yes (relates to presence/movement detection and daylight harvesting)
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	23 W	No
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	28 W	No
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	20 W	No
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	21 W	No
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	28 W	No
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	24 W	Yes (relates to presence/movement detection and daylight harvesting)
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	29 W	Yes (relates to presence/movement detection and daylight harvesting)
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	64 W	Yes (relates to presence/

PowerBalance gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
			movement detection and daylight harvesting)
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	20 W	Yes (relates to presence/ movement detection and daylight harvesting)

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	Yes	-	1%
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	Yes	-	1%
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	Yes	Interact SC200 sensor	1%
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	Yes	Interact SC200 sensor	1%
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	Yes	Interact SC200 sensor	1%
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	Yes	Interact SC200 sensor	1%
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	Yes	Interact SC200 sensor	1%
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Yes	Interact SC200 sensor	1%
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Yes	Interact SC200 sensor	1%
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Yes	Interact SC200 sensor	1%
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Yes	Interact SC200 sensor	1%
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Yes	Interact SC200 sensor	1%
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Yes	Interact SC200 sensor	1%
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	Yes	Interact SC200 sensor	1%
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	Yes	Interact SC200 sensor	1%
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	Yes	Interact SC200 sensor	1%
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	Yes	Interact SC200 sensor	1%
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	Yes	Interact SC200 sensor	1%
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	Yes	Interact SC200 sensor	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	Yes	Upgradable sensor slot with SC200 sensor	1%

PowerBalance gen2

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	Yes	Upgradable sensor slot with SC200 sensor	1%
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Yes	-	1%
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Yes	-	1%
910505100425	RC463B 34S/940 DEIA W62L62 CPC	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100426	RC463B 40S/940 DEIA W62L62 CPC	Yes	-	1%
910505100489	RC463B 34S/930 DEIA W62L62 CPC	Yes	-	1%
910505100490	RC463B 40S/930 DEIA W62L62 CPC	Yes	-	1%
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Yes	-	1%
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Yes	-	1%
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Yes	-	1%
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Yes	-	1%
910505100416	RC463B 28S/940 DEIA W62L62 VPC	Yes	-	1%
910505100417	RC463B 34S/940 DEIA W62L62 VPC	Yes	-	1%
910505100418	RC463B 34S/930 DEIA W62L62 VPC	Yes	-	1%
910505100488	RC463B 28S/930 DEIA W62L62 VPC	Yes	-	1%
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	Yes	-	1%
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	Yes	-	1%
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	Yes	-	1%
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	Yes	-	1%
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	Yes	-	1%
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	Yes	-	1%
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	Yes	-	1%
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	Yes	-	1%
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	Yes	-	1%
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	Yes	-	1%
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	Yes	-	1%
910505100419	RC463B 40S/930 DEIA W62L62 VPC	Yes	-	1%
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Yes	-	1%
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Yes	-	1%

PowerBalance gen2

Order Code	Full Product Name	Dimmable	Embedded	Maximum
			control	dim level
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Yes	-	1%
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	Yes	-	1% (no dimming in emergency mode)
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Yes	-	1%
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Yes	-	1%
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Yes	-	1%
910505100269	RC461B 34S/930 PSE W60L60 VPC	No	-	Not applicable
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Yes	-	1%
910505100595	RC461B 40S/930 DEIA W60L60 VPC	Yes	-	1%
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	Yes	-	1%
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	Yes	-	1%
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	Yes	-	1%
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	Yes	-	1%
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	Yes	-	1%
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	Yes	-	1%
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	Yes	-	1%
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	Yes	-	1%
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	Yes	-	1%
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	Yes	-	1%
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	Yes	-	1%
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	Yes	-	1%
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Yes	-	1%
910505100422	RC463B 34S/930 DEIA W31L125 VPC	Yes	-	1%
910505100423	RC463B 40S/940 DEIA W31L125 VPC	Yes	-	1%
910505100424	RC463B 40S/930 DEIA W31L125 VPC	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded	Maximum
			control	dim level
910505100427	RC463B 34S/940 DEIA W31L125 CPC	Yes	-	1%
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	Yes	-	1%
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	Yes	-	1%
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	Yes	-	1%
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	Yes	-	1%
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	Yes	-	1%
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	Yes	-	1%
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Yes	-	1%
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Yes	-	1%
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Yes	-	1%
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Yes	-	1%
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Yes	-	1%
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	Yes	-	1%
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	Yes	-	1%
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	Yes	-	1%
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	Yes	-	1%
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	Yes	-	1%
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	Yes	-	1%
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	Yes	-	1%
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	Yes	-	1%
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	Yes	-	1%
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	Yes	-	1%
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	Yes	-	1%
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	Yes	-	1%
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	Yes	-	1%

PowerBalance gen2

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	Yes	-	1%
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Yes	Interact SC200 sensor	1%
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	Yes	-	1%
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	Yes	-	1%
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	Yes	-	1%
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	Yes	Interact SC200 sensor	1%
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	Yes	Interact SC200 sensor	1%
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	Yes	-	1%
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	Yes	-	1%
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	Yes	-	1%
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	Yes	-	1%
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	Yes	Interact SC200 sensor	1%
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	Yes	Upgradable sensor slot with SC200 sensor	1%

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	-
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	-
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	-
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	-
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	-
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	-
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	-
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	-
910505103391	RC461B 80S/TWBUS EIA W30L120 VPC U4 SC	-
910505103394	RC461B 80S/TWBUS EIA W30L120 VPC U4	-
910505103395	RC463B 80S/TWBUS EIA W31L125 VPC U4	-
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	-
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	-
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	-
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	-
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	-
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	-
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	-
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	-
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	-
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	-
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	-
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	-
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	-
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	-
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	-
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	-

Order Code	Full Product Name	Optical cover type
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	-
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	-
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	-
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	-
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	-
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	-
910505103390	RC461B 80S/TWBUS EIA W60L60 VPC U4	-
910505103392	RC461B 80S/TWBUS EIA W60L60 VPC U4 SC	-
910505103393	RC463B 80S/TWBUS EIA W62L62 VPC U4	-
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	-
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	-
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	-
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	-
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	-
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	-
910505105877	RC461B 80S/TWBUS EIA W60L60 CWLVPC U4SC	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Polycarbonate bowl/cover
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Polycarbonate bowl/cover
910505100425	RC463B 34S/940 DEIA W62L62 CPC	-
910505100426	RC463B 40S/940 DEIA W62L62 CPC	-
910505100489	RC463B 34S/930 DEIA W62L62 CPC	-
910505100490	RC463B 40S/930 DEIA W62L62 CPC	-
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Polycarbonate bowl/cover

PowerBalance gen2

Order Code	Full Product Name	Optical cover type
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Polycarbonate bowl/cover
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Polycarbonate bowl/cover
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Polycarbonate bowl/cover
910505100416	RC463B 28S/940 DEIA W62L62 VPC	-
910505100417	RC463B 34S/940 DEIA W62L62 VPC	-
910505100418	RC463B 34S/930 DEIA W62L62 VPC	-
910505100488	RC463B 28S/930 DEIA W62L62 VPC	-
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	-
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	-
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	-
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	-
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	-
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	-
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	-
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	-
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	-
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	-
910505100419	RC463B 40S/930 DEIA W62L62 VPC	-
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Polycarbonate bowl/cover
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Polycarbonate bowl/cover
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Polycarbonate bowl/cover
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	Polycarbonate bowl/cover
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Polycarbonate bowl/cover
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Polycarbonate bowl/cover
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Polycarbonate bowl/cover
910505100269	RC461B 34S/930 PSE W60L60 VPC	Polycarbonate bowl/cover
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Polycarbonate bowl/cover
910505100595	RC461B 40S/930 DEIA W60L60 VPC	-
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	-
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	-
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	-
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	-
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	-
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	-
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	-
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	-
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	-
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	-
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	-

Order Code	Full Product Name	Optical cover type
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	-
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Polycarbonate bowl/cover
910505100422	RC463B 34S/930 DEIA W31L125 VPC	-
910505100423	RC463B 40S/940 DEIA W31L125 VPC	-
910505100424	RC463B 40S/930 DEIA W31L125 VPC	-
910505100427	RC463B 34S/940 DEIA W31L125 CPC	-
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	-
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	-
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	-
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	-
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	-
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	-
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Polycarbonate bowl/cover
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Polycarbonate bowl/cover
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Polycarbonate bowl/cover
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Polycarbonate bowl/cover
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Polycarbonate bowl/cover
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	-
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	-
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	-
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	-
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	-
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	-
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	-
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	-
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	-
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	-
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	-
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	-
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	-
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	-
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	-
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	-

Emergency Operation (1/2)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	Yes	DC operated central emergency lighting	-	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	Yes	DC operated central emergency lighting	-	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	Yes	DC operated central emergency lighting	-	-
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	Yes	DC operated central emergency lighting	-	-
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Yes	DC operated central emergency lighting	-	-
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting	-	-
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Yes	DC operated central emergency lighting	-	-
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	Yes	DC operated central emergency lighting	-	-
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	Yes	DC operated central emergency lighting	-	-
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	Yes	DC operated central emergency lighting	-	-
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	Yes	DC operated central emergency lighting	-	-
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	Yes	DC operated central emergency lighting	-	-
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting	-	-

PowerBalance gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting	-	-
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	Yes	DC operated central emergency lighting	-	-
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting	-	-
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting	-	-
910505103390	RC461B 80S/ TWBU SEIA W60L60 VPC U4	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505103392	RC461B 80S/ TWBU SEIA W60L60 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103393	RC463B 80S/ TWBU SEIA W62L62 VPC U4	Yes	DC operated central emergency lighting	-	-
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	Yes	DC operated central emergency lighting	-	-
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	Yes	DC operated central emergency lighting	-	-
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	Yes	DC operated central emergency lighting	-	-
910505105877	RC461B 80S/ TWBU SEIA W60L60 CWLVPC U4SC	Yes	DC operated central emergency lighting	-	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Yes	DC operated central emergency lighting	-	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Yes	DC operated central emergency lighting	-	-
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Yes	DC operated central emergency lighting	-	-

PowerBalance gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100425	RC463B 34S/940 DEIA W62L62 CPC	Yes	DC operated central emergency lighting	-	-
910505100426	RC463B 40S/940 DEIA W62L62 CPC	Yes	DC operated central emergency lighting	-	-
910505100489	RC463B 34S/930 DEIA W62L62 CPC	Yes	DC operated central emergency lighting	-	-
910505100490	RC463B 40S/930 DEIA W62L62 CPC	Yes	DC operated central emergency lighting	-	-
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Yes	DC operated central emergency lighting	-	-
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Yes	DC operated central emergency lighting	-	-
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Yes	DC operated central emergency lighting	-	-
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-
910505100416	RC463B 28S/940 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-
910505100417	RC463B 34S/940 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-
910505100418	RC463B 34S/930 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-
910505100488	RC463B 28S/930 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	No	-	-	-
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	No	-	-	-
910505101684	RC463B 28S/ BU840 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-
910505101685	RC468B 28S/ BU840 DEIA W67L67 VPC	Yes	DC operated central emergency lighting	-	-
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	No	-	-	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	No	-	-	-
910505101692	RC463B 40S/ BU840 DEIA W62L62 CPC W3W2	Yes	DC operated central emergency lighting	-	-
910505101693	RC468B 40S/ BU840 DEIA W67L67 VPC W3W2	Yes	DC operated central emergency lighting	-	-
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	Yes	DC operated central emergency lighting	-	-
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	Yes	DC operated central emergency lighting	-	-
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	Yes	DC operated central emergency lighting	-	-
910505100419	RC463B 40S/930 DEIA W62L62 VPC	Yes	DC operated central emergency lighting	-	-
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Yes	DC operated central	-	-

PowerBalance gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Yes	DC operated emergency lighting	-	-
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Yes	DC operated emergency lighting	-	-
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	No	Emergency lighting 3 hours duration with DALI interface	300 lm	Lithium
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Yes	DC operated central emergency lighting	-	-
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Yes	DC operated central emergency lighting	-	-
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Yes	DC operated central emergency lighting	-	-
910505100269	RC461B 34S/930 PSE W60L60 VPC	No	-	-	-
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Yes	DC operated central emergency lighting	-	-
910505100595	RC461B 40S/930 DEIA W60L60 VPC	Yes	DC operated central emergency lighting	-	-
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	No	Emergency lighting 3 hours duration with DALI interface	-	-
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	Yes	DC operated central emergency lighting	-	-
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	Yes	DC operated central emergency lighting	-	-
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	Yes	DC operated central emergency lighting	-	-
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	Yes	DC operated central emergency lighting	-	-
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	Yes	DC operated central emergency lighting	-	-
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	Yes	DC operated central emergency lighting	-	-
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	Yes	DC operated central emergency lighting	-	-
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	Yes	DC operated central emergency lighting	-	-
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	Yes	DC operated central emergency lighting	-	-
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	Yes	DC operated central emergency lighting	-	-
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Yes	DC operated central emergency lighting	-	-
910505100422	RC463B 34S/930 DEIA W31L125 VPC	Yes	DC operated central emergency lighting	-	-

PowerBalance gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100423	RC463B 40S/940 DEIA W31L125 VPC	Yes	DC operated central emergency lighting	-	-
910505100424	RC463B 40S/930 DEIA W31L125 VPC	Yes	DC operated central emergency lighting	-	-
910505100427	RC463B 34S/940 DEIA W31L125 CPC	Yes	DC operated central emergency lighting	-	-
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	No	-	-	-
910505101671	RC463B 28S/ BU840 DEIA W31L125 VPC	Yes	DC operated central emergency lighting	-	-
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	No	-	-	-
910505101677	RC463B 28S/ BU840 DEIA W31L125 CPC	Yes	DC operated central emergency lighting	-	-
910505103644	RC463B 34S/ UE840 DEIA W31L125 VPC	Yes	DC operated central emergency lighting	-	-
910505103646	RC463B 40S/ UE840 DEIA W31L125 VPC	Yes	DC operated central emergency lighting	-	-
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Yes	DC operated central emergency lighting	-	-
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	No	-	-	-
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	No	-	-	-
910505101669	RC461B 28S/ BU840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-
910505101670	RC461B 28S/ BU840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting	-	-
910505101675	RC461B 28S/ BU840 DEIA W30L120 PCV	Yes	DC operated central emergency lighting	-	-
910505101676	RC461B 28S/ BU840 DEIA W30L120 PCV SC	Yes	DC operated central emergency lighting	-	-
910505103619	RC461B 28S/ UE840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-
910505103621	RC461B 28S/ UE840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting	-	-
910505103623	RC461B 34S/ UE840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-
910505103627	RC461B 34S/ UE840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting	-	-
910505103631	RC461B 40S/ UE840 DEIA W30L120 VPC	Yes	DC operated central emergency lighting	-	-

PowerBalance gen2

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505103635	RC461B 40S/ UE840 DEIA W30L120 VPC SC	Yes	DC operated central emergency lighting	-	-
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	Yes	DC operated central emergency lighting	-	-
910505105879	RC461B 40S/ UE840 DEIA W60L60 CWL VPC	Yes	DC operated central emergency lighting	-	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Yes	DC operated central emergency lighting	-	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	Yes	DC operated central emergency lighting	-	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	Yes	DC operated central emergency lighting	-	-
910505105889	RC463B 34S/ UE840 DEIA W62L62 CPC CWL	Yes	DC operated central emergency lighting	-	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	Yes	DC operated central emergency lighting	-	-
910505105890	RC463B 34S/ UE840 SEIA W62L62 CPC CWL IA4	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	Yes	DC operated central emergency lighting	-	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	Yes	DC operated central emergency lighting	-	-
910505105887	RC463B 34S/ UE840 DEIA W62L62 VPC CWL	Yes	DC operated central emergency lighting	-	-
910505105871	RC461B 40S/ UE840 DEIA W30L120 VPC CWL SC	Yes	DC operated central emergency lighting	-	-
910505105872	RC461B 28S/ UE840 DEIA W30L120 VPC CWL	Yes	DC operated central emergency lighting	-	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	Yes	DC operated central emergency lighting	-	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	Yes	DC operated central emergency lighting	-	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Yes	DC operated central emergency lighting	-	-
910505105888	RC463B 34S/ UE840 SEIA W62L62 VPC CWL U4	Yes	DC operated central emergency lighting	-	-

Emergency Operation (2/2)

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	-
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	-
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	-
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	-
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	-
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	-
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	-
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	-
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	-
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	-
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	-
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	-
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	-
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	-
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	-
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	-
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	-
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	-
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	-
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	-
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	-
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	-
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	-
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	-
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	-
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	-
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	-
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	-
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	-
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	-
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	-
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	-
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	-
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	-
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	-
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	-
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	-
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	-
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	-
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	-
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	-
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	-
910505100425	RC463B 34S/940 DEIA W62L62 CPC	-
910505100426	RC463B 40S/940 DEIA W62L62 CPC	-
910505100489	RC463B 34S/930 DEIA W62L62 CPC	-
910505100490	RC463B 40S/930 DEIA W62L62 CPC	-
910505100277	RC461B 34S/940 DEIA W60L60 PCV	-
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	-
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	-
910505100278	RC463B 40S/940 DEIA W62L62 VPC	-
910505100416	RC463B 28S/940 DEIA W62L62 VPC	-
910505100417	RC463B 34S/940 DEIA W62L62 VPC	-
910505100418	RC463B 34S/930 DEIA W62L62 VPC	-
910505100488	RC463B 28S/930 DEIA W62L62 VPC	-
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	-
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	-
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	-
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	-
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	-
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	-
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	-
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	-
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	-
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	-
910505100419	RC463B 40S/930 DEIA W62L62 VPC	-
910505100245	RC461B 34S/940 DEIA W60L60 VPC	-
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	-
910505100250	RC461B 40S/940 DEIA W60L60 VPC	-
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	3 hour(s)
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	-
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	-
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	-
910505100269	RC461B 34S/930 PSE W60L60 VPC	-
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	-
910505100595	RC461B 40S/930 DEIA W60L60 VPC	-
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	-
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	-
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	-
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	-
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	-
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	-
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	-
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	-
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	-
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	-
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	-
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	-
910505100236	RC463B 40S/940 DEIA W31L125 CPC	-
910505100422	RC463B 34S/930 DEIA W31L125 VPC	-
910505100423	RC463B 40S/940 DEIA W31L125 VPC	-
910505100424	RC463B 40S/930 DEIA W31L125 VPC	-
910505100427	RC463B 34S/940 DEIA W31L125 CPC	-
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	-
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	-
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	-
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	-
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	-
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	-
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	-
910505100234	RC461B 34S/930 DEIA W30L120 VPC	-
910505100235	RC461B 40S/940 DEIA W30L120 VPC	-
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	-
910505100241	RC461B 34S/940 DEIA W30L120 VPC	-

PowerBalance gen2

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	-
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	-
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	-
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	-
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	-
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	-
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	-
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	-
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	-
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	-
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	-
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	-
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	-
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	-
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	-
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	-
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	-

Approval and Application

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	Temperature 650 °C, duration 30 s	-
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	Temperature 650 °C, duration 30 s	-
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	Temperature 650 °C, duration 30 s	0.4
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	Temperature 650 °C, duration 30 s	0.4
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Temperature 650 °C, duration 30 s	0.4

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	Temperature 650 °C, duration 30 s	0.4
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	Temperature 650 °C, duration 30 s	0.4
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	Temperature 650 °C, duration 30 s	0.4
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	Temperature 650 °C, duration 30 s	0.4
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	Temperature 650 °C, duration 30 s	0.4
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s	0.4

PowerBalance gen2

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	Temperature 650 °C, duration 30 s	0.4
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Temperature 650 °C, duration 30 s	0.4
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Temperature 650 °C, duration 30 s	0.4
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	Temperature 650 °C, duration 30 s	0.4
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	Temperature 650 °C, duration 30 s	0.4
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	Temperature 650 °C, duration 30 s	0.4
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	Temperature 650 °C, duration 30 s	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	Temperature 650 °C, duration 30 s	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100425	RC463B 34S/940 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s	0.4
910505100426	RC463B 40S/940 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s	0.4

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505100489	RC463B 34S/930 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s	0.4
910505100490	RC463B 40S/930 DEIA W62L62 CPC	Temperature 650 °C, duration 30 s	0.4
910505100277	RC461B 34S/940 DEIA W60L60 PCV	Temperature 650 °C, duration 30 s	0.4
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100278	RC463B 40S/940 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505100416	RC463B 28S/940 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505100417	RC463B 34S/940 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505100418	RC463B 34S/930 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505100488	RC463B 28S/930 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	Temperature 650 °C, duration 30 s	0.4
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	Temperature 650 °C, duration 30 s	0.4
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	Temperature 650 °C, duration 30 s	0.4
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	Temperature 650 °C, duration 30 s	0.4
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	Temperature 650 °C, duration 30 s	0.4
910505100419	RC463B 40S/930 DEIA W62L62 VPC	Temperature 650 °C, duration 30 s	0.4
910505100245	RC461B 34S/940 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s	0.4
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	Temperature 650 °C, duration 30 s	0.4

PowerBalance gen2

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505100250	RC461B 40S/940 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s	0.4
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	Temperature 850 °C, duration 30 s	0.4
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	Temperature 650 °C, duration 30 s	0.4
910505100269	RC461B 34S/930 PSE W60L60 VPC	Temperature 650 °C, duration 30 s	0.4
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	Temperature 650 °C, duration 30 s	0.4
910505100595	RC461B 40S/930 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s	0.4
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	Temperature 650 °C, duration 30 s	0.4
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	Temperature 650 °C, duration 30 s	0.4
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	Temperature 650 °C, duration 30 s	0.4
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	Temperature 650 °C, duration 30 s	0.4
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	Temperature 650 °C, duration 30 s	0.4
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	Temperature 650 °C, duration 30 s	0.4
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	Temperature 650 °C, duration 30 s	0.4
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	Temperature 650 °C, duration 30 s	0.4
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	Temperature 650 °C, duration 30 s	0.4
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	Temperature 650 °C, duration 30 s	0.4
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	Temperature 650 °C, duration 30 s	0.4
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	Temperature 650 °C, duration 30 s	0.4
910505100236	RC463B 40S/940 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s	0.4
910505100422	RC463B 34S/930 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4
910505100423	RC463B 40S/940 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4
910505100424	RC463B 40S/930 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505100427	RC463B 34S/940 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s	0.4
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s	0.4
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	Temperature 650 °C, duration 30 s	0.4
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	Temperature 650 °C, duration 30 s	0.4
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100234	RC461B 34S/930 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505100235	RC461B 40S/940 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	Temperature 650 °C, duration 30 s	0.4
910505100241	RC461B 34S/940 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s	0.4
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s	0.4
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	Temperature 650 °C, duration 30 s	0.4
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	Temperature 650 °C, duration 30 s	0.4
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s	0.4
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s	0.4
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	Temperature 650 °C, duration 30 s	0.4
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	Temperature 650 °C, duration 30 s	0.4

PowerBalance gen2

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	Temperature 650 °C, duration 30 s	-
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	Temperature 650 °C, duration 30 s	-
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	Temperature 650 °C, duration 30 s	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	Temperature 650 °C, duration 30 s	-
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	Temperature 650 °C, duration 30 s	-
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	Temperature 650 °C, duration 30 s	-
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	Temperature 650 °C, duration 30 s	-
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	Temperature 650 °C, duration 30 s	-
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	Temperature 650 °C, duration 30 s	-

Order Code	Full Product Name	Glow-wire test	Stroboscopic effect visibility measure (SVM)
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	Temperature 650 °C, duration 30 s	-
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	Temperature 650 °C, duration 30 s	-
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	Temperature 650 °C, duration 30 s	-
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	Temperature 650 °C, duration 30 s	-
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	Temperature 650 °C, duration 30 s	-
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	Temperature 650 °C, duration 30 s	-
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	Temperature 650 °C, duration 30 s	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	Temperature 650 °C, duration 30 s	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	(0.38, 0.38) SDCM ≤3
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	(0.38, 0.38) SDCM ≤3
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	(0.38, 0.38) SDCM ≤3
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	(0.38, 0.38) SDCM ≤3
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	(0.38, 0.38) SDCM ≤3
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	(0.38, 0.38) SDCM ≤3
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	(0.38, 0.38) SDCM ≤3
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	Tunable, SDCM ≤3
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	Tunable, SDCM ≤3
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	Tunable, SDCM ≤3
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	Tunable, SDCM ≤3
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	Tunable, SDCM ≤3
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	Tunable, SDCM ≤3
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	(0.38, 0.38) SDCM ≤3
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	(0.38, 0.38) SDCM ≤3
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	(0.43, 0.40) SDCM ≤3
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	(0.38, 0.38) SDCM ≤3
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	(0.38, 0.38) SDCM ≤3
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤3
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤3
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤3
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	(0.38, 0.38) SDCM ≤3
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	(0.43, 0.40) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	(0.38, 0.38) SDCM ≤3
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	(0.43, 0.40) SDCM ≤3
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	(0.38, 0.38) SDCM ≤3
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	(0.38, 0.38) SDCM ≤3
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	(0.38, 0.38) SDCM ≤3
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	Tunable, SDCM ≤3
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	Tunable, SDCM ≤3
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	Tunable, SDCM ≤3
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	Tunable, SDCM ≤3
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	Tunable, SDCM ≤3
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	Tunable, SDCM ≤3
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	(0.38, 0.38) SDCM ≤3
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	(0.38, 0.38) SDCM ≤3
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	(0.38, 0.38) SDCM ≤3
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVPC U4SC	-
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	-
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505100425	RC463B 34S/940 DEIA W62L62 CPC	(0.38, 0.38) SDCM ≤3
910505100426	RC463B 40S/940 DEIA W62L62 CPC	(0.38, 0.38) SDCM ≤3
910505100489	RC463B 34S/930 DEIA W62L62 CPC	(0.43, 0.40) SDCM ≤3
910505100490	RC463B 40S/930 DEIA W62L62 CPC	(0.43, 0.40) SDCM ≤3
910505100277	RC461B 34S/940 DEIA W60L60 PCV	(0.38, 0.38) SDCM ≤3

PowerBalance gen2

Order Code	Full Product Name	Initial chromaticity
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100278	RC463B 40S/940 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505100416	RC463B 28S/940 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505100417	RC463B 34S/940 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505100418	RC463B 34S/930 DEIA W62L62 VPC	(0.43, 0.40) SDCM ≤3
910505100488	RC463B 28S/930 DEIA W62L62 VPC	(0.43, 0.40) SDCM ≤3
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	(0.38, 0.38) SDCM ≤3
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	(0.38, 0.38) SDCM ≤3
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	(0.38, 0.38) SDCM ≤3
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	(0.38, 0.38) SDCM ≤3
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	(0.38, 0.38) SDCM ≤3
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	(0.38, 0.38) SDCM ≤3
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	(0.38, 0.38) SDCM ≤3
910505100419	RC463B 40S/930 DEIA W62L62 VPC	(0.43, 0.40) SDCM ≤3
910505100245	RC461B 34S/940 DEIA W60L60 VPC	(0.38, 0.38) SDCM ≤3
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100250	RC461B 40S/940 DEIA W60L60 VPC	(0.38, 0.38) SDCM ≤3
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	(0.38, 0.38) SDCM ≤3
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	(0.43, 0.40) SDCM ≤3
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	(0.38, 0.38) SDCM ≤3
910505100269	RC461B 34S/930 PSE W60L60 VPC	(0.43, 0.40) SDCM ≤3
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	(0.38, 0.38) SDCM ≤3
910505100595	RC461B 40S/930 DEIA W60L60 VPC	(0.43, 0.40) SDCM ≤3
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	(0.38, 0.38) SDCM ≤3
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	(0.38, 0.38) SDCM ≤3
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	(0.38, 0.38) SDCM ≤3
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	(0.38, 0.38) SDCM ≤3
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	(0.38, 0.38) SDCM ≤3
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	(0.38, 0.38) SDCM ≤3
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	(0.38, 0.38) SDCM ≤3
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	(0.38, 0.38) SDCM ≤3
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	(0.38, 0.38) SDCM ≤3
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	(0.38, 0.38) SDCM ≤3
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	(0.38, 0.38) SDCM ≤3
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	(0.38, 0.38) SDCM ≤3
910505100236	RC463B 40S/940 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505100422	RC463B 34S/930 DEIA W31L125 VPC	(0.43, 0.40) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910505100423	RC463B 40S/940 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505100424	RC463B 40S/930 DEIA W31L125 VPC	(0.43, 0.40) SDCM ≤3
910505100427	RC463B 34S/940 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	(0.38, 0.38) SDCM ≤3
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	(0.38, 0.38) SDCM ≤3
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100234	RC461B 34S/930 DEIA W30L120 VPC	(0.43, 0.40) SDCM ≤3
910505100235	RC461B 40S/940 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	(0.38, 0.38) SDCM ≤3
910505100241	RC461B 34S/940 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	(0.38, 0.38) SDCM ≤3
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	(0.38, 0.38) SDCM ≤3
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	(0.38, 0.38) SDCM ≤3
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	(0.38, 0.38) SDCM ≤3
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	(0.43, 0.40) SDCM ≤3
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	(0.38, 0.38) SDCM ≤3
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	-
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	(0.38, 0.38) SDCM ≤3
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	(0.38, 0.38) SDCM ≤3
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	(0.38, 0.38) SDCM ≤3
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	(0.38, 0.38) SDCM ≤3
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	(0.38, 0.38) SDCM ≤3
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	(0.38, 0.38) SDCM ≤3
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	(0.38, 0.38) SDCM ≤3
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	(0.38, 0.38) SDCM ≤3
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	(0.38, 0.38) SDCM ≤3
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	(0.38, 0.38) SDCM ≤3
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	(0.38, 0.38) SDCM ≤3
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	(0.38, 0.38) SDCM ≤3
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	-
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	(0.38, 0.38) SDCM ≤3

Product Data

Order Code	Full Product Name	Product family code
910505105874	RC463B 40S/940 DEIA W31L125 VPC CWL	RC463B
910505105875	RC463B 34S/UE840 DEIA W31L125 VPC CWL	RC463B
910505101727	RC461B 34S/940 SEIA W30L120 VPC U4 W3	RC461B

Order Code	Full Product Name	Product family code
910505101728	RC463B 34S/940 SEIA W31L125 VPC U4	RC463B
910505101729	RC463B 40S/940 SEIA W31L125 VPC U4	RC463B
910505101730	RC463B 60S/940 SEIA W31L125 VPC U4	RC463B

PowerBalance gen2


Order Code	Full Product Name	Product family code
910505101731	RC461B 34S/940 SEIA W30L120VPCU4 SC	RC461B
910505103384	RC461B 80S/TW9 SEIA W30L120 VPC U4 SC	RC461B
910505103387	RC461B 80S/TW9 SEIA W30L120 VPC U4	RC461B
910505103388	RC463B 80S/TW9 SEIA W31L125 VPC U4	RC463B
910505103391	RC461B 80S/TWBU SEIA W30L120 VPC U4 SC	RC461B
910505103394	RC461B 80S/TWBU SEIA W30L120 VPC U4	RC461B
910505103395	RC463B 80S/TWBU SEIA W31L125 VPC U4	RC463B
910505103625	RC461B 34S/840 SEIA W30L120 VPC U4 UE	RC461B
910505103629	RC461B 34S/840 SEIA W30L120 VPC U4 SC UE	RC461B
910505103633	RC461B 40S/840 SEIA W30L120 VPC U4 UE	RC461B
910505103637	RC461B 40S/840 SEIA W30L120 VPC U4 SC UE	RC461B
910505103645	RC463B 34S/840 SEIA W31L125 VPC U4 UE	RC461B
910505103647	RC463B 40S/840 SEIA W31L125 VPC U4 UE	RC461B
910505101710	RC461B 34S/930 SEIA W60L60 VPC U4 W3	RC461B
910505101711	RC461B 34S/940 SEIA W60L60 VPC U4 W3	RC461B
910505101712	RC461B 40S/940 SEIA W60L60 VPC U4 W3	RC461B
910505101713	RC463B 28S/940 SEIA W62L62 VPC U4	RC463B
910505101714	RC463B 34S/940 SEIA W62L62 VPC U4	RC463B
910505101715	RC463B 40S/940 SEIA W62L62 VPC U4	RC463B
910505101716	RC463B 60S/940 SEIA W62L62 VPC U4	RC463B
910505101717	RC461B 34S/930 SEIA W60L60 VPC U4	RC461B
910505101718	RC461B 34S/940 SEIA W60L60 VPC U4	RC461B
910505101719	RC461B 34S/930 SEIA W60L60 VPC U4 SC	RC461B
910505101720	RC461B 34S/940 SEIA W60L60 VPC U4 SC	RC461B
910505101721	RC461B 34S/940 SEIA W60L60 VPC U4 W3 SC	RC461B
910505101722	RC461B 40S/940 SEIA W60L60 VPC U4 SC	RC461B
910505103383	RC461B 80S/TW9 SEIA W60L60 VPC U4	RC461B
910505103385	RC461B 80S/TW9 SEIA W60L60 VPC U4 SC	RC461B
910505103386	RC463B 80S/TW9 SEIA W62L62 VPC U4	RC463B
910505103390	RC461B 80S/TWBU SEIA W60L60 VPC U4	RC468B
910505103392	RC461B 80S/TWBU SEIA W60L60 VPC U4 SC	RC461B
910505103393	RC463B 80S/TWBU SEIA W62L62 VPC U4	RC463B
910505103626	RC461B 34S/840 SEIA W60L60 VPC U4 UE	RC461B
910505103630	RC461B 34S/840 SEIA W60L60 VPC U4 SC UE	RC461B
910505103634	RC461B 40S/840 SEIA W60L60 VPC U4 UE	RC461B
910505103638	RC461B 40S/840 SEIA W60L60 VPC U4 SC UE	RC461B
910505103641	RC463B 34S/840 SEIA W62L62 VPC U4 UE	RC461B
910505103643	RC463B 40S/840 SEIA W62L62 VPC U4 UE	RC461B
910505105877	RC461B 80S/TWBU SEIA W60L60 CWLVP U4SC	RC461B
910505105878	RC461B 80S/TW9 SEIA W60L60 VPC CWL U4	RC461B
910505100265	RC461B 34S/940 DEIA W60L60 CPC W3W2	RC461B
910505100271	RC463B 34S/940 DEIA W62L62 CPC W3W2	RC463B
910505100425	RC463B 34S/940 DEIA W62L62 CPC	RC463B
910505100426	RC463B 40S/940 DEIA W62L62 CPC	RC463B
910505100489	RC463B 34S/930 DEIA W62L62 CPC	RC463B
910505100490	RC463B 40S/930 DEIA W62L62 CPC	RC463B
910505100277	RC461B 34S/940 DEIA W60L60 PCV	RC461B
910505100251	RC463B 28S/940 DEIA W62L62 VPC W3W2	RC463B
910505100259	RC463B 34S/940 DEIA W62L62 VPC W3W2	RC463B
910505100278	RC463B 40S/940 DEIA W62L62 VPC	RC463B
910505100416	RC463B 28S/940 DEIA W62L62 VPC	RC463B

Order Code	Full Product Name	Product family code
910505100417	RC463B 34S/940 DEIA W62L62 VPC	RC463B
910505100418	RC463B 34S/930 DEIA W62L62 VPC	RC463B
910505100488	RC463B 28S/930 DEIA W62L62 VPC	RC463B
910505101680	RC463B 80S/TW9 DIA W62L62 VPC	RC463B
910505101681	RC468B 80S/TW9 DIA W67L67 VPC	RC468B
910505101684	RC463B 28S/BU840 DEIA W62L62 VPC	RC463B
910505101685	RC468B 28S/BU840 DEIA W67L67 VPC	RC468B
910505101688	RC463B 80S/TW9 DIA W62L62 CPC W3W2	RC463B
910505101689	RC468B 80S/TW9 DIA W67L67 VPC W3W2	RC468B
910505101692	RC463B 40S/BU840 DEIA W62L62 CPC W3W2	RC463B
910505101693	RC468B 40S/BU840 DEIA W67L67 VPC W3W2	RC468B
910505103639	RC463B 28S/840 DEIA W62L62 VPC UE	RC463B
910505103640	RC463B 34S/840 DEIA W62L62 VPC UE	RC461B
910505103642	RC463B 40S/840 DEIA W62L62 VPC UE	RC461B
910505100419	RC463B 40S/930 DEIA W62L62 VPC	RC463B
910505100245	RC461B 34S/940 DEIA W60L60 VPC	RC461B
910505100249	RC461B 40S/940 DEIA W60L60 VPC W3W2	RC461B
910505100250	RC461B 40S/940 DEIA W60L60 VPC	RC461B
910505100252	RC461B 40S/940 DIA W60L60 VPC ELD3 PIP	RC461B
910505100256	RC461B 34S/940 DEIA W60L60 VPC W3W2	RC461B
910505100261	RC461B 40S/930 DEIA W60L60 VPC W3W2	RC461B
910505100266	RC461B 40S/940 DEIA W60L60 VPC W3W2 AIR	RC461B
910505100269	RC461B 34S/930 PSE W60L60 VPC	RC461B
910505100270	RC461B 34S/940 DEIA W60L60 VPC W3W2 SC	RC461B
910505100595	RC461B 40S/930 DEIA W60L60 VPC	RC461B
910505101678	RC461B 80S/TW9 DIA W60L60 VPC ELD3	RC461B
910505101679	RC461B 80S/TW9 DIA W60L60 VPC ELD3 PIPSC	RC461B
910505101682	RC461B 28S/BU840 DEIA W60L60 VPC	RC461B
910505101683	RC461B 28S/BU840 DEIA W60L60 VPC SC	RC461B
910505101690	RC461B 40S/BU840 DEIA W60L60 PCV W3W2	RC461B
910505101691	RC461B 40S/BU840 DEIA W60L60 PCV W3W2 SC	RC461B
910505103620	RC461B 28S/840 DEIA W60L60 VPC UE	RC461B
910505103622	RC461B 28S/840 DEIA W60L60 VPC SC UE	RC461B
910505103624	RC461B 34S/840 DEIA W60L60 VPC UE	RC461B
910505103628	RC461B 34S/840 DEIA W60L60 VPC SC UE	RC461B
910505103632	RC461B 40S/840 DEIA W60L60 VPC UE	RC461B
910505103636	RC461B 40S/840 DEIA W60L60 VPC SC UE	RC461B
910505100236	RC463B 40S/940 DEIA W31L125 CPC	RC463B
910505100422	RC463B 34S/930 DEIA W31L125 VPC	RC463B
910505100423	RC463B 40S/940 DEIA W31L125 VPC	RC463B
910505100424	RC463B 40S/930 DEIA W31L125 VPC	RC463B
910505100427	RC463B 34S/940 DEIA W31L125 CPC	RC463B
910505101668	RC463B 80S/TW9 DEIA W31L125 VPC	RC463B
910505101671	RC463B 28S/BU840 DEIA W31L125 VPC	RC463B
910505101674	RC463B 80S/TW9 DEIA W31L125 CPC	RC463B
910505101677	RC463B 28S/BU840 DEIA W31L125 CPC	RC463B
910505103644	RC463B 34S/UE840 DEIA W31L125 VPC	RC461B
910505103646	RC463B 40S/UE840 DEIA W31L125 VPC	RC461B
910505100232	RC461B 34S/940 DEIA W30L120 VPC W3W2	RC461B
910505100234	RC461B 34S/930 DEIA W30L120 VPC	RC461B
910505100235	RC461B 40S/940 DEIA W30L120 VPC	RC461B


Order Code	Full Product Name	Product family code
910505100238	RC461B 40S/940 DEIA W30L120 VPC W3W2	RC461B
910505100241	RC461B 34S/940 DEIA W30L120 VPC	RC461B
910505101666	RC461B 80S/TW9 DEIA W30L120 VPC	RC461B
910505101667	RC461B 80S/TW9 DEIA W30L120 VPC SC	RC461B
910505101669	RC461B 28S/BU840 DEIA W30L120 VPC	RC461B
910505101670	RC461B 28S/BU840 DEIA W30L120 VPC SC	RC461B
910505101675	RC461B 28S/BU840 DEIA W30L120 PCV	RC461B
910505101676	RC461B 28S/BU840 DEIA W30L120 PCV SC	RC461B
910505103619	RC461B 28S/UE840 DEIA W30L120 VPC	RC461B
910505103621	RC461B 28S/UE840 DEIA W30L120 VPC SC	RC461B
910505103623	RC461B 34S/UE840 DEIA W30L120 VPC	RC461B
910505103627	RC461B 34S/UE840 DEIA W30L120 VPC SC	RC461B
910505103631	RC461B 40S/UE840 DEIA W30L120 VPC	RC461B
910505103635	RC461B 40S/UE840 DEIA W30L120 VPC SC	RC461B
910505105876	RC461B 40S/930 DEIA W60L60 CWL VPC W5	RC461B
910505105879	RC461B 40S/UE840 DEIA W60L60 CWL VPC	RC461B

Order Code	Full Product Name	Product family code
910505105870	RC461B 80S/TW9 SEIA W30L120 VPC CWL U4	RC461B
910505105882	RC463B 34S/940 DEIA W62L62 CWL CPC	RC463B
910505105883	RC463B 40S/940 DEIA W62L62 CPC CWL	RC463B
910505105889	RC463B 34S/UE840 DEIA W62L62 CPC CWL	RC463B
910505105885	RC463B 40S/940 SEIA W62L62 CPC CWL IA4	RC463B
910505105890	RC463B 34S/UE840 SEIA W62L62 CPC CWL IA4	RC463B
910505105880	RC463B 34S/940 DEIA W62L62 CWL VPC	RC463B
910505105881	RC463B 40S/940 DEIA W62L62 CWL VPC	RC463B
910505105887	RC463B 34S/UE840 DEIA W62L62 VPC CWL	RC463B
910505105871	RC461B 40S/UE840 DEIA W30L120 VPC CWL SC	RC461B
910505105872	RC461B 28S/UE840 DEIA W30L120 VPC CWL	RC461B
910505105873	RC463B 40S/940 SEIA W31L125 VPC CWL U4	RC463B
910505105884	RC463B 40S/940 SEIA W62L62 VPC CWL U4	RC463B
910505105886	RC463B 80S/TW9 SEIA W62L62 VPC CWL U4	RC463B
910505105888	RC463B 34S/UE840 SEIA W62L62 VPC CWL U4	RC463B


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505101692




Polar Normal (separate) - RC460BP - 910505101671




Polar Normal (separate) - RC460BN - 910505100270



Polar Normal (separate) - RC460BP - 910505100235




Polar Normal (separate) - RC460BN - 910505100251




Polar Normal (separate) - RC460BN - 910505100259


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505100416




Polar Normal (separate) - RC460BN - 910505100271




Polar Normal (separate) - RC460BP - 910505100427




Polar Normal (separate) - RC460BN - 910505100425




Polar Normal (separate) - RC460BN - 910505100266




Polar Normal (separate) - RC460BN - 910505100269



Polar Normal (separate) - RC460BN - 910505100256




Polar Normal (separate) - RC460BN - 910505100426




Polar Normal (separate) - RC460BN - 910505100261


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505100265




Polar Normal (separate) - RC460BP - 910505100422




Polar Normal (separate) - RC460BN - 910505100418




Polar Normal (separate) - RC460BN - 910505100417




Polar Normal (separate) - RC460BN - 910505100245




Polar Normal (separate) - RC460BN - 910505100489



Polar Normal (separate) - RC460BP - 910505100423




Polar Normal (separate) - RC460BP - 910505100241




Polar Normal (separate) - RC460BN - 910505100419


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505100250




Polar Normal (separate) - RC460BP - 910505100424




Polar Normal (separate) - RC460BP - 910505100238




Polar Normal (separate) - RC460BP - 910505101674




Polar Normal (separate) - RC460BN - 910505101716




Polar Normal (separate) - RC460BN - 910505101680



Polar Normal (separate) - RC460BN - 910505101718




Polar Normal (separate) - RC460BN - 910505100490




Polar Normal (separate) - RC460BN - 910505101683


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505101719




Polar Normal (separate) - RC460BN - 910505101722




Polar Normal (separate) - RC460BN - 910505101715




Polar Normal (separate) - RC460BN - 910505101712




Polar Normal (separate) - RC460BP - 910505101728




Polar Normal (separate) - RC460BP - 910505101667



Polar Normal (separate) - RC460BN - 910505101713




Polar Normal (separate) - RC460BN - 910505100277




Polar Normal (separate) - RC460BN - 910505101720


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505101682




Polar Normal (separate) - RC460BN - 910505101689




Polar Normal (separate) - RC460BP - 910505101675




Polar Normal (separate) - RC460BP - 910505101670




Polar Normal (separate) - RC460BN - 910505101693




Polar Normal (separate) - RC460BN - 910505100488



Polar Normal (separate) - RC460BP - 910505101676




Polar Normal (separate) - RC460BN - 910505101688




Polar Normal (separate) - RC460BN - 910505101679


Polar Wide Diagrams




Polar Normal (separate) - RC460BP - 910505100234




Polar Normal (separate) - RC460BN - 910505101710




Polar Normal (separate) - RC460BN - 910505101681




Polar Normal (separate) - RC460BN - 910505101684




Polar Normal (separate) - RC460BP - 910505101729




Polar Normal (separate) - RC460BP - 910505101731



Polar Normal (separate) - RC460BP - 910505101727




Polar Normal (separate) - RC460BP - 910505101668




Polar Normal (separate) - RC460BP - 910505101669


Polar Wide Diagrams




Polar Normal (separate) - RC460BP - 910505101666




Polar Normal (separate) - RC460BP - 910505101677




Polar Normal (separate) - RC460BN - 910505101678




Polar Normal (separate) - RC460BN - 910505101685




Polar Normal (separate) - RC460BN - 910505101711




Polar Normal (separate) - RC460BP - 910505103619



Polar Normal (separate) - RC460BN - 910505103620






Polar Normal (separate) - RC460BP - 910505103623



Polar Normal (separate) - RC460BN - 910505103622




Polar Wide Diagrams



Polar Normal (separate) - RC460BP - 910505103621

Polar Normal (separate) - RC460BN - 910505103624




Polar Normal (separate) - RC460BP - 910505103625



Polar Normal (separate) - RC460BN - 910505103628

Polar Normal (separate) - RC460BP - 910505103627

Polar Normal (separate) - RC460BN - 910505103626




Polar Normal (separate) - RC460BN - 910505103630


Polar Normal (separate) - RC460BN - 910505103632

Polar Normal (separate) - RC460BP - 910505103633


Polar Wide Diagrams




Polar Normal (separate) - RC460BP - 910505103629




Polar Normal (separate) - RC460BP - 910505103631




Polar Normal (separate) - RC460BP - 910505103635




Polar Normal (separate) - RC460BN - 910505103634




Polar Normal (separate) - RC460BN - 910505103636




Polar Normal (separate) - RC460BP - 910505103637



Polar Normal (separate) - RC460BN - 910505103638




Polar Normal (separate) - RC460BN - 910505103642




Polar Normal (separate) - RC460BN - 910505103639


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505103641




Polar Normal (separate) - RC460BN - 910505103643




Polar Normal (separate) - RC460BN - 910505103640




Polar Normal (separate) - RC460BP - 910505103644




Polar Normal (separate) - RC460BP - 910505103645




Polar Normal (separate) - RC460BP - 910505103647



Polar Normal (separate) - RC460BP - 910505103646




Polar Normal (separate) - RC460BP - 910505103384




Polar Normal (separate) - RC460BN - 910505103383


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505103385




Polar Normal (separate) - RC460BN - 910505103386




Polar Normal (separate) - RC460BP - 910505103388




Polar Normal (separate) - RC460BP - 910505103387




Polar Normal (separate) - RC460BN - 910505103393




Polar Normal (separate) - RC460BP - 910505103394



Polar Normal (separate) - RC460BN - 910505103392




Polar Normal (separate) - RC460BP - 910505103391




Polar Normal (separate) - RC460BP - 910505103395


Polar Wide Diagrams




Polar Normal (separate) - RC460BN - 910505100252




Polar Normal (separate) - RC460BP - 910505100232




Polar Normal (separate) - RC460BN - 910505100249




Polar Normal (separate) - RC460BN - 910505100278




Polar Normal (separate) - null - 910505105870




Polar Normal (separate) - null - 910505105878




Polar Normal (separate) - null - 910505105871




Polar Normal (separate) - null - 910505105876



Polar Normal (separate) - null - 910505105883




Polar Normal (separate) - null - 910505105873




Polar Normal (separate) - null - 910505105888


Polar Wide Diagrams




Polar Normal (separate) - null - 910505105890




Polar Normal (separate) - null - 910505105886




Polar Normal (separate) - null - 910505105884




Polar Normal (separate) - null - 910505105880




Polar Normal (separate) - null - 910505105875




Polar Normal (separate) - null - 910505105882




Polar Normal (separate) - null - 910505105881




Polar Normal (separate) - null - 910505105885




Polar Normal (separate) - null - 910505105872



Polar Normal (separate) - null - 910505105889




Polar Normal (separate) - null - 910505105874




Polar Normal (separate) - null - 910505105877

PowerBalance gen2

Polar Wide Diagrams



Polar Normal (separate) - null - 910505105887



Polar Normal (separate) - null - 910505105879

