



Philips TrueLine recessed: True line of light

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, recessed

Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering
- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine recessed-RC530B L1130




TrueLineRecessed PCV ASYMMETRIC RTP



TrueLineRecessed VPC NOC IP RTP



Dimensional drawing





Recessed VPC_W8L150_no sensor

TrueLine, recessed



Dimensional drawing



Recessed VPC_W8L120_sensor/IP



Recessed VPC_W8L120_no sensor



Product details



TrueLineRecessed NOC OPTICS
DP



TrueLine_Recessed U4 DP

TrueLine, recessed

Product details

TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI5-
DPP.tif



TrueLine-
RC534B_SM534C_SP534P-DPP.tif



TrueLineRecessed OC OPTICS DP



TrueLineRecessed PCV line
CONNECTED DP1



TrueLineRecessed VPC line
CONNECTED DP2



TrueLine, recessed

Product details



TrueLineRecessed VPC line
CONNECTED DP1

TrueLine_Recessed-U3



TrueLineRecessed PCV line
CONNECTED DP2

TrueLine_Recessed-U0



TrueLineRecessed VPC LINE RTP

TrueLine_Recessed IP DP



TrueLineRecessed ASYMMETRIC
OPTICS DP

General Information

Driver included	Yes
Number of gear units	1 unit

Operating and Electrical

Line Frequency	50 to 60 Hz
----------------	-------------

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Light source replaceable	Service tag
910505103104	RC530B 15S/940 DEIA W8L113 PCV	No	Yes
910505103107	RC530B 31S/940 DEIA W8L141 PCV	No	Yes
910505103110	RC530B 43S/940 DEIA W8L141 PCV	No	Yes
910505103114	RC530B 19S/940 DEIA W8L141 PCV	No	Yes
910505103115	RC530B 34S/940 DEIA W8L113 PCV	No	Yes
910505103116	RC531B 15S/930 DEIA W8L113 PCV	No	Yes
910505103117	RC531B 15S/940 DEIA W8L113 PCV	No	Yes
910505103121	RC531B 31S/940 DEIA W8L141 PCV	No	Yes
910505103127	RC530B 50S/940 DEIA W8L141 PCV	No	Yes
910505103129	RC531B 19S/940 DEIA W8L141 PCV	No	Yes
910505103147	RC530B 40S/940 POE W8L120 VPC U0	No	Yes
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	No	Yes
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	No	Yes
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	No	Yes
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	-	-
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	-	-
910505103118	RC532B LED15S/940 PSD W8L113 PCV P15	No	-
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	No	Yes
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	No	Yes
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	No	Yes
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	No	Yes
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	No	Yes
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	No	Yes
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	No	Yes
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	No	Yes
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	No	Yes
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	No	Yes
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	No	Yes
910505103123	RC534B 50S/940 DEIA W8L141 PCV	No	Yes
910505103125	RC535B 50S/940 DEIA W8L141 PCV	No	Yes
910505103130	RC535B 43S/940 DEIA W8L141 PCV	No	Yes
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	No	Yes
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	No	Yes
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	No	Yes
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	No	Yes
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	No	Yes
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	No	Yes
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	-	-
910505103128	RC534B 43S/940 DEIA W8L141 PCV	No	Yes
910505103106	RC532B 19S/940 DEIA W8L141 PCV	No	Yes
910505103109	RC533B 15S/940 DEIA W8L113 PCV	No	Yes
910505103119	RC532B 25S/940 DEIA W8L113 PCV	No	Yes
910505103122	RC532B 31S/940 DEIA W8L141 PCV	No	Yes
910505103124	RC532B 43S/940 DEIA W8L141 PCV	No	Yes
910505103126	RC533B 31S/940 DEIA W8L141 PCV	No	Yes
910505103131	RC533B 19S/940 DEIA W8L141 PCV	No	Yes
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	No	Yes
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	No	Yes
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	No	Yes
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	No	Yes
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	-	Yes

Order Code	Full Product Name	Light source replaceable	Service tag
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	-	Yes
910505103102	RC532B 25S/940 DEIA W8L113 VPC	No	Yes
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	No	Yes
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	No	Yes
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	No	Yes
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	No	Yes
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	No	Yes
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	No	Yes
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	No	Yes
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	No	Yes
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	No	Yes
910505105963	RC530B 34S/JE840 SEIA W8L120 VPC U4 W3SC	-	-
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505103104	RC530B 15S/940 DEIA W8L113 PCV	- degree(s)	4000 K	>90	127 lm/W
910505103107	RC530B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	148 lm/W
910505103110	RC530B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	144 lm/W
910505103114	RC530B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	143 lm/W
910505103115	RC530B 34S/940 DEIA W8L113 PCV	- degree(s)	4000 K	>90	143 lm/W
910505103116	RC531B 15S/930 DEIA W8L113 PCV	- degree(s)	3000 K	>90	99 lm/W
910505103117	RC531B 15S/940 DEIA W8L113 PCV	- degree(s)	4000 K	>90	99 lm/W
910505103121	RC531B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	110 lm/W
910505103127	RC530B 50S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	139 lm/W
910505103129	RC531B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	110 lm/W
910505103147	RC530B 40S/940 POE	- degree(s)	4000 K	>90	143 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	120 degree(s)	Tunable white 2700-6500 K	>90	124 lm/W
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	120 degree(s)	4000 K	>90	143 lm/W
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	-	4000 K	>80	173 lm/W
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	-	4000 K	>80	179 lm/W
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	>90	127 lm/W
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	>90	112 lm/W
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	>90	110 lm/W
910505103141	RC530B 50S/940 DIA	- degree(s)	4000 K	>90	139 lm/W

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	W8L150 VPC ELP3				
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	>90	144 lm/W
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	- degree(s)	4000 K	>90	144 lm/W
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	>90	144 lm/W
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	>90	139 lm/W
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	>90	110 lm/W
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	>90	112 lm/W
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	- degree(s)	4000 K	>90	110 lm/W
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	>90	130 lm/W
910505103123	RC534B 50S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	132 lm/W
910505103125	RC535B 50S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	132 lm/W
910505103130	RC535B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	138 lm/W
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	- degree(s)	4000 K	>90	144 lm/W
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	- degree(s)	3000 K	>90	131 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	- degree(s)	4000 K	>90	139 lm/W
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	>90	138 lm/W
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	>90	143 lm/W
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	120 degree(s)	4000 K	>90	143 lm/W
910505105965	RC530B 43S/ BU840 DEIA W8L150 VPC IP	-	4000 K	>80	137 lm/W
910505103128	RC534B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	138 lm/W
910505103106	RC532B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	143 lm/W
910505103109	RC533B 15S/940 DEIA W8L113 PCV	- degree(s)	4000 K	>90	103 lm/W
910505103119	RC532B 25S/940 DEIA W8L113 PCV	- degree(s)	4000 K	>90	139 lm/W
910505103122	RC532B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	148 lm/W
910505103124	RC532B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	144 lm/W
910505103126	RC533B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	112 lm/W
910505103131	RC533B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	>90	110 lm/W
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	- degree(s)	4000 K	>90	143 lm/W
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	- degree(s)	4000 K	>90	143 lm/W

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	>90	91 lm/W
910505103102	RC532B 25S/940 DEIA W8L113 VPC	- degree(s)	4000 K	>90	139 lm/W
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	- degree(s)	3000 K	>90	104 lm/W
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	>90	99 lm/W
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	- degree(s)	3000 K	>90	99 lm/W
910505103156	RC530B 34S/940 SEIA	- degree(s)	4000 K	>90	149 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	W8L120 VPC U4 SC				
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	- degree(s)	3000 K	>90	133 lm/W
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	- degree(s)	3000 K	>90	133 lm/W
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	- degree(s)	3000 K	>90	133 lm/W
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	120 degree(s)	Tunable white 2700-6500 K	>90	124 lm/W
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	120 degree(s)	Tunable white 2700-6500 K	>90	93 lm/W
910505105963	RC530B 34S/ UE840 SEIA W8L120 VPC U4 W3SC	-	4000 K	>80	173 lm/W
910505105966	RC530B 34S/ BU840 SEIA W8L120 VPC U4 SC	-	4000 K	>80	139 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type
910505103104	RC530B 15S/940 DEIA W8L113 PCV	1,500 lm	Wide beam
910505103107	RC530B 31S/940 DEIA W8L141 PCV	3,100 lm	Wide beam
910505103110	RC530B 43S/940 DEIA W8L141 PCV	4,300 lm	Wide beam
910505103114	RC530B 19S/940 DEIA W8L141 PCV	1,900 lm	Wide beam
910505103115	RC530B 34S/940 DEIA W8L113 PCV	3,400 lm	Wide beam
910505103116	RC531B 15S/930 DEIA W8L113 PCV	1,500 lm	Wide beam
910505103117	RC531B 15S/940 DEIA W8L113 PCV	1,500 lm	Wide beam

Order Code	Full Product Name	Luminous Flux	Optic type
910505103121	RC531B 31S/940 DEIA W8L141 PCV	3,100 lm	Wide beam
910505103127	RC530B 50S/940 DEIA W8L141 PCV	5,000 lm	Wide beam
910505103129	RC531B 19S/940 DEIA W8L141 PCV	1,900 lm	Wide beam
910505103147	RC530B 40S/940 POE W8L120 VPC U0	4,000 lm	Wide beam
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	3,400 lm	Wide beam
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	4,000 lm	Wide beam
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	3,400 lm	Wide beam

TrueLine, recessed

Order Code	Full Product Name	Luminous Flux	Optic type	Order Code	Full Product Name	Luminous Flux	Optic type
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	3,400 lm	Wide beam office compliant	910505103106	RC532B 19S/940 DEIA W8L141 PCV	1,900 lm	Wide beam
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	5,000 lm	Wide beam office compliant	910505103109	RC533B 15S/940 DEIA W8L113 PCV	1,500 lm	Wide beam
910505103118	RC532B LED15S/940 PSD W8L113 PCV P15	1,500 lm	Wide beam	910505103119	RC532B 25S/940 DEIA W8L113 PCV	2,500 lm	Wide beam
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	3,100 lm	Wide beam	910505103122	RC532B 31S/940 DEIA W8L141 PCV	3,100 lm	Wide beam
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	1,900 lm	Wide beam	910505103124	RC532B 43S/940 DEIA W8L141 PCV	4,300 lm	Wide beam
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	5,000 lm	Wide beam	910505103126	RC533B 31S/940 DEIA W8L141 PCV	3,100 lm	Wide beam
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	4,300 lm	Wide beam	910505103131	RC533B 19S/940 DEIA W8L141 PCV	1,900 lm	Wide beam
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	4,300 lm	Wide beam	910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	4,300 lm	Wide beam
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	4,300 lm	Wide beam	910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	4,300 lm	Wide beam
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	5,000 lm	Wide beam	910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	4,300 lm	Wide beam
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	1,900 lm	Wide beam	910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	4,300 lm	Wide beam
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	3,100 lm	Wide beam	910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	5,000 lm	Wide beam office compliant
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	1,900 lm	Wide beam	910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	3,100 lm	Wide beam
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	4,000 lm	Asymmetrical mirror	910505103102	RC532B 25S/940 DEIA W8L113 VPC	2,500 lm	Wide beam
910505103123	RC534B 50S/940 DEIA W8L141 PCV	5,000 lm	Asymmetrical mirror	910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	1,900 lm	Wide beam
910505103125	RC535B 50S/940 DEIA W8L141 PCV	5,000 lm	Asymmetrical mirror	910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	1,500 lm	Wide beam
910505103130	RC535B 43S/940 DEIA W8L141 PCV	4,300 lm	Asymmetrical mirror	910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	1,500 lm	Wide beam
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	4,300 lm	Wide beam	910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	3,400 lm	Wide beam
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	3,400 lm	Wide beam	910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	3,400 lm	Wide beam
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	5,000 lm	Wide beam	910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	3,400 lm	Wide beam
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	4,000 lm	Wide beam	910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	2,500 lm	Wide beam
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	3,400 lm	Wide beam	910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	3,400 lm	Wide beam
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	3,400 lm	Wide beam	910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	2,500 lm	Wide beam
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	4,300 lm	Wide beam office compliant	910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	3,400 lm	Wide beam office compliant
910505103128	RC534B 43S/940 DEIA W8L141 PCV	4,300 lm	Asymmetrical mirror	910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	3,400 lm	Wide beam office compliant

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	12.2 W	No
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	21 W	No
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	30.5 W	No
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	14 W	No
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	24.5 W	No
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Safety class I	220 to 240 V	14.6 W	No
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	14.6 W	No
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	29 W	No
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	36 W	No
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	17.8 W	No
910505103147	RC530B 40S/940 POE III W8L120 VPC UO	Safety class	51 to 54 V	28 W	No
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	Safety class I	220 to 240 V	27.5 W	No
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Safety class I	220 to 240 V	33 W	No
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Safety class I	220 to 240 V	24.5 W	No

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910505105962	RC530B 34S/ UE840 DEIA W8L113 PCV	Safety class I	220 to 240 V	19.6 W	No
910505105964	RC530B 50S/ UE840 DEIA W8L141 PCV	Safety class I	220 to 240 V	28 W	No
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Safety class I	220 to 240 V	12.2 W	No
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	29 W	No
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	17.8 W	No
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	36 W	No
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	30.5 W	No
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	Safety class I	220 to 240 V	30.5 W	No
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	30.5 W	No
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	36 W	No
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	17.8 W	No
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	29 W	No
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	Safety class I	220 to 240 V	17.8 W	No

TrueLine, recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	31.5 W	No
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	38 W	No
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	38 W	No
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	32 W	No
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	30.5 W	No
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	24.5 W	No
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	36 W	No
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	29 W	No
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	24.5 W	No
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Safety class I	220 to 240 V	24.5 W	No
910505105965	RC530B 43S/ BU840 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	31 W	No
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	32 W	No

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910505103106	RC532B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	14 W	No
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	14.6 W	No
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	18 W	No
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	21 W	No
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	30.5 W	No
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	29 W	No
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	17.8 W	No
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Safety class I	220 to 240 V	30 W	No
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Safety class I	220 to 240 V	30 W	No
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Safety class I	220 to 240 V	35.5 W	No
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Safety class I	220 to 240 V	35.5 W	No
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	Safety class I	220 to 240 V	41.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910505105670	RC531B 31S/TW9 SEIA	Safety class I	220 to 240 V	34 W	Yes (relates to presence/

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
	W8L145 PCV U4				movement detection and daylight harvesting)
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Safety class I	220 to 240 V	18 W	No
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	17.8 W	No
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	14.6 W	No
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	14.6 W	No
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Safety class I	220 to 240 V	24 W	No
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Safety class I	220 to 240 V	25.5 W	No

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Safety class I	220 to 240 V	25.5 W	No
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Safety class I	220 to 240 V	18.8 W	No
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Safety class I	220 to 240 V	27.5 W	No
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Safety class I	220 to 240 V	27 W	No
910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	Safety class I	220 to 240 V	19.6 W	No
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	Safety class I	220 to 240 V	24 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505103104	RC530B 15S/940 DEIA W8L113 PCV	-	-	1%
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Yes	-	1%
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Yes	-	1%
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Yes	-	1%
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Yes	-	1%
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Yes	-	1%
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Yes	-	1%
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Yes	-	1%
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Yes	-	1%
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Yes	Upgradable sensor slot empty with cover	1%
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	Yes	-	1%
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Yes	-	1%
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Yes	-	1%
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	Yes	-	-

TrueLine, recessed

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	Yes	-	-
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Yes	-	1%
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	Yes	-	1%
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	Yes	-	1%
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	Yes	-	1%
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	Yes	-	1%
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	Yes	-	1%
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	Yes	-	1%
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	Yes	-	1%
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	Yes	-	1%
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	Yes	-	1%
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	Yes	-	1%
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Yes	-	1%
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Yes	-	1%
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Yes	-	1%
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Yes	-	1%
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	-	-	1%
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	-	-	1%
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Yes	-	1%
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Yes	-	1%
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Yes	-	1%
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes	-	1%
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	Yes	-	-
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Yes	-	1%
910505103106	RC532B 19S/940 DEIA W8L141 PCV	-	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Yes	-	1%
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Yes	-	1%
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Yes	-	1%
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Yes	-	1%
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Yes	-	1%
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Yes	-	1%
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103102	RC532B 25S/940 DEIA W8L113 VPC	-	-	1%
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Yes	-	1%
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Yes	-	1%
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Yes	-	1%
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor	1%

TrueLine, recessed

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	1%
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Yes	Upgradable sensor slot with SC200 sensor	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	Yes	Upgradable sensor slot with SC200 sensor	-
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor	-

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103104	RC530B 15S/940 DEIA W8L113 PCV	IK03	IP20
910505103107	RC530B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103110	RC530B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103114	RC530B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103115	RC530B 34S/940 DEIA W8L113 PCV	IK03	IP20
910505103116	RC531B 15S/930 DEIA W8L113 PCV	IK03	IP20
910505103117	RC531B 15S/940 DEIA W8L113 PCV	IK03	IP20
910505103121	RC531B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103127	RC530B 50S/940 DEIA W8L141 PCV	IK03	IP20
910505103129	RC531B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103147	RC530B 40S/940 POE W8L120 VPC UO	IK03	IP20
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	IK03	IP20
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	IK03	IP20
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	IK03	IP20
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	IK03	IP20
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	IK03	IP20
910505103118	RC532B LED15S/940 PSD W8L113 PCV P15	IK02	IP20/40
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	IK03	IP20
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	IK03	IP20
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103123	RC534B 50S/940 DEIA W8L141 PCV	IK03	IP20
910505103125	RC535B 50S/940 DEIA W8L141 PCV	IK03	IP20
910505103130	RC535B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	IK03	IP20
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	IK03	IP20
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	IK03	IP20
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	IK03	IP20
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	IK03	IP20
910505103128	RC534B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103106	RC532B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103109	RC533B 15S/940 DEIA W8L113 PCV	IK03	IP20
910505103119	RC532B 25S/940 DEIA W8L113 PCV	IK03	IP20
910505103122	RC532B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103124	RC532B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103126	RC533B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103131	RC533B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	IK03	IP20
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	IK03	IP20
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	IK03	IP20
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	IK03	IP20
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	IK03	IP20
910505103102	RC532B 25S/940 DEIA W8L113 VPC	IK03	IP20
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	IK03	IP20
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	IK03	IP20
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	IK03	IP20
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	IK03	IP20
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	IK03	IP20
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	IK03	IP20
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	IK03	IP20
910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	IK03	IP20
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	IK03	IP20

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103147	RC530B 40S/940 POE W8L120 VPC U0	-	-	-	-
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	-	-	-	-
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	-	-	-	-
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Yes	DC operated central emergency lighting	-	-

TrueLine, recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505105962	RC530B 34S/ UE840 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505105964	RC530B 50S/ UE840 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-	-	-	-
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	No	Emergency lighting 3 hours duration with DALI interface	Lithium	3 hour(s)
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103145	RC531B 31S/940 DIA	No	Emergency lighting 3 hours	Lithium	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	W8L145 PCV ELP3		duration Pro version		
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	No	Emergency lighting 3 hours duration with DALI interface	Lithium	3 hour(s)
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes	DC operated central emergency lighting	-	-

TrueLine, recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103106	RC532B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes	DC operated central emergency lighting	-	-
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting	-	-
910505103285	RC530B 43S/TW9	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	SEIA W8L145 PCV U4		emergency lighting		
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes	DC operated central emergency lighting	-	-
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting	-	-
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting	-	-
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Yes	DC operated central emergency lighting	-	-
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Yes	DC operated central emergency lighting	-	-
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes	DC operated central emergency lighting	-	-
910505103159	RC530B 25S/930 SEIA	Yes	DC operated central	-	-

TrueLine, recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	W8L120 VPC U4 W3		emergency lighting		
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103290	RC531B 25S/TW9	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	SEIA W8L120 VPC U4		emergency lighting		
910505105963	RC530B 34S/ UE840 SEIA W8L120 VPC U4 W3SC	Yes	DC operated central emergency lighting	-	-
910505105966	RC530B 34S/ BU840 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505103104	RC530B 15S/940 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103107	RC530B 31S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103110	RC530B 43S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103114	RC530B 19S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103115	RC530B 34S/940 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103116	RC531B 15S/930 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103117	RC531B 15S/940 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103121	RC531B 31S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103127	RC530B 50S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103129	RC531B 19S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103147	RC530B 40S/940 POE W8L120 VPC UO	+10 to +40 °C	1	0.4
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	+10 to +40 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	+10 to +40 °C	1	0.4
910505105962	RC530B 34S/ UE840 DEIA W8L113 PCV	+10 to +35 °C	-	-
910505105964	RC530B 50S/ UE840 DEIA W8L141 PCV	+10 to +35 °C	-	-
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	+10 to +40 °C	1	0.4
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	+10 to +40 °C	1	0.4
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	+10 to +40 °C	1	0.4
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	+10 to +40 °C	1	0.4
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	+10 to +40 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	+10 to +40 °C	1	0.4
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	+10 to +40 °C	1	0.4
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	+10 to +40 °C	1	0.4
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	+10 to +40 °C	1	0.4
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	+10 to +40 °C	1	0.4
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	+10 to +40 °C	1	0.4
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	+10 to +40 °C	1	0.4
910505103123	RC534B 50S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103125	RC535B 50S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103130	RC535B 43S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	+10 to +40 °C	1	0.4
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	+10 to +40 °C	1	0.4
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	+10 to +40 °C	1	0.4
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	+10 to +40 °C	1	0.4
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	+10 to +40 °C	1	0.4
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	+10 to +40 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505105965	RC530B 43S/ BU840 DEIA W8L150 VPC IP	+10 to +35 °C	-	-
910505103128	RC534B 43S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103106	RC532B 19S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103109	RC533B 15S/940 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103119	RC532B 25S/940 DEIA W8L113 PCV	+10 to +40 °C	1	0.4
910505103122	RC532B 31S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103124	RC532B 43S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103126	RC533B 31S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103131	RC533B 19S/940 DEIA W8L141 PCV	+10 to +40 °C	1	0.4
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	+10 to +40 °C	1	0.4
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	+10 to +40 °C	1	0.4
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	+10 to +40 °C	1	0.4
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	+10 to +40 °C	1	0.4
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	+10 to +40 °C	1	0.4
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	+10 to +40 °C	1	0.4
910505103102	RC532B 25S/940 DEIA W8L113 VPC	+10 to +40 °C	1	0.4
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	+10 to +40 °C	1	0.4
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	+10 to +40 °C	1	0.4

TrueLine, recessed

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	+10 to +40 °C	1		0.4
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	+10 to +40 °C	1		0.4
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	+10 to +40 °C	1		0.4
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	+10 to +40 °C	1		0.4
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	+10 to +40 °C	1		0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	+10 to +40 °C	1		0.4
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	+10 to +40 °C	1		0.4
910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	+10 to +35 °C	-		-
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	+10 to +35 °C	-		-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505103104	RC530B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103107	RC530B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103110	RC530B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103114	RC530B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103115	RC530B 34S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103116	RC531B 15S/930 DEIA W8L113 PCV	(0.43, 0.40) SDCM <3
910505103117	RC531B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103121	RC531B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103127	RC530B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103129	RC531B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103147	RC530B 40S/940 POE W8L120 VPC U0	(0.38, 0.38) SDCM <3
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	(0.38, 0.38) SDCM <3
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	(0.39, 0.38) SDCM <3
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	(0.39, 0.38) SDCM <3
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	(0.38, 0.38) SDCM <3
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	(0.38, 0.38) SDCM <3
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103123	RC534B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103125	RC535B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103130	RC535B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	(0.38, 0.38) SDCM <3
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	(0.39, 0.38) SDCM <3
910505103128	RC534B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103106	RC532B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103109	RC533B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103119	RC532B 25S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103122	RC532B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103124	RC532B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103126	RC533B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103131	RC533B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	(0.38, 0.38) SDCM <3
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	(0.38, 0.38) SDCM <3
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	Tunable, SDCM ≤3
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	Tunable, SDCM ≤3
910505103102	RC532B 25S/940 DEIA W8L113 VPC	(0.38, 0.38) SDCM <3
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	(0.43, 0.40) SDCM <3

TrueLine, recessed

Order Code	Full Product Name	Initial chromaticity
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	(0.43, 0.40) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	(0.38, 0.38) SDCM <3
910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	(0.39, 0.38) SDCM <3
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	(0.39, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910505103104	RC530B 15S/940 DEIA W8L113 PCV	RC530B
910505103107	RC530B 31S/940 DEIA W8L141 PCV	RC530B
910505103110	RC530B 43S/940 DEIA W8L141 PCV	RC530B
910505103114	RC530B 19S/940 DEIA W8L141 PCV	RC530B
910505103115	RC530B 34S/940 DEIA W8L113 PCV	RC530B
910505103116	RC531B 15S/930 DEIA W8L113 PCV	RC531B
910505103117	RC531B 15S/940 DEIA W8L113 PCV	RC531B
910505103121	RC531B 31S/940 DEIA W8L141 PCV	RC531B
910505103127	RC530B 50S/940 DEIA W8L141 PCV	RC530B
910505103129	RC531B 19S/940 DEIA W8L141 PCV	RC531B
910505103147	RC530B 40S/940 POE W8L120 VPC U0	RC530B
910505103284	RC530B 34S/TW9 DEIA W8L113 PCV	RC530B
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	RC530B
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	RC530B
910505105962	RC530B 34S/UE840 DEIA W8L113 PCV	RC530B
910505105964	RC530B 50S/UE840 DEIA W8L141 PCV	RC530B
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	RC532B
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	RC531B
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	RC531B
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	RC530B
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	RC530B
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	RC530B
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	RC530B
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	RC530B
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	RC531B
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	RC531B
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	RC531B
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	RC534B
910505103123	RC534B 50S/940 DEIA W8L141 PCV	RC534B
910505103125	RC535B 50S/940 DEIA W8L141 PCV	RC535B
910505103130	RC535B 43S/940 DEIA W8L141 PCV	RC535B
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	RC530B

Order Code	Full Product Name	Product family code
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	RC530B
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	RC530B
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	RC530B
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	RC530B
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	RC530B
910505105965	RC530B 43S/BU840 DEIA W8L150 VPC IP	RC530B
910505103128	RC534B 43S/940 DEIA W8L141 PCV	RC534B
910505103106	RC532B 19S/940 DEIA W8L141 PCV	RC532B
910505103109	RC533B 15S/940 DEIA W8L113 PCV	RC533B
910505103119	RC532B 25S/940 DEIA W8L113 PCV	RC532B
910505103122	RC532B 31S/940 DEIA W8L141 PCV	RC532B
910505103124	RC532B 43S/940 DEIA W8L141 PCV	RC532B
910505103126	RC533B 31S/940 DEIA W8L141 PCV	RC533B
910505103131	RC533B 19S/940 DEIA W8L141 PCV	RC533B
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	RC532B
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	RC530B
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	RC530B
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	RC530B
910505105669	RC530B 50S/TW9 SEIA W8L145 PCV U4	RC530B
910505105670	RC531B 31S/TW9 SEIA W8L145 PCV U4	RC531B
910505103102	RC532B 25S/940 DEIA W8L113 VPC	RC532B
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	RC531B
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	RC531B
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	RC531B
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	RC530B
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	RC530B
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	RC530B
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	RC530B
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	RC530B
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	RC534B
910505105963	RC530B 34S/UE840 SEIA W8L120 VPC U4 W3SC	RC530B
910505105966	RC530B 34S/BU840 SEIA W8L120 VPC U4 SC	RC530B


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103103




Polar Normal (separate) - RC530BI - 910505103127




Polar Normal (separate) - RC530BI - 910505103119




Polar Normal (separate) - RC530BI - 910505103145




Polar Normal (separate) - RC530BI - 910505103150




Polar Normal (separate) - RC530BI - 910505103139



Polar Normal (separate) - RC530BI - 910505103122




Polar Normal (separate) - RC530BI - 910505103106




Polar Normal (separate) - RC530BI - 910505103102


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103115




Polar Normal (separate) - RC530BI - 910505103153




Polar Normal (separate) - RC530BI - 910505103136




Polar Normal (separate) - RC530BI - 910505103128




Polar Normal (separate) - RC530BI - 910505103160




Polar Normal (separate) - RC530BI - 910505103120



Polar Normal (separate) - RC530BI - 910505103157




Polar Normal (separate) - RC530BI - 910505103285




Polar Normal (separate) - RC530BI - 910505103138


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103159




Polar Normal (separate) - RC530BI - 910505103156




Polar Normal (separate) - RC530BI - 910505103123




Polar Normal (separate) - RC530BI - 910505103293




Polar Normal (separate) - RC530BI - 910505103291




Polar Normal (separate) - RC530BI - 910505103117



Polar Normal (separate) - RC530BI - 910505103290




Polar Normal (separate) - RC530BI - 910505103129




Polar Normal (separate) - RC530BI - 910505103147


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103149




Polar Normal (separate) - RC530BI - 910505103112




Polar Normal (separate) - RC530BI - 910505103110




Polar Normal (separate) - RC530BI - 910505103116




Polar Normal (separate) - RC530BI - 910505103125




Polar Normal (separate) - RC530BI - 910505103101



Polar Normal (separate) - RC530BI - 910505103118




Polar Normal (separate) - RC530BI - 910505103288




Polar Normal (separate) - RC530BI - 910505103140


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103284




Polar Normal (separate) - RC530BI - 910505103155




Polar Normal (separate) - RC530BI - 910505103111




Polar Normal (separate) - RC530BI - 910505103124




Polar Normal (separate) - RC530BI - 910505103286




Polar Normal (separate) - RC530BI - 910505103104



Polar Normal (separate) - RC530BI - 910505103105




Polar Normal (separate) - RC530BI - 910505103292




Polar Normal (separate) - RC530BI - 910505103141


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103154




Polar Normal (separate) - RC530BI - 910505103144




Polar Normal (separate) - RC530BI - 910505103107




Polar Normal (separate) - RC530BI - 910505103109




Polar Normal (separate) - RC530BI - 910505103114




Polar Normal (separate) - RC530BI - 910505103113



Polar Normal (separate) - RC530BI - 910505103121




Polar Normal (separate) - RC530BI - 910505103126




Polar Normal (separate) - RC530BI - 910505103131


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103130




Polar Normal (separate) - RC530BI - 910505103135




Polar Normal (separate) - RC530BI - 910505103158




Polar Normal (separate) - RC530BI - 910505105669




Polar Normal (separate) - RC530BI - 910505105670




Polar Normal (separate) - null - 910505105966




Polar Normal (separate) - null - 910505105965



Polar Normal (separate) - null - 910505105964



Polar Normal (separate) - null - 910505105962



Polar Normal (separate) - null - 910505105963

TrueLine, recessed



© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2026, April 28 - data subject to change