



TrueLine, recessed - True line of light: elegant, energy- efficient and compliant with office lighting norms

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, recessed is able to meet both sets of requirements. TrueLine is also available in a suspended version.

Benefits

- The most uniform exit window
- Extremely high efficacy for a line luminaire
- Luminaire housing dimensions that are most popular with architects

TrueLine, recessed

Features

- Luminous efficacy > 100 lm/W
- Complies with office lighting norms
- Stand-alone and continuous lines
- Suspended version also available
- Direct and indirect light
- Homogeneous exit window
- Future-proof: PoE

Application

- General lighting for mid- and high-end office buildings


Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions




Dimensional drawing



Recessed VPC_W8L120_no sensor

TrueLine, recessed

Dimensional drawing



Product details



TrueLineRecessed NOC OPTICS
DP



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI5-
DPP.tif



TrueLine-
RC534B_SM534C_SP534P-DPP.tif



TrueLineRecessed OC OPTICS DP



TrueLineRecessed PCV line
CONNECTED DP1



TrueLineRecessed PCV line
CONNECTED DP2

TrueLine, recessed

Product details

TrueLine_Recessed IP DP



TrueLineRecessed ASYMMETRIC OPTICS DP



TrueLine, recessed

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	- degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20

Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting

Approval and Application

Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97146200	RC530B 15S/940 DEIA W8L113 PCV	127 lm/W	1,500 lm	Wide beam
97171400	RC531B 15S/940 DEIA W8L113 PCV	99 lm/W	1,500 lm	Wide beam
97178300	RC531B 31S/940 DEIA W8L141 PCV	110 lm/W	3,100 lm	Wide beam
97200100	RC534B 43S/940 DEIA W8L141 PCV	138 lm/W	4,300 lm	Asymmetrical mirror
97184400	RC532B 25S/940 DEIA W8L113 PCV	139 lm/W	2,500 lm	Wide beam

Operating and Electrical

TrueLine, recessed

Order Code	Full Product Name	Power Consumption
97146200	RC530B 15S/940 DEIA W8L113 PCV	12.2 W
97171400	RC531B 15S/940 DEIA W8L113 PCV	14.6 W
97178300	RC531B 31S/940 DEIA W8L141 PCV	29 W

Order Code	Full Product Name	Power Consumption
97200100	RC534B 43S/940 DEIA W8L141 PCV	32 W
97184400	RC532B 25S/940 DEIA W8L113 PCV	18 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
97146200	RC530B 15S/940 DEIA W8L113 PCV	-
97171400	RC531B 15S/940 DEIA W8L113 PCV	Yes
97178300	RC531B 31S/940 DEIA W8L141 PCV	Yes




Order Code	Full Product Name	Dimmable
97200100	RC534B 43S/940 DEIA W8L141 PCV	Yes
97184400	RC532B 25S/940 DEIA W8L113 PCV	Yes

Product Data


Order Code	Full Product Name	Product family code
97146200	RC530B 15S/940 DEIA W8L113 PCV	RC530B
97171400	RC531B 15S/940 DEIA W8L113 PCV	RC531B
97178300	RC531B 31S/940 DEIA W8L141 PCV	RC531B

Order Code	Full Product Name	Product family code
97200100	RC534B 43S/940 DEIA W8L141 PCV	RC534B
97184400	RC532B 25S/940 DEIA W8L113 PCV	RC532B


Polar Wide Diagrams



Polar Normal (separate) - RC530BI - 910505103119



Polar Normal (separate) - RC530BI - 910505103128



Polar Normal (separate) - RC530BI - 910505103117

Polar Normal (separate) - RC530BI - 910505103104

Polar Normal (separate) - RC530BI - 910505103121

TrueLine, recessed



© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com

2026, March 19 - data subject to change