



Philips TrueLine recessed: True line of light

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

Applications

- Offices
- Education
- Retail

Features


- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering

- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options
- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine Recessed PCV IP RTP



TrueLine recessed-RC530B L1130



TrueLine-RC530 RC531B VPC ELP3



TrueLine-RC530 RC531B PCV ELP3

TrueLine-RC534B VPC



TrueLineRecessed PCV LINE
ASYMMETRIC RTP



TrueLineRecessed VPC OC IP
RTP



TrueLineRecessed PCV
ASYMMETRIC RTP



TrueLineRecessed PCV LINE
NOSENSOR RTP



TrueLine Recessed-U3




TrueLineRecessed VPC NOC
IP RTP




TrueLineRecessed VPC OC U4
RTP



Dimensional drawing




TrueLine Recessed NOC - 930 warm white - Power supply unit
with DALI interface - Push-in connector 5-pole - White RAL 9003




Recessed VPC_W8L150_no sensor

RC530B 43S/940 DIA W8L150 VPC ELD3




Recessed VPC_W8L120_sensor/IP


RC531B 25S/TW9 SEIA W8L120 VPC U4



RC530B 34S/940 DEIA W8L113 PCV




RC535B 43S/940 DEIA W8L141 PCV




Recessed VPC_W8L120_no sensor

RC533B 15S/940 DEIA W8L113 PCV



RC534B 50S/940 DEIA W8L141 PCV



RC530B 43S/940 SEIA W8L145 PCV U4

Product details



TrueLineRecessed NOC
OPTICS DP



TrueLine_Recessed U4 DP

TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B
_PCV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B
_PCV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI
5-DPP.tif



TrueLine-
RC534B_SM534C_SP534P-
DPP.tif



TrueLineRecessed OC OPTICS
DP



TrueLineRecessed PCV line
CONNECTED DP1



TrueLineRecessed VPC line
CONNECTED DP2



TrueLineRecessed VPC line
CONNECTED DP1





TrueLine_Recessed-U3



TrueLineRecessed PCV line
CONNECTED DP2



TrueLineRecessed VPC LINE
RTP



TrueLine_Recessed IP DP



TrueLineRecessed
ASYMMETRIC OPTICS DP

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>90
-----------------------------	-----

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%
Embedded control	Upgradable sensor slot with SC200 sensor

Mechanical and Housing

Housing Color	White
---------------	-------

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Type of emergency lighting battery	Lithium

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source	Optic type
97146200	RC530B 15S/940 DEIA W8L113 PCV	1,500 lm	4000 K	127 lm/W	- degree(s)	Wide beam
97149300	RC530B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	148 lm/W	- degree(s)	Wide beam
97159200	RC530B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
97147900	RC530B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	143 lm/W	- degree(s)	Wide beam
97153000	RC530B 34S/940 DEIA W8L113 PCV	3,400 lm	4000 K	143 lm/W	- degree(s)	Wide beam
97169100	RC531B 15S/930 DEIA W8L113 PCV	1,500 lm	3000 K	99 lm/W	- degree(s)	Wide beam
97171400	RC531B 15S/940 DEIA W8L113 PCV	1,500 lm	4000 K	99 lm/W	- degree(s)	Wide beam
97178300	RC531B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97165300	RC530B 50S/940 DEIA W8L141 PCV	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source	Optic type
97174500	RC531B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97322000	RC530B 40S/TW9 DEIA W8L113 PCV	4,000 lm	Tunable white 2700-6500 K	121 lm/W	120 degree(s)	Wide beam
97328200	RC530B 34S/940 DEIA W8L113 PCV SC	3,400 lm	4000 K	143 lm/W	120 degree(s)	Wide beam
97181300	RC532B LED15S/940 PSD W8L113 PCV P15	1,500 lm	4000 K	127 lm/W	- degree(s)	Wide beam
97180600	RC531B 31S/940 DIA W8L150 VPC ELP3	3,100 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97177600	RC531B 19S/940 DIA W8L150 VPC ELP3	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97168400	RC530B 50S/940 DIA W8L150 VPC ELP3	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam
97164600	RC530B 43S/940 DIA W8L150 VPC ELP3	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
97160800	RC530B 43S/940 DIA W8L150 VPC ELD3	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
97163900	RC530B 43S/940 DIA W8L145 PCV ELP3	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
97167700	RC530B 50S/940 DIA W8L145 PCV ELP3	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam
97176900	RC531B 19S/940 DIA W8L145 PCV ELP3	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97179000	RC531B 31S/940 DIA W8L145 PCV ELP3	3,100 lm	4000 K	112 lm/W	- degree(s)	Wide beam
97175200	RC531B 19S/940 DIA W8L145 PCV ELD3	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97199800	RC534B 40S/940 DEIA W8L120 VPC IP	4,000 lm	4000 K	130 lm/W	- degree(s)	Asymmetrical mirror
97201800	RC534B 50S/940 DEIA W8L141 PCV	5,000 lm	4000 K	132 lm/W	- degree(s)	Asymmetrical mirror
97203200	RC535B 50S/940 DEIA W8L141 PCV	5,000 lm	4000 K	132 lm/W	- degree(s)	Asymmetrical mirror
97202500	RC535B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	138 lm/W	- degree(s)	Asymmetrical mirror
97161500	RC530B 43S/940 DEIA W8L150 VPC IP	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
97150900	RC530B 34S/930 DEIA W8L120 VPC IP	3,400 lm	3000 K	131 lm/W	- degree(s)	Wide beam
97166000	RC530B 50S/940 DEIA W8L150 VPC IP	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam
97158500	RC530B 40S/940 DEIA W8L120 VPC IP	4,000 lm	4000 K	138 lm/W	- degree(s)	Wide beam
97154700	RC530B 34S/940 DEIA W8L120 VPC IP	3,400 lm	4000 K	143 lm/W	- degree(s)	Wide beam
97329900	RC530B 34S/940 DEIA W8L120 VPC IP SC	3,400 lm	4000 K	143 lm/W	120 degree(s)	Wide beam
97200100	RC534B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	138 lm/W	- degree(s)	Asymmetrical mirror
97182000	RC532B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	143 lm/W	- degree(s)	Wide beam
97193600	RC533B 15S/940 DEIA W8L113 PCV	1,500 lm	4000 K	103 lm/W	- degree(s)	Wide beam
97184400	RC532B 25S/940 DEIA W8L113 PCV	2,500 lm	4000 K	139 lm/W	- degree(s)	Wide beam
97186800	RC532B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	148 lm/W	- degree(s)	Wide beam
97188200	RC532B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
97197400	RC533B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	112 lm/W	- degree(s)	Wide beam
97194300	RC533B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
97190500	RC532B 43S/940 SEIA W8L145 PCV U4 W3	4,300 lm	4000 K	143 lm/W	- degree(s)	Wide beam
97162200	RC530B 43S/940 SEIA W8L145 PCV U4	4,300 lm	4000 K	143 lm/W	- degree(s)	Wide beam
97321300	RC530B 43S/TW9 SEIA W8L145 PCV U4	4,300 lm	Tunable white 2700-6500 K	121 lm/W	120 degree(s)	Wide beam
97327500	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	4,300 lm	Tunable white 2700-6500 K	121 lm/W	120 degree(s)	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source	Optic type
97185100	RC532B 25S/940 DEIA W8L113 VPC	2,500 lm	4000 K	139 lm/W	- degree(s)	Wide beam
97173800	RC531B 19S/930 DEIA W8L150 VPC IP	1,900 lm	3000 K	104 lm/W	- degree(s)	Wide beam
97172100	RC531B 15S/940 DEIA W8L120 VPC IP	1,500 lm	4000 K	99 lm/W	- degree(s)	Wide beam
97170700	RC531B 15S/930 DEIA W8L120 VPC IP	1,500 lm	3000 K	99 lm/W	- degree(s)	Wide beam
97155400	RC530B 34S/940 SEIA W8L120 VPC U4 SC	3,400 lm	4000 K	149 lm/W	- degree(s)	Wide beam
97151600	RC530B 34S/930 SEIA W8L120 VPC U4 W3	3,400 lm	3000 K	133 lm/W	- degree(s)	Wide beam
97152300	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	3,400 lm	3000 K	133 lm/W	- degree(s)	Wide beam
97148600	RC530B 25S/930 SEIA W8L120 VPC U4 W3	2,500 lm	3000 K	133 lm/W	- degree(s)	Wide beam
97324400	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	3,400 lm	Tunable white 2700-6500 K	124 lm/W	120 degree(s)	Wide beam
97326800	RC531B 25S/TW9 SEIA W8L120 VPC U4	2,500 lm	Tunable white 2700-6500 K	93 lm/W	120 degree(s)	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
97146200	RC530B 15S/940 DEIA W8L113 PCV	12.2 W
97149300	RC530B 31S/940 DEIA W8L141 PCV	21 W
97159200	RC530B 43S/940 DEIA W8L141 PCV	30.5 W
97147900	RC530B 19S/940 DEIA W8L141 PCV	14 W
97153000	RC530B 34S/940 DEIA W8L113 PCV	24.5 W
97169100	RC531B 15S/930 DEIA W8L113 PCV	14.6 W
97171400	RC531B 15S/940 DEIA W8L113 PCV	14.6 W
97178300	RC531B 31S/940 DEIA W8L141 PCV	29 W
97165300	RC530B 50S/940 DEIA W8L141 PCV	36 W
97174500	RC531B 19S/940 DEIA W8L141 PCV	17.8 W
97322000	RC530B 40S/TW9 DEIA W8L113 PCV	33 W
97328200	RC530B 34S/940 DEIA W8L113 PCV SC	24.5 W
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	12.2 W
97180600	RC531B 31S/940 DIA W8L150 VPC ELP3	29 W
97177600	RC531B 19S/940 DIA W8L150 VPC ELP3	17.8 W
97168400	RC530B 50S/940 DIA W8L150 VPC ELP3	36 W
97164600	RC530B 43S/940 DIA W8L150 VPC ELP3	30.5 W
97160800	RC530B 43S/940 DIA W8L150 VPC ELD3	30.5 W
97163900	RC530B 43S/940 DIA W8L145 PCV ELP3	30.5 W
97167700	RC530B 50S/940 DIA W8L145 PCV ELP3	36 W
97176900	RC531B 19S/940 DIA W8L145 PCV ELP3	17.8 W
97179000	RC531B 31S/940 DIA W8L145 PCV ELP3	29 W
97175200	RC531B 19S/940 DIA W8L145 PCV ELD3	17.8 W
97199800	RC534B 40S/940 DEIA W8L120 VPC IP	31.5 W
97201800	RC534B 50S/940 DEIA W8L141 PCV	38 W

Order Code	Full Product Name	Power Consumption
97203200	RC535B 50S/940 DEIA W8L141 PCV	38 W
97202500	RC535B 43S/940 DEIA W8L141 PCV	32 W
97161500	RC530B 43S/940 DEIA W8L150 VPC IP	30.5 W
97150900	RC530B 34S/930 DEIA W8L120 VPC IP	24.5 W
97166000	RC530B 50S/940 DEIA W8L150 VPC IP	36 W
97158500	RC530B 40S/940 DEIA W8L120 VPC IP	29 W
97154700	RC530B 34S/940 DEIA W8L120 VPC IP	24.5 W
97329900	RC530B 34S/940 DEIA W8L120 VPC IP SC	24.5 W
97200100	RC534B 43S/940 DEIA W8L141 PCV	32 W
97182000	RC532B 19S/940 DEIA W8L141 PCV	14 W
97193600	RC533B 15S/940 DEIA W8L113 PCV	14.6 W
97184400	RC532B 25S/940 DEIA W8L113 PCV	18 W
97186800	RC532B 31S/940 DEIA W8L141 PCV	21 W
97188200	RC532B 43S/940 DEIA W8L141 PCV	30.5 W
97197400	RC533B 31S/940 DEIA W8L141 PCV	29 W
97194300	RC533B 19S/940 DEIA W8L141 PCV	17.8 W
97190500	RC532B 43S/940 SEIA W8L145 PCV U4 W3	30 W
97162200	RC530B 43S/940 SEIA W8L145 PCV U4	30 W
97321300	RC530B 43S/TW9 SEIA W8L145 PCV U4	35.5 W
97327500	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	35.5 W
97185100	RC532B 25S/940 DEIA W8L113 VPC	18 W
97173800	RC531B 19S/930 DEIA W8L150 VPC IP	17.8 W
97172100	RC531B 15S/940 DEIA W8L120 VPC IP	14.6 W
97170700	RC531B 15S/930 DEIA W8L120 VPC IP	14.6 W
97155400	RC530B 34S/940 SEIA W8L120 VPC U4 SC	24 W
97151600	RC530B 34S/930 SEIA W8L120 VPC U4 W3	25.5 W
97152300	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	25.5 W
97148600	RC530B 25S/930 SEIA W8L120 VPC U4 W3	18.8 W
97324400	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	27.5 W
97326800	RC531B 25S/TW9 SEIA W8L120 VPC U4	27 W

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
97146200	RC530B 15S/940 DEIA W8L113 PCV	IP20	IK03
97149300	RC530B 31S/940 DEIA W8L141 PCV	IP20	IK03
97159200	RC530B 43S/940 DEIA W8L141 PCV	IP20	IK03
97147900	RC530B 19S/940 DEIA W8L141 PCV	IP20	IK03
97153000	RC530B 34S/940 DEIA W8L113 PCV	IP20	IK03
97169100	RC531B 15S/930 DEIA W8L113 PCV	IP20	IK03
97171400	RC531B 15S/940 DEIA W8L113 PCV	IP20	IK03
97178300	RC531B 31S/940 DEIA W8L141 PCV	IP20	IK03
97165300	RC530B 50S/940 DEIA W8L141 PCV	IP20	IK03

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
97174500	RC531B 19S/940 DEIA W8L141 PCV	IP20	IK03
97322000	RC530B 40S/TW9 DEIA W8L113 PCV	IP20	IK03
97328200	RC530B 34S/940 DEIA W8L113 PCV SC	IP20	IK03
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	IP20/40	IK02
97180600	RC531B 31S/940 DIA W8L150 VPC ELP3	IP20	IK03
97177600	RC531B 19S/940 DIA W8L150 VPC ELP3	IP20	IK03
97168400	RC530B 50S/940 DIA W8L150 VPC ELP3	IP20	IK03
97164600	RC530B 43S/940 DIA W8L150 VPC ELP3	IP20	IK03
97160800	RC530B 43S/940 DIA W8L150 VPC ELD3	IP20	IK03
97163900	RC530B 43S/940 DIA W8L145 PCV ELP3	IP20	IK03
97167700	RC530B 50S/940 DIA W8L145 PCV ELP3	IP20	IK03
97176900	RC531B 19S/940 DIA W8L145 PCV ELP3	IP20	IK03
97179000	RC531B 31S/940 DIA W8L145 PCV ELP3	IP20	IK03
97175200	RC531B 19S/940 DIA W8L145 PCV ELD3	IP20	IK03
97199800	RC534B 40S/940 DEIA W8L120 VPC IP	IP20	IK03
97201800	RC534B 50S/940 DEIA W8L141 PCV	IP20	IK03
97203200	RC535B 50S/940 DEIA W8L141 PCV	IP20	IK03
97202500	RC535B 43S/940 DEIA W8L141 PCV	IP20	IK03
97161500	RC530B 43S/940 DEIA W8L150 VPC IP	IP20	IK03
97150900	RC530B 34S/930 DEIA W8L120 VPC IP	IP20	IK03
97166000	RC530B 50S/940 DEIA W8L150 VPC IP	IP20	IK03
97158500	RC530B 40S/940 DEIA W8L120 VPC IP	IP20	IK03
97154700	RC530B 34S/940 DEIA W8L120 VPC IP	IP20	IK03
97329900	RC530B 34S/940 DEIA W8L120 VPC IP SC	IP20	IK03
97200100	RC534B 43S/940 DEIA W8L141 PCV	IP20	IK03
97182000	RC532B 19S/940 DEIA W8L141 PCV	IP20	IK03
97193600	RC533B 15S/940 DEIA W8L113 PCV	IP20	IK03
97184400	RC532B 25S/940 DEIA W8L113 PCV	IP20	IK03
97186800	RC532B 31S/940 DEIA W8L141 PCV	IP20	IK03
97188200	RC532B 43S/940 DEIA W8L141 PCV	IP20	IK03
97197400	RC533B 31S/940 DEIA W8L141 PCV	IP20	IK03
97194300	RC533B 19S/940 DEIA W8L141 PCV	IP20	IK03
97190500	RC532B 43S/940 SEIA W8L145 PCV U4 W3	IP20	IK03
97162200	RC530B 43S/940 SEIA W8L145 PCV U4	IP20	IK03
97321300	RC530B 43S/TW9 SEIA W8L145 PCV U4	IP20	IK03
97327500	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	IP20	IK03
97185100	RC532B 25S/940 DEIA W8L113 VPC	IP20	IK03
97173800	RC531B 19S/930 DEIA W8L150 VPC IP	IP20	IK03
97172100	RC531B 15S/940 DEIA W8L120 VPC IP	IP20	IK03
97170700	RC531B 15S/930 DEIA W8L120 VPC IP	IP20	IK03
97155400	RC530B 34S/940 SEIA W8L120 VPC U4 SC	IP20	IK03
97151600	RC530B 34S/930 SEIA W8L120 VPC U4 W3	IP20	IK03

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
97152300	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	IP20	IK03
97148600	RC530B 25S/930 SEIA W8L120 VPC U4 W3	IP20	IK03
97324400	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	IP20	IK03
97326800	RC531B 25S/TW9 SEIA W8L120 VPC U4	IP20	IK03

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
97146200	RC530B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97149300	RC530B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97159200	RC530B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97147900	RC530B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97153000	RC530B 34S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97169100	RC531B 15S/930 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97171400	RC531B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97178300	RC531B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97165300	RC530B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97174500	RC531B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97322000	RC530B 40S/TW9 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97328200	RC530B 34S/940 DEIA W8L113 PCV SC	Yes	DC operated central emergency lighting
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	-	-
97180600	RC531B 31S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
97177600	RC531B 19S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
97168400	RC530B 50S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
97164600	RC530B 43S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
97160800	RC530B 43S/940 DIA W8L150 VPC ELD3	No	Emergency lighting 3 hours duration with DALI interface
97163900	RC530B 43S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
97167700	RC530B 50S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
97176900	RC531B 19S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
97179000	RC531B 31S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
97175200	RC531B 19S/940 DIA W8L145 PCV ELD3	No	Emergency lighting 3 hours duration with DALI interface
97199800	RC534B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
97201800	RC534B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97203200	RC535B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97202500	RC535B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97161500	RC530B 43S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting
97150900	RC530B 34S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
97166000	RC530B 50S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting
97158500	RC530B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
97154700	RC530B 34S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
97329900	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes	DC operated central emergency lighting
97200100	RC534B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97182000	RC532B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
97193600	RC533B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97184400	RC532B 25S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
97186800	RC532B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97188200	RC532B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97197400	RC533B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97194300	RC533B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
97190500	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes	DC operated central emergency lighting
97162200	RC530B 43S/940 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting
97321300	RC530B 43S/TW9 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting
97327500	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes	DC operated central emergency lighting
97185100	RC532B 25S/940 DEIA W8L113 VPC	Yes	DC operated central emergency lighting
97173800	RC531B 19S/930 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting
97172100	RC531B 15S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
97170700	RC531B 15S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
97155400	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting
97151600	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Yes	DC operated central emergency lighting
97152300	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes	DC operated central emergency lighting
97148600	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Yes	DC operated central emergency lighting
97324400	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting
97326800	RC531B 25S/TW9 SEIA W8L120 VPC U4	Yes	DC operated central emergency lighting

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
97146200	RC530B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
97149300	RC530B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97159200	RC530B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97147900	RC530B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97153000	RC530B 34S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
97169100	RC531B 15S/930 DEIA W8L113 PCV	(0.43, 0.40) SDCM <3
97171400	RC531B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
97178300	RC531B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97165300	RC530B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97174500	RC531B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97322000	RC530B 40S/TW9 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
97328200	RC530B 34S/940 DEIA W8L113 PCV SC	(0.38, 0.38) SDCM <3
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	(0.38, 0.38) SDCM <3
97180600	RC531B 31S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
97177600	RC531B 19S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
97168400	RC530B 50S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
97164600	RC530B 43S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
97160800	RC530B 43S/940 DIA W8L150 VPC ELD3	(0.38, 0.38) SDCM <3
97163900	RC530B 43S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
97167700	RC530B 50S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
97176900	RC531B 19S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
97179000	RC531B 31S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
97175200	RC531B 19S/940 DIA W8L145 PCV ELD3	(0.38, 0.38) SDCM <3
97199800	RC534B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
97201800	RC534B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97203200	RC535B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97202500	RC535B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97161500	RC530B 43S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
97150900	RC530B 34S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
97166000	RC530B 50S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
97158500	RC530B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
97154700	RC530B 34S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
97329900	RC530B 34S/940 DEIA W8L120 VPC IP SC	(0.38, 0.38) SDCM <3
97200100	RC534B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97182000	RC532B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97193600	RC533B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
97184400	RC532B 25S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
97186800	RC532B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97188200	RC532B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97197400	RC533B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97194300	RC533B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
97190500	RC532B 43S/940 SEIA W8L145 PCV U4 W3	(0.38, 0.38) SDCM <3
97162200	RC530B 43S/940 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
97321300	RC530B 43S/TW9 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
97327500	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	(0.38, 0.38) SDCM <3
97185100	RC532B 25S/940 DEIA W8L113 VPC	(0.38, 0.38) SDCM <3
97173800	RC531B 19S/930 DEIA W8L150 VPC IP	(0.43, 0.40) SDCM <3
97172100	RC531B 15S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
97170700	RC531B 15S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
97155400	RC530B 34S/940 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
97151600	RC530B 34S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
97152300	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	(0.43, 0.40) SDCM <3
97148600	RC530B 25S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
97324400	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
97326800	RC531B 25S/TW9 SEIA W8L120 VPC U4	(0.38, 0.38) SDCM <3


Product Data

Order Code	Full Product Name	Product family code
97146200	RC530B 15S/940 DEIA W8L113 PCV	RC530B
97149300	RC530B 31S/940 DEIA W8L141 PCV	RC530B
97159200	RC530B 43S/940 DEIA W8L141 PCV	RC530B


Order Code	Full Product Name	Product family code
97147900	RC530B 19S/940 DEIA W8L141 PCV	RC530B
97153000	RC530B 34S/940 DEIA W8L113 PCV	RC530B
97169100	RC531B 15S/930 DEIA W8L113 PCV	RC531B
97171400	RC531B 15S/940 DEIA W8L113 PCV	RC531B
97178300	RC531B 31S/940 DEIA W8L141 PCV	RC531B
97165300	RC530B 50S/940 DEIA W8L141 PCV	RC530B
97174500	RC531B 19S/940 DEIA W8L141 PCV	RC531B
97322000	RC530B 40S/TW9 DEIA W8L113 PCV	RC530B
97328200	RC530B 34S/940 DEIA W8L113 PCV SC	RC530B
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	RC532B
97180600	RC531B 31S/940 DIA W8L150 VPC ELP3	RC531B
97177600	RC531B 19S/940 DIA W8L150 VPC ELP3	RC531B
97168400	RC530B 50S/940 DIA W8L150 VPC ELP3	RC530B
97164600	RC530B 43S/940 DIA W8L150 VPC ELP3	RC530B
97160800	RC530B 43S/940 DIA W8L150 VPC ELD3	RC530B
97163900	RC530B 43S/940 DIA W8L145 PCV ELP3	RC530B
97167700	RC530B 50S/940 DIA W8L145 PCV ELP3	RC530B
97176900	RC531B 19S/940 DIA W8L145 PCV ELP3	RC531B
97179000	RC531B 31S/940 DIA W8L145 PCV ELP3	RC531B
97175200	RC531B 19S/940 DIA W8L145 PCV ELD3	RC531B
97199800	RC534B 40S/940 DEIA W8L120 VPC IP	RC534B
97201800	RC534B 50S/940 DEIA W8L141 PCV	RC534B
97203200	RC535B 50S/940 DEIA W8L141 PCV	RC535B
97202500	RC535B 43S/940 DEIA W8L141 PCV	RC535B
97161500	RC530B 43S/940 DEIA W8L150 VPC IP	RC530B
97150900	RC530B 34S/930 DEIA W8L120 VPC IP	RC530B
97166000	RC530B 50S/940 DEIA W8L150 VPC IP	RC530B
97158500	RC530B 40S/940 DEIA W8L120 VPC IP	RC530B
97154700	RC530B 34S/940 DEIA W8L120 VPC IP	RC530B
97329900	RC530B 34S/940 DEIA W8L120 VPC IP SC	RC530B
97200100	RC534B 43S/940 DEIA W8L141 PCV	RC534B
97182000	RC532B 19S/940 DEIA W8L141 PCV	RC532B
97193600	RC533B 15S/940 DEIA W8L113 PCV	RC533B
97184400	RC532B 25S/940 DEIA W8L113 PCV	RC532B
97186800	RC532B 31S/940 DEIA W8L141 PCV	RC532B
97188200	RC532B 43S/940 DEIA W8L141 PCV	RC532B
97197400	RC533B 31S/940 DEIA W8L141 PCV	RC533B
97194300	RC533B 19S/940 DEIA W8L141 PCV	RC533B
97190500	RC532B 43S/940 SEIA W8L145 PCV U4 W3	RC532B
97162200	RC530B 43S/940 SEIA W8L145 PCV U4	RC530B
97321300	RC530B 43S/TW9 SEIA W8L145 PCV U4	RC530B
97327500	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	RC530B

Order Code	Full Product Name	Product family code
97185100	RC532B 25S/940 DEIA W8L113 VPC	RC532B
97173800	RC531B 19S/930 DEIA W8L150 VPC IP	RC531B
97172100	RC531B 15S/940 DEIA W8L120 VPC IP	RC531B
97170700	RC531B 15S/930 DEIA W8L120 VPC IP	RC531B
97155400	RC530B 34S/940 SEIA W8L120 VPC U4 SC	RC530B
97151600	RC530B 34S/930 SEIA W8L120 VPC U4 W3	RC530B
97152300	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	RC530B
97148600	RC530B 25S/930 SEIA W8L120 VPC U4 W3	RC530B
97324400	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	RC530B
97326800	RC531B 25S/TW9 SEIA W8L120 VPC U4	RC534B


Polar normal diagrams




RC530BI - 910505103103




RC530BI - 910505103127




RC530BI - 910505103119




RC530BI - 910505103145




RC530BI - 910505103150




RC530BI - 910505103139




RC530BI - 910505103122




RC530BI - 910505103106




RC530BI - 910505103102




RC530BI - 910505103115




RC530BI - 910505103153




RC530BI - 910505103136




RC530BI - 910505103128




RC530BI - 910505103160




RC530BI - 910505103120




RC530BI - 910505103157




RC530BI - 910505103285




RC530BI - 910505103138




RC530BI - 910505103159




RC530BI - 910505103156




RC530BI - 910505103123




RC530BI - 910505103293




RC530BI - 910505103291




RC530BI - 910505103117




RC530BI - 910505103290




RC530BI - 910505103129




RC530BI - 910505103149




RC530BI - 910505103112




RC530BI - 910505103110




RC530BI - 910505103116




RC530BI - 910505103125




RC530BI - 910505103101




RC530BI - 910505103118




RC530BI - 910505103288




RC530BI - 910505103140




RC530BI - 910505103155




RC530BI - 910505103111




RC530BI - 910505103124




RC530BI - 910505103286




RC530BI - 910505103104




RC530BI - 910505103105




RC530BI - 910505103292




RC530BI - 910505103141




RC530BI - 910505103154




RC530BI - 910505103144




RC530BI - 910505103107




RC530BI - 910505103109




RC530BI - 910505103114




RC530BI - 910505103113




RC530BI - 910505103121




RC530BI - 910505103126




RC530BI - 910505103131



RC530BI - 910505103130



RC530BI - 910505103135



RC530BI - 910505103158