



Philips TrueLine recessed: True line of light

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

Applications

- Offices
- Education
- Retail

Features


- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m²)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering

- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options
- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine Recessed PCV IP RTP



TrueLine recessed-RC530B L1130



TrueLine-RC530 RC531B VPC ELP3



TrueLine-RC530 RC531B PCV ELP3

TrueLine-RC534B VPC



TrueLineRecessed PCV LINE
ASYMMETRIC RTP



TrueLineRecessed VPC OC IP
RTP



TrueLineRecessed PCV
ASYMMETRIC RTP



TrueLineRecessed PCV LINE
NOSENSOR RTP



TrueLine Recessed-U3




TrueLineRecessed VPC NOC
IP RTP




TrueLineRecessed VPC OC U4
RTP



Dimensional drawing




TrueLine Recessed OC - 940 neutral white - Power supply unit
with DALI interface - Push-in connector 5-pole - White RAL 9003




Recessed VPC_W8L150_no sensor

RC531B 31S/940 DIA W8L150 VPC ELP3




Recessed VPC_W8L120_sensor/IP


RC530B 34S/TW9 SEIA W8L120 VPC U4 SC



RC530B 15S/940 DEIA W8L113 PCV




RC533B 31S/940 DEIA W8L141 PCV




Recessed VPC_W8L120_no sensor

RC534B 40S/940 DEIA W8L120 VPC IP



RC530B 43S/940 DEIA W8L141 PCV



RC530B 50S/940 DIA W8L145 PCV ELP3

Product details



TrueLineRecessed NOC
OPTICS DP



TrueLine_Recessed U4 DP

TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B
_PCV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B
_PCV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI
5-DPP.tif



TrueLine-
RC534B_SM534C_SP534P-
DPP.tif



TrueLineRecessed OC OPTICS
DP



TrueLineRecessed PCV line
CONNECTED DP1



TrueLineRecessed VPC line
CONNECTED DP2



TrueLineRecessed VPC line
CONNECTED DP1





TrueLine_Recessed-U3



TrueLineRecessed PCV line
CONNECTED DP2



TrueLineRecessed VPC LINE
RTP



TrueLine_Recessed IP DP



TrueLineRecessed
ASYMMETRIC OPTICS DP

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>90
-----------------------------	-----

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%
Embedded control	Upgradable sensor slot with SC200 sensor

Mechanical and Housing

Housing Color	White
---------------	-------

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Type of emergency lighting battery	Lithium

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source	Optic type
910505103104	RC530B 15S/940 DEIA W8L113 PCV	1,500 lm	4000 K	127 lm/W	- degree(s)	Wide beam
910505103107	RC530B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	148 lm/W	- degree(s)	Wide beam
910505103110	RC530B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
910505103114	RC530B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	143 lm/W	- degree(s)	Wide beam
910505103115	RC530B 34S/940 DEIA W8L113 PCV	3,400 lm	4000 K	143 lm/W	- degree(s)	Wide beam
910505103116	RC531B 15S/930 DEIA W8L113 PCV	1,500 lm	3000 K	99 lm/W	- degree(s)	Wide beam
910505103117	RC531B 15S/940 DEIA W8L113 PCV	1,500 lm	4000 K	99 lm/W	- degree(s)	Wide beam
910505103121	RC531B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103127	RC530B 50S/940 DEIA W8L141 PCV	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source	Optic type
910505103129	RC531B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	4,000 lm	Tunable white 2700-6500 K	121 lm/W	120 degree(s)	Wide beam
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	3,400 lm	4000 K	143 lm/W	120 degree(s)	Wide beam
910505103118	RC532B LED15S/940 PSD W8L113 PCV P15	1,500 lm	4000 K	127 lm/W	- degree(s)	Wide beam
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	3,100 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	3,100 lm	4000 K	112 lm/W	- degree(s)	Wide beam
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	4,000 lm	4000 K	130 lm/W	- degree(s)	Asymmetrical mirror
910505103123	RC534B 50S/940 DEIA W8L141 PCV	5,000 lm	4000 K	132 lm/W	- degree(s)	Asymmetrical mirror
910505103125	RC535B 50S/940 DEIA W8L141 PCV	5,000 lm	4000 K	132 lm/W	- degree(s)	Asymmetrical mirror
910505103130	RC535B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	138 lm/W	- degree(s)	Asymmetrical mirror
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	3,400 lm	3000 K	131 lm/W	- degree(s)	Wide beam
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	5,000 lm	4000 K	139 lm/W	- degree(s)	Wide beam
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	4,000 lm	4000 K	138 lm/W	- degree(s)	Wide beam
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	3,400 lm	4000 K	143 lm/W	- degree(s)	Wide beam
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	3,400 lm	4000 K	143 lm/W	120 degree(s)	Wide beam
910505103128	RC534B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	138 lm/W	- degree(s)	Asymmetrical mirror
910505103106	RC532B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	143 lm/W	- degree(s)	Wide beam
910505103109	RC533B 15S/940 DEIA W8L113 PCV	1,500 lm	4000 K	103 lm/W	- degree(s)	Wide beam
910505103119	RC532B 25S/940 DEIA W8L113 PCV	2,500 lm	4000 K	139 lm/W	- degree(s)	Wide beam
910505103122	RC532B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	148 lm/W	- degree(s)	Wide beam
910505103124	RC532B 43S/940 DEIA W8L141 PCV	4,300 lm	4000 K	144 lm/W	- degree(s)	Wide beam
910505103126	RC533B 31S/940 DEIA W8L141 PCV	3,100 lm	4000 K	112 lm/W	- degree(s)	Wide beam
910505103131	RC533B 19S/940 DEIA W8L141 PCV	1,900 lm	4000 K	110 lm/W	- degree(s)	Wide beam
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	4,300 lm	4000 K	143 lm/W	- degree(s)	Wide beam
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	4,300 lm	4000 K	143 lm/W	- degree(s)	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficiency (rated) (Nom)	Beam angle of light source	Optic type
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	4,300 lm	Tunable white 2700-6500 K	121 lm/W	120 degree(s)	Wide beam
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	4,300 lm	Tunable white 2700-6500 K	121 lm/W	120 degree(s)	Wide beam
910505103102	RC532B 25S/940 DEIA W8L113 VPC	2,500 lm	4000 K	139 lm/W	- degree(s)	Wide beam
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	1,900 lm	3000 K	104 lm/W	- degree(s)	Wide beam
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	1,500 lm	4000 K	99 lm/W	- degree(s)	Wide beam
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	1,500 lm	3000 K	99 lm/W	- degree(s)	Wide beam
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	3,400 lm	4000 K	149 lm/W	- degree(s)	Wide beam
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	3,400 lm	3000 K	133 lm/W	- degree(s)	Wide beam
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	3,400 lm	3000 K	133 lm/W	- degree(s)	Wide beam
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	2,500 lm	3000 K	133 lm/W	- degree(s)	Wide beam
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	3,400 lm	Tunable white 2700-6500 K	124 lm/W	120 degree(s)	Wide beam
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	2,500 lm	Tunable white 2700-6500 K	93 lm/W	120 degree(s)	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505103104	RC530B 15S/940 DEIA W8L113 PCV	12.2 W
910505103107	RC530B 31S/940 DEIA W8L141 PCV	21 W
910505103110	RC530B 43S/940 DEIA W8L141 PCV	30.5 W
910505103114	RC530B 19S/940 DEIA W8L141 PCV	14 W
910505103115	RC530B 34S/940 DEIA W8L113 PCV	24.5 W
910505103116	RC531B 15S/930 DEIA W8L113 PCV	14.6 W
910505103117	RC531B 15S/940 DEIA W8L113 PCV	14.6 W
910505103121	RC531B 31S/940 DEIA W8L141 PCV	29 W
910505103127	RC530B 50S/940 DEIA W8L141 PCV	36 W
910505103129	RC531B 19S/940 DEIA W8L141 PCV	17.8 W
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	33 W
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	24.5 W
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	12.2 W
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	29 W
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	17.8 W
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	36 W
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	30.5 W
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	30.5 W
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	30.5 W
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	36 W
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	17.8 W

Order Code	Full Product Name	Power Consumption
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	29 W
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	17.8 W
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	31.5 W
910505103123	RC534B 50S/940 DEIA W8L141 PCV	38 W
910505103125	RC535B 50S/940 DEIA W8L141 PCV	38 W
910505103130	RC535B 43S/940 DEIA W8L141 PCV	32 W
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	30.5 W
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	24.5 W
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	36 W
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	29 W
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	24.5 W
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	24.5 W
910505103128	RC534B 43S/940 DEIA W8L141 PCV	32 W
910505103106	RC532B 19S/940 DEIA W8L141 PCV	14 W
910505103109	RC533B 15S/940 DEIA W8L113 PCV	14.6 W
910505103119	RC532B 25S/940 DEIA W8L113 PCV	18 W
910505103122	RC532B 31S/940 DEIA W8L141 PCV	21 W
910505103124	RC532B 43S/940 DEIA W8L141 PCV	30.5 W
910505103126	RC533B 31S/940 DEIA W8L141 PCV	29 W
910505103131	RC533B 19S/940 DEIA W8L141 PCV	17.8 W
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	30 W
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	30 W
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	35.5 W
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	35.5 W
910505103102	RC532B 25S/940 DEIA W8L113 VPC	18 W
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	17.8 W
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	14.6 W
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	14.6 W
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	24 W
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	25.5 W
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	25.5 W
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	18.8 W
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	27.5 W
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	27 W

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910505103104	RC530B 15S/940 DEIA W8L113 PCV	IP20	IK03
910505103107	RC530B 31S/940 DEIA W8L141 PCV	IP20	IK03
910505103110	RC530B 43S/940 DEIA W8L141 PCV	IP20	IK03
910505103114	RC530B 19S/940 DEIA W8L141 PCV	IP20	IK03
910505103115	RC530B 34S/940 DEIA W8L113 PCV	IP20	IK03

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910505103116	RC531B 15S/930 DEIA W8L113 PCV	IP20	IK03
910505103117	RC531B 15S/940 DEIA W8L113 PCV	IP20	IK03
910505103121	RC531B 31S/940 DEIA W8L141 PCV	IP20	IK03
910505103127	RC530B 50S/940 DEIA W8L141 PCV	IP20	IK03
910505103129	RC531B 19S/940 DEIA W8L141 PCV	IP20	IK03
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	IP20	IK03
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	IP20	IK03
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	IP20/40	IK02
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	IP20	IK03
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	IP20	IK03
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	IP20	IK03
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	IP20	IK03
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	IP20	IK03
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	IP20	IK03
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	IP20	IK03
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	IP20	IK03
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	IP20	IK03
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	IP20	IK03
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	IP20	IK03
910505103123	RC534B 50S/940 DEIA W8L141 PCV	IP20	IK03
910505103125	RC535B 50S/940 DEIA W8L141 PCV	IP20	IK03
910505103130	RC535B 43S/940 DEIA W8L141 PCV	IP20	IK03
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	IP20	IK03
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	IP20	IK03
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	IP20	IK03
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	IP20	IK03
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	IP20	IK03
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	IP20	IK03
910505103128	RC534B 43S/940 DEIA W8L141 PCV	IP20	IK03
910505103106	RC532B 19S/940 DEIA W8L141 PCV	IP20	IK03
910505103109	RC533B 15S/940 DEIA W8L113 PCV	IP20	IK03
910505103119	RC532B 25S/940 DEIA W8L113 PCV	IP20	IK03
910505103122	RC532B 31S/940 DEIA W8L141 PCV	IP20	IK03
910505103124	RC532B 43S/940 DEIA W8L141 PCV	IP20	IK03
910505103126	RC533B 31S/940 DEIA W8L141 PCV	IP20	IK03
910505103131	RC533B 19S/940 DEIA W8L141 PCV	IP20	IK03
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	IP20	IK03
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	IP20	IK03
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	IP20	IK03
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	IP20	IK03
910505103102	RC532B 25S/940 DEIA W8L113 VPC	IP20	IK03
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	IP20	IK03

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	IP20	IK03
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	IP20	IK03
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	IP20	IK03
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	IP20	IK03
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	IP20	IK03
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	IP20	IK03
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	IP20	IK03
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	IP20	IK03

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Yes	DC operated central emergency lighting
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-	-
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	No	Emergency lighting 3 hours duration with DALI interface
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	No	Emergency lighting 3 hours duration with DALI interface
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes	DC operated central emergency lighting
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103106	RC532B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes	DC operated central emergency lighting
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes	DC operated central emergency lighting
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Yes	DC operated central emergency lighting
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Yes	DC operated central emergency lighting
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes	DC operated central emergency lighting
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Yes	DC operated central emergency lighting
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Yes	DC operated central emergency lighting

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505103104	RC530B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103107	RC530B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103110	RC530B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103114	RC530B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103115	RC530B 34S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103116	RC531B 15S/930 DEIA W8L113 PCV	(0.43, 0.40) SDCM <3
910505103117	RC531B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103121	RC531B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103127	RC530B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103129	RC531B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	(0.38, 0.38) SDCM <3
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	(0.38, 0.38) SDCM <3
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	(0.38, 0.38) SDCM <3
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	(0.38, 0.38) SDCM <3
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103123	RC534B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103125	RC535B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103130	RC535B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	(0.38, 0.38) SDCM <3
910505103128	RC534B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103106	RC532B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103109	RC533B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103119	RC532B 25S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103122	RC532B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103124	RC532B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103126	RC533B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103131	RC533B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	(0.38, 0.38) SDCM <3
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	(0.38, 0.38) SDCM <3
910505103102	RC532B 25S/940 DEIA W8L113 VPC	(0.38, 0.38) SDCM <3
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	(0.43, 0.40) SDCM <3
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	(0.43, 0.40) SDCM <3
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	(0.38, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910505103104	RC530B 15S/940 DEIA W8L113 PCV	RC530B
910505103107	RC530B 31S/940 DEIA W8L141 PCV	RC530B
910505103110	RC530B 43S/940 DEIA W8L141 PCV	RC530B
910505103114	RC530B 19S/940 DEIA W8L141 PCV	RC530B
910505103115	RC530B 34S/940 DEIA W8L113 PCV	RC530B
910505103116	RC531B 15S/930 DEIA W8L113 PCV	RC531B
910505103117	RC531B 15S/940 DEIA W8L113 PCV	RC531B
910505103121	RC531B 31S/940 DEIA W8L141 PCV	RC531B
910505103127	RC530B 50S/940 DEIA W8L141 PCV	RC530B
910505103129	RC531B 19S/940 DEIA W8L141 PCV	RC531B
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	RC530B
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	RC530B
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	RC532B
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	RC531B
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	RC531B
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	RC530B
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	RC530B
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	RC530B
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	RC530B
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	RC530B
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	RC531B
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	RC531B
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	RC531B
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	RC534B
910505103123	RC534B 50S/940 DEIA W8L141 PCV	RC534B
910505103125	RC535B 50S/940 DEIA W8L141 PCV	RC535B
910505103130	RC535B 43S/940 DEIA W8L141 PCV	RC535B
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	RC530B
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	RC530B
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	RC530B
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	RC530B
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	RC530B
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	RC530B
910505103128	RC534B 43S/940 DEIA W8L141 PCV	RC534B
910505103106	RC532B 19S/940 DEIA W8L141 PCV	RC532B
910505103109	RC533B 15S/940 DEIA W8L113 PCV	RC533B
910505103119	RC532B 25S/940 DEIA W8L113 PCV	RC532B
910505103122	RC532B 31S/940 DEIA W8L141 PCV	RC532B
910505103124	RC532B 43S/940 DEIA W8L141 PCV	RC532B
910505103126	RC533B 31S/940 DEIA W8L141 PCV	RC533B
910505103131	RC533B 19S/940 DEIA W8L141 PCV	RC533B

Order Code	Full Product Name	Product family code
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	RC532B
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	RC530B
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	RC530B
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	RC530B
910505103102	RC532B 25S/940 DEIA W8L113 VPC	RC532B
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	RC531B
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	RC531B
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	RC531B
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	RC530B
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	RC530B
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	RC530B
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	RC530B
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	RC530B
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	RC534B


Polar normal diagrams




RC530BI - 910505103103




RC530BI - 910505103127




RC530BI - 910505103119




RC530BI - 910505103145




RC530BI - 910505103150




RC530BI - 910505103139




RC530BI - 910505103122




RC530BI - 910505103106




RC530BI - 910505103102




RC530BI - 910505103115




RC530BI - 910505103153




RC530BI - 910505103136




RC530BI - 910505103128




RC530BI - 910505103160




RC530BI - 910505103120




RC530BI - 910505103157




RC530BI - 910505103285




RC530BI - 910505103138




RC530BI - 910505103159




RC530BI - 910505103156




RC530BI - 910505103123




RC530BI - 910505103293




RC530BI - 910505103291




RC530BI - 910505103117




RC530BI - 910505103290




RC530BI - 910505103129




RC530BI - 910505103149




RC530BI - 910505103112




RC530BI - 910505103110




RC530BI - 910505103116




RC530BI - 910505103125




RC530BI - 910505103101




RC530BI - 910505103118




RC530BI - 910505103288




RC530BI - 910505103140




RC530BI - 910505103155




RC530BI - 910505103111




RC530BI - 910505103124




RC530BI - 910505103286




RC530BI - 910505103104




RC530BI - 910505103105




RC530BI - 910505103292




RC530BI - 910505103141




RC530BI - 910505103154




RC530BI - 910505103144




RC530BI - 910505103107




RC530BI - 910505103109




RC530BI - 910505103114




RC530BI - 910505103113




RC530BI - 910505103121




RC530BI - 910505103126




RC530BI - 910505103131



RC530BI - 910505103130



RC530BI - 910505103135



RC530BI - 910505103158