



Philips TrueLine recessed: True line of light

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, recessed

Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering
- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine recessed-RC530B L1130



TrueLineRecessed PCV LINE
ASYMMETRIC RTP





TrueLineRecessed PCV
ASYMMETRIC RTP





TrueLine Recessed-U3

TrueLine, recessed



Dimensional drawing





Recessed VPC_W8L150_no sensor



Recessed VPC_W8L120_sensor/IP



Recessed VPC_W8L120_no sensor



TrueLine, recessed

Product details



TrueLineRecessed NOC OPTICS
DP



TrueLine_Recessed U4 DP



TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI5-
DPP.tif



TrueLine-
RC534B_SM534C_SP534P-DPP.tif

TrueLine, recessed

Product details



TrueLineRecessed OC OPTICS DP



TrueLineRecessed PCV line
CONNECTED DP1



TrueLineRecessed VPC line
CONNECTED DP2



TrueLineRecessed VPC line
CONNECTED DP1



TrueLine_Recessed-U3



TrueLineRecessed PCV line
CONNECTED DP2



TrueLine_Recessed-U0



TrueLineRecessed VPC LINE RTP



TrueLine_Recessed IP DP

TrueLine, recessed

Product details



TrueLineRecessed ASYMMETRIC
OPTICS DP

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Controls and Dimming	
Maximum dim level	1%
Mechanical and Housing	
Housing Color	White
Approval and Application	
Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Service tag
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Yes
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Yes
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Yes
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Yes
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Yes
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Yes
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Yes
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Yes
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Yes
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Yes
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Yes
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Yes
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Yes
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	Yes
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	Yes
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	Yes
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	Yes
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	Yes
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	Yes
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	Yes
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	Yes
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	Yes
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	Yes
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Yes
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Yes
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Yes
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Yes
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Yes
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Yes
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Yes
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Yes
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Yes
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Yes
910505103106	RC532B 19S/940 DEIA W8L141 PCV	Yes
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Yes
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Yes
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Yes

Order Code	Full Product Name	Service tag
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Yes
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Yes
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Yes
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Yes
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Yes
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Yes
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Yes
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Yes
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Yes
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Yes
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Yes
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Yes

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103104	RC530B 15S/940 DEIA W8L113 PCV	- degree(s)	4000 K	127 lm/W	1,500 lm
910505103107	RC530B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	148 lm/W	3,100 lm
910505103110	RC530B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103114	RC530B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	143 lm/W	1,900 lm
910505103115	RC530B 34S/940 DEIA W8L113 PCV	- degree(s)	4000 K	143 lm/W	3,400 lm
910505103116	RC531B 15S/930 DEIA W8L113 PCV	- degree(s)	3000 K	99 lm/W	1,500 lm
910505103117	RC531B 15S/940 DEIA W8L113 PCV	- degree(s)	4000 K	99 lm/W	1,500 lm
910505103121	RC531B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103127	RC530B 50S/940 DEIA W8L141 PCV	- degree(s)	4000 K	139 lm/W	5,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103129	RC531B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103147	RC530B 40S/940 POE W8L120 VPC U0	- degree(s)	4000 K	143 lm/W	4,000 lm
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,000 lm
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	120 degree(s)	4000 K	143 lm/W	3,400 lm
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	112 lm/W	3,100 lm
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	110 lm/W	1,900 lm

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	139 lm/W	5,000 lm
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	139 lm/W	5,000 lm
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	- degree(s)	4000 K	112 lm/W	3,100 lm
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	130 lm/W	4,000 lm
910505103123	RC534B 50S/940 DEIA W8L141 PCV	- degree(s)	4000 K	132 lm/W	5,000 lm
910505103125	RC535B 50S/940 DEIA W8L141 PCV	- degree(s)	4000 K	132 lm/W	5,000 lm
910505103130	RC535B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	138 lm/W	4,300 lm
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	- degree(s)	4000 K	144 lm/W	4,300 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	- degree(s)	3000 K	131 lm/W	3,400 lm
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	- degree(s)	4000 K	139 lm/W	5,000 lm
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	138 lm/W	4,000 lm
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	143 lm/W	3,400 lm
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	120 degree(s)	4000 K	143 lm/W	3,400 lm
910505103128	RC534B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	138 lm/W	4,300 lm
910505103106	RC532B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	143 lm/W	1,900 lm
910505103109	RC533B 15S/940 DEIA W8L113 PCV	- degree(s)	4000 K	103 lm/W	1,500 lm
910505103119	RC532B 25S/940 DEIA W8L113 PCV	- degree(s)	4000 K	139 lm/W	2,500 lm
910505103122	RC532B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	148 lm/W	3,100 lm
910505103124	RC532B 43S/940 DEIA W8L141 PCV	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103126	RC533B 31S/940 DEIA W8L141 PCV	- degree(s)	4000 K	112 lm/W	3,100 lm
910505103131	RC533B 19S/940 DEIA W8L141 PCV	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	- degree(s)	4000 K	143 lm/W	4,300 lm

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	- degree(s)	4000 K	143 lm/W	4,300 lm
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505103102	RC532B 25S/940 DEIA W8L113 VPC	- degree(s)	4000 K	139 lm/W	2,500 lm
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	- degree(s)	3000 K	104 lm/W	1,900 lm
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	- degree(s)	4000 K	99 lm/W	1,500 lm
910505103112	RC531B 15S/930 DEIA	- degree(s)	3000 K	99 lm/W	1,500 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W8L120 VPC IP				
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	- degree(s)	4000 K	149 lm/W	3,400 lm
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	- degree(s)	3000 K	133 lm/W	2,500 lm
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	120 degree(s)	Tunable white 2700-6500 K	93 lm/W	2,500 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Wide beam
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Wide beam
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Wide beam
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Wide beam
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Wide beam
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Wide beam
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Wide beam
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Wide beam
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Wide beam
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Wide beam
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Wide beam
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Wide beam
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Wide beam
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Wide beam
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	Wide beam
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	Wide beam
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	Wide beam
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	Wide beam
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	Wide beam

Order Code	Full Product Name	Optic type
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	Wide beam
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	Wide beam
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	Wide beam
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	Wide beam
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	Wide beam
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Asymmetrical mirror
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Asymmetrical mirror
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Asymmetrical mirror
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Asymmetrical mirror
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Wide beam
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Wide beam
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Wide beam
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Wide beam
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Wide beam
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Wide beam
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Asymmetrical mirror
910505103106	RC532B 19S/940 DEIA W8L141 PCV	Wide beam
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Wide beam
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Wide beam

TrueLine, recessed

Order Code	Full Product Name	Optic type
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Wide beam
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Wide beam
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Wide beam
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Wide beam
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Wide beam
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Wide beam
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Wide beam
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Wide beam
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Wide beam

Order Code	Full Product Name	Optic type
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Wide beam
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Wide beam
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Wide beam
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Wide beam
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Wide beam
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Wide beam
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Wide beam
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Wide beam
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Wide beam

Operating and Electrical

Order Code	Full Product Name	Protection		Power	
		class IEC	Input Voltage	Consumption	
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	12.2 W	
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	21 W	
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	30.5 W	
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	14 W	
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	24.5 W	
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Safety class I	220 to 240 V	14.6 W	
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	14.6 W	
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	29 W	
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	36 W	
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	17.8 W	
910505103147	RC530B 40S/940 POE W8L120 VPC UO	Safety class III	51 to 54 V	28 W	
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Safety class I	220 to 240 V	33 W	
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Safety class I	220 to 240 V	24.5 W	
910505103118	RC532B LED15S/940 PSD W8L113 PCV P15	Safety class I	220 to 240 V	12.2 W	
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	29 W	
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	17.8 W	

Order Code	Full Product Name	Protection		Power	
		class IEC	Input Voltage	Consumption	
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	36 W	
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	Safety class I	220 to 240 V	30.5 W	
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	Safety class I	220 to 240 V	30.5 W	
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	30.5 W	
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	36 W	
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	17.8 W	
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	Safety class I	220 to 240 V	29 W	
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	Safety class I	220 to 240 V	17.8 W	
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	31.5 W	
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	38 W	
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	38 W	
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	32 W	
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	30.5 W	
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	24.5 W	

TrueLine, recessed

Order Code	Full Product Name	Protection		Power	
		class IEC	Input Voltage	Consumption	
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	36 W	
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	29 W	
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	24.5 W	
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Safety class I	220 to 240 V	24.5 W	
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	32 W	
910505103106	RC532B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	14 W	
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	14.6 W	
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Safety class I	220 to 240 V	18 W	
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	21 W	
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	30.5 W	
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	29 W	
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Safety class I	220 to 240 V	17.8 W	
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Safety class I	220 to 240 V	30 W	
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Safety class I	220 to 240 V	30 W	
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Safety class I	220 to 240 V	35.5 W	

Order Code	Full Product Name	Protection		Power	
		class IEC	Input Voltage	Consumption	
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Safety class I	220 to 240 V	35.5 W	
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Safety class I	220 to 240 V	18 W	
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Safety class I	220 to 240 V	17.8 W	
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	14.6 W	
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Safety class I	220 to 240 V	14.6 W	
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Safety class I	220 to 240 V	24 W	
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Safety class I	220 to 240 V	25.5 W	
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Safety class I	220 to 240 V	25.5 W	
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Safety class I	220 to 240 V	18.8 W	
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Safety class I	220 to 240 V	27.5 W	
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Safety class I	220 to 240 V	27 W	

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control
910505103104	RC530B 15S/940 DEIA W8L113 PCV	-	-
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Yes	-
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Yes	-
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Yes	-
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Yes	-
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Yes	-
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Yes	-
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Yes	-
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Yes	-
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Yes	Upgradable sensor slot empty with cover
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	Yes	-
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	Yes	-
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Yes	-
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	Yes	-

TrueLine, recessed

Order Code	Full Product Name	Dimmable	Embedded control
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	Yes	-
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	Yes	-
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	Yes	-
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	Yes	-
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	Yes	-
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	Yes	-
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	Yes	-
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	Yes	-
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	Yes	-
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Yes	-
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Yes	-
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Yes	-
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Yes	-
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	-	-
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	-	-
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Yes	-
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Yes	-
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Yes	-
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes	-
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Yes	-
910505103106	RC532B 19S/940 DEIA W8L141 PCV	-	-
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Yes	-
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Yes	-
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Yes	-
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Yes	-
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Yes	-
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes	Upgradable sensor slot with SC200 sensor
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Yes	Upgradable sensor slot with SC200 sensor
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Yes	Upgradable sensor slot with SC200 sensor
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes	Upgradable sensor slot with SC200 sensor
910505103102	RC532B 25S/940 DEIA W8L113 VPC	-	-
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Yes	-
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Yes	-
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Yes	-
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes	Upgradable sensor slot with SC200 sensor
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Yes	Upgradable sensor slot with SC200 sensor
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes	Upgradable sensor slot with SC200 sensor
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Yes	Upgradable sensor slot with SC200 sensor

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103104	RC530B 15S/940 DEIA W8L113 PCV	IK03	IP20
910505103107	RC530B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103110	RC530B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103114	RC530B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103115	RC530B 34S/940 DEIA W8L113 PCV	IK03	IP20
910505103116	RC531B 15S/930 DEIA W8L113 PCV	IK03	IP20
910505103117	RC531B 15S/940 DEIA W8L113 PCV	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103121	RC531B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103127	RC530B 50S/940 DEIA W8L141 PCV	IK03	IP20
910505103129	RC531B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103147	RC530B 40S/940 POE W8L120 VPC U0	IK03	IP20
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	IK03	IP20
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	IK02	IP20/40
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	IK03	IP20
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	IK03	IP20
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	IK03	IP20
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	IK03	IP20
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103123	RC534B 50S/940 DEIA W8L141 PCV	IK03	IP20
910505103125	RC535B 50S/940 DEIA W8L141 PCV	IK03	IP20
910505103130	RC535B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	IK03	IP20
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	IK03	IP20
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	IK03	IP20
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	IK03	IP20
910505103128	RC534B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103106	RC532B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103109	RC533B 15S/940 DEIA W8L113 PCV	IK03	IP20
910505103119	RC532B 25S/940 DEIA W8L113 PCV	IK03	IP20
910505103122	RC532B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103124	RC532B 43S/940 DEIA W8L141 PCV	IK03	IP20
910505103126	RC533B 31S/940 DEIA W8L141 PCV	IK03	IP20
910505103131	RC533B 19S/940 DEIA W8L141 PCV	IK03	IP20
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	IK03	IP20
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	IK03	IP20
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	IK03	IP20
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	IK03	IP20
910505103102	RC532B 25S/940 DEIA W8L113 VPC	IK03	IP20
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	IK03	IP20
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	IK03	IP20
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	IK03	IP20
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	IK03	IP20
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	IK03	IP20
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	IK03	IP20
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	IK03	IP20
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	IK03	IP20
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	IK03	IP20

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505103104	RC530B 15S/940 DEIA W8L113 PCV	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting	Rated duration of the emergency lighting (when fully charged)
			emergency lighting		

TrueLine, recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103107	RC530B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103110	RC530B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103114	RC530B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103115	RC530B 34S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103116	RC531B 15S/930 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103117	RC531B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103121	RC531B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103127	RC530B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103129	RC531B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103147	RC530B 40S/940 POE W8L120 VPC U0	-	-	-	-
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	-	-	-	-
910505103292	RC530B 34S/940	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	DEIA W8L113 PCV SC		emergency lighting		
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-	-	-	-
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	No	Emergency lighting 3 hours duration with DALI interface	Lithium	3 hour(s)
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	No	Emergency lighting 3 hours duration with DALI interface	Lithium	3 hour(s)

TrueLine, recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103123	RC534B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103125	RC535B 50S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103130	RC535B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	Yes	DC operated central emergency lighting	-	-
910505103128	RC534B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103106	RC532B 19S/940	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	DEIA W8L141 PCV		emergency lighting		
910505103109	RC533B 15S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103119	RC532B 25S/940 DEIA W8L113 PCV	Yes	DC operated central emergency lighting	-	-
910505103122	RC532B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103124	RC532B 43S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103126	RC533B 31S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103131	RC533B 19S/940 DEIA W8L141 PCV	Yes	DC operated central emergency lighting	-	-
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	Yes	DC operated central emergency lighting	-	-
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting	-	-
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	Yes	DC operated central emergency lighting	-	-
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	Yes	DC operated central emergency lighting	-	-
910505103102	RC532B 25S/940 DEIA W8L113 VPC	Yes	DC operated central emergency lighting	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	Yes	DC operated central emergency lighting	-	-
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103157	RC530B 34S/930	Yes	DC operated central	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	Yes	DC operated central emergency lighting	-	-
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	Yes	DC operated central emergency lighting	-	-
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	Yes	DC operated central emergency lighting	-	-
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	Yes	DC operated central emergency lighting	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505103104	RC530B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103107	RC530B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103110	RC530B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103114	RC530B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103115	RC530B 34S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103116	RC531B 15S/930 DEIA W8L113 PCV	(0.43, 0.40) SDCM <3
910505103117	RC531B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103121	RC531B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103127	RC530B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103129	RC531B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103147	RC530B 40S/940 POE W8L120 VPC U0	(0.38, 0.38) SDCM <3
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	(0.38, 0.38) SDCM <3
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	(0.38, 0.38) SDCM <3
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	(0.38, 0.38) SDCM <3
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	(0.38, 0.38) SDCM <3
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103123	RC534B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103125	RC535B 50S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103130	RC535B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	(0.38, 0.38) SDCM <3
910505103128	RC534B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103106	RC532B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103109	RC533B 15S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103119	RC532B 25S/940 DEIA W8L113 PCV	(0.38, 0.38) SDCM <3
910505103122	RC532B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103124	RC532B 43S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103126	RC533B 31S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103131	RC533B 19S/940 DEIA W8L141 PCV	(0.38, 0.38) SDCM <3
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	(0.38, 0.38) SDCM <3
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	(0.38, 0.38) SDCM <3

TrueLine, recessed

Order Code	Full Product Name	Initial chromaticity
910505103102	RC532B 25S/940 DEIA W8L113 VPC	(0.38, 0.38) SDCM <3
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	(0.43, 0.40) SDCM <3
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	(0.43, 0.40) SDCM <3
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	(0.43, 0.40) SDCM <3
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	(0.43, 0.40) SDCM <3
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	(0.38, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910505103104	RC530B 15S/940 DEIA W8L113 PCV	RC530B
910505103107	RC530B 31S/940 DEIA W8L141 PCV	RC530B
910505103110	RC530B 43S/940 DEIA W8L141 PCV	RC530B
910505103114	RC530B 19S/940 DEIA W8L141 PCV	RC530B
910505103115	RC530B 34S/940 DEIA W8L113 PCV	RC530B
910505103116	RC531B 15S/930 DEIA W8L113 PCV	RC531B
910505103117	RC531B 15S/940 DEIA W8L113 PCV	RC531B
910505103121	RC531B 31S/940 DEIA W8L141 PCV	RC531B
910505103127	RC530B 50S/940 DEIA W8L141 PCV	RC530B
910505103129	RC531B 19S/940 DEIA W8L141 PCV	RC531B
910505103147	RC530B 40S/940 POE W8L120 VPC UO	RC530B
910505103286	RC530B 40S/TW9 DEIA W8L113 PCV	RC530B
910505103292	RC530B 34S/940 DEIA W8L113 PCV SC	RC530B
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	RC532B
910505103138	RC531B 31S/940 DIA W8L150 VPC ELP3	RC531B
910505103140	RC531B 19S/940 DIA W8L150 VPC ELP3	RC531B
910505103141	RC530B 50S/940 DIA W8L150 VPC ELP3	RC530B
910505103144	RC530B 43S/940 DIA W8L150 VPC ELP3	RC530B
910505103154	RC530B 43S/940 DIA W8L150 VPC ELD3	RC530B
910505103135	RC530B 43S/940 DIA W8L145 PCV ELP3	RC530B
910505103136	RC530B 50S/940 DIA W8L145 PCV ELP3	RC530B
910505103139	RC531B 19S/940 DIA W8L145 PCV ELP3	RC531B
910505103145	RC531B 31S/940 DIA W8L145 PCV ELP3	RC531B
910505103153	RC531B 19S/940 DIA W8L145 PCV ELD3	RC531B
910505103120	RC534B 40S/940 DEIA W8L120 VPC IP	RC534B
910505103123	RC534B 50S/940 DEIA W8L141 PCV	RC534B
910505103125	RC535B 50S/940 DEIA W8L141 PCV	RC535B
910505103130	RC535B 43S/940 DEIA W8L141 PCV	RC535B

Order Code	Full Product Name	Product family code
910505103101	RC530B 43S/940 DEIA W8L150 VPC IP	RC530B
910505103105	RC530B 34S/930 DEIA W8L120 VPC IP	RC530B
910505103113	RC530B 50S/940 DEIA W8L150 VPC IP	RC530B
910505103149	RC530B 40S/940 DEIA W8L120 VPC IP	RC530B
910505103150	RC530B 34S/940 DEIA W8L120 VPC IP	RC530B
910505103293	RC530B 34S/940 DEIA W8L120 VPC IP SC	RC530B
910505103128	RC534B 43S/940 DEIA W8L141 PCV	RC534B
910505103106	RC532B 19S/940 DEIA W8L141 PCV	RC532B
910505103109	RC533B 15S/940 DEIA W8L113 PCV	RC533B
910505103119	RC532B 25S/940 DEIA W8L113 PCV	RC532B
910505103122	RC532B 31S/940 DEIA W8L141 PCV	RC532B
910505103124	RC532B 43S/940 DEIA W8L141 PCV	RC532B
910505103126	RC533B 31S/940 DEIA W8L141 PCV	RC533B
910505103131	RC533B 19S/940 DEIA W8L141 PCV	RC533B
910505103155	RC532B 43S/940 SEIA W8L145 PCV U4 W3	RC532B
910505103160	RC530B 43S/940 SEIA W8L145 PCV U4	RC530B
910505103285	RC530B 43S/TW9 SEIA W8L145 PCV U4	RC530B
910505103291	RC530B 43S/TW9 SEIA W8L145 PCV U4 SC	RC530B
910505103102	RC532B 25S/940 DEIA W8L113 VPC	RC532B
910505103103	RC531B 19S/930 DEIA W8L150 VPC IP	RC531B
910505103111	RC531B 15S/940 DEIA W8L120 VPC IP	RC531B
910505103112	RC531B 15S/930 DEIA W8L120 VPC IP	RC531B
910505103156	RC530B 34S/940 SEIA W8L120 VPC U4 SC	RC530B
910505103157	RC530B 34S/930 SEIA W8L120 VPC U4 W3	RC530B
910505103158	RC530B 34S/930 SEIA W8L120 VPC U4 W3 SC	RC530B
910505103159	RC530B 25S/930 SEIA W8L120 VPC U4 W3	RC530B
910505103288	RC530B 34S/TW9 SEIA W8L120 VPC U4 SC	RC530B
910505103290	RC531B 25S/TW9 SEIA W8L120 VPC U4	RC534B


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103103




Polar Normal (separate) - RC530BI - 910505103127




Polar Normal (separate) - RC530BI - 910505103119




Polar Normal (separate) - RC530BI - 910505103145




Polar Normal (separate) - RC530BI - 910505103150




Polar Normal (separate) - RC530BI - 910505103139



Polar Normal (separate) - RC530BI - 910505103122




Polar Normal (separate) - RC530BI - 910505103106




Polar Normal (separate) - RC530BI - 910505103102


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103115




Polar Normal (separate) - RC530BI - 910505103153




Polar Normal (separate) - RC530BI - 910505103136




Polar Normal (separate) - RC530BI - 910505103128




Polar Normal (separate) - RC530BI - 910505103160




Polar Normal (separate) - RC530BI - 910505103120



Polar Normal (separate) - RC530BI - 910505103157




Polar Normal (separate) - RC530BI - 910505103285




Polar Normal (separate) - RC530BI - 910505103138


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103159




Polar Normal (separate) - RC530BI - 910505103156




Polar Normal (separate) - RC530BI - 910505103123




Polar Normal (separate) - RC530BI - 910505103293




Polar Normal (separate) - RC530BI - 910505103291




Polar Normal (separate) - RC530BI - 910505103117



Polar Normal (separate) - RC530BI - 910505103290




Polar Normal (separate) - RC530BI - 910505103129




Polar Normal (separate) - RC530BI - 910505103147


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103149




Polar Normal (separate) - RC530BI - 910505103112




Polar Normal (separate) - RC530BI - 910505103110




Polar Normal (separate) - RC530BI - 910505103116




Polar Normal (separate) - RC530BI - 910505103125




Polar Normal (separate) - RC530BI - 910505103101



Polar Normal (separate) - RC530BI - 910505103118




Polar Normal (separate) - RC530BI - 910505103288




Polar Normal (separate) - RC530BI - 910505103140


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103155




Polar Normal (separate) - RC530BI - 910505103111




Polar Normal (separate) - RC530BI - 910505103124




Polar Normal (separate) - RC530BI - 910505103286




Polar Normal (separate) - RC530BI - 910505103104




Polar Normal (separate) - RC530BI - 910505103105



Polar Normal (separate) - RC530BI - 910505103292




Polar Normal (separate) - RC530BI - 910505103141




Polar Normal (separate) - RC530BI - 910505103154


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103144




Polar Normal (separate) - RC530BI - 910505103107




Polar Normal (separate) - RC530BI - 910505103109




Polar Normal (separate) - RC530BI - 910505103114




Polar Normal (separate) - RC530BI - 910505103113




Polar Normal (separate) - RC530BI - 910505103121



Polar Normal (separate) - RC530BI - 910505103126




Polar Normal (separate) - RC530BI - 910505103131




Polar Normal (separate) - RC530BI - 910505103130

TrueLine, recessed

Polar Wide Diagrams



Polar Normal (separate) - RC530BI -
910505103135



Polar Normal (separate) - RC530BI -
910505103158

