



# DALI Square Track – flexibility enabling energy savings

## DALI Square Track

Designed for use with DALI projectors with a dedicated adaptor, the DALI Square Track is ideal for users who want lighting flexibility to create a specific ambience in their shop and to reduce energy consumption. The system is made up of a solid aluminum track, which is available in various lengths and with a choice of electrical conductors. Any given configuration can be easily created – horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can easily be moved to alter the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material.

### Faydaları

- Allows flexible light settings
- Enables energy savings
- Unobtrusive smart track

### Özellikler

- Integration of the DALI protocol within an unobtrusive retail spot track widely used for dimming and control
- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Seven electrical conductors: L1/L2/L3/neutral/ground 16A/400V, IP20 + DA/DA 2x1A/50V FELV AC (DALI)
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

## DALI Square Track

### Uygulama

- Accent lighting in retail outlets, shopping malls, museums
- All indoor architectural lighting applications

### Versions



RCS750 track, white



RCS750 track, alu







RBS750 recessed track, alu




RCS750 track, black

### Boyutlu çizim



# DALI Square Track

## Boyutlu çizim



## ÜRÜN BİLGİLERİ

IPDP\_RCS750i\_0001-Detail photo



IPDP\_RCS750i\_0003-Detail photo



# DALI Square Track

## Çalıştırma ve Elektrik

Koruma sınıfı IEC	Güvenlik sınıfı I
Koruma sınıfı IEC	Güvenlik sınıfı I

## Mekanik ve Muhafaza

Girişime Karşı Koruma Sınıfı	IP30
Girişime Karşı Koruma Sınıfı	IP30

## Onay ve Uygulama

CE işareti	Evet
CE işareti	Evet
Ateşleme teli testi	Sıcaklık 850 °C, süre 5 sn
Ateşleme teli testi	Sıcaklık 850 °C, süre 5 sn

## Mekanik ve Muhafaza

Order Code	Full Product Name	Aksesuar rengi
06546400	RBS750 5C6 L3000 WH (XTSCF6300-3)	Beyaz
06549500	RBS750 5C6 L2000 WH (XTSCF6200-3)	Beyaz
06531000	RCS750 5C6 L4000 WH (XTSC6400-3)	Beyaz
06534100	RCS750 5C6 L3000 WH (XTSC6300-3)	Beyaz
06537200	RCS750 5C6 L2000 WH (XTSC6200-3)	Beyaz
06540200	RCS750 5C6 L1000 WH (XTSC6100-3)	Beyaz
06529700	RCS750 5C6 L4000 ALU (XTSC6400-1)	Alüminyum
06532700	RCS750 5C6 L3000 ALU (XTSC6300-1)	Alüminyum
06535800	RCS750 5C6 L2000 ALU (XTSC6200-1)	Alüminyum
06538900	RCS750 5C6 L1000 ALU (XTSC6100-1)	Alüminyum
06545700	RBS750 5C6 L3000 BK (XTSCF6300-2)	Siyah
06548800	RBS750 5C6 L2000 BK (XTSCF6200-2)	Siyah
06551800	RBS750 5C6 L1000 BK (XTSCF6100-2)	Siyah
06544000	RBS750 5C6 L3000 ALU (XTSCF6300-1)	Alüminyum
06547100	RBS750 5C6 L2000 ALU (XTSCF6200-1)	Alüminyum
06550100	RBS750 5C6 L1000 ALU (XTSCF6100-1)	Alüminyum
06536500	RCS750 5C6 L2000 BK (XTSC6200-2)	Siyah

